

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P928516

Luminaire Tested: DFN2DIP-HX4F0-040D100US930-FLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P928516
REPORT IS A COMBINATION OF REPORTS P900927 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-040D100US930-FLLONL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11295.9 lumens
Efficiency: N/A
Efficacy: 103.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 109.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9977
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P928516

CATALOG NUMBER: DFN2DIP-HX4F0-040D100US930-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P928516

CATALOG NUMBER: DFN2DIP-HX4F0-040D100US930-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36
1	93	89	85	82	83	80	77	74	62	60	58	47	45	44	32	31	31
2	85	77	72	67	76	70	65	60	55	51	48	41	39	37	28	27	26
3	77	68	61	55	69	61	55	50	48	44	41	36	33	31	25	23	22
4	71	60	53	47	63	54	48	43	43	38	34	32	29	27	22	21	19
5	65	53	46	40	58	48	41	36	38	33	30	29	26	23	20	18	16
6	59	48	40	34	53	43	36	31	34	29	26	26	23	20	18	16	14
7	55	43	35	30	49	39	32	27	31	26	23	24	20	18	17	14	13
8	51	39	31	26	45	35	29	24	28	23	20	22	18	16	15	13	11
9	47	35	28	23	42	32	26	21	26	21	18	20	16	14	14	12	10
10	44	32	25	21	39	29	23	19	24	19	16	18	15	13	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	943	943	943
5°	945	930	936
10°	937	918	924
15°	923	903	904
20°	905	882	884
25°	886	857	860
30°	863	834	831
35°	841	806	799
40°	814	778	769
45°	787	751	738
50°	758	721	703
55°	727	688	670
60°	693	648	633
65°	655	606	589
70°	606	556	541
75°	539	495	498
80°	459	418	414
85°	333	285	275

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1411 cd/sqm

TEST NUMBER: P928516

CATALOG NUMBER: DFN2DIP-HX4F0-040D100US930-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	119.4	1.1
10°-20°	335.9	3.0
20°-30°	493.7	4.4
30°-40°	573.4	5.1
40°-50°	572.7	5.1
50°-60°	499.3	4.4
60°-70°	369.1	3.3
70°-80°	208.8	1.8
80°-90°	60.0	0.5
90°-100°	90.7	0.8
100°-110°	338.1	3.0
110°-120°	896.7	7.9
120°-130°	1487.3	13.2
130°-140°	1579.8	14.0
140°-150°	1468.3	13.0
150°-160°	1180.4	10.5
160°-170°	760.6	6.7
170°-180°	261.8	2.3
0°-30°	949.0	8.4
0°-40°	1522.3	13.5
0°-60°	2594.3	23.0
0°-90°	3232.2	28.6
90°-120°	1325.5	11.7
90°-150°	5860.8	51.9
90°-180°	8064.0	71.4
0°-180°	11295.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1268	1268	1268	1268	1268	
5°	1268	1264	1250	1260	1258	120
15°	1208	1200	1184	1189	1183	340
25°	1093	1083	1062	1065	1062	503
35°	943	931	911	904	898	589
45°	767	759	740	727	722	592
55°	581	573	559	544	538	519
65°	392	384	372	361	355	387
75°	205	202	196	189	192	219
85°	50	49	48	44	43	56
90°	2	24	40	50	54	10
95°	129	64	78	88	86	153
105°	605	665	122	143	151	646
115°	1144	1178	1228	306	163	1127
125°	1618	1644	1682	1696	1702	1443
135°	2002	2034	2052	2072	2068	1547
145°	2323	2321	2354	2368	2358	1453
155°	2558	2540	2564	2575	2560	1178
165°	2695	2683	2689	2703	2689	761
175°	2756	2742	2746	2760	2741	262
180°	2750	2750	2750	2750	2750	

TEST NUMBER: P928516

CATALOG NUMBER: DFN2DIP-HX4F0-040D100US930-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1268.5	1268.5	1268.5	1268.5	1268.5
2.5°	1275.9	1269.8	1256.3	1268.5	1266.2
5°	1268.5	1263.7	1250.2	1259.9	1257.6
7.5°	1259.9	1252.7	1239.2	1249.1	1246.6
10°	1246.6	1238.1	1223.5	1233.2	1229.5
12.5°	1228.2	1221.0	1206.4	1212.5	1209.9
15°	1207.5	1200.3	1184.4	1189.2	1183.2
17.5°	1181.9	1174.7	1158.8	1164.8	1158.8
20°	1153.8	1146.5	1129.5	1133.1	1128.4
22.5°	1125.8	1114.8	1098.9	1098.9	1096.5
25°	1092.8	1083.1	1062.4	1064.8	1062.4
27.5°	1056.2	1047.7	1032.0	1028.3	1022.3
30°	1019.7	1009.9	991.7	988.0	983.1
32.5°	980.7	973.4	953.9	946.5	941.6
35°	942.9	930.7	911.2	903.8	897.7
37.5°	900.2	889.2	869.6	861.1	855.0
40°	856.3	846.5	826.9	816.1	811.2
42.5°	813.6	803.8	784.4	772.0	764.8
45°	767.2	758.8	740.3	727.1	722.1
47.5°	722.1	713.5	694.1	680.6	673.4
50°	674.5	668.4	651.3	634.2	628.1
52.5°	628.1	619.6	603.8	590.4	581.8
55°	580.7	573.3	558.7	544.0	538.0
57.5°	533.0	527.0	511.0	496.4	491.5
60°	485.4	480.6	463.6	450.1	446.5
62.5°	439.1	430.6	418.4	406.2	401.3
65°	391.6	384.2	372.0	361.0	355.0
67.5°	342.8	336.6	325.8	317.2	312.3
70°	297.6	292.7	281.7	273.2	268.4
72.5°	251.3	246.4	240.3	231.8	228.1
75°	204.9	202.5	196.3	189.1	191.5
77.5°	163.4	158.5	156.1	152.4	148.8
80°	122.0	120.7	118.3	114.7	112.2
82.5°	83.0	83.0	81.8	76.9	76.9
85°	50.0	48.8	47.6	43.8	42.7
87.5°	22.0	19.6	17.1	13.4	12.1
90°	1.9	23.9	39.7	49.9	53.6
92.5°	49.9	41.8	47.8	51.8	53.6
95°	129.3	63.6	77.5	87.7	85.6
97.5°	232.8	69.7	101.4	107.5	109.5
100°	352.4	79.6	113.4	129.3	133.3
102.5°	483.5	479.8	117.4	139.2	145.3
105°	605.1	664.8	121.5	143.2	151.3
107.5°	746.4	796.0	125.5	147.3	155.3
110°	881.7	923.4	348.3	149.4	157.1

TEST NUMBER: P928516

CATALOG NUMBER: DFN2DIP-HX4F0-040D100US930-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1009.1	1044.8	1011.1	153.1	159.3
115°	1144.3	1178.2	1228.0	306.5	163.3
117.5°	1261.8	1301.6	1335.5	1050.8	529.4
120°	1393.2	1423.0	1458.9	1482.8	1214.1
122.5°	1504.6	1536.4	1576.4	1588.2	1590.3
125°	1618.0	1644.0	1681.8	1695.8	1701.6
127.5°	1721.5	1749.4	1779.4	1799.3	1801.2
130°	1819.1	1851.0	1872.8	1894.7	1892.8
132.5°	1918.6	1944.6	1966.4	1984.3	1982.4
135°	2002.3	2034.2	2051.9	2072.0	2068.0
137.5°	2089.7	2113.6	2133.7	2153.6	2147.6
140°	2175.2	2191.4	2213.1	2231.1	2221.1
142.5°	2247.1	2261.1	2286.8	2302.6	2292.8
145°	2322.8	2320.6	2354.5	2368.4	2358.4
147.5°	2388.2	2382.3	2416.1	2426.0	2418.3
150°	2452.0	2438.1	2470.0	2481.8	2471.9
152.5°	2505.6	2489.8	2519.7	2531.6	2517.7
155°	2557.5	2539.7	2563.6	2575.4	2559.6
157.5°	2599.3	2583.5	2601.4	2615.3	2599.3
160°	2635.2	2623.2	2635.2	2647.0	2633.1
162.5°	2666.8	2655.0	2665.0	2678.9	2661.0
165°	2694.7	2682.9	2688.8	2702.8	2688.8
167.5°	2716.7	2704.7	2710.9	2724.8	2706.8
170°	2734.7	2722.7	2726.7	2740.6	2722.7
172.5°	2746.5	2734.7	2738.7	2752.7	2734.7
175°	2756.4	2742.5	2746.5	2760.5	2740.6
177.5°	2760.5	2746.5	2748.7	2762.6	2744.6
180°	2750.5	2750.5	2750.5	2750.5	2750.5

TEST NUMBER: P928516

CATALOG NUMBER: DFN2DIP-HX4F0-040D100US930-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	4.66	5.36	5.78	6.47	8.02	4.23	4.93	5.35	6.04	7.59
	3H	6.31	6.94	7.44	8.06	9.62	5.84	6.46	6.97	7.59	9.15
	4H	6.89	7.49	8.03	8.61	10.18	6.42	7.01	7.56	8.14	9.70
	6H	7.28	7.83	8.43	8.96	10.54	6.81	7.35	7.96	8.48	10.06
	8H	7.38	7.90	8.53	9.05	10.62	6.91	7.43	8.06	8.57	10.14
	12H	7.43	7.92	8.58	9.06	10.65	6.95	7.44	8.10	8.57	10.17
4H	2H	5.11	5.70	6.25	6.82	8.39	4.76	5.35	5.91	6.48	8.05
	3H	6.96	7.45	8.11	8.60	10.18	6.56	7.06	7.72	8.21	9.79
	4H	7.67	8.12	8.82	9.26	10.86	7.26	7.71	8.41	8.85	10.45
	6H	8.17	8.56	9.33	9.72	11.31	7.76	8.15	8.92	9.31	10.90
	8H	8.32	8.68	9.48	9.83	11.44	7.91	8.27	9.07	9.42	11.03
	12H	8.38	8.71	9.56	9.88	11.49	7.96	8.29	9.14	9.46	11.07
8H	4H	7.85	8.21	9.01	9.37	10.97	7.49	7.85	8.65	9.01	10.61
	6H	8.47	8.77	9.65	9.97	11.57	8.11	8.41	9.29	9.61	11.21
	8H	8.69	8.96	9.88	10.13	11.75	8.33	8.59	9.51	9.76	11.39
	12H	8.82	9.05	10.01	10.22	11.88	8.43	8.66	9.62	9.84	11.49
12H	4H	7.83	8.16	9.00	9.32	10.93	7.47	7.80	8.65	8.97	10.58
	6H	8.50	8.77	9.69	9.94	11.56	8.15	8.41	9.34	9.59	11.21
	8H	8.74	8.97	9.93	10.14	11.80	8.38	8.61	9.57	9.78	11.44