

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P916341

Luminaire Tested: DFN2DIP-HX4F0-040D110US930-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P916341
REPORT IS A COMBINATION OF REPORTS P899426 AND P896188
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-040D110US930-RLLFLL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10708.9 lumens
Efficiency: N/A
Efficacy: 108.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 98.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9977
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P916341

CATALOG NUMBER: DFN2DIP-HX4F0-040D110US930-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P916341

CATALOG NUMBER: DFN2DIP-HX4F0-040D110US930-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34
1	93	89	85	82	82	79	76	73	62	60	58	45	44	43	30	30	29
2	85	78	72	67	75	69	65	61	54	51	48	40	38	36	27	26	25
3	77	68	61	56	69	61	55	51	48	44	41	36	33	31	24	23	21
4	71	61	53	47	63	54	48	43	43	38	35	32	29	27	22	20	19
5	65	54	46	41	58	48	42	37	38	34	30	29	26	23	20	18	16
6	60	48	41	35	53	43	37	32	34	30	26	26	23	20	18	16	15
7	55	43	36	31	49	39	33	28	31	26	23	24	20	18	16	14	13
8	51	39	32	27	46	36	29	25	28	24	20	21	18	16	15	13	12
9	47	36	29	24	42	32	26	22	26	21	18	20	17	14	14	12	11
10	44	33	26	21	40	30	24	20	24	19	16	18	15	13	13	11	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1002	1002	1002
5°	1004	986	993
10°	994	967	960
15°	980	935	911
20°	962	891	849
25°	944	842	790
30°	919	791	715
35°	895	737	649
40°	870	681	574
45°	841	618	505
50°	812	555	438
55°	781	488	374
60°	745	417	308
65°	704	346	277
70°	654	279	251
75°	591	246	228
80°	500	207	198
85°	349	139	150

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2138 cd/sqm

TEST NUMBER: P916341

CATALOG NUMBER: DFN2DIP-HX4F0-040D110US930-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.3	1.2
10°-20°	346.8	3.2
20°-30°	486.9	4.5
30°-40°	530.7	5.0
40°-50°	487.8	4.6
50°-60°	383.1	3.6
60°-70°	249.3	2.3
70°-80°	128.4	1.2
80°-90°	40.8	0.4
90°-100°	175.5	1.6
100°-110°	557.7	5.2
110°-120°	954.3	8.9
120°-130°	1255.1	11.7
130°-140°	1408.8	13.2
140°-150°	1381.5	12.9
150°-160°	1158.9	10.8
160°-170°	768.5	7.2
170°-180°	268.6	2.5
0°-30°	960.0	9.0
0°-40°	1490.7	13.9
0°-60°	2361.5	22.1
0°-90°	2780.1	26.0
90°-120°	1687.5	15.8
90°-150°	5732.8	53.5
90°-180°	7929.0	74.0
0°-180°	10708.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1348	1348	1348	1348	1348	
5°	1348	1342	1326	1337	1333	128
15°	1282	1268	1227	1204	1192	361
25°	1164	1125	1044	994	976	535
35°	1003	940	833	756	729	628
45°	820	738	610	523	494	633
55°	623	528	396	323	300	557
65°	421	322	212	171	167	417
75°	224	139	98	89	88	237
85°	52	27	23	23	23	60
90°	2	31	84	79	81	11
95°	125	149	153	153	149	139
105°	515	522	527	531	531	543
115°	958	971	967	965	958	947
125°	1393	1414	1407	1400	1397	1245
135°	1802	1828	1833	1831	1824	1393
145°	2187	2204	2218	2221	2211	1367
155°	2501	2508	2516	2528	2520	1151
165°	2721	2718	2718	2735	2723	768
175°	2831	2824	2819	2836	2822	269
180°	2836	2836	2836	2836	2836	

TEST NUMBER: P916341

CATALOG NUMBER: DFN2DIP-HX4F0-040D110US930-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1347.9	1347.9	1347.9	1347.9	1347.9
2.5°	1354.0	1347.9	1334.4	1346.7	1344.2
5°	1347.9	1341.7	1325.8	1336.8	1333.3
7.5°	1336.8	1329.6	1312.5	1317.3	1311.2
10°	1322.3	1313.7	1289.3	1285.6	1278.4
12.5°	1304.0	1293.0	1260.0	1252.7	1239.3
15°	1282.0	1268.5	1227.1	1204.0	1191.8
17.5°	1256.4	1236.8	1185.5	1158.8	1139.2
20°	1227.1	1202.6	1141.7	1111.3	1084.3
22.5°	1195.4	1167.3	1096.5	1055.1	1036.9
25°	1163.7	1124.6	1044.1	994.2	975.7
27.5°	1125.9	1084.3	995.3	938.0	909.9
30°	1085.7	1039.2	941.6	879.5	846.5
32.5°	1046.6	990.4	890.5	817.3	786.7
35°	1002.7	940.4	833.2	756.3	729.4
37.5°	960.0	892.8	779.4	695.2	664.8
40°	914.8	841.7	723.3	636.7	605.0
42.5°	868.5	790.4	667.2	576.9	546.5
45°	819.7	737.9	609.9	523.3	494.0
47.5°	773.4	686.8	555.1	468.4	441.6
50°	722.1	635.5	501.3	417.1	391.6
52.5°	672.1	580.6	450.1	369.6	346.4
55°	623.3	528.2	396.4	323.3	300.1
57.5°	573.3	475.7	348.9	280.5	261.1
60°	522.0	424.4	298.8	236.7	217.2
62.5°	472.1	374.5	256.1	197.6	187.9
65°	420.9	322.0	212.2	170.8	167.1
67.5°	372.1	273.2	170.8	150.0	146.3
70°	320.8	225.7	141.5	129.3	124.3
72.5°	272.1	181.7	118.3	108.6	106.2
75°	224.4	139.0	97.6	89.0	87.9
77.5°	176.9	98.7	76.9	72.0	69.5
80°	132.9	70.8	58.5	53.7	53.7
82.5°	92.7	47.6	40.3	37.7	37.7
85°	52.4	26.8	23.2	23.2	23.2
87.5°	19.6	9.7	9.7	8.6	8.6
90°	2.5	30.8	83.8	78.7	81.2
92.5°	53.0	71.8	74.4	77.0	77.0
95°	124.8	148.8	153.0	153.0	148.8
97.5°	207.8	230.0	239.5	239.5	239.5
100°	303.5	323.2	330.0	330.0	327.5
102.5°	404.5	419.0	428.4	431.0	428.4
105°	514.8	521.6	526.8	531.0	531.0
107.5°	624.2	634.5	634.5	636.2	624.2
110°	730.3	744.0	744.0	744.0	737.1

TEST NUMBER: P916341

CATALOG NUMBER: DFN2DIP-HX4F0-040D110US930-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	844.8	859.3	856.8	849.9	844.8
115°	957.7	971.3	967.1	964.6	957.7
117.5°	1069.8	1088.5	1076.5	1069.8	1062.9
120°	1182.6	1201.4	1182.6	1182.6	1174.9
122.5°	1285.2	1309.1	1297.1	1290.3	1285.2
125°	1392.9	1414.3	1407.4	1399.8	1397.2
127.5°	1498.1	1524.6	1515.2	1505.0	1498.1
130°	1596.4	1627.3	1622.9	1617.8	1608.4
132.5°	1706.7	1730.7	1732.4	1720.4	1713.6
135°	1801.6	1828.1	1833.3	1830.8	1823.9
137.5°	1907.7	1929.1	1933.3	1931.6	1921.4
140°	2000.9	2022.3	2034.3	2034.3	2024.9
142.5°	2096.7	2118.1	2124.9	2127.4	2118.1
145°	2187.3	2204.4	2218.1	2220.6	2211.3
147.5°	2268.6	2289.9	2300.2	2304.4	2295.1
150°	2352.4	2366.9	2376.3	2384.0	2376.3
152.5°	2426.7	2441.2	2453.2	2462.7	2453.2
155°	2501.2	2507.9	2515.7	2527.7	2519.9
157.5°	2565.3	2570.4	2574.6	2591.8	2579.8
160°	2622.6	2627.7	2630.2	2644.8	2634.6
162.5°	2675.6	2675.6	2678.2	2694.4	2682.4
165°	2720.9	2718.3	2718.3	2735.4	2723.4
167.5°	2761.9	2754.2	2754.2	2771.4	2759.4
170°	2792.7	2785.9	2783.3	2800.4	2785.9
172.5°	2814.1	2807.2	2804.7	2821.8	2807.2
175°	2831.2	2824.4	2819.2	2836.3	2821.8
177.5°	2840.6	2833.7	2828.6	2843.2	2828.6
180°	2836.3	2836.3	2836.3	2836.3	2836.3

TEST NUMBER: P916341

CATALOG NUMBER: DFN2DIP-HX4F0-040D110US930-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	4.33	5.00	5.47	6.13	7.71	0.30	0.97	1.45	2.10	3.68
	3H	6.00	6.59	7.15	7.73	9.33	1.48	2.08	2.63	3.21	4.81
	4H	6.60	7.16	7.76	8.30	9.90	1.92	2.49	3.09	3.63	5.23
	6H	7.01	7.53	8.18	8.67	10.28	2.24	2.76	3.41	3.90	5.51
	8H	7.13	7.63	8.30	8.78	10.39	2.33	2.82	3.50	3.98	5.58
	12H	7.19	7.66	8.36	8.81	10.43	2.36	2.83	3.54	3.98	5.61
4H	2H	4.33	4.89	5.50	6.03	7.63	0.88	1.44	2.05	2.58	4.18
	3H	6.14	6.62	7.32	7.78	9.39	2.22	2.69	3.39	3.85	5.46
	4H	6.83	7.26	8.00	8.42	10.05	2.76	3.19	3.93	4.34	5.98
	6H	7.34	7.71	8.52	8.88	10.50	3.17	3.54	4.35	4.72	6.34
	8H	7.51	7.86	8.69	9.02	10.66	3.30	3.64	4.48	4.81	6.45
	12H	7.60	7.91	8.79	9.09	10.73	3.36	3.67	4.55	4.85	6.49
8H	4H	6.79	7.13	7.96	8.30	9.94	3.03	3.37	4.21	4.54	6.18
	6H	7.35	7.63	8.55	8.84	10.48	3.54	3.83	4.74	5.04	6.67
	8H	7.56	7.81	8.77	9.00	10.65	3.73	3.98	4.94	5.17	6.82
	12H	7.70	7.91	8.90	9.10	10.78	3.85	4.06	5.05	5.25	6.93
12H	4H	6.73	7.04	7.92	8.22	9.86	3.02	3.34	4.22	4.52	6.16
	6H	7.32	7.57	8.53	8.76	10.41	3.59	3.84	4.79	5.03	6.68
	8H	7.54	7.76	8.74	8.94	10.63	3.80	4.01	5.00	5.20	6.88

END OF REPORT