

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P905433

Luminaire Tested: DFN2DIP-HX4F0-050D040US835-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P905433
REPORT IS A COMBINATION OF REPORTS P899302 AND P896188
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-050D040US835-RLLFLL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7790.0 lumens
Efficiency: N/A
Efficacy: 115.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 67.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9957
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P905433

CATALOG NUMBER: DFN2DIP-HX4F0-050D040US835-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P905433

CATALOG NUMBER: DFN2DIP-HX4F0-050D040US835-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	86	86	86	73	73	73	60	60	60
1	99	95	91	88	92	89	85	82	76	74	72	65	63	62	54	53	52
2	91	84	78	73	84	78	73	69	67	63	60	57	55	52	48	46	45
3	83	74	67	61	77	69	63	58	60	55	51	51	48	45	43	41	39
4	76	66	58	52	71	62	55	50	54	48	44	46	42	39	39	36	34
5	70	59	51	45	65	55	48	43	48	43	38	42	37	34	35	32	30
6	65	53	45	40	60	50	43	38	44	38	34	38	33	30	32	29	26
7	60	48	40	35	56	45	38	33	40	34	30	35	30	27	30	26	24
8	56	44	36	31	52	41	34	30	36	31	27	32	27	24	27	24	21
9	52	40	33	28	49	38	31	27	34	28	24	29	25	22	25	22	19
10	49	37	30	25	46	35	28	24	31	26	22	27	23	20	24	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1537	1537	1537
5°	1539	1512	1522
10°	1524	1483	1472
15°	1503	1434	1396
20°	1476	1367	1302
25°	1447	1291	1211
30°	1409	1213	1096
35°	1372	1130	995
40°	1334	1044	880
45°	1290	948	774
50°	1245	851	672
55°	1197	748	573
60°	1142	640	472
65°	1079	530	425
70°	1002	428	385
75°	906	377	350
80°	766	317	304
85°	536	212	229

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1290 cd/sqm

TEST NUMBER: P905433

CATALOG NUMBER: DFN2DIP-HX4F0-050D040US835-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	193.7	2.5
10°-20°	531.7	6.8
20°-30°	746.5	9.6
30°-40°	813.7	10.4
40°-50°	747.9	9.6
50°-60°	587.3	7.5
60°-70°	382.3	4.9
70°-80°	196.8	2.5
80°-90°	53.8	0.7
90°-100°	78.3	1.0
100°-110°	248.7	3.2
110°-120°	425.6	5.5
120°-130°	559.8	7.2
130°-140°	628.3	8.1
140°-150°	616.2	7.9
150°-160°	516.9	6.6
160°-170°	342.8	4.4
170°-180°	119.8	1.5
0°-30°	1471.8	18.9
0°-40°	2285.5	29.3
0°-60°	3620.7	46.5
0°-90°	4253.6	54.6
90°-120°	752.7	9.7
90°-150°	2556.9	32.8
90°-180°	3536.0	45.4
0°-180°	7790.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2066	2066	2066	2066	2066	
5°	2066	2057	2033	2050	2044	196
15°	1966	1945	1881	1846	1827	554
25°	1784	1724	1601	1524	1496	821
35°	1537	1442	1277	1160	1118	962
45°	1257	1131	935	802	757	971
55°	956	810	608	496	460	854
65°	645	494	325	262	256	640
75°	344	213	150	136	135	364
85°	80	41	36	36	36	92
90°	1	14	37	35	36	8
95°	56	66	68	68	66	62
105°	230	233	235	237	237	242
115°	427	433	431	430	427	422
125°	621	631	628	624	623	555
135°	804	815	818	816	814	621
145°	976	983	989	990	986	610
155°	1116	1119	1122	1127	1124	513
165°	1214	1212	1212	1220	1215	342
175°	1263	1260	1257	1265	1259	120
180°	1265	1265	1265	1265	1265	

TEST NUMBER: P905433

CATALOG NUMBER: DFN2DIP-HX4F0-050D040US835-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2066.5	2066.5	2066.5	2066.5	2066.5
2.5°	2075.8	2066.5	2045.9	2064.7	2060.9
5°	2066.5	2057.2	2032.8	2049.6	2044.1
7.5°	2049.6	2038.5	2012.3	2019.7	2010.3
10°	2027.2	2014.1	1976.8	1971.1	1959.9
12.5°	1999.2	1982.4	1931.8	1920.7	1900.0
15°	1965.5	1944.9	1881.4	1845.9	1827.2
17.5°	1926.2	1896.3	1817.7	1776.6	1746.6
20°	1881.4	1843.9	1750.4	1703.8	1662.5
22.5°	1832.8	1789.7	1681.2	1617.7	1589.7
25°	1784.1	1724.2	1600.8	1524.2	1496.0
27.5°	1726.2	1662.5	1526.0	1438.1	1395.1
30°	1664.5	1593.3	1443.7	1348.4	1297.8
32.5°	1604.6	1518.5	1365.3	1253.0	1206.2
35°	1537.3	1441.9	1277.4	1159.5	1118.3
37.5°	1471.8	1368.9	1195.1	1065.9	1019.3
40°	1402.6	1290.5	1108.9	976.2	927.6
42.5°	1331.6	1211.9	1023.0	884.5	837.9
45°	1256.8	1131.4	935.1	802.2	757.3
47.5°	1185.7	1053.0	851.0	718.1	677.0
50°	1107.2	974.4	768.7	639.5	600.4
52.5°	1030.4	890.1	690.1	566.7	531.2
55°	955.6	809.7	607.7	495.6	460.1
57.5°	879.0	729.4	534.9	430.2	400.2
60°	800.4	650.8	458.1	362.9	332.9
62.5°	723.8	574.2	392.7	303.0	288.1
65°	645.2	493.7	325.4	261.9	256.2
67.5°	570.4	418.9	261.9	230.0	224.4
70°	491.9	346.0	216.9	198.2	190.7
72.5°	417.1	278.6	181.4	166.5	162.7
75°	344.1	213.1	149.6	136.5	134.7
77.5°	271.2	151.4	117.9	110.3	106.5
80°	203.8	108.5	89.7	82.3	82.3
82.5°	142.1	73.0	61.7	57.9	57.9
85°	80.4	41.1	35.5	35.5	35.5
87.5°	30.0	14.9	14.9	13.1	13.1
90°	1.1	13.7	37.4	35.1	36.2
92.5°	23.6	32.0	33.2	34.3	34.3
95°	55.7	66.4	68.3	68.3	66.4
97.5°	92.7	102.6	106.8	106.8	106.8
100°	135.4	144.2	147.2	147.2	146.1
102.5°	180.4	186.9	191.1	192.2	191.1
105°	229.6	232.6	234.9	236.8	236.8
107.5°	278.4	283.0	283.0	283.7	278.4
110°	325.7	331.8	331.8	331.8	328.8

TEST NUMBER: P905433

CATALOG NUMBER: DFN2DIP-HX4F0-050D040US835-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	376.8	383.3	382.1	379.1	376.8
115°	427.1	433.3	431.3	430.2	427.1
117.5°	477.1	485.5	480.2	477.1	474.1
120°	527.5	535.8	527.5	527.5	524.0
122.5°	573.2	583.9	578.6	575.5	573.2
125°	621.3	630.8	627.8	624.3	623.2
127.5°	668.2	680.0	675.8	671.2	668.2
130°	712.0	725.8	723.9	721.6	717.4
132.5°	761.2	771.9	772.7	767.3	764.3
135°	803.6	815.4	817.7	816.5	813.5
137.5°	850.9	860.4	862.3	861.5	857.0
140°	892.4	902.0	907.3	907.3	903.1
142.5°	935.2	944.7	947.7	948.9	944.7
145°	975.6	983.2	989.3	990.5	986.3
147.5°	1011.8	1021.3	1025.9	1027.8	1023.6
150°	1049.2	1055.7	1059.9	1063.3	1059.9
152.5°	1082.4	1088.8	1094.2	1098.4	1094.2
155°	1115.5	1118.6	1122.0	1127.4	1123.9
157.5°	1144.2	1146.4	1148.3	1156.0	1150.6
160°	1169.7	1172.0	1173.1	1179.6	1175.0
162.5°	1193.3	1193.3	1194.5	1201.7	1196.4
165°	1213.6	1212.4	1212.4	1220.0	1214.7
167.5°	1231.9	1228.4	1228.4	1236.1	1230.7
170°	1245.6	1242.5	1241.4	1249.0	1242.5
172.5°	1255.1	1252.1	1250.9	1258.6	1252.1
175°	1262.8	1259.7	1257.4	1265.0	1258.6
177.5°	1267.0	1263.9	1261.6	1268.1	1261.6
180°	1265.0	1265.0	1265.0	1265.0	1265.0

TEST NUMBER: P905433

CATALOG NUMBER: DFN2DIP-HX4F0-050D040US835-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.06	9.93	9.98	10.87	12.07	5.03	5.90	5.96	6.84	8.05
	3H	10.74	11.52	11.68	12.46	13.69	6.23	7.00	7.16	7.95	9.18
	4H	11.35	12.09	12.30	13.04	14.28	6.68	7.41	7.63	8.36	9.60
	6H	11.78	12.45	12.74	13.41	14.66	7.00	7.68	7.96	8.64	9.89
	8H	11.90	12.55	12.87	13.52	14.77	7.10	7.74	8.06	8.71	9.96
	12H	11.97	12.58	12.94	13.55	14.82	7.14	7.75	8.11	8.72	9.99
4H	2H	9.08	9.82	10.04	10.77	12.01	5.63	6.37	6.59	7.32	8.56
	3H	10.92	11.53	11.88	12.51	13.76	6.99	7.60	7.95	8.58	9.83
	4H	11.61	12.17	12.59	13.14	14.42	7.54	8.10	8.51	9.07	10.35
	6H	12.13	12.61	13.12	13.61	14.88	7.96	8.44	8.95	9.44	10.72
	8H	12.31	12.75	13.29	13.74	15.04	8.09	8.54	9.08	9.53	10.82
	12H	12.40	12.81	13.41	13.81	15.11	8.16	8.56	9.17	9.57	10.87
8H	4H	11.58	12.03	12.57	13.02	14.31	7.82	8.27	8.81	9.26	10.55
	6H	12.15	12.52	13.16	13.55	14.84	8.34	8.71	9.36	9.75	11.04
	8H	12.37	12.69	13.39	13.71	15.02	8.54	8.86	9.56	9.88	11.19
	12H	12.51	12.80	13.53	13.81	15.16	8.66	8.95	9.68	9.96	11.31
12H	4H	11.54	11.94	12.54	12.95	14.24	7.83	8.23	8.84	9.24	10.54
	6H	12.13	12.45	13.15	13.47	14.78	8.39	8.72	9.42	9.74	11.05
	8H	12.35	12.64	13.37	13.65	15.00	8.61	8.89	9.63	9.91	11.26