

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P916346

Luminaire Tested: DFN2DIP-HX4F0-050D050US930-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P916346
REPORT IS A COMBINATION OF REPORTS P899319 AND P896188
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-050D050US930-FLLFLL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7643.4 lumens
Efficiency: N/A
Efficacy: 105.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 72.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9957
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P916346

CATALOG NUMBER: DFN2DIP-HX4F0-050D050US930-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P916346

CATALOG NUMBER: DFN2DIP-HX4F0-050D050US930-FLLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59
1	98	94	90	87	91	87	84	81	74	72	70	63	61	59	52	51	50
2	90	82	76	71	83	76	71	66	65	61	58	55	52	50	46	44	42
3	82	72	65	59	75	67	61	55	58	53	49	49	45	42	41	38	36
4	75	64	56	50	69	60	52	47	51	46	41	43	39	36	36	33	31
5	69	57	49	43	63	53	46	40	46	40	36	39	35	31	33	29	27
6	63	51	43	37	58	48	40	35	41	36	31	35	31	27	30	26	24
7	59	46	38	33	54	43	36	31	37	32	28	32	28	24	27	24	21
8	54	42	34	29	50	39	32	27	34	29	24	29	25	22	25	21	19
9	51	38	31	26	47	36	29	24	31	26	22	27	23	19	23	20	17
10	47	35	28	23	44	33	26	22	29	23	20	25	21	18	21	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1179	1179	1179
5°	1181	1163	1171
10°	1172	1148	1155
15°	1155	1129	1130
20°	1132	1103	1105
25°	1109	1071	1076
30°	1080	1042	1039
35°	1052	1008	999
40°	1018	973	962
45°	985	939	923
50°	948	902	879
55°	910	860	838
60°	866	810	792
65°	819	758	736
70°	758	695	677
75°	674	619	622
80°	574	523	518
85°	417	356	344

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 985 cd/sqm

TEST NUMBER: P916346

CATALOG NUMBER: DFN2DIP-HX4F0-050D050US930-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.3	2.0
10°-20°	420.0	5.5
20°-30°	617.3	8.1
30°-40°	717.0	9.4
40°-50°	716.1	9.4
50°-60°	624.4	8.2
60°-70°	461.6	6.0
70°-80°	261.1	3.4
80°-90°	72.6	0.9
90°-100°	79.8	1.0
100°-110°	253.5	3.3
110°-120°	433.8	5.7
120°-130°	570.5	7.5
130°-140°	640.4	8.4
140°-150°	627.9	8.2
150°-160°	526.8	6.9
160°-170°	349.3	4.6
170°-180°	122.1	1.6
0°-30°	1186.6	15.5
0°-40°	1903.6	24.9
0°-60°	3244.1	42.4
0°-90°	4039.4	52.8
90°-120°	767.0	10.0
90°-150°	2605.8	34.1
90°-180°	3604.0	47.2
0°-180°	7643.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1586	1586	1586	1586	1586	
5°	1586	1580	1563	1576	1573	151
15°	1510	1501	1481	1487	1480	425
25°	1367	1354	1328	1332	1328	629
35°	1179	1164	1139	1130	1123	736
45°	959	949	926	909	903	740
55°	726	717	698	680	673	649
65°	490	480	465	452	444	484
75°	256	253	246	236	240	273
85°	62	61	60	55	53	70
90°	1	14	38	36	37	7
95°	57	68	70	70	68	63
105°	234	237	240	241	241	247
115°	435	442	440	438	435	431
125°	633	643	640	636	635	566
135°	819	831	833	832	829	633
145°	994	1002	1008	1009	1005	621
155°	1137	1140	1144	1149	1145	523
165°	1237	1236	1236	1243	1238	349
175°	1287	1284	1282	1289	1283	122
180°	1289	1289	1289	1289	1289	

TEST NUMBER: P916346

CATALOG NUMBER: DFN2DIP-HX4F0-050D050US930-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1586.2	1586.2	1586.2	1586.2	1586.2
2.5°	1595.4	1587.8	1571.0	1586.2	1583.3
5°	1586.2	1580.2	1563.3	1575.5	1572.6
7.5°	1575.5	1566.4	1549.6	1561.9	1558.9
10°	1558.9	1548.2	1529.9	1542.0	1537.5
12.5°	1535.9	1526.8	1508.5	1516.1	1513.0
15°	1509.9	1500.9	1481.0	1487.2	1479.5
17.5°	1477.9	1468.8	1448.9	1456.5	1448.9
20°	1442.8	1433.8	1412.4	1416.9	1411.0
22.5°	1407.9	1394.1	1374.2	1374.2	1371.1
25°	1366.6	1354.5	1328.5	1331.5	1328.5
27.5°	1320.8	1310.1	1290.4	1285.8	1278.2
30°	1275.1	1262.9	1240.1	1235.5	1229.4
32.5°	1226.3	1217.2	1192.8	1183.6	1177.5
35°	1179.0	1163.8	1139.4	1130.2	1122.6
37.5°	1125.6	1111.9	1087.4	1076.8	1069.2
40°	1070.8	1058.5	1034.0	1020.4	1014.3
42.5°	1017.4	1005.1	980.8	965.4	956.3
45°	959.4	948.8	925.8	909.1	902.9
47.5°	902.9	892.3	867.9	851.0	842.0
50°	843.4	835.8	814.5	793.1	785.5
52.5°	785.5	774.8	755.0	738.3	727.6
55°	726.1	716.9	698.5	680.3	672.7
57.5°	666.5	658.9	639.0	620.8	614.6
60°	607.0	601.0	579.7	562.8	558.3
62.5°	549.1	538.4	523.2	507.9	501.8
65°	489.7	480.5	465.2	451.5	443.8
67.5°	428.7	420.9	407.3	396.6	390.4
70°	372.2	366.1	352.3	341.6	335.7
72.5°	314.3	308.1	300.5	289.8	285.3
75°	256.2	253.2	245.5	236.4	239.5
77.5°	204.4	198.2	195.2	190.6	186.1
80°	152.6	151.0	147.9	143.4	140.3
82.5°	103.7	103.7	102.2	96.1	96.1
85°	62.5	61.0	59.5	54.9	53.4
87.5°	27.5	24.5	21.4	16.8	15.2
90°	1.1	14.0	38.1	35.8	36.9
92.5°	24.1	32.6	33.8	35.0	35.0
95°	56.7	67.7	69.5	69.5	67.7
97.5°	94.4	104.5	108.8	108.8	108.8
100°	137.9	146.9	150.0	150.0	148.9
102.5°	183.8	190.5	194.7	195.9	194.7
105°	234.0	237.1	239.5	241.3	241.3
107.5°	283.7	288.4	288.4	289.2	283.7
110°	331.9	338.2	338.2	338.2	335.0

TEST NUMBER: P916346

CATALOG NUMBER: DFN2DIP-HX4F0-050D050US930-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	384.0	390.6	389.5	386.4	384.0
115°	435.3	441.6	439.6	438.5	435.3
117.5°	486.2	494.8	489.3	486.2	483.1
120°	537.5	546.1	537.5	537.5	534.0
122.5°	584.2	595.1	589.6	586.5	584.2
125°	633.2	642.9	639.8	636.3	635.1
127.5°	680.9	693.0	688.8	684.0	680.9
130°	725.7	739.6	737.7	735.4	731.1
132.5°	775.8	786.7	787.5	782.0	778.9
135°	819.0	831.0	833.3	832.2	829.1
137.5°	867.2	876.9	878.8	878.0	873.3
140°	909.5	919.2	924.6	924.6	920.4
142.5°	953.0	962.8	965.9	967.0	962.8
145°	994.3	1002.0	1008.2	1009.4	1005.1
147.5°	1031.2	1040.9	1045.5	1047.5	1043.2
150°	1069.3	1075.9	1080.1	1083.6	1080.1
152.5°	1103.1	1109.7	1115.1	1119.4	1115.1
155°	1136.9	1140.0	1143.5	1148.9	1145.4
157.5°	1166.0	1168.3	1170.3	1178.1	1172.6
160°	1192.0	1194.4	1195.6	1202.2	1197.5
162.5°	1216.2	1216.2	1217.3	1224.7	1219.3
165°	1236.8	1235.6	1235.6	1243.4	1237.9
167.5°	1255.4	1251.9	1251.9	1259.7	1254.3
170°	1269.4	1266.3	1265.2	1272.9	1266.3
172.5°	1279.1	1276.0	1274.9	1282.6	1276.0
175°	1286.9	1283.8	1281.5	1289.2	1282.6
177.5°	1291.2	1288.1	1285.7	1292.3	1285.7
180°	1289.2	1289.2	1289.2	1289.2	1289.2

TEST NUMBER: P916346

CATALOG NUMBER: DFN2DIP-HX4F0-050D050US930-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.10	8.99	9.04	9.94	11.17	7.67	8.56	8.61	9.51	10.74
	3H	9.77	10.56	10.71	11.52	12.78	9.29	10.09	10.24	11.05	12.30
	4H	10.36	11.11	11.32	12.07	13.34	9.88	10.64	10.84	11.60	12.86
	6H	10.76	11.45	11.73	12.42	13.70	10.28	10.98	11.25	11.95	13.22
	8H	10.86	11.53	11.84	12.51	13.78	10.39	11.05	11.37	12.04	13.31
	12H	10.91	11.54	11.90	12.52	13.82	10.43	11.06	11.41	12.04	13.34
4H	2H	8.57	9.32	9.53	10.29	11.55	8.23	8.98	9.19	9.94	11.20
	3H	10.44	11.07	11.41	12.06	13.34	10.05	10.68	11.02	11.67	12.94
	4H	11.16	11.73	12.14	12.72	14.02	10.75	11.32	11.73	12.31	13.61
	6H	11.67	12.17	12.67	13.18	14.48	11.26	11.76	12.26	12.77	14.07
	8H	11.82	12.29	12.82	13.29	14.60	11.41	11.87	12.41	12.88	14.19
	12H	11.90	12.32	12.91	13.34	14.65	11.48	11.89	12.49	12.91	14.23
8H	4H	11.35	11.82	12.35	12.82	14.13	10.99	11.46	11.99	12.46	13.77
	6H	11.99	12.37	13.01	13.42	14.73	11.63	12.01	12.65	13.05	14.36
	8H	12.21	12.55	13.24	13.58	14.91	11.84	12.18	12.87	13.21	14.54
	12H	12.34	12.64	13.38	13.67	15.04	11.96	12.26	12.99	13.28	14.66
12H	4H	11.34	11.76	12.36	12.78	14.10	10.99	11.41	12.00	12.43	13.75
	6H	12.02	12.36	13.05	13.39	14.72	11.67	12.01	12.70	13.04	14.37
	8H	12.26	12.56	13.30	13.59	14.96	11.91	12.20	12.94	13.23	14.60