

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P905472

Luminaire Tested: DFN2DIP-HX4F0-070D060US835-FLLFLL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P905472  
REPORT IS A COMBINATION OF REPORTS P899341 AND P896188  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-HX4F0-070D060US835-FLLFLL  
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 12240.0 lumens  
Efficiency: N/A  
Efficacy: 122.0 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29  
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 100.3  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9972  
Total Harmonic Distortion (THDi): 0.128  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P905472  
CATALOG NUMBER: DFN2DIP-HX4F0-070D060US835-FLLFLL

### Luminous Intensity Polar Plot





TEST NUMBER: P905472

CATALOG NUMBER: DFN2DIP-HX4F0-070D060US835-FLLFLL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	57
1	99	95	91	87	92	88	85	82	76	74	72	65	63	62	55	54	53	48
2	90	83	77	71	84	77	72	67	67	63	59	57	54	52	48	46	44	40
3	82	73	65	60	76	68	62	56	59	54	50	51	47	44	43	40	38	34
4	75	65	57	50	70	60	53	48	53	47	43	45	41	37	38	35	33	29
5	69	58	49	43	64	54	47	41	47	41	37	41	36	32	35	31	28	25
6	64	52	43	38	59	48	41	36	42	36	32	37	32	28	31	28	25	22
7	59	47	39	33	55	44	37	31	38	33	28	33	29	25	29	25	22	20
8	55	42	35	29	51	40	33	28	35	29	25	31	26	23	26	23	20	18
9	51	39	31	26	48	37	30	25	32	27	23	28	24	20	24	21	18	16
10	48	36	28	23	45	34	27	22	30	24	20	26	22	18	23	19	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	2025	2025	2025
5°	2029	1997	2011
10°	2012	1971	1983
15°	1983	1938	1941
20°	1943	1893	1898
25°	1904	1840	1847
30°	1854	1790	1783
35°	1807	1731	1716
40°	1749	1671	1651
45°	1691	1612	1586
50°	1628	1549	1509
55°	1562	1477	1439
60°	1487	1391	1359
65°	1406	1302	1264
70°	1302	1193	1163
75°	1158	1063	1069
80°	985	898	889
85°	715	612	591

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1691 cd/sqm



TEST NUMBER: P905472

CATALOG NUMBER: DFN2DIP-HX4F0-070D060US835-FLLFLL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	256.4	2.1
10°-20°	721.3	5.9
20°-30°	1060.0	8.7
30°-40°	1231.1	10.1
40°-50°	1229.6	10.0
50°-60°	1072.2	8.8
60°-70°	792.6	6.5
70°-80°	448.4	3.7
80°-90°	123.8	1.0
90°-100°	117.4	1.0
100°-110°	373.1	3.0
110°-120°	638.5	5.2
120°-130°	839.7	6.9
130°-140°	942.5	7.7
140°-150°	924.2	7.6
150°-160°	775.3	6.3
160°-170°	514.2	4.2
170°-180°	179.7	1.5
0°-30°	2037.7	16.6
0°-40°	3268.8	26.7
0°-60°	5570.6	45.5
0°-90°	6935.4	56.7
90°-120°	1129.0	9.2
90°-150°	3835.4	31.3
90°-180°	5305.0	43.3
0°-180°	12240.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2724	2724	2724	2724	2724	
5°	2724	2714	2685	2705	2700	259
15°	2593	2577	2543	2554	2541	730
25°	2347	2326	2281	2286	2281	1080
35°	2025	1998	1956	1941	1928	1264
45°	1648	1629	1590	1561	1550	1271
55°	1247	1231	1200	1168	1155	1115
65°	841	825	799	775	762	831
75°	440	435	422	406	411	470
85°	107	105	102	94	92	120
90°	2	21	56	53	54	12
95°	84	100	102	102	100	93
105°	344	349	352	355	355	363
115°	641	650	647	645	641	634
125°	932	946	942	936	935	833
135°	1205	1223	1226	1225	1220	932
145°	1463	1475	1484	1486	1479	914
155°	1673	1678	1683	1691	1686	770
165°	1820	1819	1819	1830	1822	514
175°	1894	1890	1886	1898	1888	180
180°	1898	1898	1898	1898	1898	



TEST NUMBER: P905472

CATALOG NUMBER: DFN2DIP-HX4F0-070D060US835-FLLFL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2723.7	2723.7	2723.7	2723.7	2723.7
2.5°	2739.6	2726.5	2697.6	2723.7	2718.7
5°	2723.7	2713.5	2684.6	2705.4	2700.4
7.5°	2705.4	2689.8	2660.9	2682.1	2676.8
10°	2676.8	2658.4	2627.0	2647.9	2640.1
12.5°	2637.3	2621.8	2590.4	2603.4	2598.1
15°	2592.9	2577.3	2543.1	2553.7	2540.6
17.5°	2537.8	2522.3	2488.1	2501.2	2488.1
20°	2477.5	2462.0	2425.3	2433.1	2422.8
22.5°	2417.5	2393.9	2359.7	2359.7	2354.4
25°	2346.7	2325.8	2281.4	2286.4	2281.4
27.5°	2268.0	2249.7	2215.8	2208.0	2194.9
30°	2189.7	2168.5	2129.4	2121.6	2111.0
32.5°	2105.7	2090.2	2048.2	2032.4	2021.8
35°	2024.6	1998.5	1956.5	1940.7	1927.6
37.5°	1932.9	1909.3	1867.3	1849.0	1835.9
40°	1838.7	1817.6	1775.6	1752.3	1741.7
42.5°	1747.0	1725.9	1684.2	1657.8	1642.2
45°	1647.5	1629.2	1589.7	1561.1	1550.5
47.5°	1550.5	1532.2	1490.2	1461.3	1445.8
50°	1448.3	1435.2	1398.5	1361.9	1348.8
52.5°	1348.8	1330.5	1296.6	1267.7	1249.3
55°	1246.8	1231.0	1199.6	1168.2	1155.1
57.5°	1144.6	1131.5	1097.3	1065.9	1055.4
60°	1042.3	1032.0	995.4	966.5	958.7
62.5°	942.8	924.5	898.4	872.3	861.7
65°	840.9	825.0	798.9	775.3	762.2
67.5°	736.1	722.8	699.4	681.1	670.5
70°	639.1	628.6	604.9	586.6	576.3
72.5°	539.6	529.1	516.0	497.7	489.9
75°	439.9	434.9	421.5	406.0	411.3
77.5°	351.0	340.4	335.1	327.3	319.6
80°	262.0	259.3	254.0	246.2	240.9
82.5°	178.1	178.1	175.6	165.1	165.1
85°	107.3	104.8	102.3	94.2	91.7
87.5°	47.2	42.0	36.7	28.9	26.1
90°	1.7	20.6	56.1	52.6	54.3
92.5°	35.5	48.1	49.8	51.5	51.5
95°	83.5	99.5	102.4	102.4	99.5
97.5°	139.0	153.9	160.2	160.2	160.2
100°	203.1	216.2	220.8	220.8	219.1
102.5°	270.6	280.3	286.6	288.3	286.6
105°	344.4	349.0	352.4	355.3	355.3
107.5°	417.6	424.5	424.5	425.6	417.6
110°	488.6	497.7	497.7	497.7	493.1



TEST NUMBER: P905472

CATALOG NUMBER: DFN2DIP-HX4F0-070D060US835-FLLFLL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	565.2	574.9	573.2	568.6	565.2
115°	640.7	649.9	647.0	645.3	640.7
117.5°	715.7	728.3	720.2	715.7	711.1
120°	791.2	803.8	791.2	791.2	786.0
122.5°	859.8	875.8	867.8	863.3	859.8
125°	931.9	946.2	941.6	936.5	934.8
127.5°	1002.3	1020.0	1013.7	1006.9	1002.3
130°	1068.1	1088.7	1085.8	1082.4	1076.1
132.5°	1141.9	1157.9	1159.0	1151.0	1146.4
135°	1205.4	1223.1	1226.5	1224.8	1220.2
137.5°	1276.3	1290.6	1293.5	1292.3	1285.5
140°	1338.7	1353.0	1361.0	1361.0	1354.7
142.5°	1402.7	1417.0	1421.6	1423.3	1417.0
145°	1463.4	1474.8	1484.0	1485.7	1479.4
147.5°	1517.7	1532.0	1538.9	1541.7	1535.4
150°	1573.8	1583.5	1589.8	1594.9	1589.8
152.5°	1623.5	1633.3	1641.3	1647.6	1641.3
155°	1673.3	1677.9	1683.0	1691.1	1685.9
157.5°	1716.2	1719.7	1722.5	1734.0	1726.0
160°	1754.6	1758.0	1759.7	1769.4	1762.6
162.5°	1790.0	1790.0	1791.7	1802.6	1794.6
165°	1820.3	1818.6	1818.6	1830.1	1822.1
167.5°	1847.8	1842.7	1842.7	1854.1	1846.1
170°	1868.4	1863.8	1862.1	1873.5	1863.8
172.5°	1882.7	1878.1	1876.4	1887.8	1878.1
175°	1894.1	1889.6	1886.1	1897.6	1887.8
177.5°	1900.4	1895.9	1892.4	1902.1	1892.4
180°	1897.6	1897.6	1897.6	1897.6	1897.6



TEST NUMBER: P905472  
 CATALOG NUMBER: DFN2DIP-HX4F0-070D060US835-FLLFLL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.32	11.24	11.21	12.16	13.33	9.88	10.81	10.78	11.73	12.90
	3H	11.98	12.81	12.89	13.74	14.94	11.51	12.34	12.42	13.27	14.46
	4H	12.57	13.36	13.50	14.29	15.50	12.10	12.89	13.03	13.82	15.02
	6H	12.98	13.70	13.91	14.64	15.86	12.50	13.23	13.44	14.16	15.38
	8H	13.08	13.77	14.03	14.73	15.95	12.61	13.30	13.55	14.25	15.47
	12H	13.14	13.79	14.09	14.74	15.98	12.65	13.31	13.60	14.26	15.50
4H	2H	10.79	11.57	11.72	12.50	13.71	10.44	11.23	11.37	12.16	13.37
	3H	12.66	13.31	13.60	14.28	15.50	12.27	12.92	13.21	13.88	15.11
	4H	13.38	13.98	14.33	14.93	16.18	12.97	13.57	13.92	14.53	15.77
	6H	13.90	14.41	14.86	15.39	16.64	13.49	14.00	14.45	14.98	16.23
	8H	14.05	14.53	15.01	15.51	16.77	13.64	14.12	14.60	15.09	16.35
	12H	14.13	14.56	15.11	15.55	16.82	13.70	14.14	14.69	15.13	16.40
8H	4H	13.58	14.06	14.55	15.04	16.30	13.22	13.70	14.18	14.68	15.94
	6H	14.22	14.61	15.21	15.63	16.89	13.85	14.25	14.84	15.27	16.53
	8H	14.44	14.79	15.44	15.79	17.07	14.07	14.42	15.07	15.42	16.70
	12H	14.57	14.88	15.58	15.88	17.20	14.19	14.50	15.19	15.50	16.82
12H	4H	13.57	14.00	14.55	15.00	16.26	13.22	13.65	14.20	14.64	15.91
	6H	14.25	14.60	15.25	15.60	16.88	13.89	14.25	14.89	15.25	16.53
	8H	14.49	14.80	15.50	15.80	17.12	14.13	14.44	15.14	15.44	16.77