

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P928564

Luminaire Tested: DFN2DIP-HX4F0-060D040US930-FLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P928564
REPORT IS A COMBINATION OF REPORTS P900823 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-060D040US930-FLLONL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8068.5 lumens
Efficiency: N/A
Efficacy: 95.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 84.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P928564

CATALOG NUMBER: DFN2DIP-HX4F0-060D040US930-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P928564

CATALOG NUMBER: DFN2DIP-HX4F0-060D040US930-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	65	65	65
1	100	96	92	88	93	90	86	83	78	75	73	67	66	64	58	56	55
2	91	84	77	72	85	78	73	68	68	64	61	59	56	53	51	49	47
3	83	73	66	60	77	69	62	57	60	55	51	52	48	45	45	42	40
4	76	65	57	51	71	61	54	48	54	48	44	47	42	39	40	37	34
5	70	58	50	44	65	55	47	42	48	42	38	42	37	34	36	33	30
6	64	52	44	38	60	49	42	36	43	37	33	38	33	30	33	29	26
7	60	47	39	33	56	44	37	32	39	33	29	35	30	26	30	26	23
8	55	43	35	30	52	40	33	28	36	30	26	32	27	23	28	24	21
9	52	39	32	26	48	37	30	25	33	27	23	29	24	21	26	22	19
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	24	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1415	1415	1415
5°	1417	1395	1405
10°	1406	1377	1386
15°	1385	1354	1356
20°	1357	1323	1326
25°	1330	1285	1291
30°	1295	1250	1246
35°	1262	1209	1199
40°	1222	1167	1154
45°	1181	1126	1108
50°	1137	1082	1054
55°	1091	1031	1005
60°	1039	971	949
65°	982	909	883
70°	910	833	812
75°	809	743	747
80°	688	627	621
85°	499	427	413

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1181 cd/sqm

TEST NUMBER: P928564

CATALOG NUMBER: DFN2DIP-HX4F0-060D040US930-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	179.1	2.2
10°-20°	503.9	6.2
20°-30°	740.5	9.2
30°-40°	860.0	10.7
40°-50°	859.0	10.6
50°-60°	749.0	9.3
60°-70°	553.7	6.9
70°-80°	313.3	3.9
80°-90°	84.6	1.0
90°-100°	36.3	0.4
100°-110°	135.2	1.7
110°-120°	358.7	4.4
120°-130°	594.9	7.4
130°-140°	631.9	7.8
140°-150°	587.3	7.3
150°-160°	472.2	5.9
160°-170°	304.3	3.8
170°-180°	104.7	1.3
0°-30°	1423.5	17.6
0°-40°	2283.5	28.3
0°-60°	3891.5	48.2
0°-90°	4843.0	60.0
90°-120°	530.2	6.6
90°-150°	2344.3	29.1
90°-180°	3225.0	40.0
0°-180°	8068.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1903	1903	1903	1903	1903	
5°	1903	1896	1875	1890	1886	181
15°	1811	1800	1776	1784	1775	510
25°	1639	1625	1594	1597	1594	754
35°	1414	1396	1367	1356	1346	883
45°	1151	1138	1110	1091	1083	888
55°	871	860	838	816	807	779
65°	587	576	558	542	532	581
75°	307	304	294	284	287	328
85°	75	73	71	66	64	84
90°	1	10	16	20	21	7
95°	52	25	31	35	34	61
105°	242	266	49	57	60	259
115°	458	471	491	123	65	451
125°	647	658	673	678	681	577
135°	801	814	821	829	827	619
145°	929	928	942	947	943	581
155°	1023	1016	1025	1030	1024	471
165°	1078	1073	1076	1081	1076	305
175°	1102	1097	1099	1104	1096	105
180°	1100	1100	1100	1100	1100	

TEST NUMBER: P928564

CATALOG NUMBER: DFN2DIP-HX4F0-060D040US930-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1902.7	1902.7	1902.7	1902.7	1902.7
2.5°	1913.8	1904.7	1884.4	1902.7	1899.2
5°	1902.7	1895.5	1875.3	1889.9	1886.4
7.5°	1889.9	1879.1	1858.9	1873.6	1869.9
10°	1869.9	1857.1	1835.1	1849.7	1844.3
12.5°	1842.4	1831.5	1809.5	1818.7	1815.0
15°	1811.3	1800.4	1776.5	1784.0	1774.8
17.5°	1772.9	1762.0	1738.2	1747.2	1738.2
20°	1730.7	1719.9	1694.2	1699.7	1692.5
22.5°	1688.8	1672.3	1648.4	1648.4	1644.8
25°	1639.3	1624.8	1593.7	1597.2	1593.7
27.5°	1584.4	1571.6	1547.8	1542.5	1533.3
30°	1529.7	1514.8	1487.5	1482.1	1474.7
32.5°	1471.0	1460.2	1430.8	1419.7	1412.4
35°	1414.4	1396.1	1366.8	1355.7	1346.5
37.5°	1350.3	1333.7	1304.5	1291.6	1282.5
40°	1284.4	1269.7	1240.4	1224.1	1216.7
42.5°	1220.4	1205.6	1176.5	1158.1	1147.2
45°	1150.9	1138.1	1110.5	1090.6	1083.1
47.5°	1083.1	1070.3	1041.1	1020.9	1009.9
50°	1011.7	1002.6	977.0	951.3	942.2
52.5°	942.2	929.4	905.7	885.6	872.8
55°	871.0	859.9	838.0	816.1	806.9
57.5°	799.6	790.5	766.6	744.7	737.2
60°	728.1	720.9	695.4	675.1	669.7
62.5°	658.6	645.8	627.6	609.3	602.0
65°	587.4	576.4	558.1	541.6	532.4
67.5°	514.2	504.9	488.6	475.8	468.4
70°	446.5	439.1	422.6	409.8	402.6
72.5°	376.9	369.6	360.5	347.7	342.2
75°	307.3	303.8	294.5	283.6	287.3
77.5°	245.2	237.8	234.1	228.7	223.2
80°	183.0	181.1	177.4	172.0	168.3
82.5°	124.5	124.5	122.7	115.3	115.3
85°	74.9	73.2	71.4	65.8	64.1
87.5°	33.0	29.3	25.6	20.2	18.3
90°	0.7	9.5	15.9	20.0	21.4
92.5°	20.0	16.7	19.1	20.7	21.4
95°	51.7	25.4	31.0	35.0	34.2
97.5°	93.2	27.9	40.6	43.0	43.8
100°	140.9	31.9	45.4	51.7	53.3
102.5°	193.4	191.9	46.9	55.7	58.1
105°	242.0	265.9	48.6	57.3	60.5
107.5°	298.5	318.4	50.2	58.9	62.1
110°	352.7	369.4	139.4	59.7	62.8

TEST NUMBER: P928564

CATALOG NUMBER: DFN2DIP-HX4F0-060D040US930-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	403.7	417.9	404.4	61.3	63.7
115°	457.7	471.2	491.2	122.6	65.4
117.5°	504.7	520.6	534.2	420.3	211.7
120°	557.3	569.2	583.5	593.2	485.7
122.5°	601.8	614.6	630.6	635.3	636.1
125°	647.2	657.6	672.7	678.3	680.7
127.5°	688.6	699.8	711.7	719.7	720.5
130°	727.6	740.4	749.1	757.9	757.1
132.5°	767.4	777.8	786.6	793.7	793.0
135°	800.9	813.7	820.8	828.8	827.2
137.5°	835.9	845.4	853.5	861.4	859.0
140°	870.1	876.5	885.3	892.4	888.4
142.5°	898.9	904.4	914.8	921.0	917.1
145°	929.1	928.3	941.7	947.4	943.4
147.5°	955.3	952.9	966.4	970.4	967.3
150°	980.8	975.2	988.0	992.8	988.8
152.5°	1002.3	995.9	1007.8	1012.6	1007.1
155°	1023.0	1015.9	1025.4	1030.2	1023.8
157.5°	1039.7	1033.3	1040.6	1046.1	1039.7
160°	1054.0	1049.2	1054.0	1058.8	1053.2
162.5°	1066.8	1062.0	1066.0	1071.6	1064.4
165°	1077.9	1073.2	1075.6	1081.1	1075.6
167.5°	1086.7	1081.8	1084.4	1089.9	1082.7
170°	1093.9	1089.1	1090.6	1096.3	1089.1
172.5°	1098.6	1093.9	1095.5	1101.1	1093.9
175°	1102.5	1097.0	1098.6	1104.2	1096.3
177.5°	1104.2	1098.6	1099.4	1105.1	1097.9
180°	1100.2	1100.2	1100.2	1100.2	1100.2

TEST NUMBER: P928564

CATALOG NUMBER: DFN2DIP-HX4F0-060D040US930-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.36	10.31	10.22	11.20	12.32	8.92	9.88	9.79	10.77	11.89
	3H	11.02	11.89	11.90	12.78	13.93	10.55	11.41	11.43	12.31	13.46
	4H	11.62	12.43	12.51	13.33	14.49	11.14	11.96	12.04	12.86	14.02
	6H	12.02	12.77	12.93	13.68	14.85	11.55	12.30	12.45	13.21	14.38
	8H	12.13	12.85	13.04	13.77	14.94	11.65	12.37	12.57	13.30	14.47
	12H	12.18	12.86	13.10	13.78	14.98	11.70	12.38	12.62	13.30	14.50
4H	2H	9.83	10.64	10.73	11.55	12.70	9.48	10.30	10.38	11.20	12.36
	3H	11.71	12.38	12.62	13.32	14.49	11.31	11.99	12.22	12.93	14.10
	4H	12.42	13.04	13.35	13.97	15.17	12.02	12.64	12.94	13.57	14.77
	6H	12.95	13.48	13.88	14.43	15.63	12.54	13.07	13.47	14.03	15.22
	8H	13.10	13.60	14.04	14.55	15.76	12.69	13.19	13.62	14.13	15.35
	12H	13.18	13.63	14.13	14.59	15.81	12.75	13.21	13.71	14.17	15.39
8H	4H	12.63	13.13	13.57	14.08	15.29	12.27	12.77	13.21	13.72	14.93
	6H	13.27	13.68	14.23	14.67	15.88	12.90	13.32	13.87	14.31	15.52
	8H	13.49	13.86	14.46	14.83	16.06	13.12	13.49	14.09	14.46	15.69
	12H	13.63	13.95	14.60	14.92	16.20	13.24	13.56	14.22	14.54	15.81
12H	4H	12.62	13.07	13.58	14.04	15.25	12.27	12.72	13.22	13.68	14.90
	6H	13.30	13.66	14.27	14.64	15.87	12.95	13.31	13.92	14.29	15.52
	8H	13.55	13.87	14.52	14.84	16.12	13.19	13.51	14.16	14.48	15.76