

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P928586

Luminaire Tested: DFN2DIP-HX4F0-060D090US930-RLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P928586
REPORT IS A COMBINATION OF REPORTS P900914 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-060D090US930-RLLONL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11418.1 lumens
Efficiency: N/A
Efficacy: 93.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 122.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P928586

CATALOG NUMBER: DFN2DIP-HX4F0-060D090US930-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P928586

CATALOG NUMBER: DFN2DIP-HX4F0-060D090US930-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44
1	95	91	87	84	86	83	80	77	67	65	63	52	51	50	39	38	38
2	87	80	74	69	78	73	68	63	59	56	53	46	44	42	35	33	32
3	79	70	63	58	72	64	58	53	52	48	45	41	38	36	31	29	28
4	73	63	55	49	66	57	51	46	47	42	38	37	34	31	28	26	24
5	67	56	48	42	60	51	44	39	42	37	33	33	30	27	25	23	21
6	62	50	42	37	56	46	39	34	38	33	29	30	27	24	23	21	19
7	57	45	38	32	52	41	35	30	34	29	26	28	24	21	21	19	17
8	53	41	34	29	48	38	31	27	31	26	23	25	22	19	20	17	15
9	49	37	30	25	45	34	28	24	29	24	20	23	20	17	18	16	14
10	46	34	27	23	42	32	25	21	26	22	18	22	18	15	17	14	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1503	1503	1503
5°	1505	1479	1488
10°	1491	1450	1440
15°	1470	1402	1365
20°	1443	1336	1273
25°	1415	1263	1185
30°	1378	1187	1072
35°	1342	1105	973
40°	1305	1021	860
45°	1262	927	757
50°	1217	833	657
55°	1171	732	561
60°	1117	626	462
65°	1055	519	416
70°	980	418	376
75°	886	369	343
80°	749	310	297
85°	524	208	224

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1269 cd/sqm

TEST NUMBER: P928586

CATALOG NUMBER: DFN2DIP-HX4F0-060D090US930-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.4	1.7
10°-20°	520.0	4.6
20°-30°	730.0	6.4
30°-40°	795.8	7.0
40°-50°	731.4	6.4
50°-60°	574.4	5.0
60°-70°	373.9	3.3
70°-80°	192.5	1.7
80°-90°	53.5	0.5
90°-100°	81.6	0.7
100°-110°	304.3	2.7
110°-120°	807.0	7.1
120°-130°	1338.5	11.7
130°-140°	1421.8	12.5
140°-150°	1321.4	11.6
150°-160°	1062.4	9.3
160°-170°	684.6	6.0
170°-180°	235.6	2.1
0°-30°	1439.4	12.6
0°-40°	2235.2	19.6
0°-60°	3541.0	31.0
0°-90°	4160.8	36.4
90°-120°	1193.0	10.4
90°-150°	5274.7	46.2
90°-180°	7257.0	63.6
0°-180°	11418.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2021	2021	2021	2021	2021	
5°	2021	2012	1988	2005	1999	192
15°	1922	1902	1840	1805	1787	542
25°	1745	1686	1566	1491	1463	802
35°	1504	1410	1249	1134	1094	941
45°	1229	1106	915	784	741	949
55°	935	792	594	485	450	835
65°	631	483	318	256	250	626
75°	336	208	146	134	132	356
85°	79	40	35	35	35	90
90°	2	22	36	45	48	11
95°	116	57	70	79	77	138
105°	544	598	109	129	136	582
115°	1030	1060	1105	276	147	1014
125°	1456	1480	1514	1526	1532	1299
135°	1802	1831	1847	1865	1861	1392
145°	2090	2088	2119	2132	2123	1307
155°	2302	2286	2307	2318	2304	1061
165°	2425	2415	2420	2432	2420	685
175°	2481	2468	2472	2484	2466	236
180°	2476	2476	2476	2476	2476	

TEST NUMBER: P928586

CATALOG NUMBER: DFN2DIP-HX4F0-060D090US930-RLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2021.0	2021.0	2021.0	2021.0	2021.0
2.5°	2030.2	2021.0	2000.8	2019.2	2015.6
5°	2021.0	2011.9	1988.0	2004.6	1999.1
7.5°	2004.6	1993.7	1968.1	1975.2	1966.1
10°	1982.6	1969.8	1933.3	1927.7	1916.8
12.5°	1955.3	1938.7	1889.3	1878.4	1858.2
15°	1922.3	1902.0	1839.9	1805.2	1787.0
17.5°	1883.9	1854.5	1777.7	1737.5	1708.2
20°	1839.9	1803.3	1711.9	1666.3	1625.9
22.5°	1792.4	1750.3	1644.2	1582.1	1554.7
25°	1744.9	1686.3	1565.6	1490.7	1463.2
27.5°	1688.3	1625.9	1492.4	1406.4	1364.4
30°	1627.9	1558.2	1411.9	1318.8	1269.3
32.5°	1569.3	1485.1	1335.3	1225.4	1179.6
35°	1503.5	1410.2	1249.3	1134.0	1093.6
37.5°	1439.5	1338.7	1168.8	1042.5	996.8
40°	1371.7	1262.1	1084.5	954.7	907.2
42.5°	1302.3	1185.3	1000.5	865.0	819.5
45°	1229.1	1106.4	914.6	784.5	740.7
47.5°	1159.7	1029.8	832.3	702.3	662.1
50°	1082.8	953.0	751.8	625.4	587.2
52.5°	1007.7	870.5	674.9	554.2	519.5
55°	934.6	791.9	594.4	484.8	450.0
57.5°	859.7	713.3	523.1	420.7	391.4
60°	782.8	636.5	448.1	354.9	325.6
62.5°	707.9	561.6	384.0	296.3	281.7
65°	631.1	482.8	318.3	256.2	250.5
67.5°	557.9	409.6	256.2	224.9	219.5
70°	481.0	338.4	212.1	193.9	186.5
72.5°	407.9	272.5	177.3	162.8	159.1
75°	336.5	208.4	146.3	133.5	131.8
77.5°	265.3	148.1	115.2	107.9	104.2
80°	199.3	106.1	87.7	80.5	80.5
82.5°	139.0	71.4	60.3	56.6	56.6
85°	78.6	40.2	34.7	34.7	34.7
87.5°	29.3	14.6	14.6	12.8	12.8
90°	1.7	21.5	35.7	44.9	48.2
92.5°	44.9	37.7	43.0	46.6	48.2
95°	116.4	57.2	69.8	78.9	77.0
97.5°	209.5	62.8	91.3	96.7	98.5
100°	317.1	71.7	102.1	116.4	120.0
102.5°	435.2	431.8	105.7	125.3	130.8
105°	544.5	598.4	109.3	128.9	136.1
107.5°	671.7	716.4	113.0	132.5	139.8
110°	793.6	831.1	313.5	134.4	141.5

TEST NUMBER: P928586

CATALOG NUMBER: DFN2DIP-HX4F0-060D090US930-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	908.2	940.3	909.9	137.8	143.4
115°	1029.9	1060.3	1105.2	275.9	146.9
117.5°	1135.6	1171.4	1202.0	945.7	476.4
120°	1253.9	1280.7	1313.0	1334.5	1092.7
122.5°	1354.1	1382.8	1418.8	1429.3	1431.3
125°	1456.2	1479.6	1513.6	1526.2	1531.5
127.5°	1549.3	1574.4	1601.5	1619.3	1621.0
130°	1637.2	1665.9	1685.5	1705.2	1703.6
132.5°	1726.7	1750.1	1769.7	1785.9	1784.2
135°	1802.0	1830.7	1846.7	1864.8	1861.2
137.5°	1880.8	1902.2	1920.3	1938.2	1932.9
140°	1957.7	1972.2	1991.8	2007.9	1999.0
142.5°	2022.4	2035.0	2058.1	2072.4	2063.5
145°	2090.5	2088.5	2119.0	2131.6	2122.6
147.5°	2149.4	2144.1	2174.5	2183.5	2176.4
150°	2206.9	2194.3	2223.0	2233.6	2224.7
152.5°	2255.1	2240.8	2267.7	2278.5	2265.9
155°	2301.7	2285.7	2307.2	2317.9	2303.6
157.5°	2339.4	2325.1	2341.3	2353.8	2339.4
160°	2371.6	2360.8	2371.6	2382.3	2369.8
162.5°	2400.2	2389.5	2398.5	2411.0	2394.9
165°	2425.3	2414.6	2420.0	2432.5	2420.0
167.5°	2445.1	2434.2	2439.7	2452.3	2436.1
170°	2461.2	2450.4	2454.0	2466.5	2450.4
172.5°	2471.9	2461.2	2464.8	2477.4	2461.2
175°	2480.8	2468.2	2471.9	2484.4	2466.5
177.5°	2484.4	2471.9	2473.8	2486.3	2470.2
180°	2475.5	2475.5	2475.5	2475.5	2475.5

TEST NUMBER: P928586

CATALOG NUMBER: DFN2DIP-HX4F0-060D090US930-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.15	7.88	8.22	8.95	10.40	3.12	3.85	4.19	4.92	6.38
	3H	8.82	9.47	9.90	10.55	12.02	4.30	4.96	5.38	6.03	7.51
	4H	9.42	10.04	10.51	11.12	12.60	4.75	5.37	5.84	6.45	7.93
	6H	9.84	10.41	10.94	11.49	12.98	5.07	5.64	6.17	6.72	8.21
	8H	9.96	10.51	11.07	11.60	13.09	5.16	5.70	6.26	6.80	8.28
	12H	10.02	10.54	11.13	11.63	13.14	5.20	5.71	6.31	6.80	8.31
4H	2H	7.15	7.77	8.25	8.85	10.33	3.71	4.32	4.80	5.40	6.88
	3H	8.98	9.49	10.08	10.60	12.09	5.05	5.56	6.15	6.67	8.16
	4H	9.66	10.14	10.77	11.23	12.75	5.59	6.07	6.70	7.16	8.67
	6H	10.18	10.58	11.29	11.70	13.20	6.01	6.41	7.13	7.53	9.04
	8H	10.35	10.73	11.47	11.84	13.36	6.14	6.51	7.25	7.63	9.15
	12H	10.44	10.78	11.57	11.91	13.43	6.20	6.54	7.33	7.66	9.19
8H	4H	9.63	10.00	10.74	11.11	12.64	5.87	6.24	6.98	7.36	8.88
	6H	10.19	10.50	11.33	11.65	13.17	6.38	6.70	7.52	7.85	9.37
	8H	10.41	10.68	11.55	11.81	13.35	6.58	6.85	7.72	7.98	9.52
	12H	10.54	10.78	11.69	11.91	13.49	6.69	6.93	7.84	8.06	9.64
12H	4H	9.57	9.91	10.71	11.04	12.56	5.87	6.21	7.00	7.33	8.86
	6H	10.16	10.44	11.31	11.57	13.11	6.43	6.71	7.58	7.84	9.38
	8H	10.38	10.62	11.53	11.75	13.33	6.64	6.88	7.79	8.01	9.58

END OF REPORT