

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P928612

Luminaire Tested: DFN2DIP-HX4F0-070D070US930-FLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P928612
REPORT IS A COMBINATION OF REPORTS P900879 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-070D070US930-FLONL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11296.0 lumens
Efficiency: N/A
Efficacy: 95.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 118.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9972
Total Harmonic Distortion (THDi): 0.128
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P928612
CATALOG NUMBER: DFN2DIP-HX4F0-070D070US930-FLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P928612

CATALOG NUMBER: DFN2DIP-HX4F0-070D070US930-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	56	56	56	50
1	98	93	90	86	90	86	83	80	73	71	68	61	59	58	50	48	47	50	48	47	42
2	89	82	75	70	82	76	70	66	64	60	57	53	51	48	44	42	40	44	42	40	35
3	81	72	64	59	75	66	60	55	56	52	48	47	44	41	39	36	34	39	36	34	30
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	35	32	29	35	32	29	26
5	68	57	48	42	63	53	45	40	45	39	35	38	34	30	31	28	26	31	28	26	22
6	63	51	43	37	58	47	40	35	40	35	31	34	30	27	28	25	23	28	25	23	20
7	58	46	38	32	53	43	36	30	37	31	27	31	27	23	26	23	20	26	23	20	17
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	24	20	18	24	20	18	16
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	19	16	22	19	16	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1651	1651	1651
5°	1653	1628	1639
10°	1640	1606	1617
15°	1616	1580	1582
20°	1584	1543	1547
25°	1551	1499	1506
30°	1511	1459	1454
35°	1473	1411	1398
40°	1425	1362	1346
45°	1378	1313	1292
50°	1327	1262	1230
55°	1273	1203	1173
60°	1212	1133	1108
65°	1146	1061	1031
70°	1061	972	948
75°	944	866	871
80°	803	732	725
85°	583	499	482

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1378 cd/sqm



TEST NUMBER: P928612

CATALOG NUMBER: DFN2DIP-HX4F0-070D070US930-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	208.9	1.8
10°-20°	587.9	5.2
20°-30°	863.9	7.6
30°-40°	1003.4	8.9
40°-50°	1002.1	8.9
50°-60°	873.8	7.7
60°-70°	646.0	5.7
70°-80°	365.5	3.2
80°-90°	99.9	0.9
90°-100°	63.5	0.6
100°-110°	236.7	2.1
110°-120°	627.7	5.6
120°-130°	1041.1	9.2
130°-140°	1105.9	9.8
140°-150°	1027.8	9.1
150°-160°	826.3	7.3
160°-170°	532.4	4.7
170°-180°	183.3	1.6
0°-30°	1660.7	14.7
0°-40°	2664.1	23.6
0°-60°	4540.1	40.2
0°-90°	5651.4	50.0
90°-120°	927.9	8.2
90°-150°	4102.6	36.3
90°-180°	5645.0	50.0
0°-180°	11296.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2220	2220	2220	2220	2220	
5°	2220	2212	2188	2205	2201	211
15°	2113	2100	2073	2081	2071	595
25°	1913	1896	1859	1863	1859	880
35°	1650	1629	1594	1582	1571	1030
45°	1343	1328	1296	1272	1264	1036
55°	1016	1003	978	952	941	908
65°	685	672	651	632	621	678
75°	358	354	344	331	335	383
85°	87	85	83	77	75	98
90°	1	17	28	35	38	10
95°	90	44	54	61	60	107
105°	424	465	85	100	106	453
115°	801	825	860	215	114	789
125°	1133	1151	1177	1187	1191	1010
135°	1402	1424	1436	1450	1448	1083
145°	1626	1624	1648	1658	1651	1017
155°	1790	1778	1794	1803	1792	825
165°	1886	1878	1882	1892	1882	533
175°	1930	1920	1923	1932	1918	184
180°	1925	1925	1925	1925	1925	



TEST NUMBER: P928612

CATALOG NUMBER: DFN2DIP-HX4F0-070D070US930-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2219.8	2219.8	2219.8	2219.8	2219.8
2.5°	2232.8	2222.1	2198.5	2219.8	2215.7
5°	2219.8	2211.5	2187.9	2204.9	2200.8
7.5°	2204.9	2192.2	2168.6	2185.9	2181.6
10°	2181.6	2166.6	2141.0	2158.0	2151.7
12.5°	2149.4	2136.8	2111.2	2121.8	2117.5
15°	2113.2	2100.5	2072.6	2081.3	2070.6
17.5°	2068.3	2055.7	2027.8	2038.5	2027.8
20°	2019.2	2006.5	1976.6	1983.0	1974.6
22.5°	1970.3	1951.0	1923.2	1923.2	1918.8
25°	1912.6	1895.5	1859.3	1863.4	1859.3
27.5°	1848.4	1833.5	1805.9	1799.5	1788.8
30°	1784.6	1767.3	1735.5	1729.1	1720.5
32.5°	1716.1	1703.5	1669.3	1656.4	1647.8
35°	1650.0	1628.8	1594.5	1581.7	1571.0
37.5°	1575.3	1556.1	1521.8	1506.9	1496.3
40°	1498.5	1481.3	1447.1	1428.1	1419.5
42.5°	1423.8	1406.6	1372.6	1351.1	1338.4
45°	1342.7	1327.8	1295.6	1272.3	1263.7
47.5°	1263.7	1248.7	1214.5	1191.0	1178.3
50°	1180.4	1169.7	1139.8	1109.9	1099.3
52.5°	1099.3	1084.4	1056.7	1033.2	1018.2
55°	1016.1	1003.3	977.7	952.1	941.4
57.5°	932.8	922.2	894.3	868.7	860.2
60°	849.5	841.1	811.3	787.7	781.3
62.5°	768.4	753.5	732.2	710.9	702.3
65°	685.3	672.4	651.1	631.9	621.2
67.5°	599.9	589.1	570.0	555.1	546.5
70°	520.9	512.3	493.0	478.1	469.7
72.5°	439.8	431.2	420.5	405.6	399.3
75°	358.5	354.4	343.5	330.9	335.2
77.5°	286.1	277.4	273.1	266.7	260.5
80°	213.5	211.3	207.0	200.7	196.3
82.5°	145.2	145.2	143.1	134.6	134.6
85°	87.4	85.4	83.4	76.8	74.7
87.5°	38.5	34.2	29.9	23.6	21.3
90°	1.3	16.7	27.8	34.9	37.6
92.5°	34.9	29.3	33.4	36.3	37.6
95°	90.5	44.5	54.3	61.4	59.9
97.5°	162.9	48.8	71.0	75.3	76.6
100°	246.7	55.7	79.4	90.5	93.3
102.5°	338.5	335.9	82.2	97.5	101.7
105°	423.6	465.4	85.0	100.2	105.9
107.5°	522.4	557.2	87.9	103.1	108.7
110°	617.3	646.4	243.8	104.6	110.0



TEST NUMBER: P928612

CATALOG NUMBER: DFN2DIP-HX4F0-070D070US930-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	706.4	731.4	707.7	107.2	111.5
115°	801.1	824.7	859.6	214.6	114.3
117.5°	883.3	911.1	934.9	735.5	370.6
120°	975.2	996.1	1021.3	1038.0	849.9
122.5°	1053.1	1075.5	1103.5	1111.7	1113.2
125°	1132.6	1150.8	1177.3	1187.0	1191.1
127.5°	1205.1	1224.5	1245.6	1259.5	1260.8
130°	1273.4	1295.7	1310.9	1326.3	1325.0
132.5°	1343.0	1361.2	1376.5	1389.0	1387.7
135°	1401.6	1423.9	1436.4	1450.4	1447.6
137.5°	1462.8	1479.6	1493.6	1507.5	1503.3
140°	1522.7	1533.9	1549.2	1561.7	1554.8
142.5°	1572.9	1582.7	1600.7	1611.8	1604.9
145°	1625.9	1624.5	1648.1	1657.9	1650.9
147.5°	1671.7	1667.7	1691.3	1698.2	1692.8
150°	1716.4	1706.7	1729.0	1737.3	1730.3
152.5°	1754.0	1742.9	1763.7	1772.1	1762.4
155°	1790.2	1777.8	1794.5	1802.8	1791.7
157.5°	1819.5	1808.4	1821.0	1830.7	1819.5
160°	1844.7	1836.2	1844.7	1852.9	1843.1
162.5°	1866.8	1858.5	1865.5	1875.2	1862.7
165°	1886.3	1878.1	1882.2	1891.9	1882.2
167.5°	1901.7	1893.2	1897.6	1907.3	1894.8
170°	1914.3	1905.9	1908.6	1918.4	1905.9
172.5°	1922.6	1914.3	1917.1	1926.8	1914.3
175°	1929.5	1919.7	1922.6	1932.3	1918.4
177.5°	1932.3	1922.6	1924.1	1933.8	1921.2
180°	1925.4	1925.4	1925.4	1925.4	1925.4



TEST NUMBER: P928612
 CATALOG NUMBER: DFN2DIP-HX4F0-070D070US930-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.02	9.88	9.97	10.85	12.12	8.58	9.45	9.54	10.42	11.69
	3H	10.68	11.45	11.65	12.43	13.73	10.21	10.98	11.17	11.96	13.25
	4H	11.27	12.00	12.25	12.98	14.28	10.79	11.52	11.77	12.51	13.81
	6H	11.67	12.34	12.66	13.33	14.65	11.19	11.87	12.18	12.86	14.17
	8H	11.77	12.41	12.77	13.42	14.73	11.30	11.94	12.30	12.95	14.26
	12H	11.82	12.43	12.83	13.43	14.77	11.34	11.95	12.34	12.95	14.29
4H	2H	9.48	10.21	10.47	11.20	12.50	9.13	9.87	10.12	10.85	12.15
	3H	11.35	11.96	12.34	12.97	14.29	10.95	11.56	11.95	12.58	13.89
	4H	12.06	12.62	13.07	13.63	14.97	11.66	12.21	12.66	13.22	14.56
	6H	12.58	13.06	13.59	14.09	15.43	12.17	12.65	13.18	13.68	15.02
	8H	12.73	13.18	13.75	14.20	15.55	12.32	12.76	13.33	13.79	15.14
	12H	12.80	13.21	13.84	14.25	15.60	12.38	12.79	13.42	13.82	15.18
8H	4H	12.26	12.71	13.28	13.73	15.08	11.90	12.35	12.92	13.37	14.72
	6H	12.89	13.26	13.93	14.33	15.68	12.53	12.90	13.57	13.97	15.31
	8H	13.11	13.44	14.16	14.49	15.86	12.74	13.07	13.79	14.12	15.49
	12H	13.25	13.53	14.30	14.58	15.99	12.86	13.15	13.91	14.19	15.60
12H	4H	12.24	12.65	13.28	13.69	15.05	11.89	12.30	12.93	13.34	14.69
	6H	12.92	13.25	13.97	14.30	15.67	12.57	12.90	13.62	13.95	15.32
	8H	13.16	13.45	14.22	14.50	15.91	12.81	13.10	13.86	14.14	15.55