

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P928658

Luminaire Tested: DFN2DIP-HX4F0-080D090US930-RLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P928658
REPORT IS A COMBINATION OF REPORTS P900918 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-080D090US930-RLLONL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12803.7 lumens
Efficiency: N/A
Efficacy: 88.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 144.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9613
Total Harmonic Distortion (THDi): 0.083
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P928658

CATALOG NUMBER: DFN2DIP-HX4F0-080D090US930-RLONL

Luminous Intensity Polar Plot



TEST NUMBER: P928658

CATALOG NUMBER: DFN2DIP-HX4F0-080D090US930-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50
1	97	93	89	86	88	85	82	79	70	68	66	57	56	54	45	44	43
2	88	81	75	71	81	75	70	65	62	59	55	51	48	46	40	38	37
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	36	34	32
4	74	64	56	50	68	59	52	47	49	44	40	40	37	34	32	30	28
5	68	57	49	43	62	53	46	41	44	39	35	36	33	30	29	27	24
6	63	51	43	38	57	47	40	35	40	35	31	33	29	26	27	24	22
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	24	22	19
8	54	42	35	30	49	39	32	28	33	28	24	28	24	21	23	20	18
9	50	39	31	26	46	36	29	25	31	25	22	26	22	19	21	18	16
10	47	35	28	24	43	33	27	22	28	23	20	24	20	17	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2004	2004	2004
5°	2007	1972	1985
10°	1987	1934	1920
15°	1960	1870	1820
20°	1924	1782	1698
25°	1887	1683	1580
30°	1838	1582	1430
35°	1789	1474	1298
40°	1740	1361	1147
45°	1682	1236	1010
50°	1623	1110	876
55°	1561	975	748
60°	1489	835	616
65°	1407	691	554
70°	1307	558	502
75°	1181	492	457
80°	999	414	396
85°	699	277	299

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1682 cd/sqm

TEST NUMBER: P928658

CATALOG NUMBER: DFN2DIP-HX4F0-080D090US930-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	252.6	2.0
10°-20°	693.3	5.4
20°-30°	973.4	7.6
30°-40°	1061.0	8.3
40°-50°	975.2	7.6
50°-60°	765.9	6.0
60°-70°	498.5	3.9
70°-80°	256.6	2.0
80°-90°	69.9	0.5
90°-100°	81.6	0.6
100°-110°	304.3	2.4
110°-120°	807.0	6.3
120°-130°	1338.5	10.5
130°-140°	1421.8	11.1
140°-150°	1321.4	10.3
150°-160°	1062.4	8.3
160°-170°	684.6	5.3
170°-180°	235.6	1.8
0°-30°	1919.2	15.0
0°-40°	2980.3	23.3
0°-60°	4721.4	36.9
0°-90°	5546.4	43.3
90°-120°	1193.0	9.3
90°-150°	5274.7	41.2
90°-180°	7257.0	56.7
0°-180°	12803.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2695	2695	2695	2695	2695	
5°	2695	2683	2651	2673	2666	256
15°	2563	2536	2453	2407	2383	722
25°	2326	2248	2088	1988	1951	1070
35°	2005	1880	1666	1512	1458	1255
45°	1639	1475	1219	1046	988	1266
55°	1246	1056	792	646	600	1113
65°	841	644	424	342	334	834
75°	449	278	195	178	176	475
85°	105	54	46	46	46	120
90°	2	22	36	45	48	12
95°	116	57	70	79	77	138
105°	544	598	109	129	136	582
115°	1030	1060	1105	276	147	1014
125°	1456	1480	1514	1526	1532	1299
135°	1802	1831	1847	1865	1861	1392
145°	2090	2088	2119	2132	2123	1307
155°	2302	2286	2307	2318	2304	1061
165°	2425	2415	2420	2432	2420	685
175°	2481	2468	2472	2484	2466	236
180°	2476	2476	2476	2476	2476	

TEST NUMBER: P928658

CATALOG NUMBER: DFN2DIP-HX4F0-080D090US930-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2694.7	2694.7	2694.7	2694.7	2694.7
2.5°	2706.9	2694.7	2667.8	2692.4	2687.5
5°	2694.7	2682.6	2650.7	2672.7	2665.5
7.5°	2672.7	2658.2	2624.1	2633.7	2621.4
10°	2643.5	2626.4	2577.8	2570.3	2555.8
12.5°	2607.0	2585.0	2519.0	2504.5	2477.6
15°	2563.0	2536.1	2453.3	2407.0	2382.7
17.5°	2511.7	2472.7	2370.3	2316.7	2277.6
20°	2453.3	2404.4	2282.6	2221.8	2167.9
22.5°	2389.9	2333.8	2192.3	2109.5	2073.0
25°	2326.5	2248.4	2087.5	1987.6	1950.9
27.5°	2250.9	2167.9	1989.9	1875.3	1819.2
30°	2170.5	2077.6	1882.6	1758.4	1692.3
32.5°	2092.3	1980.1	1780.4	1633.9	1572.9
35°	2004.7	1880.2	1665.7	1512.1	1458.2
37.5°	1919.2	1785.0	1558.4	1389.9	1329.1
40°	1829.0	1682.8	1446.1	1272.9	1209.5
42.5°	1736.4	1580.4	1334.0	1153.5	1092.6
45°	1638.8	1475.3	1219.4	1046.1	987.6
47.5°	1546.2	1373.1	1109.7	936.4	882.8
50°	1443.7	1270.7	1002.4	833.9	782.9
52.5°	1343.6	1160.6	899.8	739.0	692.7
55°	1246.1	1055.9	792.5	646.3	600.0
57.5°	1146.2	951.1	697.6	561.0	521.8
60°	1043.7	848.7	597.4	473.2	434.2
62.5°	943.9	748.7	512.1	395.1	375.7
65°	841.4	643.7	424.3	341.6	334.0
67.5°	743.9	546.2	341.6	299.8	292.7
70°	641.4	451.3	282.8	258.4	248.7
72.5°	543.8	363.2	236.5	217.1	212.1
75°	448.7	277.9	195.1	178.0	175.7
77.5°	353.7	197.4	153.7	143.8	139.0
80°	265.7	141.6	117.0	107.3	107.3
82.5°	185.2	95.2	80.4	75.6	75.6
85°	104.8	53.5	46.3	46.3	46.3
87.5°	39.0	19.4	19.4	17.1	17.1
90°	1.7	21.5	35.7	44.9	48.2
92.5°	44.9	37.7	43.0	46.6	48.2
95°	116.4	57.2	69.8	78.9	77.0
97.5°	209.5	62.8	91.3	96.7	98.5
100°	317.1	71.7	102.1	116.4	120.0
102.5°	435.2	431.8	105.7	125.3	130.8
105°	544.5	598.4	109.3	128.9	136.1
107.5°	671.7	716.4	113.0	132.5	139.8
110°	793.6	831.1	313.5	134.4	141.5

TEST NUMBER: P928658

CATALOG NUMBER: DFN2DIP-HX4F0-080D090US930-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	908.2	940.3	909.9	137.8	143.4
115°	1029.9	1060.3	1105.2	275.9	146.9
117.5°	1135.6	1171.4	1202.0	945.7	476.4
120°	1253.9	1280.7	1313.0	1334.5	1092.7
122.5°	1354.1	1382.8	1418.8	1429.3	1431.3
125°	1456.2	1479.6	1513.6	1526.2	1531.5
127.5°	1549.3	1574.4	1601.5	1619.3	1621.0
130°	1637.2	1665.9	1685.5	1705.2	1703.6
132.5°	1726.7	1750.1	1769.7	1785.9	1784.2
135°	1802.0	1830.7	1846.7	1864.8	1861.2
137.5°	1880.8	1902.2	1920.3	1938.2	1932.9
140°	1957.7	1972.2	1991.8	2007.9	1999.0
142.5°	2022.4	2035.0	2058.1	2072.4	2063.5
145°	2090.5	2088.5	2119.0	2131.6	2122.6
147.5°	2149.4	2144.1	2174.5	2183.5	2176.4
150°	2206.9	2194.3	2223.0	2233.6	2224.7
152.5°	2255.1	2240.8	2267.7	2278.5	2265.9
155°	2301.7	2285.7	2307.2	2317.9	2303.6
157.5°	2339.4	2325.1	2341.3	2353.8	2339.4
160°	2371.6	2360.8	2371.6	2382.3	2369.8
162.5°	2400.2	2389.5	2398.5	2411.0	2394.9
165°	2425.3	2414.6	2420.0	2432.5	2420.0
167.5°	2445.1	2434.2	2439.7	2452.3	2436.1
170°	2461.2	2450.4	2454.0	2466.5	2450.4
172.5°	2471.9	2461.2	2464.8	2477.4	2461.2
175°	2480.8	2468.2	2471.9	2484.4	2466.5
177.5°	2484.4	2471.9	2473.8	2486.3	2470.2
180°	2475.5	2475.5	2475.5	2475.5	2475.5

TEST NUMBER: P928658

CATALOG NUMBER: DFN2DIP-HX4F0-080D090US930-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.91	9.68	9.92	10.71	12.07	4.88	5.66	5.90	6.68	8.05
	3H	10.58	11.28	11.61	12.31	13.69	6.07	6.76	7.09	7.79	9.18
	4H	11.19	11.85	12.23	12.88	14.27	6.51	7.17	7.56	8.21	9.60
	6H	11.61	12.21	12.66	13.25	14.66	6.83	7.44	7.89	8.48	9.88
	8H	11.73	12.31	12.79	13.36	14.76	6.92	7.50	7.98	8.56	9.96
	12H	11.79	12.34	12.85	13.39	14.81	6.97	7.51	8.03	8.56	9.99
4H	2H	8.92	9.58	9.97	10.61	12.00	5.47	6.13	6.52	7.16	8.56
	3H	10.74	11.29	11.80	12.35	13.76	6.82	7.36	7.87	8.43	9.83
	4H	11.43	11.94	12.50	12.99	14.42	7.36	7.86	8.42	8.92	10.35
	6H	11.95	12.38	13.02	13.45	14.88	7.78	8.21	8.85	9.29	10.71
	8H	12.12	12.52	13.19	13.59	15.03	7.91	8.31	8.98	9.38	10.82
	12H	12.22	12.58	13.30	13.66	15.11	7.97	8.34	9.06	9.42	10.86
8H	4H	11.40	11.80	12.47	12.87	14.31	7.64	8.04	8.71	9.11	10.55
	6H	11.96	12.30	13.06	13.41	14.84	8.16	8.49	9.25	9.60	11.04
	8H	12.18	12.47	13.28	13.57	15.02	8.35	8.64	9.45	9.74	11.19
	12H	12.32	12.57	13.42	13.66	15.16	8.47	8.72	9.57	9.81	11.31
12H	4H	11.35	11.71	12.44	12.79	14.24	7.64	8.01	8.73	9.09	10.53
	6H	11.94	12.23	13.04	13.32	14.78	8.21	8.50	9.31	9.59	11.05
	8H	12.16	12.41	13.26	13.50	15.00	8.42	8.67	9.52	9.76	11.26