

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P927400

Luminaire Tested: DFN2DIP-HX4F0-090D100US835-FLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P927400
REPORT IS A COMBINATION OF REPORTS P900937 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-090D100US835-FLLONL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 18810.0 lumens
Efficiency: N/A
Efficacy: 114.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 164.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9821
Total Harmonic Distortion (THDi): 0.08
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P927400

CATALOG NUMBER: DFN2DIP-HX4F0-090D100US835-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P927400

CATALOG NUMBER: DFN2DIP-HX4F0-090D100US835-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	47	47	47
1	97	93	89	86	89	86	82	79	72	69	67	59	57	56	47	46	45	40	40	40
2	89	81	75	70	81	75	70	65	63	59	56	52	49	47	42	40	38	33	33	33
3	81	71	64	58	74	66	59	54	55	51	47	46	42	40	37	35	33	28	28	28
4	74	63	55	49	68	58	51	46	49	44	40	41	37	34	33	30	28	24	24	24
5	68	56	48	42	62	52	45	40	44	39	34	37	33	29	30	27	24	21	21	21
6	62	50	42	37	57	47	40	34	40	34	30	33	29	26	27	24	22	19	19	19
7	58	45	38	32	53	42	35	30	36	30	26	30	26	23	25	22	19	16	16	16
8	54	41	34	28	49	38	31	27	33	27	23	28	23	20	23	20	17	15	15	15
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	21	18	15	13	13	13
10	47	35	27	23	43	32	26	21	28	22	19	23	19	16	19	16	14	12	12	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2604	2604	2604
5°	2608	2568	2585
10°	2587	2534	2550
15°	2550	2492	2496
20°	2498	2434	2440
25°	2447	2365	2375
30°	2384	2301	2293
35°	2323	2225	2206
40°	2248	2149	2123
45°	2174	2072	2039
50°	2093	1992	1941
55°	2008	1898	1851
60°	1912	1788	1748
65°	1807	1673	1626
70°	1674	1534	1495
75°	1489	1367	1374
80°	1267	1154	1143
85°	919	787	760

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2174 cd/sqm

TEST NUMBER: P927400

CATALOG NUMBER: DFN2DIP-HX4F0-090D100US835-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	329.6	1.8
10°-20°	927.4	4.9
20°-30°	1362.9	7.2
30°-40°	1582.9	8.4
40°-50°	1580.9	8.4
50°-60°	1378.5	7.3
60°-70°	1019.0	5.4
70°-80°	576.6	3.1
80°-90°	158.1	0.8
90°-100°	111.3	0.6
100°-110°	414.9	2.2
110°-120°	1100.3	5.8
120°-130°	1824.9	9.7
130°-140°	1938.4	10.3
140°-150°	1801.5	9.6
150°-160°	1448.4	7.7
160°-170°	933.3	5.0
170°-180°	321.2	1.7
0°-30°	2619.9	13.9
0°-40°	4202.8	22.3
0°-60°	7162.3	38.1
0°-90°	8915.9	47.4
90°-120°	1626.4	8.6
90°-150°	7191.2	38.2
90°-180°	9894.0	52.6
0°-180°	18810.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3502	3502	3502	3502	3502	
5°	3502	3489	3452	3478	3472	332
15°	3334	3314	3270	3283	3266	939
25°	3017	2990	2933	2940	2933	1388
35°	2603	2570	2516	2495	2478	1626
45°	2118	2095	2044	2007	1994	1635
55°	1603	1583	1542	1502	1485	1433
65°	1081	1061	1027	997	980	1069
75°	566	559	542	522	529	604
85°	138	135	132	121	118	154
90°	2	29	49	61	66	17
95°	159	78	95	108	105	188
105°	742	816	149	176	186	793
115°	1404	1446	1507	376	200	1382
125°	1985	2017	2064	2081	2088	1771
135°	2457	2496	2518	2542	2537	1898
145°	2850	2847	2889	2906	2894	1782
155°	3138	3116	3146	3160	3141	1446
165°	3306	3292	3299	3316	3299	934
175°	3382	3365	3370	3387	3363	322
180°	3375	3375	3375	3375	3375	

TEST NUMBER: P927400

CATALOG NUMBER: DFN2DIP-HX4F0-090D100US835-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3501.9	3501.9	3501.9	3501.9	3501.9
2.5°	3522.3	3505.5	3468.4	3501.9	3495.5
5°	3501.9	3488.7	3451.6	3478.4	3471.9
7.5°	3478.4	3458.4	3421.2	3448.4	3441.6
10°	3441.6	3418.0	3377.6	3404.4	3394.4
12.5°	3390.8	3370.8	3330.5	3347.2	3340.5
15°	3333.7	3313.7	3269.7	3283.3	3266.5
17.5°	3262.9	3242.9	3199.0	3215.8	3199.0
20°	3185.4	3165.4	3118.2	3128.2	3115.0
22.5°	3108.2	3077.9	3033.9	3033.9	3027.1
25°	3017.1	2990.3	2933.2	2939.6	2933.2
27.5°	2916.0	2892.4	2848.9	2838.9	2822.1
30°	2815.3	2788.1	2737.7	2727.7	2714.2
32.5°	2707.4	2687.4	2633.4	2613.1	2599.5
35°	2603.1	2569.5	2515.5	2495.2	2478.4
37.5°	2485.2	2454.8	2400.8	2377.3	2360.5
40°	2364.0	2336.9	2282.9	2252.9	2239.4
42.5°	2246.1	2219.0	2165.4	2131.5	2111.5
45°	2118.2	2094.7	2043.9	2007.1	1993.6
47.5°	1993.6	1970.0	1916.0	1878.9	1858.9
50°	1862.1	1845.3	1798.1	1751.0	1734.2
52.5°	1734.2	1710.6	1667.0	1629.9	1606.3
55°	1603.1	1582.7	1542.3	1502.0	1485.2
57.5°	1471.6	1454.8	1410.9	1370.5	1356.9
60°	1340.1	1326.9	1279.7	1242.6	1232.6
62.5°	1212.2	1188.6	1155.0	1121.5	1107.9
65°	1081.1	1060.7	1027.1	996.8	980.0
67.5°	946.4	929.3	899.2	875.7	862.1
70°	821.7	808.1	777.8	754.2	741.0
72.5°	693.8	680.2	663.4	639.9	629.9
75°	565.6	559.1	542.0	522.0	528.8
77.5°	451.2	437.7	430.9	420.9	410.9
80°	336.9	333.3	326.5	316.5	309.8
82.5°	229.0	229.0	225.8	212.2	212.2
85°	137.9	134.7	131.5	121.1	117.9
87.5°	60.7	53.9	47.2	37.2	33.6
90°	2.3	29.3	48.7	61.2	65.8
92.5°	61.2	51.3	58.6	63.5	65.8
95°	158.6	78.0	95.1	107.6	105.0
97.5°	285.6	85.5	124.4	131.9	134.3
100°	432.4	97.7	139.2	158.6	163.6
102.5°	593.3	588.7	144.1	170.8	178.3
105°	742.4	815.7	149.1	175.7	185.6
107.5°	915.8	976.7	154.0	180.7	190.5
110°	1081.9	1133.0	427.4	183.3	192.8

TEST NUMBER: P927400

CATALOG NUMBER: DFN2DIP-HX4F0-090D100US835-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1238.2	1282.0	1240.6	187.9	195.5
115°	1404.1	1445.6	1506.8	376.1	200.4
117.5°	1548.2	1597.0	1638.7	1289.3	649.6
120°	1709.5	1746.0	1790.1	1819.4	1489.7
122.5°	1846.1	1885.2	1934.2	1948.7	1951.3
125°	1985.3	2017.2	2063.6	2080.7	2087.9
127.5°	2112.3	2146.5	2183.3	2207.7	2210.0
130°	2232.0	2271.2	2297.9	2324.8	2322.5
132.5°	2354.1	2386.0	2412.7	2434.7	2432.4
135°	2456.8	2495.9	2517.7	2542.3	2537.4
137.5°	2564.1	2593.4	2618.0	2642.4	2635.1
140°	2669.0	2688.8	2715.4	2737.5	2725.3
142.5°	2757.2	2774.3	2805.9	2825.3	2813.2
145°	2850.0	2847.4	2888.9	2906.0	2893.8
147.5°	2930.3	2923.1	2964.5	2976.7	2967.2
150°	3008.6	2991.5	3030.7	3045.2	3033.0
152.5°	3074.4	3055.0	3091.6	3106.3	3089.2
155°	3138.0	3116.2	3145.5	3160.0	3140.6
157.5°	3189.3	3169.9	3191.9	3209.0	3189.3
160°	3233.4	3218.6	3233.4	3247.9	3230.8
162.5°	3272.2	3257.7	3269.9	3287.0	3265.0
165°	3306.4	3291.9	3299.2	3316.3	3299.2
167.5°	3333.4	3318.6	3326.2	3343.3	3321.2
170°	3355.4	3340.7	3345.6	3362.7	3340.7
172.5°	3369.9	3355.4	3360.4	3377.5	3355.4
175°	3382.1	3365.0	3369.9	3387.1	3362.7
177.5°	3387.1	3369.9	3372.6	3389.7	3367.6
180°	3374.9	3374.9	3374.9	3374.9	3374.9

TEST NUMBER: P927400

CATALOG NUMBER: DFN2DIP-HX4F0-090D100US835-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.35	11.19	11.33	12.18	13.49	9.92	10.76	10.90	11.75	13.06
	3H	12.01	12.76	13.00	13.77	15.09	11.54	12.29	12.53	13.29	14.62
	4H	12.60	13.31	13.60	14.32	15.65	12.13	12.84	13.13	13.84	15.18
	6H	13.00	13.65	14.01	14.66	16.01	12.52	13.18	13.54	14.19	15.54
	8H	13.10	13.73	14.12	14.75	16.10	12.63	13.25	13.65	14.28	15.62
	12H	13.15	13.74	14.18	14.76	16.14	12.67	13.26	13.69	14.28	15.65
4H	2H	10.81	11.52	11.82	12.53	13.87	10.47	11.18	11.48	12.18	13.52
	3H	12.68	13.27	13.69	14.30	15.66	12.28	12.88	13.30	13.91	15.26
	4H	13.39	13.93	14.42	14.96	16.33	12.99	13.53	14.01	14.55	15.93
	6H	13.91	14.37	14.94	15.42	16.79	13.50	13.96	14.53	15.01	16.38
	8H	14.06	14.49	15.09	15.53	16.92	13.64	14.08	14.68	15.12	16.51
	12H	14.13	14.52	15.18	15.58	16.97	13.71	14.10	14.76	15.16	16.55
8H	4H	13.59	14.02	14.62	15.07	16.45	13.23	13.66	14.26	14.71	16.09
	6H	14.22	14.58	15.28	15.66	17.05	13.86	14.22	14.92	15.30	16.68
	8H	14.44	14.76	15.51	15.83	17.23	14.07	14.39	15.14	15.46	16.86
	12H	14.57	14.85	15.64	15.91	17.36	14.19	14.47	15.26	15.53	16.97
12H	4H	13.57	13.97	14.63	15.02	16.41	13.22	13.61	14.27	14.67	16.06
	6H	14.25	14.57	15.32	15.63	17.04	13.90	14.21	14.97	15.28	16.68
	8H	14.49	14.77	15.56	15.83	17.28	14.13	14.41	15.21	15.48	16.92

END OF REPORT