

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P905529

Luminaire Tested: DFN2DIP-HX4F0-100D070US835-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P905529
REPORT IS A COMBINATION OF REPORTS P899366 AND P896188
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-100D070US835-RLLFLL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 14695.0 lumens
Efficiency: N/A
Efficacy: 105.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 138.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.946
Total Harmonic Distortion (THDi): 0.132
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P905529

CATALOG NUMBER: DFN2DIP-HX4F0-100D070US835-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P905529

CATALOG NUMBER: DFN2DIP-HX4F0-100D070US835-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	63	63	63
1	100	96	92	89	93	90	86	83	78	75	73	67	65	64	57	56	55
2	92	84	79	74	85	79	74	69	69	65	62	59	57	54	51	49	47
3	84	75	68	62	78	70	64	59	61	56	52	53	49	46	45	43	41
4	77	67	59	53	72	62	56	50	55	49	45	48	44	40	41	38	35
5	71	60	52	46	66	56	49	44	49	44	39	43	39	35	37	34	31
6	66	54	46	40	61	51	43	38	45	39	35	39	35	31	34	31	28
7	61	49	41	35	57	46	39	34	41	35	31	36	31	28	31	28	25
8	57	44	37	32	53	42	35	30	37	32	28	33	28	25	29	25	23
9	53	41	33	28	49	39	32	27	34	29	25	30	26	23	27	23	20
10	49	38	30	26	46	36	29	25	32	26	23	28	24	21	25	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3073	3073	3073
5°	3078	3025	3044
10°	3048	2966	2945
15°	3006	2868	2792
20°	2951	2733	2604
25°	2895	2582	2423
30°	2818	2427	2193
35°	2744	2260	1991
40°	2668	2088	1759
45°	2580	1896	1549
50°	2489	1703	1344
55°	2394	1496	1147
60°	2284	1280	944
65°	2157	1060	850
70°	2004	855	769
75°	1811	755	700
80°	1532	634	608
85°	1071	425	458

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2580 cd/sqm

TEST NUMBER: P905529

CATALOG NUMBER: DFN2DIP-HX4F0-100D070US835-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	387.3	2.6
10°-20°	1063.3	7.2
20°-30°	1492.9	10.2
30°-40°	1627.4	11.1
40°-50°	1495.7	10.2
50°-60°	1174.7	8.0
60°-70°	764.6	5.2
70°-80°	393.6	2.7
80°-90°	106.8	0.7
90°-100°	137.0	0.9
100°-110°	435.3	3.0
110°-120°	744.9	5.1
120°-130°	979.6	6.7
130°-140°	1099.6	7.5
140°-150°	1078.3	7.3
150°-160°	904.5	6.2
160°-170°	599.9	4.1
170°-180°	209.7	1.4
0°-30°	2943.6	20.0
0°-40°	4571.0	31.1
0°-60°	7241.3	49.3
0°-90°	8506.3	57.9
90°-120°	1317.2	9.0
90°-150°	4474.7	30.5
90°-180°	6189.0	42.1
0°-180°	14695.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4133	4133	4133	4133	4133	
5°	4133	4114	4066	4099	4088	392
15°	3931	3890	3763	3692	3654	1108
25°	3568	3448	3202	3048	2992	1641
35°	3075	2884	2555	2319	2236	1924
45°	2514	2263	1870	1604	1515	1941
55°	1911	1620	1216	991	920	1708
65°	1290	987	651	524	512	1279
75°	688	426	299	273	269	728
85°	161	82	71	71	71	184
90°	2	24	65	61	63	14
95°	97	116	120	120	116	108
105°	402	407	411	414	414	424
115°	748	758	755	753	748	739
125°	1087	1104	1099	1093	1091	972
135°	1406	1427	1431	1429	1424	1087
145°	1707	1721	1731	1733	1726	1067
155°	1952	1958	1964	1973	1967	899
165°	2124	2122	2122	2135	2126	599
175°	2210	2204	2200	2214	2202	210
180°	2214	2214	2214	2214	2214	

TEST NUMBER: P905529

CATALOG NUMBER: DFN2DIP-HX4F0-100D070US835-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4133.0	4133.0	4133.0	4133.0	4133.0
2.5°	4151.6	4133.0	4091.7	4129.4	4121.9
5°	4133.0	4114.3	4065.5	4099.3	4088.1
7.5°	4099.3	4077.0	4024.6	4039.3	4020.7
10°	4054.4	4028.2	3953.6	3942.1	3919.9
12.5°	3998.5	3964.7	3863.5	3841.3	3800.0
15°	3931.0	3889.7	3762.7	3691.7	3654.4
17.5°	3852.4	3792.5	3635.4	3553.2	3493.3
20°	3762.7	3687.7	3500.8	3407.6	3325.0
22.5°	3665.5	3579.4	3362.3	3235.4	3179.4
25°	3568.3	3448.5	3201.6	3048.4	2992.1
27.5°	3452.4	3325.0	3052.0	2876.2	2790.1
30°	3329.0	3186.5	2887.3	2696.9	2595.7
32.5°	3209.2	3036.9	2730.6	2506.0	2412.3
35°	3074.6	2883.8	2554.8	2319.1	2236.5
37.5°	2943.7	2737.7	2390.1	2131.8	2038.5
40°	2805.2	2581.0	2217.9	1952.4	1855.2
42.5°	2663.1	2423.8	2046.1	1769.1	1675.8
45°	2513.5	2262.7	1870.3	1604.4	1514.7
47.5°	2371.5	2106.0	1702.0	1436.1	1354.0
50°	2214.3	1948.8	1537.3	1279.0	1200.8
52.5°	2060.7	1780.2	1380.2	1133.3	1062.3
55°	1911.1	1619.5	1215.5	991.3	920.2
57.5°	1758.0	1458.7	1069.9	860.3	800.4
60°	1600.8	1301.6	916.3	725.8	665.9
62.5°	1447.6	1148.4	785.3	606.0	576.2
65°	1290.5	987.3	650.8	523.8	512.3
67.5°	1140.9	837.7	523.8	459.9	448.8
70°	983.7	692.1	433.7	396.4	381.4
72.5°	834.1	557.1	362.7	332.9	325.4
75°	688.1	426.2	299.2	273.0	269.4
77.5°	542.5	302.8	235.7	220.6	213.1
80°	407.5	217.1	179.4	164.7	164.7
82.5°	284.1	146.0	123.4	115.9	115.9
85°	160.7	82.1	71.0	71.0	71.0
87.5°	59.9	29.8	29.8	26.2	26.2
90°	2.0	24.0	65.4	61.4	63.4
92.5°	41.4	56.1	58.1	60.1	60.1
95°	97.4	116.1	119.5	119.5	116.1
97.5°	162.2	179.5	186.9	186.9	186.9
100°	236.9	252.3	257.6	257.6	255.6
102.5°	315.7	327.0	334.4	336.4	334.4
105°	401.8	407.1	411.1	414.5	414.5
107.5°	487.2	495.2	495.2	496.6	487.2
110°	570.0	580.7	580.7	580.7	575.3



TEST NUMBER: P905529

CATALOG NUMBER: DFN2DIP-HX4F0-100D070US835-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	659.4	670.8	668.8	663.4	659.4
115°	747.5	758.2	754.9	752.9	747.5
117.5°	834.9	849.6	840.3	834.9	829.6
120°	923.0	937.7	923.0	923.0	917.0
122.5°	1003.1	1021.8	1012.5	1007.1	1003.1
125°	1087.2	1103.9	1098.6	1092.6	1090.6
127.5°	1169.3	1190.0	1182.7	1174.7	1169.3
130°	1246.1	1270.1	1266.8	1262.8	1255.4
132.5°	1332.2	1350.9	1352.2	1342.9	1337.5
135°	1406.3	1426.9	1431.0	1428.9	1423.6
137.5°	1489.0	1505.7	1509.0	1507.7	1499.7
140°	1561.8	1578.5	1587.8	1587.8	1580.5
142.5°	1636.5	1653.2	1658.5	1660.5	1653.2
145°	1707.3	1720.6	1731.3	1733.3	1726.0
147.5°	1770.7	1787.4	1795.4	1798.7	1791.4
150°	1836.1	1847.4	1854.8	1860.8	1854.8
152.5°	1894.1	1905.5	1914.8	1922.2	1914.8
155°	1952.2	1957.5	1963.6	1972.9	1966.9
157.5°	2002.3	2006.3	2009.6	2023.0	2013.6
160°	2047.0	2051.0	2053.0	2064.3	2056.3
162.5°	2088.4	2088.4	2090.4	2103.0	2093.7
165°	2123.7	2121.7	2121.7	2135.1	2125.7
167.5°	2155.8	2149.8	2149.8	2163.1	2153.8
170°	2179.8	2174.5	2172.5	2185.8	2174.5
172.5°	2196.5	2191.1	2189.1	2202.5	2191.1
175°	2209.8	2204.5	2200.5	2213.8	2202.5
177.5°	2217.2	2211.8	2207.8	2219.2	2207.8
180°	2213.8	2213.8	2213.8	2213.8	2213.8

TEST NUMBER: P905529

CATALOG NUMBER: DFN2DIP-HX4F0-100D070US835-RLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.75	12.65	12.65	13.56	14.72	7.73	8.63	8.62	9.53	10.69
	3H	13.44	14.24	14.34	15.16	16.34	8.92	9.73	9.83	10.64	11.83
	4H	14.05	14.81	14.97	15.73	16.92	9.38	10.14	10.30	11.06	12.25
	6H	14.48	15.17	15.41	16.10	17.31	9.70	10.40	10.64	11.33	12.54
	8H	14.60	15.27	15.54	16.22	17.42	9.80	10.46	10.74	11.41	12.61
	12H	14.67	15.30	15.61	16.24	17.47	9.84	10.48	10.79	11.42	12.64
4H	2H	11.78	12.54	12.71	13.46	14.65	8.33	9.09	9.26	10.01	11.21
	3H	13.62	14.25	14.55	15.20	16.41	9.69	10.32	10.63	11.27	12.48
	4H	14.31	14.89	15.26	15.84	17.07	10.24	10.82	11.19	11.77	13.00
	6H	14.83	15.33	15.79	16.30	17.53	10.67	11.16	11.63	12.13	13.37
	8H	15.01	15.47	15.97	16.44	17.68	10.80	11.26	11.76	12.23	13.47
	12H	15.11	15.52	16.09	16.51	17.76	10.87	11.28	11.85	12.27	13.52
8H	4H	14.29	14.75	15.25	15.71	16.96	10.53	10.99	11.49	11.96	13.20
	6H	14.86	15.24	15.84	16.25	17.49	11.05	11.43	12.04	12.44	13.68
	8H	15.07	15.41	16.07	16.41	17.67	11.24	11.58	12.24	12.58	13.84
	12H	15.22	15.51	16.21	16.50	17.81	11.37	11.66	12.37	12.65	13.96
12H	4H	14.24	14.66	15.22	15.64	16.89	10.54	10.95	11.52	11.93	13.18
	6H	14.83	15.17	15.83	16.17	17.43	11.10	11.44	12.10	12.43	13.70
	8H	15.06	15.35	16.05	16.34	17.65	11.32	11.61	12.31	12.60	13.91

END OF REPORT

FIELD PERFORMANCE MAY DIFFER FROM LABORATORY PERFORMANCE

8 of 8