

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P927462

Luminaire Tested: DFN2DIP-HX4F0-110D070US835-RLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P927462
REPORT IS A COMBINATION OF REPORTS P900888 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-110D070US835-RLLONL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 16280.0 lumens
Efficiency: N/A
Efficacy: 99.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 164.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9967
Total Harmonic Distortion (THDi): 0.063
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P927462

CATALOG NUMBER: DFN2DIP-HX4F0-110D070US835-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P927462

CATALOG NUMBER: DFN2DIP-HX4F0-110D070US835-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	109	109	109	109		101	101	101	101		87	87	87		75	75	75		63	63	63
1	100	96	92	89		93	89	86	83		78	75	73		67	65	63		57	55	54
2	92	84	78	73		85	79	74	69		69	65	61		59	56	54		50	48	47
3	84	75	68	62		78	70	64	59		61	56	52		53	49	46		45	43	40
4	77	66	59	53		72	62	56	50		55	49	45		47	43	40		41	38	35
5	71	60	52	46		66	56	49	44		49	44	39		43	39	35		37	34	31
6	66	54	46	40		61	51	43	38		45	39	35		39	35	31		34	30	28
7	61	49	41	35		57	46	39	34		41	35	31		36	31	28		31	27	25
8	57	44	37	32		53	42	35	30		37	32	28		33	28	25		29	25	22
9	53	41	33	28		49	38	32	27		34	29	25		30	26	23		27	23	20
10	49	37	30	26		46	35	29	25		32	26	23		28	24	21		25	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3380	3380	3380
5°	3386	3327	3348
10°	3353	3262	3240
15°	3307	3155	3071
20°	3246	3006	2865
25°	3184	2840	2665
30°	3100	2670	2412
35°	3018	2486	2190
40°	2935	2296	1935
45°	2838	2086	1704
50°	2738	1873	1478
55°	2633	1646	1261
60°	2512	1408	1039
65°	2373	1166	935
70°	2204	941	846
75°	1993	830	770
80°	1686	697	669
85°	1179	467	504

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2838 cd/sqm

TEST NUMBER: P927462

CATALOG NUMBER: DFN2DIP-HX4F0-110D070US835-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	426.1	2.6
10°-20°	1169.7	7.2
20°-30°	1642.2	10.1
30°-40°	1790.1	11.0
40°-50°	1645.3	10.1
50°-60°	1292.1	7.9
60°-70°	841.1	5.2
70°-80°	432.9	2.7
80°-90°	114.7	0.7
90°-100°	77.9	0.5
100°-110°	290.4	1.8
110°-120°	770.2	4.7
120°-130°	1277.4	7.8
130°-140°	1356.9	8.3
140°-150°	1261.1	7.7
150°-160°	1013.9	6.2
160°-170°	653.3	4.0
170°-180°	224.9	1.4
0°-30°	3238.0	19.9
0°-40°	5028.1	30.9
0°-60°	7965.5	48.9
0°-90°	9354.2	57.5
90°-120°	1138.5	7.0
90°-150°	5033.8	30.9
90°-180°	6926.0	42.5
0°-180°	16280.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4546	4546	4546	4546	4546	
5°	4546	4526	4472	4509	4497	431
15°	4324	4279	4139	4061	4020	1218
25°	3925	3793	3522	3353	3291	1805
35°	3382	3172	2810	2551	2460	2117
45°	2765	2489	2057	1765	1666	2135
55°	2102	1781	1337	1090	1012	1879
65°	1420	1086	716	576	564	1407
75°	757	469	329	300	296	801
85°	177	90	78	78	78	203
90°	2	20	34	43	46	15
95°	111	55	67	75	74	131
105°	520	571	104	123	130	555
115°	983	1012	1055	263	140	968
125°	1390	1412	1444	1456	1462	1239
135°	1720	1747	1762	1780	1776	1328
145°	1995	1993	2022	2034	2026	1248
155°	2197	2181	2202	2212	2198	1012
165°	2314	2304	2309	2321	2309	654
175°	2368	2356	2359	2371	2354	225
180°	2362	2362	2362	2362	2362	

TEST NUMBER: P927462

CATALOG NUMBER: DFN2DIP-HX4F0-110D070US835-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4546.3	4546.3	4546.3	4546.3	4546.3
2.5°	4566.8	4546.3	4500.9	4542.4	4534.1
5°	4546.3	4525.8	4472.1	4509.2	4497.0
7.5°	4509.2	4484.7	4427.1	4443.3	4422.7
10°	4459.9	4431.0	4349.0	4336.3	4311.9
12.5°	4398.3	4361.2	4249.9	4225.4	4180.0
15°	4324.1	4278.7	4139.0	4060.9	4019.8
17.5°	4237.7	4171.8	3998.9	3908.5	3842.6
20°	4139.0	4056.5	3850.9	3748.3	3657.5
22.5°	4032.1	3937.3	3698.6	3558.9	3497.3
25°	3925.1	3793.3	3521.8	3353.3	3291.3
27.5°	3797.7	3657.5	3357.2	3163.8	3069.1
30°	3661.9	3505.2	3176.1	2966.5	2855.2
32.5°	3530.1	3340.6	3003.6	2756.6	2653.6
35°	3382.1	3172.1	2810.3	2551.0	2460.2
37.5°	3238.1	3011.5	2629.1	2344.9	2242.4
40°	3085.7	2839.1	2439.7	2147.6	2040.7
42.5°	2929.4	2666.2	2250.7	1946.0	1843.4
45°	2764.9	2489.0	2057.3	1764.8	1666.2
47.5°	2608.6	2316.6	1872.2	1579.7	1489.4
50°	2435.7	2143.7	1691.1	1406.9	1320.9
52.5°	2266.8	1958.2	1518.2	1246.7	1168.5
55°	2102.2	1781.4	1337.0	1090.4	1012.3
57.5°	1933.8	1604.6	1176.8	946.4	880.4
60°	1760.9	1431.8	1007.9	798.4	732.5
62.5°	1592.4	1263.3	863.9	666.6	633.8
65°	1419.5	1086.0	715.9	576.2	563.5
67.5°	1255.0	921.5	576.2	505.9	493.7
70°	1082.1	761.3	477.1	436.1	419.5
72.5°	917.5	612.9	399.0	366.2	357.9
75°	756.9	468.8	329.1	300.3	296.4
77.5°	596.7	333.1	259.3	242.7	234.4
80°	448.3	238.8	197.3	181.2	181.2
82.5°	312.5	160.6	135.8	127.5	127.5
85°	176.8	90.4	78.1	78.1	78.1
87.5°	65.9	32.7	32.7	28.8	28.8
90°	1.6	20.5	34.1	42.8	46.1
92.5°	42.8	35.9	41.0	44.5	46.1
95°	111.0	54.6	66.6	75.3	73.5
97.5°	199.9	59.9	87.1	92.4	94.0
100°	302.7	68.4	97.4	111.0	114.5
102.5°	415.3	412.1	100.9	119.6	124.8
105°	519.7	571.0	104.3	123.0	129.9
107.5°	641.0	683.7	107.8	126.5	133.4
110°	757.4	793.1	299.2	128.3	135.0

TEST NUMBER: P927462

CATALOG NUMBER: DFN2DIP-HX4F0-110D070US835-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	866.8	897.4	868.4	131.5	136.8
115°	982.9	1011.9	1054.7	263.3	140.3
117.5°	1083.8	1117.9	1147.1	902.5	454.7
120°	1196.6	1222.2	1253.1	1273.6	1042.8
122.5°	1292.2	1319.6	1354.0	1364.1	1365.9
125°	1389.7	1412.0	1444.5	1456.5	1461.5
127.5°	1478.6	1502.5	1528.3	1545.4	1547.0
130°	1562.4	1589.8	1608.5	1627.4	1625.8
132.5°	1647.9	1670.2	1688.9	1704.3	1702.7
135°	1719.7	1747.1	1762.4	1779.6	1776.2
137.5°	1794.8	1815.4	1832.6	1849.7	1844.6
140°	1868.3	1882.1	1900.8	1916.2	1907.7
142.5°	1930.0	1942.0	1964.1	1977.7	1969.2
145°	1995.0	1993.2	2022.2	2034.2	2025.7
147.5°	2051.2	2046.2	2075.2	2083.7	2077.0
150°	2106.0	2094.1	2121.5	2131.6	2123.1
152.5°	2152.1	2138.5	2164.1	2174.4	2162.5
155°	2196.6	2181.3	2201.8	2212.0	2198.4
157.5°	2232.5	2218.9	2234.3	2246.3	2232.5
160°	2263.4	2253.0	2263.4	2273.5	2261.5
162.5°	2290.6	2280.4	2288.9	2300.9	2285.5
165°	2314.5	2304.4	2309.4	2321.4	2309.4
167.5°	2333.4	2323.0	2328.3	2340.3	2324.9
170°	2348.8	2338.5	2341.9	2353.9	2338.5
172.5°	2359.0	2348.8	2352.3	2364.2	2348.8
175°	2367.5	2355.5	2359.0	2370.9	2353.9
177.5°	2370.9	2359.0	2360.8	2372.8	2357.3
180°	2362.4	2362.4	2362.4	2362.4	2362.4

TEST NUMBER: P927462

CATALOG NUMBER: DFN2DIP-HX4F0-110D070US835-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.05	12.94	12.95	13.86	15.02	8.02	8.92	8.92	9.83	10.99
	3H	13.73	14.53	14.64	15.45	16.64	9.22	10.02	10.13	10.94	12.13
	4H	14.34	15.10	15.27	16.03	17.23	9.67	10.43	10.60	11.36	12.55
	6H	14.77	15.47	15.71	16.40	17.61	10.00	10.69	10.93	11.63	12.84
	8H	14.90	15.56	15.84	16.51	17.72	10.09	10.75	11.04	11.70	12.91
	12H	14.96	15.59	15.91	16.54	17.77	10.14	10.77	11.09	11.71	12.95
4H	2H	12.08	12.83	13.01	13.76	14.96	8.63	9.38	9.56	10.31	11.51
	3H	13.91	14.54	14.85	15.50	16.71	9.98	10.61	10.92	11.57	12.78
	4H	14.61	15.18	15.56	16.13	17.37	10.54	11.11	11.49	12.06	13.30
	6H	15.13	15.62	16.09	16.60	17.83	10.96	11.45	11.92	12.43	13.67
	8H	15.30	15.76	16.27	16.73	17.98	11.09	11.55	12.06	12.52	13.77
	12H	15.40	15.82	16.39	16.80	18.06	11.16	11.58	12.15	12.56	13.82
8H	4H	14.58	15.04	15.55	16.01	17.26	10.82	11.28	11.79	12.25	13.50
	6H	15.15	15.53	16.14	16.54	17.79	11.34	11.72	12.34	12.74	13.99
	8H	15.37	15.70	16.37	16.70	17.97	11.54	11.87	12.54	12.87	14.14
	12H	15.51	15.81	16.51	16.80	18.11	11.66	11.96	12.66	12.95	14.26
12H	4H	14.54	14.95	15.52	15.94	17.19	10.83	11.24	11.81	12.23	13.49
	6H	15.13	15.46	16.13	16.46	17.73	11.39	11.73	12.39	12.73	14.00
	8H	15.35	15.65	16.35	16.64	17.95	11.61	11.90	12.61	12.90	14.21