

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P927466

Luminaire Tested: DFN2DIP-HX4F0-110D080US835-RLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P927466
REPORT IS A COMBINATION OF REPORTS P900906 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-110D080US835-RLLONL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 17270.0 lumens
Efficiency: N/A
Efficacy: 101.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 170.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9967
Total Harmonic Distortion (THDi): 0.063
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P927466

CATALOG NUMBER: DFN2DIP-HX4F0-110D080US835-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P927466

CATALOG NUMBER: DFN2DIP-HX4F0-110D080US835-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60
1	99	95	91	88	92	88	85	82	76	74	71	64	63	61	54	53	52
2	91	84	78	73	84	78	73	68	67	63	60	57	54	52	48	46	44
3	83	74	67	61	77	69	63	58	60	55	51	51	48	45	43	40	38
4	76	66	58	52	71	62	55	49	53	48	44	46	42	39	39	36	33
5	70	59	51	45	65	55	48	43	48	43	38	41	37	34	35	32	30
6	65	53	45	40	60	50	43	38	44	38	34	38	33	30	32	29	26
7	60	48	40	35	56	45	38	33	40	34	30	34	30	27	29	26	24
8	56	44	36	31	52	41	34	30	36	31	27	32	27	24	27	24	21
9	52	40	33	28	49	38	31	27	33	28	24	29	25	22	25	22	19
10	49	37	30	25	45	35	28	24	31	26	22	27	23	20	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3380	3380	3380
5°	3386	3327	3348
10°	3353	3262	3240
15°	3307	3155	3071
20°	3246	3006	2865
25°	3184	2840	2665
30°	3100	2670	2412
35°	3018	2486	2190
40°	2935	2296	1935
45°	2838	2086	1704
50°	2738	1873	1478
55°	2633	1646	1261
60°	2512	1408	1039
65°	2373	1166	935
70°	2204	941	846
75°	1993	830	770
80°	1686	697	669
85°	1179	467	504

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2838 cd/sqm

TEST NUMBER: P927466

CATALOG NUMBER: DFN2DIP-HX4F0-110D080US835-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	426.1	2.5
10°-20°	1169.7	6.8
20°-30°	1642.2	9.5
30°-40°	1790.1	10.4
40°-50°	1645.3	9.5
50°-60°	1292.1	7.5
60°-70°	841.1	4.9
70°-80°	432.9	2.5
80°-90°	115.3	0.7
90°-100°	89.0	0.5
100°-110°	331.9	1.9
110°-120°	880.2	5.1
120°-130°	1459.9	8.5
130°-140°	1550.7	9.0
140°-150°	1441.2	8.3
150°-160°	1158.7	6.7
160°-170°	746.6	4.3
170°-180°	257.0	1.5
0°-30°	3238.0	18.7
0°-40°	5028.1	29.1
0°-60°	7965.5	46.1
0°-90°	9354.7	54.2
90°-120°	1301.1	7.5
90°-150°	5752.9	33.3
90°-180°	7915.0	45.8
0°-180°	17270.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4546	4546	4546	4546	4546	
5°	4546	4526	4472	4509	4497	431
15°	4324	4279	4139	4061	4020	1218
25°	3925	3793	3522	3353	3291	1805
35°	3382	3172	2810	2551	2460	2117
45°	2765	2489	2057	1765	1666	2135
55°	2102	1781	1337	1090	1012	1879
65°	1420	1086	716	576	564	1407
75°	757	469	329	300	296	801
85°	177	90	78	78	78	203
90°	2	23	39	49	53	16
95°	127	62	76	86	84	150
105°	594	653	119	141	148	635
115°	1123	1156	1205	301	160	1106
125°	1588	1614	1651	1664	1670	1416
135°	1965	1997	2014	2034	2030	1518
145°	2280	2278	2311	2325	2315	1426
155°	2510	2493	2516	2528	2512	1157
165°	2645	2634	2639	2653	2639	747
175°	2706	2692	2696	2710	2690	258
180°	2700	2700	2700	2700	2700	

TEST NUMBER: P927466

CATALOG NUMBER: DFN2DIP-HX4F0-110D080US835-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4546.3	4546.3	4546.3	4546.3	4546.3
2.5°	4566.8	4546.3	4500.9	4542.4	4534.1
5°	4546.3	4525.8	4472.1	4509.2	4497.0
7.5°	4509.2	4484.7	4427.1	4443.3	4422.7
10°	4459.9	4431.0	4349.0	4336.3	4311.9
12.5°	4398.3	4361.2	4249.9	4225.4	4180.0
15°	4324.1	4278.7	4139.0	4060.9	4019.8
17.5°	4237.7	4171.8	3998.9	3908.5	3842.6
20°	4139.0	4056.5	3850.9	3748.3	3657.5
22.5°	4032.1	3937.3	3698.6	3558.9	3497.3
25°	3925.1	3793.3	3521.8	3353.3	3291.3
27.5°	3797.7	3657.5	3357.2	3163.8	3069.1
30°	3661.9	3505.2	3176.1	2966.5	2855.2
32.5°	3530.1	3340.6	3003.6	2756.6	2653.6
35°	3382.1	3172.1	2810.3	2551.0	2460.2
37.5°	3238.1	3011.5	2629.1	2344.9	2242.4
40°	3085.7	2839.1	2439.7	2147.6	2040.7
42.5°	2929.4	2666.2	2250.7	1946.0	1843.4
45°	2764.9	2489.0	2057.3	1764.8	1666.2
47.5°	2608.6	2316.6	1872.2	1579.7	1489.4
50°	2435.7	2143.7	1691.1	1406.9	1320.9
52.5°	2266.8	1958.2	1518.2	1246.7	1168.5
55°	2102.2	1781.4	1337.0	1090.4	1012.3
57.5°	1933.8	1604.6	1176.8	946.4	880.4
60°	1760.9	1431.8	1007.9	798.4	732.5
62.5°	1592.4	1263.3	863.9	666.6	633.8
65°	1419.5	1086.0	715.9	576.2	563.5
67.5°	1255.0	921.5	576.2	505.9	493.7
70°	1082.1	761.3	477.1	436.1	419.5
72.5°	917.5	612.9	399.0	366.2	357.9
75°	756.9	468.8	329.1	300.3	296.4
77.5°	596.7	333.1	259.3	242.7	234.4
80°	448.3	238.8	197.3	181.2	181.2
82.5°	312.5	160.6	135.8	127.5	127.5
85°	176.8	90.4	78.1	78.1	78.1
87.5°	65.9	32.7	32.7	28.8	28.8
90°	1.9	23.4	39.0	48.9	52.7
92.5°	48.9	41.1	46.9	50.8	52.7
95°	126.9	62.4	76.1	86.1	84.0
97.5°	228.5	68.4	99.5	105.6	107.4
100°	345.9	78.2	111.4	126.9	130.8
102.5°	474.7	470.9	115.3	136.6	142.7
105°	593.9	652.6	119.2	140.6	148.5
107.5°	732.6	781.3	123.2	144.5	152.4
110°	865.6	906.4	342.0	146.6	154.3

TEST NUMBER: P927466

CATALOG NUMBER: DFN2DIP-HX4F0-110D080US835-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	990.6	1025.6	992.5	150.3	156.4
115°	1123.3	1156.5	1205.4	300.9	160.3
117.5°	1238.6	1277.6	1311.0	1031.4	519.7
120°	1367.6	1396.8	1432.1	1455.5	1191.7
122.5°	1476.8	1508.2	1547.4	1559.0	1561.1
125°	1588.2	1613.7	1650.8	1664.5	1670.3
127.5°	1689.8	1717.2	1746.7	1766.1	1768.0
130°	1785.6	1816.9	1838.3	1859.9	1858.0
132.5°	1883.3	1908.8	1930.2	1947.8	1945.9
135°	1965.4	1996.7	2014.1	2033.9	2029.9
137.5°	2051.3	2074.7	2094.4	2113.9	2108.1
140°	2135.2	2151.0	2172.4	2190.0	2180.2
142.5°	2205.8	2219.4	2244.7	2260.3	2250.5
145°	2280.0	2277.9	2311.1	2324.8	2315.0
147.5°	2344.3	2338.5	2371.6	2381.4	2373.7
150°	2406.9	2393.2	2424.5	2436.1	2426.4
152.5°	2459.6	2444.0	2473.2	2485.1	2471.4
155°	2510.4	2493.0	2516.4	2528.0	2512.5
157.5°	2551.4	2535.9	2553.5	2567.2	2551.4
160°	2586.7	2574.9	2586.7	2598.3	2584.6
162.5°	2617.8	2606.2	2615.9	2629.6	2612.0
165°	2645.2	2633.6	2639.4	2653.0	2639.4
167.5°	2666.7	2654.9	2660.9	2674.6	2657.0
170°	2684.4	2672.5	2676.5	2690.2	2672.5
172.5°	2696.0	2684.4	2688.3	2702.0	2684.4
175°	2705.7	2692.0	2696.0	2709.6	2690.2
177.5°	2709.6	2696.0	2698.0	2711.7	2694.1
180°	2699.9	2699.9	2699.9	2699.9	2699.9

TEST NUMBER: P927466

CATALOG NUMBER: DFN2DIP-HX4F0-110D080US835-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.76	12.63	12.69	13.57	14.78	7.73	8.60	8.66	9.54	10.75
	3H	13.44	14.22	14.38	15.17	16.40	8.93	9.70	9.87	10.65	11.89
	4H	14.05	14.78	15.01	15.74	16.98	9.38	10.11	10.33	11.07	12.31
	6H	14.48	15.15	15.44	16.11	17.37	9.71	10.38	10.67	11.34	12.60
	8H	14.60	15.24	15.58	16.22	17.48	9.80	10.44	10.77	11.41	12.67
	12H	14.67	15.28	15.64	16.25	17.53	9.84	10.45	10.82	11.42	12.70
4H	2H	11.78	12.51	12.74	13.47	14.72	8.33	9.07	9.29	10.02	11.27
	3H	13.62	14.22	14.59	15.21	16.47	9.69	10.30	10.66	11.28	12.54
	4H	14.31	14.87	15.29	15.84	17.13	10.24	10.79	11.22	11.77	13.06
	6H	14.83	15.31	15.82	16.31	17.59	10.66	11.14	11.65	12.14	13.43
	8H	15.01	15.45	16.00	16.45	17.74	10.79	11.24	11.79	12.23	13.53
	12H	15.10	15.50	16.11	16.52	17.82	10.86	11.26	11.87	12.27	13.58
8H	4H	14.28	14.73	15.27	15.72	17.02	10.52	10.97	11.52	11.96	13.26
	6H	14.85	15.22	15.87	16.26	17.55	11.05	11.41	12.06	12.45	13.75
	8H	15.07	15.39	16.09	16.42	17.73	11.24	11.56	12.26	12.59	13.90
	12H	15.21	15.49	16.24	16.51	17.87	11.36	11.65	12.39	12.66	14.02
12H	4H	14.24	14.64	15.25	15.65	16.95	10.53	10.93	11.54	11.94	13.25
	6H	14.83	15.15	15.85	16.18	17.49	11.10	11.42	12.12	12.44	13.76
	8H	15.05	15.33	16.08	16.35	17.71	11.31	11.59	12.34	12.61	13.97