

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P928720

Luminaire Tested: DFN2DIP-HX4F0-100D070US930-FLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P928720
REPORT IS A COMBINATION OF REPORTS P900885 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-100D070US930-FLLONL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 13716.5 lumens
Efficiency: N/A
Efficacy: 90.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 151.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.946
Total Harmonic Distortion (THDi): 0.132
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P928720

CATALOG NUMBER: DFN2DIP-HX4F0-100D070US930-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P928720

CATALOG NUMBER: DFN2DIP-HX4F0-100D070US930-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64
1	100	95	91	88	93	89	86	83	77	75	73	67	65	63	57	56	54
2	91	83	77	72	85	78	72	68	68	64	60	59	55	53	50	48	46
3	83	73	66	60	77	69	62	57	60	55	51	52	48	45	44	41	39
4	76	65	57	51	71	61	54	48	53	48	43	46	42	38	40	36	34
5	70	58	50	44	65	54	47	41	48	42	37	42	37	33	36	32	29
6	64	52	44	38	60	49	41	36	43	37	33	38	33	29	32	29	26
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	30	26	23
8	55	43	35	29	51	40	33	28	36	30	26	31	27	23	27	23	21
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	19
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	23	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2358	2358	2358
5°	2362	2325	2341
10°	2343	2294	2309
15°	2309	2257	2260
20°	2262	2204	2209
25°	2216	2142	2151
30°	2158	2084	2076
35°	2104	2015	1998
40°	2036	1946	1923
45°	1969	1876	1846
50°	1895	1803	1757
55°	1818	1719	1676
60°	1731	1619	1582
65°	1637	1516	1472
70°	1516	1389	1354
75°	1348	1238	1244
80°	1147	1045	1035
85°	833	713	689

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1969 cd/sqm

TEST NUMBER: P928720

CATALOG NUMBER: DFN2DIP-HX4F0-100D070US930-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	298.5	2.2
10°-20°	839.8	6.1
20°-30°	1234.2	9.0
30°-40°	1433.4	10.5
40°-50°	1431.6	10.4
50°-60°	1248.3	9.1
60°-70°	922.8	6.7
70°-80°	522.1	3.8
80°-90°	141.2	1.0
90°-100°	63.5	0.5
100°-110°	236.7	1.7
110°-120°	627.7	4.6
120°-130°	1041.1	7.6
130°-140°	1105.9	8.1
140°-150°	1027.8	7.5
150°-160°	826.3	6.0
160°-170°	532.4	3.9
170°-180°	183.3	1.3
0°-30°	2372.4	17.3
0°-40°	3805.8	27.7
0°-60°	6485.8	47.3
0°-90°	8071.9	58.8
90°-120°	927.9	6.8
90°-150°	4102.6	29.9
90°-180°	5645.0	41.2
0°-180°	13716.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3171	3171	3171	3171	3171	
5°	3171	3159	3126	3150	3144	301
15°	3019	3001	2961	2973	2958	850
25°	2732	2708	2656	2662	2656	1257
35°	2357	2327	2278	2260	2244	1472
45°	1918	1897	1851	1818	1805	1480
55°	1452	1433	1397	1360	1345	1298
65°	979	961	930	903	888	968
75°	512	506	491	473	479	547
85°	125	122	119	110	107	139
90°	1	17	28	35	38	13
95°	90	44	54	61	60	107
105°	424	465	85	100	106	453
115°	801	825	860	215	114	789
125°	1133	1151	1177	1187	1191	1010
135°	1402	1424	1436	1450	1448	1083
145°	1626	1624	1648	1658	1651	1017
155°	1790	1778	1794	1803	1792	825
165°	1886	1878	1882	1892	1882	533
175°	1930	1920	1923	1932	1918	184
180°	1925	1925	1925	1925	1925	

TEST NUMBER: P928720

CATALOG NUMBER: DFN2DIP-HX4F0-100D070US930-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3171.2	3171.2	3171.2	3171.2	3171.2
2.5°	3189.7	3174.4	3140.8	3171.2	3165.4
5°	3171.2	3159.3	3125.6	3149.9	3144.0
7.5°	3149.9	3131.7	3098.1	3122.7	3116.6
10°	3116.6	3095.2	3058.6	3082.9	3073.9
12.5°	3070.6	3052.5	3015.9	3031.1	3025.0
15°	3018.8	3000.7	2960.9	2973.2	2958.0
17.5°	2954.8	2936.7	2896.8	2912.1	2896.8
20°	2884.5	2866.4	2823.7	2832.8	2820.8
22.5°	2814.7	2787.2	2747.4	2747.4	2741.3
25°	2732.2	2707.9	2656.2	2662.0	2656.2
27.5°	2640.6	2619.2	2579.8	2570.8	2555.5
30°	2549.4	2524.8	2479.1	2470.1	2457.8
32.5°	2451.7	2433.6	2384.7	2366.3	2354.0
35°	2357.2	2326.8	2277.9	2259.5	2244.3
37.5°	2250.5	2222.9	2174.1	2152.7	2137.5
40°	2140.8	2116.1	2067.3	2040.2	2027.9
42.5°	2034.0	2009.4	1960.9	1930.2	1912.1
45°	1918.2	1896.8	1850.9	1817.5	1805.3
47.5°	1805.3	1784.0	1735.1	1701.4	1683.3
50°	1686.2	1671.0	1628.3	1585.6	1570.4
52.5°	1570.4	1549.1	1509.5	1476.0	1454.6
55°	1451.7	1433.3	1396.7	1360.1	1344.9
57.5°	1332.6	1317.4	1277.6	1241.1	1228.8
60°	1213.5	1201.6	1158.8	1125.2	1116.1
62.5°	1097.7	1076.4	1046.0	1015.6	1003.3
65°	979.0	960.6	930.2	902.6	887.5
67.5°	857.1	841.5	814.3	793.0	780.7
70°	744.1	731.8	704.3	683.0	671.0
72.5°	628.3	616.0	600.8	579.5	570.3
75°	512.1	506.4	490.8	472.7	478.8
77.5°	408.6	396.3	390.1	381.1	372.0
80°	305.1	301.9	295.7	286.6	280.5
82.5°	207.4	207.4	204.5	192.2	192.2
85°	124.9	122.0	119.1	109.7	106.8
87.5°	55.0	48.8	42.7	33.7	30.4
90°	1.3	16.7	27.8	34.9	37.6
92.5°	34.9	29.3	33.4	36.3	37.6
95°	90.5	44.5	54.3	61.4	59.9
97.5°	162.9	48.8	71.0	75.3	76.6
100°	246.7	55.7	79.4	90.5	93.3
102.5°	338.5	335.9	82.2	97.5	101.7
105°	423.6	465.4	85.0	100.2	105.9
107.5°	522.4	557.2	87.9	103.1	108.7
110°	617.3	646.4	243.8	104.6	110.0

TEST NUMBER: P928720

CATALOG NUMBER: DFN2DIP-HX4F0-100D070US930-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	706.4	731.4	707.7	107.2	111.5
115°	801.1	824.7	859.6	214.6	114.3
117.5°	883.3	911.1	934.9	735.5	370.6
120°	975.2	996.1	1021.3	1038.0	849.9
122.5°	1053.1	1075.5	1103.5	1111.7	1113.2
125°	1132.6	1150.8	1177.3	1187.0	1191.1
127.5°	1205.1	1224.5	1245.6	1259.5	1260.8
130°	1273.4	1295.7	1310.9	1326.3	1325.0
132.5°	1343.0	1361.2	1376.5	1389.0	1387.7
135°	1401.6	1423.9	1436.4	1450.4	1447.6
137.5°	1462.8	1479.6	1493.6	1507.5	1503.3
140°	1522.7	1533.9	1549.2	1561.7	1554.8
142.5°	1572.9	1582.7	1600.7	1611.8	1604.9
145°	1625.9	1624.5	1648.1	1657.9	1650.9
147.5°	1671.7	1667.7	1691.3	1698.2	1692.8
150°	1716.4	1706.7	1729.0	1737.3	1730.3
152.5°	1754.0	1742.9	1763.7	1772.1	1762.4
155°	1790.2	1777.8	1794.5	1802.8	1791.7
157.5°	1819.5	1808.4	1821.0	1830.7	1819.5
160°	1844.7	1836.2	1844.7	1852.9	1843.1
162.5°	1866.8	1858.5	1865.5	1875.2	1862.7
165°	1886.3	1878.1	1882.2	1891.9	1882.2
167.5°	1901.7	1893.2	1897.6	1907.3	1894.8
170°	1914.3	1905.9	1908.6	1918.4	1905.9
172.5°	1922.6	1914.3	1917.1	1926.8	1914.3
175°	1929.5	1919.7	1922.6	1932.3	1918.4
177.5°	1932.3	1922.6	1924.1	1933.8	1921.2
180°	1925.4	1925.4	1925.4	1925.4	1925.4

TEST NUMBER: P928720

CATALOG NUMBER: DFN2DIP-HX4F0-100D070US930-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.03	11.98	11.91	12.88	14.02	10.60	11.55	11.48	12.45	13.58
	3H	12.70	13.55	13.59	14.46	15.62	12.23	13.08	13.12	13.98	15.15
	4H	13.29	14.10	14.20	15.01	16.18	12.82	13.62	13.72	14.54	15.71
	6H	13.70	14.44	14.61	15.36	16.54	13.22	13.96	14.14	14.88	16.07
	8H	13.80	14.51	14.73	15.45	16.63	13.33	14.03	14.25	14.97	16.16
	12H	13.86	14.53	14.79	15.46	16.67	13.37	14.05	14.30	14.98	16.19
4H	2H	11.50	12.31	12.41	13.22	14.40	11.16	11.96	12.07	12.88	14.05
	3H	13.38	14.05	14.30	14.99	16.18	12.99	13.66	13.91	14.60	15.79
	4H	14.10	14.71	15.03	15.65	16.86	13.69	14.30	14.62	15.24	16.46
	6H	14.62	15.15	15.56	16.11	17.33	14.21	14.74	15.15	15.70	16.92
	8H	14.77	15.27	15.72	16.22	17.45	14.36	14.85	15.31	15.81	17.04
	12H	14.85	15.29	15.82	16.27	17.50	14.43	14.87	15.39	15.85	17.08
8H	4H	14.30	14.80	15.25	15.75	16.98	13.94	14.44	14.89	15.39	16.62
	6H	14.94	15.35	15.91	16.35	17.57	14.58	14.98	15.55	15.98	17.21
	8H	15.16	15.52	16.14	16.51	17.76	14.79	15.15	15.77	16.14	17.39
	12H	15.30	15.62	16.28	16.60	17.89	14.91	15.23	15.90	16.21	17.50
12H	4H	14.29	14.74	15.26	15.71	16.95	13.94	14.39	14.91	15.36	16.59
	6H	14.97	15.33	15.95	16.32	17.56	14.62	14.98	15.60	15.97	17.21
	8H	15.22	15.53	16.20	16.52	17.81	14.86	15.18	15.85	16.16	17.45

END OF REPORT