

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P927476

Luminaire Tested: DFN2DIP-HX4F0-110D110US835-FLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P927476
REPORT IS A COMBINATION OF REPORTS P900959 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-110D110US835-FLLONL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 21780.0 lumens
Efficiency: N/A
Efficacy: 109.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 199.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9967
Total Harmonic Distortion (THDi): 0.063
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P927476
CATALOG NUMBER: DFN2DIP-HX4F0-110D110US835-FLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P927476

CATALOG NUMBER: DFN2DIP-HX4F0-110D110US835-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	56	56	56	50
1	98	93	90	86	90	86	83	80	73	71	68	61	59	58	50	48	47	50	48	47	42
2	89	82	75	70	82	76	70	66	64	60	57	53	51	48	44	42	40	44	42	40	35
3	81	72	64	59	75	66	60	55	56	52	48	47	44	41	39	36	34	39	36	34	30
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	35	32	29	35	32	29	26
5	68	57	48	42	63	53	45	40	45	39	35	38	34	30	31	28	26	31	28	26	22
6	63	51	43	37	58	47	40	35	40	35	31	34	30	27	28	25	23	28	25	23	20
7	58	46	38	32	53	43	36	30	37	31	27	31	27	23	26	23	20	26	23	20	17
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	24	20	18	24	20	18	16
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	19	16	22	19	16	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3183	3183	3183
5°	3188	3139	3160
10°	3162	3097	3117
15°	3116	3046	3050
20°	3054	2975	2982
25°	2991	2891	2903
30°	2913	2812	2803
35°	2839	2720	2696
40°	2748	2626	2595
45°	2657	2533	2492
50°	2558	2434	2372
55°	2454	2320	2262
60°	2337	2185	2136
65°	2209	2045	1987
70°	2046	1875	1827
75°	1820	1671	1680
80°	1549	1411	1397
85°	1124	961	929

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2657 cd/sqm



TEST NUMBER: P927476

CATALOG NUMBER: DFN2DIP-HX4F0-110D110US835-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	402.8	1.8
10°-20°	1133.5	5.2
20°-30°	1665.7	7.6
30°-40°	1934.7	8.9
40°-50°	1932.3	8.9
50°-60°	1684.9	7.7
60°-70°	1245.5	5.7
70°-80°	704.7	3.2
80°-90°	192.5	0.9
90°-100°	122.4	0.6
100°-110°	456.3	2.1
110°-120°	1210.3	5.6
120°-130°	2007.3	9.2
130°-140°	2132.2	9.8
140°-150°	1981.7	9.1
150°-160°	1593.2	7.3
160°-170°	1026.6	4.7
170°-180°	353.3	1.6
0°-30°	3202.1	14.7
0°-40°	5136.7	23.6
0°-60°	8753.8	40.2
0°-90°	10896.5	50.0
90°-120°	1789.0	8.2
90°-150°	7910.3	36.3
90°-180°	10883.0	50.0
0°-180°	21780.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4280	4280	4280	4280	4280	
5°	4280	4264	4219	4251	4244	406
15°	4074	4050	3996	4013	3992	1148
25°	3688	3655	3585	3593	3585	1697
35°	3182	3140	3074	3050	3029	1987
45°	2589	2560	2498	2453	2437	1998
55°	1959	1934	1885	1836	1815	1752
65°	1321	1296	1255	1218	1198	1306
75°	691	683	662	638	646	738
85°	169	165	161	148	144	188
90°	3	32	54	67	72	20
95°	174	86	105	118	116	207
105°	817	897	164	193	204	873
115°	1544	1590	1658	414	220	1521
125°	2184	2219	2270	2289	2297	1948
135°	2702	2746	2769	2797	2791	2088
145°	3135	3132	3178	3197	3183	1961
155°	3452	3428	3460	3476	3455	1591
165°	3637	3621	3629	3648	3629	1028
175°	3720	3702	3707	3726	3699	354
180°	3712	3712	3712	3712	3712	



TEST NUMBER: P927476

CATALOG NUMBER: DFN2DIP-HX4F0-110D110US835-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4280.2	4280.2	4280.2	4280.2	4280.2
2.5°	4305.0	4284.5	4239.1	4280.2	4272.3
5°	4280.2	4264.0	4218.6	4251.3	4243.5
7.5°	4251.3	4226.9	4181.5	4214.7	4206.4
10°	4206.4	4177.5	4128.2	4160.9	4148.7
12.5°	4144.4	4119.9	4070.6	4091.1	4082.8
15°	4074.5	4050.0	3996.3	4012.9	3992.4
17.5°	3988.0	3963.6	3909.9	3930.4	3909.9
20°	3893.3	3868.8	3811.2	3823.4	3807.3
22.5°	3799.0	3761.8	3708.1	3708.1	3699.8
25°	3687.6	3654.9	3585.0	3592.9	3585.0
27.5°	3564.0	3535.2	3481.9	3469.7	3449.2
30°	3440.9	3407.7	3346.1	3333.9	3317.3
32.5°	3309.0	3284.6	3218.6	3193.7	3177.1
35°	3181.5	3140.5	3074.5	3049.6	3029.1
37.5°	3037.4	3000.3	2934.4	2905.5	2885.0
40°	2889.4	2856.2	2790.3	2753.6	2737.0
42.5°	2745.3	2712.1	2646.6	2605.1	2580.7
45°	2589.0	2560.1	2498.1	2453.2	2436.6
47.5°	2436.6	2407.8	2341.8	2296.4	2271.9
50°	2275.9	2255.4	2197.7	2140.1	2119.6
52.5°	2119.6	2090.7	2037.5	1992.0	1963.2
55°	1959.3	1934.4	1885.1	1835.7	1815.2
57.5°	1798.6	1778.1	1724.4	1675.0	1658.4
60°	1637.9	1621.8	1564.1	1518.7	1506.5
62.5°	1481.6	1452.8	1411.7	1370.7	1354.1
65°	1321.3	1296.4	1255.4	1218.3	1197.8
67.5°	1156.7	1135.8	1099.1	1070.3	1053.7
70°	1004.3	987.7	950.6	921.8	905.6
72.5°	848.0	831.4	810.9	782.1	769.8
75°	691.2	683.4	662.4	638.0	646.3
77.5°	551.5	534.9	526.6	514.4	502.2
80°	411.8	407.4	399.1	386.9	378.6
82.5°	279.9	279.9	276.0	259.4	259.4
85°	168.6	164.6	160.7	148.0	144.1
87.5°	74.2	65.9	57.6	45.4	41.0
90°	2.6	32.2	53.6	67.3	72.4
92.5°	67.3	56.5	64.4	69.9	72.4
95°	174.5	85.8	104.6	118.3	115.5
97.5°	314.2	94.1	136.8	145.1	147.7
100°	475.6	107.5	153.1	174.5	179.9
102.5°	652.6	647.5	158.5	187.9	196.2
105°	816.6	897.3	164.0	193.3	204.2
107.5°	1007.4	1074.3	169.4	198.7	209.6
110°	1190.1	1246.3	470.2	201.6	212.1



TEST NUMBER: P927476

CATALOG NUMBER: DFN2DIP-HX4F0-110D110US835-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1362.1	1410.2	1364.6	206.7	215.0
115°	1544.5	1590.1	1657.5	413.7	220.4
117.5°	1703.1	1756.7	1802.6	1418.2	714.5
120°	1880.4	1920.6	1969.1	2001.3	1638.6
122.5°	2030.7	2073.7	2127.6	2143.6	2146.5
125°	2183.8	2218.9	2269.9	2288.7	2296.7
127.5°	2323.5	2361.1	2401.6	2428.4	2431.0
130°	2455.2	2498.3	2527.6	2557.3	2554.8
132.5°	2589.5	2624.6	2654.0	2678.2	2675.7
135°	2702.5	2745.5	2769.4	2796.6	2791.1
137.5°	2820.5	2852.7	2879.8	2906.6	2898.6
140°	2936.0	2957.6	2987.0	3011.2	2997.8
142.5°	3032.9	3051.7	3086.5	3107.9	3094.5
145°	3135.0	3132.1	3177.7	3196.6	3183.2
147.5°	3223.4	3215.4	3261.0	3274.4	3263.9
150°	3309.5	3290.7	3333.7	3349.7	3336.3
152.5°	3381.9	3360.5	3400.7	3417.0	3398.2
155°	3451.8	3427.8	3460.0	3476.0	3454.6
157.5°	3508.2	3486.8	3511.1	3529.9	3508.2
160°	3556.7	3540.4	3556.7	3572.6	3553.8
162.5°	3599.4	3583.5	3596.9	3615.7	3591.5
165°	3637.1	3621.1	3629.1	3647.9	3629.1
167.5°	3666.7	3650.5	3658.8	3677.6	3653.4
170°	3691.0	3674.7	3680.1	3699.0	3674.7
172.5°	3706.9	3691.0	3696.4	3715.2	3691.0
175°	3720.3	3701.5	3706.9	3725.8	3699.0
177.5°	3725.8	3706.9	3709.8	3728.6	3704.4
180°	3712.4	3712.4	3712.4	3712.4	3712.4



TEST NUMBER: P927476
 CATALOG NUMBER: DFN2DIP-HX4F0-110D110US835-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.30	12.16	12.25	13.13	14.40	10.87	11.73	11.82	12.70	13.97
	3H	12.96	13.73	13.93	14.71	16.01	12.49	13.26	13.45	14.24	15.53
	4H	13.55	14.28	14.53	15.26	16.57	13.07	13.81	14.06	14.79	16.09
	6H	13.95	14.62	14.94	15.61	16.93	13.47	14.15	14.46	15.14	16.45
	8H	14.05	14.69	15.05	15.70	17.01	13.58	14.22	14.58	15.23	16.54
	12H	14.10	14.71	15.11	15.71	17.05	13.62	14.23	14.62	15.23	16.57
4H	2H	11.76	12.49	12.75	13.48	14.78	11.42	12.15	12.40	13.13	14.43
	3H	13.63	14.24	14.62	15.25	16.57	13.23	13.84	14.23	14.86	16.17
	4H	14.34	14.90	15.35	15.91	17.25	13.94	14.50	14.94	15.50	16.84
	6H	14.86	15.34	15.88	16.37	17.71	14.45	14.93	15.47	15.96	17.30
	8H	15.01	15.46	16.03	16.48	17.83	14.60	15.05	15.61	16.07	17.42
	12H	15.08	15.49	16.12	16.53	17.88	14.66	15.07	15.70	16.11	17.46
8H	4H	14.54	14.99	15.56	16.01	17.36	14.18	14.63	15.20	15.65	17.00
	6H	15.17	15.54	16.21	16.61	17.96	14.81	15.18	15.85	16.25	17.60
	8H	15.39	15.72	16.44	16.77	18.14	15.02	15.35	16.08	16.40	17.77
	12H	15.53	15.81	16.58	16.86	18.27	15.14	15.43	16.20	16.48	17.89
12H	4H	14.53	14.93	15.56	15.97	17.33	14.17	14.58	15.21	15.62	16.97
	6H	15.20	15.53	16.25	16.58	17.95	14.85	15.18	15.90	16.23	17.60
	8H	15.45	15.73	16.50	16.78	18.19	15.09	15.38	16.14	16.42	17.83