

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P905558

Luminaire Tested: DFN2DIP-HX4F0-120D040US835-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P905558
REPORT IS A COMBINATION OF REPORTS P899315 AND P896188
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-120D040US835-FLLFLL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15420.0 lumens
Efficiency: N/A
Efficacy: 102.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 149.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9954
Total Harmonic Distortion (THDi): 0.076
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P905558

CATALOG NUMBER: DFN2DIP-HX4F0-120D040US835-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P905558

CATALOG NUMBER: DFN2DIP-HX4F0-120D040US835-FLLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	114	114	114	114	108	108	108	108	98	98	98	89	89	89	81	81	81
1	104	99	95	92	99	95	91	88	86	84	81	79	77	75	72	70	68
2	95	87	80	75	90	83	77	72	76	71	67	69	66	62	63	60	58
3	86	76	69	63	82	73	66	61	67	61	57	61	57	53	56	52	49
4	79	68	59	53	75	65	57	52	60	53	48	55	50	45	50	46	42
5	73	61	52	46	69	58	50	44	53	47	42	49	44	39	45	41	37
6	67	55	46	40	64	52	45	39	48	42	37	45	39	35	41	36	33
7	62	49	41	35	59	48	40	34	44	37	33	41	35	31	37	33	29
8	58	45	37	31	55	43	36	31	40	34	29	37	32	28	34	30	26
9	54	41	33	28	52	40	32	27	37	31	26	34	29	25	32	27	24
10	51	38	30	25	48	37	30	25	34	28	24	32	26	23	30	25	22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3472	3472	3472
5°	3478	3424	3447
10°	3450	3378	3400
15°	3399	3323	3328
20°	3331	3246	3253
25°	3263	3154	3167
30°	3178	3068	3057
35°	3097	2967	2941
40°	2998	2865	2831
45°	2899	2763	2718
50°	2791	2655	2588
55°	2677	2531	2468
60°	2549	2384	2330
65°	2410	2231	2168
70°	2232	2045	1993
75°	1985	1822	1832
80°	1689	1539	1524
85°	1226	1049	1014

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2899 cd/sqm

TEST NUMBER: P905558

CATALOG NUMBER: DFN2DIP-HX4F0-120D040US835-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	439.5	2.9
10°-20°	1236.5	8.0
20°-30°	1817.2	11.8
30°-40°	2110.5	13.7
40°-50°	2107.9	13.7
50°-60°	1838.0	11.9
60°-70°	1358.7	8.8
70°-80°	768.7	5.0
80°-90°	206.5	1.3
90°-100°	78.3	0.5
100°-110°	248.7	1.6
110°-120°	425.6	2.8
120°-130°	559.8	3.6
130°-140°	628.3	4.1
140°-150°	616.2	4.0
150°-160°	516.9	3.4
160°-170°	342.8	2.2
170°-180°	119.8	0.8
0°-30°	3493.1	22.7
0°-40°	5603.7	36.3
0°-60°	9549.6	61.9
0°-90°	11883.6	77.1
90°-120°	752.7	4.9
90°-150°	2556.9	16.6
90°-180°	3536.0	22.9
0°-180°	15420.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4669	4669	4669	4669	4669	
5°	4669	4652	4602	4638	4629	443
15°	4445	4418	4360	4378	4355	1252
25°	4023	3987	3911	3920	3911	1851
35°	3471	3426	3354	3327	3304	2167
45°	2824	2793	2725	2676	2658	2180
55°	2137	2110	2056	2003	1980	1911
65°	1442	1414	1370	1329	1307	1425
75°	754	746	723	696	705	805
85°	184	180	175	162	157	205
90°	1	14	37	35	36	15
95°	56	66	68	68	66	62
105°	230	233	235	237	237	242
115°	427	433	431	430	427	422
125°	621	631	628	624	623	555
135°	804	815	818	816	814	621
145°	976	983	989	990	986	610
155°	1116	1119	1122	1127	1124	513
165°	1214	1212	1212	1220	1215	342
175°	1263	1260	1257	1265	1259	120
180°	1265	1265	1265	1265	1265	

TEST NUMBER: P905558

CATALOG NUMBER: DFN2DIP-HX4F0-120D040US835-FLLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4669.3	4669.3	4669.3	4669.3	4669.3
2.5°	4696.4	4674.0	4624.5	4669.3	4660.7
5°	4669.3	4651.6	4602.1	4637.8	4629.2
7.5°	4637.8	4611.1	4561.6	4597.8	4588.8
10°	4588.8	4557.3	4503.5	4539.2	4525.9
12.5°	4521.1	4494.4	4440.6	4463.0	4453.9
15°	4444.9	4418.2	4359.6	4377.7	4355.3
17.5°	4350.6	4323.9	4265.3	4287.7	4265.3
20°	4247.2	4220.5	4157.7	4171.0	4153.4
22.5°	4144.3	4103.8	4045.2	4045.2	4036.2
25°	4022.8	3987.1	3910.9	3919.5	3910.9
27.5°	3888.0	3856.6	3798.5	3785.1	3762.8
30°	3753.7	3717.5	3650.3	3637.0	3618.9
32.5°	3609.8	3583.2	3511.2	3484.1	3466.0
35°	3470.7	3426.0	3354.0	3326.9	3304.5
37.5°	3313.5	3273.1	3201.1	3169.7	3147.3
40°	3152.1	3115.9	3043.9	3003.9	2985.8
42.5°	2994.9	2958.7	2887.2	2842.0	2815.3
45°	2824.3	2792.9	2725.2	2676.2	2658.1
47.5°	2658.1	2626.6	2554.7	2505.2	2478.5
50°	2482.8	2460.4	2397.5	2334.6	2312.2
52.5°	2312.2	2280.8	2222.7	2173.1	2141.7
55°	2137.4	2110.3	2056.4	2002.6	1980.2
57.5°	1962.1	1939.7	1881.1	1827.3	1809.2
60°	1786.8	1769.2	1706.3	1656.8	1643.4
62.5°	1616.3	1584.8	1540.1	1495.3	1477.2
65°	1441.5	1414.3	1369.5	1329.0	1306.7
67.5°	1261.9	1239.0	1199.0	1167.6	1149.5
70°	1095.6	1077.5	1037.0	1005.6	988.0
72.5°	925.1	907.0	884.6	853.2	839.8
75°	754.1	745.5	722.6	696.0	705.0
77.5°	601.6	583.5	574.5	561.1	547.8
80°	449.2	444.4	435.4	422.1	413.0
82.5°	305.3	305.3	301.1	283.0	283.0
85°	183.9	179.6	175.3	161.5	157.2
87.5°	81.0	71.9	62.9	49.5	44.8
90°	1.1	13.7	37.4	35.1	36.2
92.5°	23.6	32.0	33.2	34.3	34.3
95°	55.7	66.4	68.3	68.3	66.4
97.5°	92.7	102.6	106.8	106.8	106.8
100°	135.4	144.2	147.2	147.2	146.1
102.5°	180.4	186.9	191.1	192.2	191.1
105°	229.6	232.6	234.9	236.8	236.8
107.5°	278.4	283.0	283.0	283.7	278.4
110°	325.7	331.8	331.8	331.8	328.8

TEST NUMBER: P905558

CATALOG NUMBER: DFN2DIP-HX4F0-120D040US835-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	376.8	383.3	382.1	379.1	376.8
115°	427.1	433.3	431.3	430.2	427.1
117.5°	477.1	485.5	480.2	477.1	474.1
120°	527.5	535.8	527.5	527.5	524.0
122.5°	573.2	583.9	578.6	575.5	573.2
125°	621.3	630.8	627.8	624.3	623.2
127.5°	668.2	680.0	675.8	671.2	668.2
130°	712.0	725.8	723.9	721.6	717.4
132.5°	761.2	771.9	772.7	767.3	764.3
135°	803.6	815.4	817.7	816.5	813.5
137.5°	850.9	860.4	862.3	861.5	857.0
140°	892.4	902.0	907.3	907.3	903.1
142.5°	935.2	944.7	947.7	948.9	944.7
145°	975.6	983.2	989.3	990.5	986.3
147.5°	1011.8	1021.3	1025.9	1027.8	1023.6
150°	1049.2	1055.7	1059.9	1063.3	1059.9
152.5°	1082.4	1088.8	1094.2	1098.4	1094.2
155°	1115.5	1118.6	1122.0	1127.4	1123.9
157.5°	1144.2	1146.4	1148.3	1156.0	1150.6
160°	1169.7	1172.0	1173.1	1179.6	1175.0
162.5°	1193.3	1193.3	1194.5	1201.7	1196.4
165°	1213.6	1212.4	1212.4	1220.0	1214.7
167.5°	1231.9	1228.4	1228.4	1236.1	1230.7
170°	1245.6	1242.5	1241.4	1249.0	1242.5
172.5°	1255.1	1252.1	1250.9	1258.6	1252.1
175°	1262.8	1259.7	1257.4	1265.0	1258.6
177.5°	1267.0	1263.9	1261.6	1268.1	1261.6
180°	1265.0	1265.0	1265.0	1265.0	1265.0

TEST NUMBER: P905558

CATALOG NUMBER: DFN2DIP-HX4F0-120D040US835-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.80	14.97	14.48	15.67	16.49	13.36	14.53	14.05	15.24	16.06
	3H	15.48	16.53	16.18	17.24	18.10	15.01	16.06	15.70	16.77	17.63
	4H	16.08	17.07	16.80	17.80	18.67	15.61	16.60	16.32	17.32	18.19
	6H	16.50	17.42	17.23	18.15	19.03	16.02	16.94	16.75	17.67	18.56
	8H	16.61	17.49	17.35	18.24	19.13	16.14	17.01	16.88	17.76	18.65
	12H	16.67	17.51	17.42	18.25	19.17	16.19	17.02	16.94	17.77	18.68
4H	2H	14.29	15.29	15.01	16.01	16.88	13.95	14.94	14.67	15.67	16.54
	3H	16.19	17.02	16.92	17.78	18.67	15.80	16.63	16.53	17.39	18.27
	4H	16.92	17.67	17.66	18.43	19.35	16.51	17.26	17.26	18.03	18.94
	6H	17.45	18.10	18.22	18.89	19.81	17.04	17.69	17.81	18.48	19.40
	8H	17.61	18.22	18.38	19.00	19.94	17.19	17.81	17.97	18.59	19.53
	12H	17.70	18.25	18.49	19.05	19.99	17.27	17.82	18.06	18.63	19.57
8H	4H	17.14	17.75	17.91	18.53	19.47	16.78	17.39	17.55	18.17	19.11
	6H	17.78	18.29	18.58	19.12	20.05	17.42	17.93	18.22	18.75	19.69
	8H	18.01	18.46	18.82	19.28	20.24	17.64	18.09	18.45	18.91	19.87
	12H	18.15	18.55	18.97	19.37	20.38	17.77	18.17	18.58	18.98	19.99
12H	4H	17.14	17.69	17.93	18.49	19.44	16.79	17.34	17.58	18.14	19.08
	6H	17.82	18.27	18.63	19.09	20.05	17.46	17.92	18.28	18.74	19.69
	8H	18.07	18.47	18.89	19.29	20.30	17.72	18.11	18.53	18.93	19.94