

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P927488

Luminaire Tested: DFN2DIP-HX4F0-120D050US835-FLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P927488
REPORT IS A COMBINATION OF REPORTS P900853 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-120D050US835-FLLONL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 16830.0 lumens
Efficiency: N/A
Efficacy: 102.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 163.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9954
Total Harmonic Distortion (THDi): 0.076
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P927488

CATALOG NUMBER: DFN2DIP-HX4F0-120D050US835-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P927488

CATALOG NUMBER: DFN2DIP-HX4F0-120D050US835-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	106	106	106	106	95	95	95	84	84	84	75	75	75
1	102	98	94	90	97	93	89	86	83	81	78	74	72	71	66	65	63
2	93	86	79	74	88	81	76	71	73	69	65	65	62	59	58	56	53
3	85	75	68	62	80	72	65	59	64	59	54	58	54	50	52	48	46
4	78	67	59	52	73	64	56	50	57	51	47	52	47	43	46	42	39
5	72	60	51	45	68	57	49	43	51	45	40	46	41	37	42	38	34
6	66	54	45	39	62	51	43	38	46	40	35	42	37	33	38	34	30
7	61	49	40	35	58	46	39	33	42	36	31	38	33	29	35	30	27
8	57	44	36	31	54	42	35	30	39	32	28	35	30	26	32	27	24
9	53	40	33	28	50	39	32	27	35	29	25	32	27	23	29	25	22
10	50	37	30	25	47	36	29	24	33	27	23	30	25	21	27	23	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3472	3472	3472
5°	3478	3424	3447
10°	3450	3378	3400
15°	3399	3323	3328
20°	3331	3246	3253
25°	3263	3154	3167
30°	3178	3068	3057
35°	3097	2967	2941
40°	2998	2865	2831
45°	2899	2763	2718
50°	2791	2655	2588
55°	2677	2531	2468
60°	2549	2384	2330
65°	2410	2231	2168
70°	2232	2045	1993
75°	1985	1822	1832
80°	1689	1539	1524
85°	1226	1049	1014

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2899 cd/sqm

TEST NUMBER: P927488

CATALOG NUMBER: DFN2DIP-HX4F0-120D050US835-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	439.5	2.6
10°-20°	1236.5	7.3
20°-30°	1817.2	10.8
30°-40°	2110.5	12.5
40°-50°	2107.9	12.5
50°-60°	1838.0	10.9
60°-70°	1358.7	8.1
70°-80°	768.7	4.6
80°-90°	205.9	1.2
90°-100°	55.7	0.3
100°-110°	207.4	1.2
110°-120°	550.1	3.3
120°-130°	912.4	5.4
130°-140°	969.2	5.8
140°-150°	900.8	5.4
150°-160°	724.2	4.3
160°-170°	466.6	2.8
170°-180°	160.6	1.0
0°-30°	3493.1	20.8
0°-40°	5603.7	33.3
0°-60°	9549.6	56.7
0°-90°	11883.0	70.6
90°-120°	813.2	4.8
90°-150°	3595.6	21.4
90°-180°	4947.0	29.4
0°-180°	16830.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4669	4669	4669	4669	4669	
5°	4669	4652	4602	4638	4629	443
15°	4445	4418	4360	4378	4355	1252
25°	4023	3987	3911	3920	3911	1851
35°	3471	3426	3354	3327	3304	2167
45°	2824	2793	2725	2676	2658	2180
55°	2137	2110	2056	2003	1980	1911
65°	1442	1414	1370	1329	1307	1425
75°	754	746	723	696	705	805
85°	184	180	175	162	157	205
90°	1	15	24	31	33	16
95°	79	39	48	54	52	94
105°	371	408	74	88	93	397
115°	702	723	753	188	100	691
125°	993	1009	1032	1040	1044	885
135°	1228	1248	1259	1271	1269	949
145°	1425	1424	1444	1453	1447	891
155°	1569	1558	1573	1580	1570	723
165°	1653	1646	1650	1658	1650	467
175°	1691	1682	1685	1694	1681	161
180°	1687	1687	1687	1687	1687	

TEST NUMBER: P927488

CATALOG NUMBER: DFN2DIP-HX4F0-120D050US835-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4669.3	4669.3	4669.3	4669.3	4669.3
2.5°	4696.4	4674.0	4624.5	4669.3	4660.7
5°	4669.3	4651.6	4602.1	4637.8	4629.2
7.5°	4637.8	4611.1	4561.6	4597.8	4588.8
10°	4588.8	4557.3	4503.5	4539.2	4525.9
12.5°	4521.1	4494.4	4440.6	4463.0	4453.9
15°	4444.9	4418.2	4359.6	4377.7	4355.3
17.5°	4350.6	4323.9	4265.3	4287.7	4265.3
20°	4247.2	4220.5	4157.7	4171.0	4153.4
22.5°	4144.3	4103.8	4045.2	4045.2	4036.2
25°	4022.8	3987.1	3910.9	3919.5	3910.9
27.5°	3888.0	3856.6	3798.5	3785.1	3762.8
30°	3753.7	3717.5	3650.3	3637.0	3618.9
32.5°	3609.8	3583.2	3511.2	3484.1	3466.0
35°	3470.7	3426.0	3354.0	3326.9	3304.5
37.5°	3313.5	3273.1	3201.1	3169.7	3147.3
40°	3152.1	3115.9	3043.9	3003.9	2985.8
42.5°	2994.9	2958.7	2887.2	2842.0	2815.3
45°	2824.3	2792.9	2725.2	2676.2	2658.1
47.5°	2658.1	2626.6	2554.7	2505.2	2478.5
50°	2482.8	2460.4	2397.5	2334.6	2312.2
52.5°	2312.2	2280.8	2222.7	2173.1	2141.7
55°	2137.4	2110.3	2056.4	2002.6	1980.2
57.5°	1962.1	1939.7	1881.1	1827.3	1809.2
60°	1786.8	1769.2	1706.3	1656.8	1643.4
62.5°	1616.3	1584.8	1540.1	1495.3	1477.2
65°	1441.5	1414.3	1369.5	1329.0	1306.7
67.5°	1261.9	1239.0	1199.0	1167.6	1149.5
70°	1095.6	1077.5	1037.0	1005.6	988.0
72.5°	925.1	907.0	884.6	853.2	839.8
75°	754.1	745.5	722.6	696.0	705.0
77.5°	601.6	583.5	574.5	561.1	547.8
80°	449.2	444.4	435.4	422.1	413.0
82.5°	305.3	305.3	301.1	283.0	283.0
85°	183.9	179.6	175.3	161.5	157.2
87.5°	81.0	71.9	62.9	49.5	44.8
90°	1.2	14.6	24.4	30.6	32.9
92.5°	30.6	25.7	29.3	31.8	32.9
95°	79.3	39.0	47.6	53.8	52.5
97.5°	142.8	42.8	62.2	66.0	67.1
100°	216.2	48.9	69.6	79.3	81.8
102.5°	296.7	294.3	72.1	85.4	89.2
105°	371.2	407.9	74.5	87.9	92.8
107.5°	457.9	488.3	77.0	90.3	95.3
110°	541.0	566.5	213.7	91.6	96.4

TEST NUMBER: P927488

CATALOG NUMBER: DFN2DIP-HX4F0-120D050US835-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	619.1	641.0	620.3	94.0	97.7
115°	702.1	722.8	753.4	188.1	100.2
117.5°	774.1	798.5	819.4	644.6	324.8
120°	854.7	873.0	895.0	909.7	744.8
122.5°	923.0	942.6	967.1	974.4	975.7
125°	992.6	1008.6	1031.8	1040.3	1044.0
127.5°	1056.1	1073.2	1091.7	1103.8	1105.0
130°	1116.0	1135.6	1148.9	1162.4	1161.3
132.5°	1177.1	1193.0	1206.3	1217.4	1216.2
135°	1228.4	1248.0	1258.8	1271.2	1268.7
137.5°	1282.0	1296.7	1309.0	1321.2	1317.6
140°	1334.5	1344.4	1357.7	1368.7	1362.7
142.5°	1378.6	1387.2	1403.0	1412.7	1406.6
145°	1425.0	1423.7	1444.4	1453.0	1446.9
147.5°	1465.2	1461.5	1482.3	1488.4	1483.6
150°	1504.3	1495.8	1515.3	1522.6	1516.5
152.5°	1537.2	1527.5	1545.8	1553.2	1544.6
155°	1569.0	1558.1	1572.7	1580.0	1570.3
157.5°	1594.6	1584.9	1595.9	1604.5	1594.6
160°	1616.7	1609.3	1616.7	1623.9	1615.4
162.5°	1636.1	1628.9	1634.9	1643.5	1632.5
165°	1653.2	1646.0	1649.6	1658.1	1649.6
167.5°	1666.7	1659.3	1663.1	1671.6	1660.6
170°	1677.7	1670.3	1672.8	1681.3	1670.3
172.5°	1685.0	1677.7	1680.2	1688.7	1677.7
175°	1691.1	1682.5	1685.0	1693.5	1681.3
177.5°	1693.5	1685.0	1686.3	1694.8	1683.8
180°	1687.4	1687.4	1687.4	1687.4	1687.4

TEST NUMBER: P927488

CATALOG NUMBER: DFN2DIP-HX4F0-120D050US835-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.31	14.40	14.07	15.18	16.12	12.88	13.96	13.64	14.74	15.69
	3H	14.99	15.96	15.76	16.75	17.73	14.52	15.49	15.29	16.28	17.25
	4H	15.59	16.51	16.38	17.31	18.29	15.11	16.03	15.90	16.83	17.82
	6H	16.00	16.85	16.80	17.65	18.65	15.52	16.37	16.33	17.18	18.18
	8H	16.11	16.92	16.92	17.75	18.75	15.64	16.44	16.45	17.27	18.27
	12H	16.17	16.94	16.98	17.76	18.78	15.69	16.46	16.50	17.28	18.30
4H	2H	13.80	14.72	14.59	15.52	16.50	13.46	14.38	14.25	15.17	16.16
	3H	15.69	16.46	16.49	17.29	18.29	15.30	16.06	16.10	16.89	17.90
	4H	16.41	17.11	17.23	17.94	18.97	16.01	16.70	16.83	17.54	18.57
	6H	16.94	17.55	17.78	18.40	19.44	16.53	17.14	17.37	17.99	19.03
	8H	17.10	17.66	17.94	18.51	19.56	16.68	17.25	17.52	18.10	19.15
	12H	17.18	17.69	18.04	18.56	19.61	16.76	17.27	17.62	18.14	19.19
8H	4H	16.63	17.19	17.47	18.04	19.09	16.27	16.83	17.11	17.68	18.73
	6H	17.27	17.74	18.14	18.63	19.68	16.91	17.37	17.77	18.27	19.31
	8H	17.49	17.91	18.37	18.80	19.86	17.12	17.54	18.00	18.43	19.49
	12H	17.64	18.00	18.52	18.88	20.00	17.25	17.62	18.13	18.50	19.61
12H	4H	16.62	17.13	17.48	18.00	19.06	16.27	16.78	17.13	17.65	18.70
	6H	17.30	17.72	18.18	18.61	19.67	16.95	17.37	17.83	18.25	19.32
	8H	17.55	17.92	18.44	18.80	19.92	17.20	17.56	18.08	18.44	19.56

END OF REPORT