

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P928762

Luminaire Tested: DFN2DIP-HX4F0-110D080US930-RLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P928762
REPORT IS A COMBINATION OF REPORTS P900906 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-110D080US930-RLLONL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 14075.1 lumens
Efficiency: N/A
Efficacy: 82.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 170.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9967
Total Harmonic Distortion (THDi): 0.063
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P928762

CATALOG NUMBER: DFN2DIP-HX4F0-110D080US930-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P928762

CATALOG NUMBER: DFN2DIP-HX4F0-110D080US930-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60
1	99	95	91	88	92	88	85	82	76	74	71	64	63	61	54	53	52
2	91	84	78	73	84	78	73	68	67	63	60	57	54	52	48	46	44
3	83	74	67	61	77	69	63	58	60	55	51	51	48	45	43	40	38
4	76	66	58	52	71	62	55	49	53	48	44	46	42	39	39	36	33
5	70	59	51	45	65	55	48	43	48	43	38	41	37	34	35	32	30
6	65	53	45	40	60	50	43	38	44	38	34	38	33	30	32	29	26
7	60	48	40	35	56	45	38	33	40	34	30	34	30	27	29	26	24
8	56	44	36	31	52	41	34	30	36	31	27	32	27	24	27	24	21
9	52	40	33	28	49	38	31	27	33	28	24	29	25	22	25	22	19
10	49	37	30	25	45	35	28	24	31	26	22	27	23	20	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2755	2755	2755
5°	2760	2712	2729
10°	2733	2659	2640
15°	2695	2571	2503
20°	2646	2450	2335
25°	2595	2315	2172
30°	2527	2176	1966
35°	2460	2026	1785
40°	2392	1872	1577
45°	2313	1700	1389
50°	2231	1526	1205
55°	2146	1341	1028
60°	2047	1147	846
65°	1934	951	762
70°	1797	767	690
75°	1624	676	628
80°	1374	568	545
85°	961	381	411

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2313 cd/sqm

TEST NUMBER: P928762

CATALOG NUMBER: DFN2DIP-HX4F0-110D080US930-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	347.3	2.5
10°-20°	953.3	6.8
20°-30°	1338.4	9.5
30°-40°	1458.9	10.4
40°-50°	1340.9	9.5
50°-60°	1053.1	7.5
60°-70°	685.5	4.9
70°-80°	352.9	2.5
80°-90°	94.0	0.7
90°-100°	72.6	0.5
100°-110°	270.5	1.9
110°-120°	717.4	5.1
120°-130°	1189.8	8.5
130°-140°	1263.8	9.0
140°-150°	1174.6	8.3
150°-160°	944.4	6.7
160°-170°	608.5	4.3
170°-180°	209.4	1.5
0°-30°	2638.9	18.7
0°-40°	4097.9	29.1
0°-60°	6491.9	46.1
0°-90°	7624.1	54.2
90°-120°	1060.4	7.5
90°-150°	4688.7	33.3
90°-180°	6451.0	45.8
0°-180°	14075.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3705	3705	3705	3705	3705	
5°	3705	3688	3645	3675	3665	351
15°	3524	3487	3373	3310	3276	993
25°	3199	3092	2870	2733	2682	1471
35°	2756	2585	2290	2079	2005	1725
45°	2253	2028	1677	1438	1358	1740
55°	1713	1452	1090	889	825	1531
65°	1157	885	584	470	459	1147
75°	617	382	268	245	242	652
85°	144	74	64	64	64	165
90°	2	19	32	40	43	13
95°	103	51	62	70	68	122
105°	484	532	97	115	121	517
115°	916	942	982	245	131	901
125°	1294	1315	1345	1357	1361	1154
135°	1602	1627	1642	1658	1654	1237
145°	1858	1856	1884	1895	1887	1162
155°	2046	2032	2051	2060	2048	943
165°	2156	2146	2151	2162	2151	609
175°	2205	2194	2197	2208	2192	210
180°	2200	2200	2200	2200	2200	

TEST NUMBER: P928762

CATALOG NUMBER: DFN2DIP-HX4F0-110D080US930-RLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3705.2	3705.2	3705.2	3705.2	3705.2
2.5°	3721.9	3705.2	3668.2	3702.1	3695.3
5°	3705.2	3688.5	3644.8	3675.0	3665.1
7.5°	3675.0	3655.0	3608.1	3621.3	3604.5
10°	3634.8	3611.3	3544.4	3534.1	3514.2
12.5°	3584.6	3554.4	3463.7	3443.7	3406.7
15°	3524.1	3487.1	3373.3	3309.6	3276.1
17.5°	3453.7	3400.0	3259.1	3185.4	3131.7
20°	3373.3	3306.0	3138.5	3054.9	2980.9
22.5°	3286.2	3208.9	3014.4	2900.5	2850.3
25°	3199.0	3091.5	2870.3	2732.9	2682.4
27.5°	3095.1	2980.9	2736.1	2578.5	2501.3
30°	2984.4	2856.7	2588.5	2417.7	2327.0
32.5°	2877.0	2722.6	2447.9	2246.6	2162.7
35°	2756.4	2585.3	2290.4	2079.1	2005.1
37.5°	2639.1	2454.4	2142.7	1911.1	1827.6
40°	2514.8	2313.9	1988.4	1750.3	1663.2
42.5°	2387.5	2173.0	1834.3	1586.0	1502.4
45°	2253.4	2028.5	1676.7	1438.3	1358.0
47.5°	2126.0	1888.0	1525.8	1287.5	1213.9
50°	1985.1	1747.1	1378.2	1146.6	1076.5
52.5°	1847.4	1595.9	1237.3	1016.1	952.3
55°	1713.3	1451.8	1089.7	888.7	825.0
57.5°	1576.0	1307.7	959.1	771.3	717.5
60°	1435.1	1166.9	821.4	650.7	597.0
62.5°	1297.8	1029.6	704.1	543.3	516.5
65°	1156.9	885.1	583.5	469.6	459.3
67.5°	1022.8	751.0	469.6	412.3	402.4
70°	881.9	620.5	388.8	355.4	341.9
72.5°	747.8	499.5	325.2	298.5	291.7
75°	616.9	382.1	268.2	244.7	241.6
77.5°	486.3	271.5	211.3	197.8	191.0
80°	365.4	194.6	160.8	147.7	147.7
82.5°	254.7	130.9	110.7	103.9	103.9
85°	144.1	73.7	63.7	63.7	63.7
87.5°	53.7	26.7	26.7	23.5	23.5
90°	1.5	19.1	31.8	39.9	43.0
92.5°	39.9	33.5	38.2	41.4	43.0
95°	103.4	50.9	62.0	70.2	68.5
97.5°	186.2	55.7	81.1	86.1	87.5
100°	281.9	63.7	90.8	103.4	106.6
102.5°	386.9	383.8	94.0	111.3	116.3
105°	484.0	531.9	97.1	114.6	121.0
107.5°	597.1	636.8	100.4	117.8	124.2
110°	705.5	738.7	278.7	119.5	125.8

TEST NUMBER: P928762

CATALOG NUMBER: DFN2DIP-HX4F0-110D080US930-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	807.3	835.9	808.9	122.5	127.5
115°	915.5	942.5	982.4	245.2	130.6
117.5°	1009.5	1041.2	1068.5	840.6	423.6
120°	1114.6	1138.4	1167.2	1186.2	971.2
122.5°	1203.6	1229.2	1261.1	1270.6	1272.3
125°	1294.4	1315.2	1345.4	1356.6	1361.3
127.5°	1377.2	1399.5	1423.6	1439.4	1440.9
130°	1455.3	1480.8	1498.2	1515.8	1514.3
132.5°	1534.9	1555.7	1573.1	1587.5	1585.9
135°	1601.8	1627.3	1641.5	1657.6	1654.4
137.5°	1671.8	1690.9	1706.9	1722.8	1718.1
140°	1740.2	1753.1	1770.5	1784.8	1776.9
142.5°	1797.7	1808.8	1829.4	1842.1	1834.2
145°	1858.2	1856.5	1883.5	1894.7	1886.7
147.5°	1910.6	1905.9	1932.9	1940.8	1934.6
150°	1961.6	1950.5	1976.0	1985.4	1977.5
152.5°	2004.6	1991.9	2015.7	2025.4	2014.2
155°	2046.0	2031.8	2050.9	2060.3	2047.7
157.5°	2079.4	2066.8	2081.1	2092.3	2079.4
160°	2108.2	2098.5	2108.2	2117.6	2106.4
162.5°	2133.5	2124.1	2132.0	2143.1	2128.8
165°	2155.8	2146.4	2151.1	2162.2	2151.1
167.5°	2173.4	2163.7	2168.6	2179.8	2165.5
170°	2187.8	2178.1	2181.3	2192.5	2178.1
172.5°	2197.2	2187.8	2191.0	2202.1	2187.8
175°	2205.1	2194.0	2197.2	2208.3	2192.5
177.5°	2208.3	2197.2	2198.9	2210.0	2195.7
180°	2200.4	2200.4	2200.4	2200.4	2200.4

TEST NUMBER: P928762

CATALOG NUMBER: DFN2DIP-HX4F0-110D080US930-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.05	11.92	11.98	12.86	14.07	7.02	7.89	7.95	8.83	10.04
	3H	12.73	13.51	13.67	14.45	15.69	8.22	8.99	9.16	9.94	11.18
	4H	13.34	14.07	14.30	15.03	16.27	8.67	9.40	9.62	10.36	11.60
	6H	13.77	14.44	14.73	15.40	16.66	8.99	9.67	9.96	10.63	11.89
	8H	13.89	14.53	14.87	15.51	16.77	9.09	9.73	10.06	10.70	11.96
	12H	13.96	14.57	14.93	15.54	16.82	9.13	9.74	10.11	10.71	11.99
4H	2H	11.07	11.80	12.03	12.76	14.00	7.62	8.35	8.58	9.31	10.56
	3H	12.91	13.51	13.88	14.50	15.76	8.98	9.59	9.95	10.57	11.83
	4H	13.60	14.16	14.58	15.13	16.42	9.53	10.08	10.51	11.06	12.35
	6H	14.12	14.60	15.11	15.60	16.88	9.95	10.43	10.94	11.43	12.71
	8H	14.30	14.74	15.29	15.74	17.03	10.08	10.53	11.08	11.52	12.82
	12H	14.39	14.79	15.40	15.81	17.11	10.15	10.55	11.16	11.56	12.87
8H	4H	13.57	14.02	14.56	15.01	16.31	9.81	10.26	10.80	11.25	12.55
	6H	14.14	14.51	15.16	15.54	16.84	10.34	10.70	11.35	11.74	13.03
	8H	14.36	14.68	15.38	15.71	17.02	10.53	10.85	11.55	11.88	13.19
	12H	14.50	14.78	15.53	15.80	17.16	10.65	10.94	11.68	11.95	13.31
12H	4H	13.53	13.93	14.54	14.94	16.24	9.82	10.22	10.83	11.23	12.53
	6H	14.12	14.44	15.14	15.46	16.78	10.38	10.71	11.41	11.73	13.05
	8H	14.34	14.62	15.37	15.64	17.00	10.60	10.88	11.63	11.90	13.26