

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P905565

Luminaire Tested: DFN2DIP-HX4F0-120D070US835-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P905565
REPORT IS A COMBINATION OF REPORTS P899370 AND P896188
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-120D070US835-RLLFLL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 16395.0 lumens
Efficiency: N/A
Efficacy: 98.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 165.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9954
Total Harmonic Distortion (THDi): 0.076
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P905565
CATALOG NUMBER: DFN2DIP-HX4F0-120D070US835-RLFL

Luminous Intensity Polar Plot





TEST NUMBER: P905565

CATALOG NUMBER: DFN2DIP-HX4F0-120D070US835-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	67	67	67	62
1	101	97	93	90	95	91	88	85	80	78	75	70	68	66	60	59	58	60	59	58	54
2	93	85	79	74	87	80	75	71	71	67	63	62	59	56	54	52	50	54	52	50	46
3	85	76	68	63	79	71	65	60	63	58	54	55	52	48	48	46	43	48	46	43	40
4	78	67	60	54	73	64	57	51	56	51	47	50	46	42	44	40	38	44	40	38	34
5	72	60	52	47	67	57	50	45	51	45	41	45	41	37	40	36	33	40	36	33	30
6	66	55	47	41	62	52	44	39	46	40	36	41	36	33	36	32	30	36	32	30	27
7	62	49	42	36	58	47	40	35	42	36	32	38	33	29	33	29	27	33	29	27	24
8	57	45	37	32	54	43	36	31	39	33	29	34	30	26	31	27	24	31	27	24	22
9	54	41	34	29	50	39	33	28	36	30	26	32	27	24	28	25	22	28	25	22	20
10	50	38	31	26	47	36	30	25	33	27	24	30	25	22	26	23	20	26	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3688	3688	3688
5°	3694	3630	3653
10°	3658	3559	3534
15°	3608	3441	3350
20°	3541	3280	3125
25°	3473	3098	2907
30°	3382	2912	2631
35°	3293	2712	2389
40°	3202	2505	2111
45°	3096	2275	1859
50°	2987	2043	1613
55°	2873	1795	1376
60°	2741	1536	1133
65°	2589	1272	1020
70°	2405	1026	923
75°	2174	906	840
80°	1839	761	729
85°	1286	510	549

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3096 cd/sqm



TEST NUMBER: P905565

CATALOG NUMBER: DFN2DIP-HX4F0-120D070US835-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	464.8	2.8
10°-20°	1276.0	7.8
20°-30°	1791.5	10.9
30°-40°	1952.8	11.9
40°-50°	1794.9	10.9
50°-60°	1409.6	8.6
60°-70°	917.5	5.6
70°-80°	472.3	2.9
80°-90°	126.9	0.8
90°-100°	137.0	0.8
100°-110°	435.3	2.7
110°-120°	744.9	4.5
120°-130°	979.6	6.0
130°-140°	1099.6	6.7
140°-150°	1078.3	6.6
150°-160°	904.5	5.5
160°-170°	599.9	3.7
170°-180°	209.7	1.3
0°-30°	3532.3	21.5
0°-40°	5485.2	33.5
0°-60°	8689.6	53.0
0°-90°	10206.3	62.3
90°-120°	1317.2	8.0
90°-150°	4474.7	27.3
90°-180°	6189.0	37.7
0°-180°	16395.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4960	4960	4960	4960	4960	
5°	4960	4937	4879	4919	4906	470
15°	4717	4668	4515	4430	4385	1329
25°	4282	4138	3842	3658	3590	1969
35°	3690	3460	3066	2783	2684	2309
45°	3016	2715	2244	1925	1818	2329
55°	2293	1943	1459	1190	1104	2049
65°	1549	1185	781	629	615	1535
75°	826	511	359	328	323	873
85°	193	99	85	85	85	221
90°	2	24	65	61	63	16
95°	97	116	120	120	116	108
105°	402	407	411	414	414	424
115°	748	758	755	753	748	739
125°	1087	1104	1099	1093	1091	972
135°	1406	1427	1431	1429	1424	1087
145°	1707	1721	1731	1733	1726	1067
155°	1952	1958	1964	1973	1967	899
165°	2124	2122	2122	2135	2126	599
175°	2210	2204	2200	2214	2202	210
180°	2214	2214	2214	2214	2214	



TEST NUMBER: P905565

CATALOG NUMBER: DFN2DIP-HX4F0-120D070US835-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4959.6	4959.6	4959.6	4959.6	4959.6
2.5°	4982.0	4959.6	4910.1	4955.3	4946.2
5°	4959.6	4937.2	4878.6	4919.1	4905.8
7.5°	4919.1	4892.4	4829.6	4847.2	4824.8
10°	4865.3	4833.9	4744.3	4730.5	4703.9
12.5°	4798.1	4757.7	4636.2	4609.6	4560.1
15°	4717.2	4667.7	4515.3	4430.0	4385.3
17.5°	4622.9	4551.0	4362.4	4263.9	4192.0
20°	4515.3	4425.3	4201.0	4089.1	3990.0
22.5°	4398.6	4295.3	4034.8	3882.4	3815.3
25°	4282.0	4138.1	3841.9	3658.1	3590.5
27.5°	4142.9	3990.0	3662.4	3451.5	3348.1
30°	3994.8	3823.9	3464.8	3236.2	3114.8
32.5°	3851.0	3644.3	3276.7	3007.2	2894.8
35°	3689.6	3460.5	3065.7	2782.9	2683.8
37.5°	3532.4	3285.3	2868.1	2558.1	2446.2
40°	3366.2	3097.2	2661.5	2342.9	2226.2
42.5°	3195.7	2908.6	2455.3	2122.9	2011.0
45°	3016.2	2715.3	2244.3	1925.3	1817.6
47.5°	2845.7	2527.2	2042.4	1723.4	1624.8
50°	2657.2	2338.6	1844.8	1534.8	1441.0
52.5°	2472.9	2136.2	1656.2	1360.0	1274.8
55°	2293.4	1943.4	1458.6	1189.5	1104.3
57.5°	2109.5	1750.5	1283.8	1032.4	960.5
60°	1921.0	1561.9	1099.5	871.0	799.1
62.5°	1737.2	1378.1	942.4	727.2	691.4
65°	1548.6	1184.8	781.0	628.6	614.8
67.5°	1369.1	1005.2	628.6	551.9	538.6
70°	1180.5	830.5	520.5	475.7	457.6
72.5°	1001.0	668.6	435.2	399.5	390.5
75°	825.7	511.4	359.1	327.6	323.3
77.5°	651.0	363.3	282.9	264.8	255.7
80°	489.1	260.5	215.2	197.6	197.6
82.5°	341.0	175.2	148.1	139.0	139.0
85°	192.9	98.6	85.2	85.2	85.2
87.5°	71.9	35.7	35.7	31.4	31.4
90°	2.0	24.0	65.4	61.4	63.4
92.5°	41.4	56.1	58.1	60.1	60.1
95°	97.4	116.1	119.5	119.5	116.1
97.5°	162.2	179.5	186.9	186.9	186.9
100°	236.9	252.3	257.6	257.6	255.6
102.5°	315.7	327.0	334.4	336.4	334.4
105°	401.8	407.1	411.1	414.5	414.5
107.5°	487.2	495.2	495.2	496.6	487.2
110°	570.0	580.7	580.7	580.7	575.3



TEST NUMBER: P905565

CATALOG NUMBER: DFN2DIP-HX4F0-120D070US835-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	659.4	670.8	668.8	663.4	659.4
115°	747.5	758.2	754.9	752.9	747.5
117.5°	834.9	849.6	840.3	834.9	829.6
120°	923.0	937.7	923.0	923.0	917.0
122.5°	1003.1	1021.8	1012.5	1007.1	1003.1
125°	1087.2	1103.9	1098.6	1092.6	1090.6
127.5°	1169.3	1190.0	1182.7	1174.7	1169.3
130°	1246.1	1270.1	1266.8	1262.8	1255.4
132.5°	1332.2	1350.9	1352.2	1342.9	1337.5
135°	1406.3	1426.9	1431.0	1428.9	1423.6
137.5°	1489.0	1505.7	1509.0	1507.7	1499.7
140°	1561.8	1578.5	1587.8	1587.8	1580.5
142.5°	1636.5	1653.2	1658.5	1660.5	1653.2
145°	1707.3	1720.6	1731.3	1733.3	1726.0
147.5°	1770.7	1787.4	1795.4	1798.7	1791.4
150°	1836.1	1847.4	1854.8	1860.8	1854.8
152.5°	1894.1	1905.5	1914.8	1922.2	1914.8
155°	1952.2	1957.5	1963.6	1972.9	1966.9
157.5°	2002.3	2006.3	2009.6	2023.0	2013.6
160°	2047.0	2051.0	2053.0	2064.3	2056.3
162.5°	2088.4	2088.4	2090.4	2103.0	2093.7
165°	2123.7	2121.7	2121.7	2135.1	2125.7
167.5°	2155.8	2149.8	2149.8	2163.1	2153.8
170°	2179.8	2174.5	2172.5	2185.8	2174.5
172.5°	2196.5	2191.1	2189.1	2202.5	2191.1
175°	2209.8	2204.5	2200.5	2213.8	2202.5
177.5°	2217.2	2211.8	2207.8	2219.2	2207.8
180°	2213.8	2213.8	2213.8	2213.8	2213.8



TEST NUMBER: P905565
 CATALOG NUMBER: DFN2DIP-HX4F0-120D070US835-RLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.75	13.70	13.61	14.56	15.65	8.73	9.67	9.58	10.54	11.62
	3H	14.44	15.28	15.31	16.16	17.28	9.93	10.77	10.79	11.65	12.76
	4H	15.06	15.85	15.94	16.73	17.86	10.38	11.18	11.26	12.06	13.19
	6H	15.48	16.21	16.38	17.11	18.24	10.71	11.44	11.60	12.33	13.47
	8H	15.61	16.31	16.51	17.22	18.36	10.81	11.50	11.71	12.41	13.55
	12H	15.68	16.34	16.58	17.24	18.41	10.85	11.52	11.76	12.42	13.58
4H	2H	12.79	13.58	13.67	14.46	15.59	9.34	10.13	10.22	11.02	12.14
	3H	14.63	15.29	15.52	16.20	17.34	10.70	11.36	11.59	12.27	13.41
	4H	15.32	15.92	16.23	16.84	18.00	11.25	11.85	12.16	12.77	13.93
	6H	15.85	16.36	16.77	17.30	18.47	11.68	12.20	12.60	13.13	14.30
	8H	16.02	16.51	16.95	17.44	18.62	11.81	12.29	12.74	13.23	14.41
	12H	16.12	16.56	17.07	17.51	18.69	11.88	12.32	12.83	13.27	14.45
8H	4H	15.30	15.78	16.22	16.71	17.89	11.54	12.02	12.47	12.95	14.14
	6H	15.87	16.27	16.82	17.24	18.42	12.07	12.47	13.02	13.44	14.62
	8H	16.09	16.44	17.05	17.41	18.60	12.26	12.61	13.22	13.57	14.77
	12H	16.23	16.54	17.20	17.50	18.75	12.38	12.70	13.35	13.65	14.90
12H	4H	15.26	15.69	16.20	16.64	17.83	11.55	11.99	12.49	12.93	14.12
	6H	15.85	16.20	16.81	17.16	18.36	12.12	12.47	13.08	13.43	14.63
	8H	16.07	16.38	17.04	17.34	18.59	12.33	12.64	13.30	13.60	14.85