

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P916471

Luminaire Tested: DFN2DIP-HX4F0-120D040US930-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P916471
REPORT IS A COMBINATION OF REPORTS P899316 AND P896188
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-120D040US930-RLLFLL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11202.2 lumens
Efficiency: N/A
Efficacy: 74.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 149.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9954
Total Harmonic Distortion (THDi): 0.076
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P916471

CATALOG NUMBER: DFN2DIP-HX4F0-120D040US930-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P916471

CATALOG NUMBER: DFN2DIP-HX4F0-120D040US930-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	113	113	113	113	107	107	107	107	97	97	97	87	87	87	78	78	78
1	104	100	96	93	99	95	92	89	86	84	81	78	76	74	70	69	68
2	95	88	82	77	90	84	79	74	76	72	68	69	66	63	63	60	58
3	87	78	71	65	83	75	68	63	68	63	58	62	58	54	56	53	50
4	80	70	62	56	76	67	60	54	61	55	51	56	51	47	51	47	44
5	74	63	54	48	70	60	53	47	55	49	44	51	45	42	46	42	39
6	69	57	48	43	65	54	47	41	50	44	39	46	41	37	42	38	35
7	64	51	43	38	61	49	42	37	46	39	35	42	37	33	39	34	31
8	59	47	39	34	57	45	38	33	42	36	31	39	34	30	36	31	28
9	56	43	36	31	53	42	35	30	39	33	28	36	31	27	33	29	26
10	52	40	33	28	50	39	32	27	36	30	26	33	28	25	31	27	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3007	3007	3007
5°	3012	2959	2978
10°	2982	2901	2881
15°	2941	2806	2732
20°	2887	2674	2548
25°	2832	2526	2370
30°	2757	2374	2145
35°	2685	2211	1948
40°	2610	2042	1721
45°	2524	1855	1516
50°	2435	1666	1315
55°	2342	1464	1122
60°	2234	1252	924
65°	2111	1037	831
70°	1961	837	753
75°	1772	738	685
80°	1500	620	595
85°	1049	416	448

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2524 cd/sqm

TEST NUMBER: P916471

CATALOG NUMBER: DFN2DIP-HX4F0-120D040US930-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	379.0	3.4
10°-20°	1040.3	9.3
20°-30°	1460.6	13.0
30°-40°	1592.1	14.2
40°-50°	1463.4	13.1
50°-60°	1149.2	10.3
60°-70°	748.0	6.7
70°-80°	385.1	3.4
80°-90°	101.2	0.9
90°-100°	63.8	0.6
100°-110°	202.8	1.8
110°-120°	347.0	3.1
120°-130°	456.4	4.1
130°-140°	512.3	4.6
140°-150°	502.4	4.5
150°-160°	421.4	3.8
160°-170°	279.5	2.5
170°-180°	97.7	0.9
0°-30°	2879.9	25.7
0°-40°	4472.0	39.9
0°-60°	7084.6	63.2
0°-90°	8319.0	74.3
90°-120°	613.6	5.5
90°-150°	2084.7	18.6
90°-180°	2883.0	25.7
0°-180°	11202.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4044	4044	4044	4044	4044	
5°	4044	4025	3978	4010	4000	383
15°	3846	3806	3681	3612	3575	1084
25°	3491	3374	3132	2982	2927	1606
35°	3008	2821	2500	2269	2188	1883
45°	2459	2214	1830	1570	1482	1899
55°	1870	1584	1189	970	900	1671
65°	1263	966	637	512	501	1252
75°	673	417	293	267	264	712
85°	157	80	70	70	70	181
90°	1	11	30	29	30	11
95°	45	54	56	56	54	51
105°	187	190	192	193	193	198
115°	348	353	352	351	348	344
125°	506	514	512	509	508	453
135°	655	665	667	666	663	506
145°	795	802	807	808	804	497
155°	910	912	915	919	916	419
165°	989	988	988	995	990	279
175°	1030	1027	1025	1031	1026	98
180°	1031	1031	1031	1031	1031	

TEST NUMBER: P916471

CATALOG NUMBER: DFN2DIP-HX4F0-120D040US930-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4043.6	4043.6	4043.6	4043.6	4043.6
2.5°	4061.8	4043.6	4003.2	4040.0	4032.6
5°	4043.6	4025.3	3977.5	4010.5	3999.7
7.5°	4010.5	3988.8	3937.6	3951.9	3933.7
10°	3966.7	3941.1	3868.0	3856.8	3835.1
12.5°	3911.9	3878.9	3779.9	3758.2	3717.8
15°	3845.9	3805.6	3681.3	3611.8	3575.3
17.5°	3769.0	3710.4	3556.7	3476.4	3417.7
20°	3681.3	3607.9	3425.1	3333.8	3253.0
22.5°	3586.2	3502.0	3289.6	3165.3	3110.6
25°	3491.1	3373.8	3132.3	2982.4	2927.3
27.5°	3377.7	3253.0	2985.9	2814.0	2729.7
30°	3257.0	3117.6	2824.8	2638.5	2539.5
32.5°	3139.7	2971.2	2671.5	2451.8	2360.1
35°	3008.1	2821.3	2499.5	2268.9	2188.1
37.5°	2880.0	2678.5	2338.4	2085.6	1994.4
40°	2744.5	2525.1	2169.9	1910.2	1815.0
42.5°	2605.4	2371.4	2001.8	1730.8	1639.6
45°	2459.1	2213.8	1829.8	1569.7	1481.9
47.5°	2320.1	2060.4	1665.2	1405.1	1324.7
50°	2166.4	1906.7	1504.1	1251.3	1174.8
52.5°	2016.2	1741.6	1350.3	1108.8	1039.3
55°	1869.8	1584.5	1189.2	969.8	900.3
57.5°	1719.9	1427.2	1046.7	841.7	783.1
60°	1566.2	1273.4	896.4	710.1	651.5
62.5°	1416.3	1123.6	768.3	592.9	563.7
65°	1262.6	966.0	636.7	512.5	501.2
67.5°	1116.2	819.5	512.5	450.0	439.1
70°	962.5	677.1	424.4	387.8	373.1
72.5°	816.1	545.1	354.8	325.7	318.4
75°	673.2	416.9	292.8	267.1	263.6
77.5°	530.8	296.2	230.6	215.9	208.5
80°	398.8	212.4	175.5	161.1	161.1
82.5°	278.0	142.8	120.7	113.3	113.3
85°	157.3	80.4	69.5	69.5	69.5
87.5°	58.6	29.1	29.1	25.6	25.6
90°	0.9	11.2	30.5	28.6	29.5
92.5°	19.2	26.1	27.1	28.0	28.0
95°	45.4	54.1	55.7	55.7	54.1
97.5°	75.6	83.6	87.1	87.1	87.1
100°	110.4	117.6	120.0	120.0	119.1
102.5°	147.1	152.4	155.8	156.7	155.8
105°	187.2	189.6	191.5	193.1	193.1
107.5°	227.0	230.7	230.7	231.3	227.0
110°	265.5	270.5	270.5	270.5	268.1

TEST NUMBER: P916471

CATALOG NUMBER: DFN2DIP-HX4F0-120D040US930-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	307.2	312.5	311.5	309.1	307.2
115°	348.2	353.3	351.6	350.7	348.2
117.5°	389.0	395.8	391.5	389.0	386.5
120°	430.1	436.8	430.1	430.1	427.2
122.5°	467.3	476.1	471.7	469.2	467.3
125°	506.5	514.3	511.8	509.0	508.1
127.5°	544.8	554.4	551.0	547.2	544.8
130°	580.5	591.7	590.2	588.3	584.9
132.5°	620.6	629.3	630.0	625.6	623.1
135°	655.2	664.8	666.7	665.7	663.2
137.5°	693.7	701.5	703.0	702.4	698.7
140°	727.6	735.4	739.7	739.7	736.3
142.5°	762.5	770.2	772.7	773.6	770.2
145°	795.4	801.6	806.6	807.6	804.1
147.5°	824.9	832.7	836.4	838.0	834.5
150°	855.4	860.7	864.1	866.9	864.1
152.5°	882.5	887.7	892.1	895.5	892.1
155°	909.5	912.0	914.8	919.2	916.3
157.5°	932.9	934.7	936.2	942.5	938.1
160°	953.7	955.5	956.4	961.7	958.0
162.5°	972.9	972.9	973.9	979.7	975.4
165°	989.4	988.5	988.5	994.7	990.3
167.5°	1004.4	1001.5	1001.5	1007.8	1003.4
170°	1015.5	1013.0	1012.1	1018.3	1013.0
172.5°	1023.3	1020.8	1019.9	1026.1	1020.8
175°	1029.6	1027.0	1025.2	1031.4	1026.1
177.5°	1033.0	1030.5	1028.6	1033.9	1028.6
180°	1031.4	1031.4	1031.4	1031.4	1031.4

TEST NUMBER: P916471

CATALOG NUMBER: DFN2DIP-HX4F0-120D040US930-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.99	14.07	13.72	14.81	15.69	8.97	10.04	9.69	10.78	11.66
	3H	14.69	15.65	15.43	16.40	17.31	10.17	11.14	10.91	11.89	12.80
	4H	15.31	16.22	16.07	16.98	17.90	10.64	11.55	11.39	12.30	13.23
	6H	15.74	16.58	16.51	17.35	18.29	10.97	11.81	11.74	12.58	13.51
	8H	15.88	16.67	16.66	17.46	18.40	11.07	11.87	11.85	12.65	13.59
	12H	15.95	16.71	16.73	17.49	18.45	11.12	11.88	11.91	12.66	13.63
4H	2H	13.04	13.95	13.80	14.71	15.63	9.59	10.50	10.35	11.26	12.18
	3H	14.89	15.65	15.66	16.44	17.38	10.97	11.72	11.74	12.51	13.45
	4H	15.60	16.28	16.38	17.07	18.04	11.52	12.21	12.31	13.00	13.97
	6H	16.13	16.72	16.93	17.53	18.51	11.96	12.55	12.76	13.37	14.35
	8H	16.31	16.86	17.11	17.67	18.66	12.09	12.64	12.90	13.46	14.45
	12H	16.41	16.91	17.24	17.74	18.74	12.17	12.67	13.00	13.50	14.50
8H	4H	15.58	16.13	16.39	16.95	17.94	11.82	12.37	12.63	13.19	14.18
	6H	16.16	16.61	16.99	17.47	18.46	12.35	12.81	13.19	13.67	14.65
	8H	16.38	16.78	17.22	17.64	18.64	12.55	12.95	13.39	13.81	14.81
	12H	16.53	16.88	17.38	17.73	18.79	12.68	13.03	13.53	13.88	14.94
12H	4H	15.54	16.04	16.37	16.88	17.87	11.84	12.33	12.67	13.17	14.16
	6H	16.13	16.54	16.98	17.39	18.40	12.40	12.81	13.25	13.66	14.67
	8H	16.37	16.72	17.22	17.57	18.63	12.63	12.98	13.47	13.83	14.89