

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P928794

Luminaire Tested: DFN2DIP-HX4F0-120D070US930-RLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P928794
REPORT IS A COMBINATION OF REPORTS P900890 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-120D070US930-RLLONL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 13961.0 lumens
Efficiency: N/A
Efficacy: 78.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 178.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9954
Total Harmonic Distortion (THDi): 0.076
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P928794

CATALOG NUMBER: DFN2DIP-HX4F0-120D070US930-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P928794

CATALOG NUMBER: DFN2DIP-HX4F0-120D070US930-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	89	89	89	76	76	76	65	65	65
1	101	96	93	89	94	90	87	84	79	76	74	68	66	65	58	57	56
2	92	85	79	74	86	80	74	70	70	66	62	60	58	55	52	50	48
3	84	75	68	62	79	71	64	59	62	57	53	54	50	47	47	44	42
4	77	67	59	53	72	63	56	51	55	50	46	48	44	41	42	39	36
5	71	60	52	46	67	56	49	44	50	44	40	44	39	36	38	35	32
6	66	54	46	40	62	51	44	39	45	39	35	40	35	32	35	31	28
7	61	49	41	36	57	46	39	34	41	35	31	36	32	28	32	28	26
8	57	45	37	32	53	42	35	31	38	32	28	34	29	26	30	26	23
9	53	41	34	29	50	39	32	27	35	29	25	31	26	23	27	24	21
10	50	38	31	26	47	36	29	25	32	27	23	29	24	21	25	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3006	3006	3006
5°	3011	2958	2977
10°	2981	2900	2880
15°	2940	2805	2731
20°	2886	2673	2547
25°	2831	2525	2370
30°	2756	2373	2145
35°	2684	2210	1947
40°	2609	2042	1720
45°	2523	1854	1515
50°	2434	1665	1314
55°	2341	1463	1121
60°	2234	1252	923
65°	2110	1037	831
70°	1960	837	752
75°	1771	738	685
80°	1499	620	594
85°	1048	415	448

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2523 cd/sqm

TEST NUMBER: P928794

CATALOG NUMBER: DFN2DIP-HX4F0-120D070US930-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	378.8	2.7
10°-20°	1040.0	7.4
20°-30°	1460.1	10.5
30°-40°	1591.6	11.4
40°-50°	1462.8	10.5
50°-60°	1148.8	8.2
60°-70°	747.8	5.4
70°-80°	384.9	2.8
80°-90°	101.6	0.7
90°-100°	63.5	0.5
100°-110°	236.7	1.7
110°-120°	627.7	4.5
120°-130°	1041.1	7.5
130°-140°	1105.9	7.9
140°-150°	1027.8	7.4
150°-160°	826.3	5.9
160°-170°	532.4	3.8
170°-180°	183.3	1.3
0°-30°	2878.9	20.6
0°-40°	4470.4	32.0
0°-60°	7082.1	50.7
0°-90°	8316.4	59.6
90°-120°	927.9	6.6
90°-150°	4102.6	29.4
90°-180°	5645.0	40.4
0°-180°	13961.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4042	4042	4042	4042	4042	
5°	4042	4024	3976	4009	3998	383
15°	3844	3804	3680	3610	3574	1083
25°	3490	3373	3131	2981	2926	1605
35°	3007	2820	2498	2268	2187	1882
45°	2458	2213	1829	1569	1481	1898
55°	1869	1584	1189	969	900	1670
65°	1262	966	636	512	501	1251
75°	673	417	293	267	264	712
85°	157	80	69	69	69	180
90°	1	17	28	35	38	13
95°	90	44	54	61	60	107
105°	424	465	85	100	106	453
115°	801	825	860	215	114	789
125°	1133	1151	1177	1187	1191	1010
135°	1402	1424	1436	1450	1448	1083
145°	1626	1624	1648	1658	1651	1017
155°	1790	1778	1794	1803	1792	825
165°	1886	1878	1882	1892	1882	533
175°	1930	1920	1923	1932	1918	184
180°	1925	1925	1925	1925	1925	

TEST NUMBER: P928794

CATALOG NUMBER: DFN2DIP-HX4F0-120D070US930-RLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4042.1	4042.1	4042.1	4042.1	4042.1
2.5°	4060.3	4042.1	4001.7	4038.6	4031.2
5°	4042.1	4023.8	3976.1	4009.1	3998.2
7.5°	4009.1	3987.3	3936.1	3950.5	3932.2
10°	3965.2	3939.6	3866.6	3855.4	3833.7
12.5°	3910.5	3877.5	3778.5	3756.8	3716.5
15°	3844.5	3804.2	3680.0	3610.4	3574.0
17.5°	3767.7	3709.1	3555.4	3475.1	3416.5
20°	3680.0	3606.6	3423.8	3332.6	3251.8
22.5°	3584.9	3500.7	3288.4	3164.2	3109.5
25°	3489.8	3372.6	3131.1	2981.4	2926.3
27.5°	3376.5	3251.8	2984.9	2813.0	2728.7
30°	3255.8	3116.5	2823.8	2637.5	2538.6
32.5°	3138.6	2970.1	2670.5	2450.9	2359.3
35°	3007.0	2820.3	2498.5	2268.1	2187.3
37.5°	2878.9	2677.5	2337.5	2084.9	1993.7
40°	2743.5	2524.2	2169.1	1909.5	1814.4
42.5°	2604.5	2370.5	2001.1	1730.2	1639.0
45°	2458.2	2213.0	1829.1	1569.1	1481.3
47.5°	2319.2	2059.7	1664.6	1404.6	1324.2
50°	2165.6	1906.0	1503.5	1250.9	1174.4
52.5°	2015.4	1741.0	1349.8	1108.4	1039.0
55°	1869.1	1583.9	1188.8	969.4	900.0
57.5°	1719.2	1426.7	1046.3	841.4	782.8
60°	1565.6	1272.9	896.1	709.9	651.3
62.5°	1415.8	1123.2	768.1	592.7	563.5
65°	1262.1	965.6	636.5	512.3	501.1
67.5°	1115.8	819.2	512.3	449.8	439.0
70°	962.1	676.9	424.2	387.7	372.9
72.5°	815.8	544.9	354.7	325.6	318.3
75°	672.9	416.8	292.7	267.0	263.5
77.5°	530.6	296.1	230.6	215.8	208.4
80°	398.6	212.3	175.4	161.0	161.0
82.5°	277.9	142.8	120.7	113.3	113.3
85°	157.2	80.4	69.4	69.4	69.4
87.5°	58.6	29.1	29.1	25.6	25.6
90°	1.3	16.7	27.8	34.9	37.6
92.5°	34.9	29.3	33.4	36.3	37.6
95°	90.5	44.5	54.3	61.4	59.9
97.5°	162.9	48.8	71.0	75.3	76.6
100°	246.7	55.7	79.4	90.5	93.3
102.5°	338.5	335.9	82.2	97.5	101.7
105°	423.6	465.4	85.0	100.2	105.9
107.5°	522.4	557.2	87.9	103.1	108.7
110°	617.3	646.4	243.8	104.6	110.0



TEST NUMBER: P928794

CATALOG NUMBER: DFN2DIP-HX4F0-120D070US930-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	706.4	731.4	707.7	107.2	111.5
115°	801.1	824.7	859.6	214.6	114.3
117.5°	883.3	911.1	934.9	735.5	370.6
120°	975.2	996.1	1021.3	1038.0	849.9
122.5°	1053.1	1075.5	1103.5	1111.7	1113.2
125°	1132.6	1150.8	1177.3	1187.0	1191.1
127.5°	1205.1	1224.5	1245.6	1259.5	1260.8
130°	1273.4	1295.7	1310.9	1326.3	1325.0
132.5°	1343.0	1361.2	1376.5	1389.0	1387.7
135°	1401.6	1423.9	1436.4	1450.4	1447.6
137.5°	1462.8	1479.6	1493.6	1507.5	1503.3
140°	1522.7	1533.9	1549.2	1561.7	1554.8
142.5°	1572.9	1582.7	1600.7	1611.8	1604.9
145°	1625.9	1624.5	1648.1	1657.9	1650.9
147.5°	1671.7	1667.7	1691.3	1698.2	1692.8
150°	1716.4	1706.7	1729.0	1737.3	1730.3
152.5°	1754.0	1742.9	1763.7	1772.1	1762.4
155°	1790.2	1777.8	1794.5	1802.8	1791.7
157.5°	1819.5	1808.4	1821.0	1830.7	1819.5
160°	1844.7	1836.2	1844.7	1852.9	1843.1
162.5°	1866.8	1858.5	1865.5	1875.2	1862.7
165°	1886.3	1878.1	1882.2	1891.9	1882.2
167.5°	1901.7	1893.2	1897.6	1907.3	1894.8
170°	1914.3	1905.9	1908.6	1918.4	1905.9
172.5°	1922.6	1914.3	1917.1	1926.8	1914.3
175°	1929.5	1919.7	1922.6	1932.3	1918.4
177.5°	1932.3	1922.6	1924.1	1933.8	1921.2
180°	1925.4	1925.4	1925.4	1925.4	1925.4

TEST NUMBER: P928794

CATALOG NUMBER: DFN2DIP-HX4F0-120D070US930-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.82	12.74	12.70	13.63	14.76	7.79	8.71	8.67	9.60	10.73
	3H	13.51	14.32	14.40	15.23	16.38	8.99	9.81	9.88	10.71	11.87
	4H	14.12	14.89	15.02	15.80	16.97	9.45	10.22	10.35	11.13	12.29
	6H	14.55	15.26	15.46	16.17	17.35	9.77	10.48	10.69	11.40	12.58
	8H	14.67	15.35	15.60	16.28	17.46	9.87	10.54	10.79	11.48	12.65
	12H	14.74	15.38	15.67	16.31	17.51	9.91	10.56	10.84	11.48	12.69
4H	2H	11.85	12.62	12.76	13.53	14.70	8.40	9.17	9.31	10.08	11.25
	3H	13.69	14.33	14.61	15.27	16.45	9.76	10.40	10.68	11.34	12.52
	4H	14.38	14.97	15.32	15.90	17.11	10.31	10.90	11.24	11.83	13.04
	6H	14.90	15.41	15.85	16.37	17.57	10.74	11.24	11.68	12.20	13.41
	8H	15.08	15.55	16.03	16.50	17.73	10.87	11.34	11.82	12.29	13.51
	12H	15.18	15.60	16.15	16.57	17.80	10.94	11.36	11.91	12.33	13.56
8H	4H	14.36	14.83	15.31	15.78	17.00	10.60	11.07	11.55	12.02	13.24
	6H	14.93	15.32	15.90	16.31	17.53	11.12	11.51	12.10	12.51	13.73
	8H	15.15	15.49	16.13	16.47	17.71	11.32	11.66	12.30	12.64	13.88
	12H	15.29	15.59	16.27	16.57	17.85	11.44	11.74	12.42	12.72	14.00
12H	4H	14.31	14.74	15.28	15.71	16.93	10.61	11.03	11.57	12.00	13.23
	6H	14.90	15.25	15.89	16.23	17.47	11.17	11.52	12.16	12.50	13.74
	8H	15.13	15.43	16.11	16.41	17.69	11.39	11.69	12.37	12.67	13.95