

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P927540

Luminaire Tested: DFN2DIP-HX4F0-040D090US840-FLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P927540
REPORT IS A COMBINATION OF REPORTS P900909 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-040D090US840-FLLONL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12996.1 lumens
Efficiency: N/A
Efficacy: 128.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 101.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9977
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P927540

CATALOG NUMBER: DFN2DIP-HX4F0-040D090US840-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P927540

CATALOG NUMBER: DFN2DIP-HX4F0-040D090US840-FLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	38	38	38
1	93	89	86	82	84	80	77	74	64	61	59	48	47	46	34	33	32
2	85	78	72	67	76	70	65	61	56	52	49	42	40	38	30	29	27
3	78	68	61	56	69	62	56	51	49	45	41	37	35	32	26	25	23
4	71	60	53	47	63	55	48	43	44	39	35	33	30	27	24	22	20
5	65	54	46	40	58	49	42	37	39	34	30	30	26	24	21	19	17
6	60	48	40	35	53	44	37	32	35	30	26	27	23	21	19	17	15
7	55	43	36	30	49	39	33	28	32	27	23	24	21	18	18	15	14
8	51	39	32	27	46	36	29	24	29	24	20	22	19	16	16	14	12
9	47	36	28	24	43	32	26	22	26	21	18	20	17	14	15	13	11
10	44	33	26	21	40	30	23	19	24	19	16	19	15	13	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1169	1169	1169
5°	1171	1152	1160
10°	1161	1137	1145
15°	1144	1118	1120
20°	1121	1093	1095
25°	1098	1062	1066
30°	1070	1033	1029
35°	1043	999	990
40°	1009	964	953
45°	976	930	915
50°	939	894	871
55°	901	852	831
60°	858	802	784
65°	811	751	730
70°	751	688	671
75°	668	614	617
80°	569	518	513
85°	413	353	341

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1574 cd/sqm

TEST NUMBER: P927540

CATALOG NUMBER: DFN2DIP-HX4F0-040D090US840-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	147.9	1.1
10°-20°	416.2	3.2
20°-30°	611.7	4.7
30°-40°	710.4	5.5
40°-50°	709.5	5.5
50°-60°	618.7	4.8
60°-70°	457.3	3.5
70°-80°	258.8	2.0
80°-90°	73.7	0.6
90°-100°	101.1	0.8
100°-110°	377.0	2.9
110°-120°	999.9	7.7
120°-130°	1658.4	12.8
130°-140°	1761.7	13.6
140°-150°	1637.3	12.6
150°-160°	1316.3	10.1
160°-170°	848.2	6.5
170°-180°	291.9	2.2
0°-30°	1175.8	9.0
0°-40°	1886.2	14.5
0°-60°	3214.4	24.7
0°-90°	4004.2	30.8
90°-120°	1478.1	11.4
90°-150°	6535.5	50.3
90°-180°	8992.0	69.2
0°-180°	12996.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1572	1572	1572	1572	1572	
5°	1572	1566	1549	1561	1558	149
15°	1496	1487	1467	1474	1466	421
25°	1354	1342	1316	1319	1316	623
35°	1168	1153	1129	1120	1112	730
45°	951	940	917	901	895	734
55°	720	710	692	674	667	643
65°	485	476	461	447	440	480
75°	254	251	243	234	237	271
85°	62	60	59	54	53	69
90°	2	27	44	56	60	12
95°	144	71	86	98	95	171
105°	675	741	135	160	169	721
115°	1276	1314	1369	342	182	1256
125°	1804	1833	1875	1891	1898	1609
135°	2233	2268	2288	2310	2306	1725
145°	2590	2588	2626	2641	2630	1620
155°	2852	2832	2859	2872	2854	1314
165°	3005	2992	2998	3014	2998	849
175°	3074	3058	3063	3078	3056	293
180°	3067	3067	3067	3067	3067	

TEST NUMBER: P927540

CATALOG NUMBER: DFN2DIP-HX4F0-040D090US840-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1571.7	1571.7	1571.7	1571.7	1571.7
2.5°	1580.8	1573.3	1556.6	1571.7	1568.8
5°	1571.7	1565.7	1549.0	1561.0	1558.2
7.5°	1561.0	1552.1	1535.4	1547.6	1544.6
10°	1544.6	1534.0	1515.9	1527.9	1523.4
12.5°	1521.8	1512.8	1494.7	1502.3	1499.1
15°	1496.1	1487.1	1467.4	1473.5	1466.0
17.5°	1464.4	1455.4	1435.7	1443.2	1435.7
20°	1429.6	1420.6	1399.5	1403.9	1398.1
22.5°	1394.9	1381.3	1361.6	1361.6	1358.6
25°	1354.0	1342.0	1316.4	1319.3	1316.4
27.5°	1308.7	1298.1	1278.6	1274.1	1266.6
30°	1263.5	1251.3	1228.7	1224.2	1218.1
32.5°	1215.1	1206.1	1181.9	1172.8	1166.6
35°	1168.2	1153.2	1129.0	1119.9	1112.3
37.5°	1115.3	1101.7	1077.5	1067.0	1059.4
40°	1061.0	1048.8	1024.5	1011.1	1005.1
42.5°	1008.1	995.9	971.8	956.6	947.6
45°	950.6	940.1	917.3	900.8	894.7
47.5°	894.7	884.1	859.9	843.3	834.3
50°	835.7	828.1	807.0	785.8	778.3
52.5°	778.3	767.8	748.2	731.5	720.9
55°	719.5	710.3	692.2	674.0	666.6
57.5°	660.4	652.9	633.1	615.1	609.0
60°	601.4	595.5	574.4	557.7	553.2
62.5°	544.1	533.5	518.4	503.3	497.2
65°	485.2	476.0	461.0	447.3	439.9
67.5°	424.7	417.0	403.6	393.0	387.0
70°	368.8	362.7	349.1	338.5	332.5
72.5°	311.4	305.3	297.8	287.2	282.6
75°	253.9	250.9	243.3	234.3	237.3
77.5°	202.5	196.4	193.4	188.8	184.4
80°	151.2	149.6	146.5	142.1	139.0
82.5°	102.8	102.8	101.4	95.2	95.2
85°	61.9	60.5	59.0	54.3	52.9
87.5°	27.3	24.2	21.2	16.7	15.0
90°	2.1	26.7	44.2	55.6	59.8
92.5°	55.6	46.7	53.2	57.8	59.8
95°	144.2	70.9	86.4	97.7	95.4
97.5°	259.6	77.8	113.1	119.9	122.0
100°	392.9	88.9	126.5	144.2	148.6
102.5°	539.2	535.0	131.0	155.2	162.1
105°	674.6	741.4	135.4	159.8	168.6
107.5°	832.3	887.6	140.0	164.2	173.2
110°	983.2	1029.7	388.5	166.5	175.3

TEST NUMBER: P927540

CATALOG NUMBER: DFN2DIP-HX4F0-040D090US840-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1125.3	1165.1	1127.4	170.8	177.6
115°	1276.1	1313.7	1369.4	341.8	182.1
117.5°	1407.1	1451.4	1489.3	1171.8	590.3
120°	1553.6	1586.8	1626.9	1653.4	1353.8
122.5°	1677.8	1713.3	1757.9	1771.0	1773.4
125°	1804.2	1833.2	1875.4	1891.0	1897.5
127.5°	1919.6	1950.7	1984.3	2006.4	2008.5
130°	2028.5	2064.1	2088.4	2112.8	2110.8
132.5°	2139.5	2168.4	2192.7	2212.8	2210.7
135°	2232.8	2268.3	2288.1	2310.5	2306.1
137.5°	2330.3	2356.9	2379.3	2401.4	2394.8
140°	2425.6	2443.6	2467.9	2487.8	2476.8
142.5°	2505.8	2521.4	2550.0	2567.7	2556.7
145°	2590.1	2587.7	2625.5	2641.0	2629.9
147.5°	2663.1	2656.6	2694.2	2705.4	2696.6
150°	2734.3	2718.8	2754.3	2767.5	2756.5
152.5°	2794.1	2776.4	2809.7	2823.1	2807.5
155°	2851.9	2832.1	2858.6	2871.9	2854.2
157.5°	2898.5	2880.9	2900.9	2916.4	2898.5
160°	2938.5	2925.1	2938.5	2951.7	2936.2
162.5°	2973.9	2960.6	2971.7	2987.3	2967.3
165°	3005.0	2991.7	2998.4	3014.0	2998.4
167.5°	3029.5	3016.1	3022.8	3038.4	3018.4
170°	3049.5	3036.1	3040.5	3056.1	3036.1
172.5°	3062.7	3049.5	3053.9	3069.5	3049.5
175°	3073.7	3058.2	3062.7	3078.2	3056.1
177.5°	3078.2	3062.7	3065.0	3080.6	3060.6
180°	3067.2	3067.2	3067.2	3067.2	3067.2

TEST NUMBER: P927540

CATALOG NUMBER: DFN2DIP-HX4F0-040D090US840-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.71	6.42	6.82	7.52	9.05	5.28	5.99	6.38	7.09	8.61
	3H	7.36	8.00	8.47	9.11	10.65	6.89	7.52	8.00	8.64	10.17
	4H	7.94	8.55	9.07	9.66	11.20	7.47	8.07	8.59	9.18	10.73
	6H	8.33	8.89	9.47	10.00	11.56	7.86	8.42	8.99	9.53	11.08
	8H	8.43	8.96	9.57	10.09	11.64	7.96	8.49	9.10	9.62	11.17
	12H	8.48	8.98	9.62	10.10	11.68	8.00	8.50	9.14	9.62	11.19
4H	2H	6.15	6.76	7.29	7.87	9.41	5.81	6.41	6.94	7.53	9.07
	3H	8.01	8.51	9.14	9.65	11.21	7.61	8.12	8.75	9.26	10.81
	4H	8.72	9.18	9.86	10.31	11.88	8.31	8.78	9.45	9.90	11.48
	6H	9.22	9.62	10.37	10.77	12.34	8.81	9.21	9.96	10.36	11.93
	8H	9.37	9.74	10.52	10.88	12.47	8.96	9.33	10.10	10.47	12.05
	12H	9.44	9.77	10.60	10.93	12.51	9.01	9.35	10.18	10.50	12.09
8H	4H	8.90	9.27	10.05	10.41	12.00	8.54	8.91	9.69	10.05	11.64
	6H	9.53	9.83	10.69	11.02	12.60	9.16	9.47	10.33	10.65	12.23
	8H	9.75	10.02	10.92	11.18	12.78	9.38	9.65	10.55	10.81	12.41
	12H	9.87	10.11	11.05	11.27	12.90	9.49	9.72	10.66	10.88	12.52
12H	4H	8.88	9.22	10.04	10.37	11.96	8.53	8.86	9.69	10.02	11.61
	6H	9.56	9.82	10.73	10.99	12.59	9.20	9.47	10.38	10.63	12.24
	8H	9.79	10.03	10.97	11.19	12.82	9.43	9.67	10.61	10.83	12.46

END OF REPORT