

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P927548

Luminaire Tested: DFN2DIP-HX4F0-040D110US840-FLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P927548
REPORT IS A COMBINATION OF REPORTS P900945 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-040D110US840-FLLONL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 14995.5 lumens
Efficiency: N/A
Efficacy: 124.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 120.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9977
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P927548

CATALOG NUMBER: DFN2DIP-HX4F0-040D110US840-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P927548

CATALOG NUMBER: DFN2DIP-HX4F0-040D110US840-FLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	35	35	35
1	93	88	85	81	82	79	76	73	62	59	58	45	44	43	31	30	29
2	84	77	71	66	75	69	64	60	54	51	48	40	38	36	27	26	25
3	77	68	61	55	68	61	55	50	47	43	40	35	33	30	24	22	21
4	70	60	52	46	62	54	47	42	42	38	34	31	28	26	21	20	18
5	64	53	45	40	57	48	41	36	38	33	29	28	25	22	19	17	16
6	59	48	40	34	53	43	36	31	34	29	25	25	22	19	17	15	14
7	55	43	35	30	49	39	32	27	30	26	22	23	20	17	16	14	12
8	50	39	31	26	45	35	28	24	28	23	19	21	18	15	15	12	11
9	47	35	28	23	42	32	25	21	25	21	17	19	16	14	13	11	10
10	44	32	25	21	39	29	23	19	23	19	15	18	14	12	12	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1169	1169	1169
5°	1171	1152	1160
10°	1161	1137	1145
15°	1144	1118	1120
20°	1121	1093	1095
25°	1098	1062	1066
30°	1070	1033	1029
35°	1043	999	990
40°	1009	964	953
45°	976	930	915
50°	939	894	871
55°	901	852	831
60°	858	802	784
65°	811	751	730
70°	751	688	671
75°	668	614	617
80°	569	518	513
85°	413	353	341

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1925 cd/sqm

TEST NUMBER: P927548

CATALOG NUMBER: DFN2DIP-HX4F0-040D110US840-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	147.9	1.0
10°-20°	416.2	2.8
20°-30°	611.7	4.1
30°-40°	710.4	4.7
40°-50°	709.5	4.7
50°-60°	618.7	4.1
60°-70°	457.3	3.0
70°-80°	258.8	1.7
80°-90°	74.9	0.5
90°-100°	123.6	0.8
100°-110°	460.8	3.1
110°-120°	1222.1	8.2
120°-130°	2027.0	13.5
130°-140°	2153.1	14.4
140°-150°	2001.1	13.3
150°-160°	1608.8	10.7
160°-170°	1036.7	6.9
170°-180°	356.8	2.4
0°-30°	1175.8	7.8
0°-40°	1886.2	12.6
0°-60°	3214.4	21.4
0°-90°	4005.4	26.7
90°-120°	1806.5	12.0
90°-150°	7987.8	53.3
90°-180°	10990.0	73.3
0°-180°	14995.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1572	1572	1572	1572	1572	
5°	1572	1566	1549	1561	1558	149
15°	1496	1487	1467	1474	1466	421
25°	1354	1342	1316	1319	1316	623
35°	1168	1153	1129	1120	1112	730
45°	951	940	917	901	895	734
55°	720	710	692	674	667	643
65°	485	476	461	447	440	480
75°	254	251	243	234	237	271
85°	62	60	59	54	53	69
90°	3	32	54	68	73	14
95°	176	87	106	120	117	209
105°	825	906	166	195	206	881
115°	1560	1606	1674	418	223	1535
125°	2205	2241	2292	2311	2319	1967
135°	2729	2772	2796	2824	2818	2108
145°	3166	3163	3209	3228	3214	1980
155°	3486	3461	3494	3510	3488	1606
165°	3673	3657	3665	3684	3665	1038
175°	3757	3738	3743	3762	3735	358
180°	3749	3749	3749	3749	3749	

TEST NUMBER: P927548

CATALOG NUMBER: DFN2DIP-HX4F0-040D110US840-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1571.7	1571.7	1571.7	1571.7	1571.7
2.5°	1580.8	1573.3	1556.6	1571.7	1568.8
5°	1571.7	1565.7	1549.0	1561.0	1558.2
7.5°	1561.0	1552.1	1535.4	1547.6	1544.6
10°	1544.6	1534.0	1515.9	1527.9	1523.4
12.5°	1521.8	1512.8	1494.7	1502.3	1499.1
15°	1496.1	1487.1	1467.4	1473.5	1466.0
17.5°	1464.4	1455.4	1435.7	1443.2	1435.7
20°	1429.6	1420.6	1399.5	1403.9	1398.1
22.5°	1394.9	1381.3	1361.6	1361.6	1358.6
25°	1354.0	1342.0	1316.4	1319.3	1316.4
27.5°	1308.7	1298.1	1278.6	1274.1	1266.6
30°	1263.5	1251.3	1228.7	1224.2	1218.1
32.5°	1215.1	1206.1	1181.9	1172.8	1166.6
35°	1168.2	1153.2	1129.0	1119.9	1112.3
37.5°	1115.3	1101.7	1077.5	1067.0	1059.4
40°	1061.0	1048.8	1024.5	1011.1	1005.1
42.5°	1008.1	995.9	971.8	956.6	947.6
45°	950.6	940.1	917.3	900.8	894.7
47.5°	894.7	884.1	859.9	843.3	834.3
50°	835.7	828.1	807.0	785.8	778.3
52.5°	778.3	767.8	748.2	731.5	720.9
55°	719.5	710.3	692.2	674.0	666.6
57.5°	660.4	652.9	633.1	615.1	609.0
60°	601.4	595.5	574.4	557.7	553.2
62.5°	544.1	533.5	518.4	503.3	497.2
65°	485.2	476.0	461.0	447.3	439.9
67.5°	424.7	417.0	403.6	393.0	387.0
70°	368.8	362.7	349.1	338.5	332.5
72.5°	311.4	305.3	297.8	287.2	282.6
75°	253.9	250.9	243.3	234.3	237.3
77.5°	202.5	196.4	193.4	188.8	184.4
80°	151.2	149.6	146.5	142.1	139.0
82.5°	102.8	102.8	101.4	95.2	95.2
85°	61.9	60.5	59.0	54.3	52.9
87.5°	27.3	24.2	21.2	16.7	15.0
90°	2.6	32.5	54.1	68.0	73.1
92.5°	68.0	57.1	65.0	70.6	73.1
95°	176.2	86.6	105.6	119.5	116.6
97.5°	317.3	95.0	138.1	146.5	149.1
100°	480.3	108.6	154.6	176.2	181.7
102.5°	659.0	653.8	160.1	189.7	198.1
105°	824.6	906.1	165.6	195.2	206.2
107.5°	1017.3	1084.8	171.1	200.6	211.7
110°	1201.8	1258.5	474.8	203.6	214.2

TEST NUMBER: P927548

CATALOG NUMBER: DFN2DIP-HX4F0-040D110US840-FLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1375.4	1424.0	1378.0	208.7	217.1
115°	1559.6	1605.7	1673.7	417.8	222.6
117.5°	1719.8	1773.9	1820.3	1432.1	721.5
120°	1898.8	1939.4	1988.4	2020.9	1654.7
122.5°	2050.6	2094.0	2148.5	2164.6	2167.5
125°	2205.2	2240.6	2292.1	2311.1	2319.2
127.5°	2346.3	2384.2	2425.1	2452.2	2454.8
130°	2479.3	2522.8	2552.4	2582.4	2579.8
132.5°	2614.9	2650.3	2680.0	2704.4	2701.9
135°	2729.0	2772.4	2796.5	2824.0	2818.5
137.5°	2848.1	2880.7	2908.0	2935.1	2927.0
140°	2964.8	2986.6	3016.3	3040.7	3027.2
142.5°	3062.6	3081.6	3116.7	3138.4	3124.8
145°	3165.7	3162.8	3208.8	3227.9	3214.4
147.5°	3255.0	3246.9	3293.0	3306.5	3295.9
150°	3341.9	3322.9	3366.4	3382.5	3369.0
152.5°	3415.0	3393.4	3434.0	3450.5	3431.5
155°	3485.6	3461.4	3493.9	3510.1	3488.5
157.5°	3542.6	3521.0	3545.5	3564.5	3542.6
160°	3591.6	3575.1	3591.6	3607.6	3588.6
162.5°	3634.7	3618.6	3632.1	3651.1	3626.7
165°	3672.7	3656.6	3664.7	3683.6	3664.7
167.5°	3702.6	3686.3	3694.7	3713.6	3689.2
170°	3727.2	3710.7	3716.2	3735.3	3710.7
172.5°	3743.2	3727.2	3732.6	3751.6	3727.2
175°	3756.8	3737.8	3743.2	3762.3	3735.3
177.5°	3762.3	3743.2	3746.2	3765.1	3740.7
180°	3748.8	3748.8	3748.8	3748.8	3748.8

TEST NUMBER: P927548

CATALOG NUMBER: DFN2DIP-HX4F0-040D110US840-FLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.13	5.81	6.26	6.94	8.51	4.70	5.38	5.83	6.51	8.08
	3H	6.78	7.39	7.92	8.52	10.11	6.30	6.92	7.45	8.05	9.64
	4H	7.36	7.94	8.51	9.07	10.66	6.88	7.47	8.04	8.60	10.19
	6H	7.75	8.28	8.91	9.42	11.02	7.27	7.81	8.43	8.95	10.55
	8H	7.85	8.36	9.01	9.51	11.10	7.37	7.88	8.54	9.03	10.63
	12H	7.89	8.37	9.06	9.52	11.14	7.41	7.89	8.58	9.04	10.66
4H	2H	5.57	6.15	6.73	7.29	8.88	5.23	5.81	6.38	6.94	8.53
	3H	7.42	7.91	8.58	9.07	10.67	7.03	7.51	8.19	8.67	10.28
	4H	8.13	8.58	9.29	9.72	11.35	7.72	8.17	8.89	9.32	10.94
	6H	8.63	9.02	9.81	10.19	11.80	8.22	8.61	9.40	9.78	11.39
	8H	8.78	9.14	9.95	10.30	11.93	8.37	8.73	9.54	9.89	11.52
	12H	8.85	9.17	10.03	10.34	11.98	8.42	8.75	9.61	9.92	11.55
8H	4H	8.31	8.67	9.48	9.83	11.46	7.95	8.31	9.12	9.47	11.10
	6H	8.94	9.23	10.13	10.44	12.06	8.57	8.87	9.76	10.07	11.70
	8H	9.16	9.41	10.35	10.60	12.24	8.79	9.04	9.98	10.23	11.87
	12H	9.28	9.51	10.48	10.69	12.36	8.90	9.12	10.09	10.30	11.98
12H	4H	8.29	8.61	9.48	9.79	11.42	7.94	8.26	9.12	9.43	11.07
	6H	8.97	9.22	10.16	10.40	12.05	8.61	8.87	9.81	10.05	11.70
	8H	9.20	9.43	10.40	10.61	12.28	8.84	9.07	10.04	10.25	11.92

END OF REPORT