

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P927550

Luminaire Tested: DFN2DIP-HX4F0-040D110US840-RLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P927550
REPORT IS A COMBINATION OF REPORTS P900946 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-040D110US840-RLLONL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 14430.0 lumens
Efficiency: N/A
Efficacy: 119.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 120.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9977
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P927550

CATALOG NUMBER: DFN2DIP-HX4F0-040D110US840-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P927550

CATALOG NUMBER: DFN2DIP-HX4F0-040D110US840-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	32	32	32
1	92	88	84	81	82	78	75	73	60	58	57	44	43	42	29	28	27
2	84	77	71	67	75	69	64	60	53	50	47	39	37	35	25	24	23
3	77	68	61	56	68	61	55	50	47	43	40	34	32	30	23	21	20
4	70	60	53	47	62	54	48	43	42	38	34	31	28	26	20	19	18
5	64	53	46	40	57	48	41	37	37	33	29	28	25	22	19	17	15
6	59	48	40	35	53	43	36	32	34	29	26	25	22	20	17	15	14
7	55	43	36	30	49	39	32	28	30	26	22	23	20	17	15	14	12
8	51	39	32	27	45	35	29	24	28	23	20	21	18	15	14	12	11
9	47	36	28	24	42	32	26	22	25	21	18	19	16	14	13	11	10
10	44	32	26	21	39	29	23	19	23	19	16	18	15	12	12	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1241	1241	1241
5°	1243	1222	1229
10°	1231	1198	1190
15°	1214	1158	1128
20°	1192	1104	1052
25°	1169	1043	979
30°	1138	980	886
35°	1108	913	804
40°	1078	843	711
45°	1042	766	626
50°	1005	688	543
55°	967	604	463
60°	922	517	381
65°	871	428	343
70°	810	346	311
75°	732	305	283
80°	619	256	245
85°	433	172	185

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1925 cd/sqm

TEST NUMBER: P927550

CATALOG NUMBER: DFN2DIP-HX4F0-040D110US840-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	156.5	1.1
10°-20°	429.5	3.0
20°-30°	603.0	4.2
30°-40°	657.3	4.6
40°-50°	604.2	4.2
50°-60°	474.5	3.3
60°-70°	308.9	2.1
70°-80°	159.0	1.1
80°-90°	47.2	0.3
90°-100°	123.6	0.9
100°-110°	460.8	3.2
110°-120°	1222.1	8.5
120°-130°	2027.0	14.0
130°-140°	2153.1	14.9
140°-150°	2001.1	13.9
150°-160°	1608.8	11.1
160°-170°	1036.7	7.2
170°-180°	356.8	2.5
0°-30°	1189.0	8.2
0°-40°	1846.3	12.8
0°-60°	2924.9	20.3
0°-90°	3439.9	23.8
90°-120°	1806.5	12.5
90°-150°	7987.8	55.4
90°-180°	10990.0	76.2
0°-180°	14430.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1669	1669	1669	1669	1669	
5°	1669	1662	1642	1656	1651	158
15°	1588	1571	1520	1491	1476	447
25°	1441	1393	1293	1231	1208	663
35°	1242	1165	1032	937	903	777
45°	1015	914	755	648	612	784
55°	772	654	491	400	372	690
65°	521	399	263	212	207	517
75°	278	172	121	110	109	294
85°	65	33	29	29	29	75
90°	3	32	54	68	73	13
95°	176	87	106	120	117	209
105°	825	906	166	195	206	881
115°	1560	1606	1674	418	223	1535
125°	2205	2241	2292	2311	2319	1967
135°	2729	2772	2796	2824	2818	2108
145°	3166	3163	3209	3228	3214	1980
155°	3486	3461	3494	3510	3488	1606
165°	3673	3657	3665	3684	3665	1038
175°	3757	3738	3743	3762	3735	358
180°	3749	3749	3749	3749	3749	

TEST NUMBER: P927550

CATALOG NUMBER: DFN2DIP-HX4F0-040D110US840-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1669.4	1669.4	1669.4	1669.4	1669.4
2.5°	1677.0	1669.4	1652.7	1668.0	1664.9
5°	1669.4	1661.8	1642.1	1655.8	1651.3
7.5°	1655.8	1646.8	1625.7	1631.5	1624.1
10°	1637.7	1627.1	1596.9	1592.3	1583.4
12.5°	1615.1	1601.4	1560.5	1551.6	1534.9
15°	1587.8	1571.1	1519.8	1491.2	1476.1
17.5°	1556.1	1531.9	1468.4	1435.2	1411.0
20°	1519.8	1489.6	1414.0	1376.4	1343.0
22.5°	1480.6	1445.8	1358.1	1306.8	1284.3
25°	1441.3	1392.9	1293.1	1231.4	1208.5
27.5°	1394.5	1343.0	1232.8	1161.8	1126.9
30°	1344.6	1287.1	1166.2	1089.3	1048.5
32.5°	1296.3	1226.7	1102.9	1012.2	974.4
35°	1242.0	1164.8	1031.9	936.7	903.4
37.5°	1189.0	1105.8	965.4	861.1	823.4
40°	1133.1	1042.5	895.9	788.7	749.4
42.5°	1075.6	979.0	826.4	714.5	676.9
45°	1015.3	914.0	755.4	648.1	611.8
47.5°	957.9	850.7	687.5	580.1	546.9
50°	894.4	787.1	620.9	516.6	485.0
52.5°	832.4	719.1	557.5	457.7	429.1
55°	772.0	654.1	491.0	400.4	371.7
57.5°	710.1	589.2	432.1	347.5	323.3
60°	646.6	525.7	370.1	293.1	269.0
62.5°	584.8	463.9	317.2	244.8	232.8
65°	521.3	398.8	262.9	211.6	206.9
67.5°	460.9	338.4	211.6	185.8	181.3
70°	397.4	279.5	175.2	160.2	154.0
72.5°	337.0	225.1	146.5	134.5	131.5
75°	277.9	172.2	120.9	110.3	108.9
77.5°	219.1	122.3	95.2	89.2	86.0
80°	164.6	87.7	72.4	66.5	66.5
82.5°	114.8	59.0	49.9	46.8	46.8
85°	64.9	33.2	28.7	28.7	28.7
87.5°	24.2	12.0	12.0	10.6	10.6
90°	2.6	32.5	54.1	68.0	73.1
92.5°	68.0	57.1	65.0	70.6	73.1
95°	176.2	86.6	105.6	119.5	116.6
97.5°	317.3	95.0	138.1	146.5	149.1
100°	480.3	108.6	154.6	176.2	181.7
102.5°	659.0	653.8	160.1	189.7	198.1
105°	824.6	906.1	165.6	195.2	206.2
107.5°	1017.3	1084.8	171.1	200.6	211.7
110°	1201.8	1258.5	474.8	203.6	214.2

TEST NUMBER: P927550

CATALOG NUMBER: DFN2DIP-HX4F0-040D110US840-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1375.4	1424.0	1378.0	208.7	217.1
115°	1559.6	1605.7	1673.7	417.8	222.6
117.5°	1719.8	1773.9	1820.3	1432.1	721.5
120°	1898.8	1939.4	1988.4	2020.9	1654.7
122.5°	2050.6	2094.0	2148.5	2164.6	2167.5
125°	2205.2	2240.6	2292.1	2311.1	2319.2
127.5°	2346.3	2384.2	2425.1	2452.2	2454.8
130°	2479.3	2522.8	2552.4	2582.4	2579.8
132.5°	2614.9	2650.3	2680.0	2704.4	2701.9
135°	2729.0	2772.4	2796.5	2824.0	2818.5
137.5°	2848.1	2880.7	2908.0	2935.1	2927.0
140°	2964.8	2986.6	3016.3	3040.7	3027.2
142.5°	3062.6	3081.6	3116.7	3138.4	3124.8
145°	3165.7	3162.8	3208.8	3227.9	3214.4
147.5°	3255.0	3246.9	3293.0	3306.5	3295.9
150°	3341.9	3322.9	3366.4	3382.5	3369.0
152.5°	3415.0	3393.4	3434.0	3450.5	3431.5
155°	3485.6	3461.4	3493.9	3510.1	3488.5
157.5°	3542.6	3521.0	3545.5	3564.5	3542.6
160°	3591.6	3575.1	3591.6	3607.6	3588.6
162.5°	3634.7	3618.6	3632.1	3651.1	3626.7
165°	3672.7	3656.6	3664.7	3683.6	3664.7
167.5°	3702.6	3686.3	3694.7	3713.6	3689.2
170°	3727.2	3710.7	3716.2	3735.3	3710.7
172.5°	3743.2	3727.2	3732.6	3751.6	3727.2
175°	3756.8	3737.8	3743.2	3762.3	3735.3
177.5°	3762.3	3743.2	3746.2	3765.1	3740.7
180°	3748.8	3748.8	3748.8	3748.8	3748.8

TEST NUMBER: P927550

CATALOG NUMBER: DFN2DIP-HX4F0-040D110US840-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	4.74	5.39	5.90	6.53	8.14	0.71	1.37	1.87	2.51	4.11
	3H	6.40	6.99	7.57	8.14	9.76	1.89	2.47	3.05	3.62	5.24
	4H	7.00	7.56	8.18	8.71	10.33	2.33	2.89	3.50	4.04	5.66
	6H	7.42	7.93	8.60	9.08	10.71	2.64	3.16	3.83	4.31	5.94
	8H	7.54	8.02	8.72	9.19	10.82	2.73	3.22	3.91	4.38	6.01
	12H	7.60	8.06	8.78	9.22	10.86	2.77	3.23	3.96	4.39	6.04
4H	2H	4.73	5.29	5.92	6.44	8.06	1.28	1.84	2.47	2.99	4.61
	3H	6.55	7.01	7.73	8.19	9.82	2.62	3.08	3.81	4.26	5.89
	4H	7.23	7.66	8.42	8.82	10.48	3.16	3.59	4.35	4.75	6.41
	6H	7.74	8.11	8.93	9.29	10.93	3.58	3.94	4.77	5.13	6.77
	8H	7.91	8.25	9.10	9.43	11.09	3.70	4.04	4.89	5.22	6.88
	12H	8.00	8.31	9.21	9.50	11.16	3.76	4.07	4.96	5.26	6.92
8H	4H	7.19	7.53	8.38	8.71	10.37	3.43	3.77	4.62	4.95	6.61
	6H	7.75	8.03	8.96	9.25	10.91	3.95	4.23	5.15	5.45	7.10
	8H	7.97	8.21	9.18	9.41	11.08	4.14	4.38	5.35	5.58	7.25
	12H	8.10	8.31	9.32	9.51	11.21	4.25	4.46	5.47	5.66	7.37
12H	4H	7.13	7.44	8.34	8.63	10.29	3.43	3.74	4.63	4.92	6.59
	6H	7.73	7.97	8.94	9.17	10.84	3.99	4.24	5.21	5.43	7.11
	8H	7.94	8.15	9.16	9.35	11.05	4.20	4.41	5.42	5.61	7.31

END OF REPORT