

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P927564

Luminaire Tested: DFN2DIP-HX4F0-050D060US840-FLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P927564
REPORT IS A COMBINATION OF REPORTS P900857 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-050D060US840-FLLONL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10996.7 lumens
Efficiency: N/A
Efficacy: 125.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 87.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9957
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P927564

CATALOG NUMBER: DFN2DIP-HX4F0-050D060US840-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P927564

CATALOG NUMBER: DFN2DIP-HX4F0-050D060US840-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52
1	97	92	89	85	89	85	82	79	71	68	66	58	56	55	46	45	44
2	88	81	75	70	81	74	69	65	62	58	55	51	48	46	40	39	37
3	80	71	64	58	73	65	59	54	55	50	46	45	42	39	36	33	31
4	74	63	55	49	67	58	51	46	49	43	39	40	36	33	32	29	27
5	67	56	48	42	62	52	45	39	43	38	34	36	32	29	29	26	24
6	62	50	42	36	57	46	39	34	39	34	30	32	28	25	26	23	21
7	57	45	37	32	53	42	35	30	35	30	26	30	25	22	24	21	18
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	17
9	50	37	30	25	45	35	28	24	30	24	21	25	21	18	20	17	15
10	46	34	27	22	42	32	25	21	27	22	19	23	19	16	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1461	1461	1461
5°	1463	1441	1450
10°	1451	1421	1431
15°	1430	1398	1400
20°	1402	1366	1369
25°	1373	1327	1332
30°	1337	1291	1286
35°	1303	1248	1238
40°	1261	1205	1191
45°	1220	1162	1144
50°	1174	1117	1089
55°	1126	1065	1038
60°	1073	1003	980
65°	1014	939	912
70°	939	860	839
75°	835	767	771
80°	711	648	641
85°	516	441	426

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1220 cd/sqm

TEST NUMBER: P927564

CATALOG NUMBER: DFN2DIP-HX4F0-050D060US840-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	184.9	1.7
10°-20°	520.3	4.7
20°-30°	764.6	7.0
30°-40°	888.0	8.1
40°-50°	886.9	8.1
50°-60°	773.4	7.0
60°-70°	571.7	5.2
70°-80°	323.4	2.9
80°-90°	89.0	0.8
90°-100°	67.4	0.6
100°-110°	251.3	2.3
110°-120°	666.6	6.1
120°-130°	1105.6	10.1
130°-140°	1174.4	10.7
140°-150°	1091.5	9.9
150°-160°	877.5	8.0
160°-170°	565.5	5.1
170°-180°	194.6	1.8
0°-30°	1469.7	13.4
0°-40°	2357.8	21.4
0°-60°	4018.0	36.5
0°-90°	5002.1	45.5
90°-120°	985.4	9.0
90°-150°	4357.0	39.6
90°-180°	5995.0	54.5
0°-180°	10996.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1965	1965	1965	1965	1965	
5°	1965	1957	1936	1951	1948	186
15°	1870	1859	1834	1842	1832	527
25°	1693	1678	1646	1649	1646	779
35°	1460	1442	1411	1400	1390	912
45°	1188	1175	1147	1126	1118	917
55°	899	888	865	843	833	804
65°	606	595	576	559	550	600
75°	317	314	304	293	297	339
85°	77	76	74	68	66	86
90°	1	18	30	37	40	10
95°	96	47	58	65	64	114
105°	450	494	90	106	112	481
115°	851	876	913	228	121	838
125°	1203	1222	1250	1261	1265	1073
135°	1488	1512	1525	1540	1537	1150
145°	1727	1725	1750	1761	1753	1080
155°	1901	1888	1906	1915	1903	876
165°	2003	1995	1999	2009	1999	566
175°	2049	2039	2042	2052	2037	195
180°	2045	2045	2045	2045	2045	

TEST NUMBER: P927564

CATALOG NUMBER: DFN2DIP-HX4F0-050D060US840-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1964.6	1964.6	1964.6	1964.6	1964.6
2.5°	1976.0	1966.6	1945.8	1964.6	1961.0
5°	1964.6	1957.2	1936.3	1951.3	1947.8
7.5°	1951.3	1940.1	1919.3	1934.6	1930.7
10°	1930.7	1917.5	1894.9	1909.8	1904.3
12.5°	1902.3	1891.1	1868.4	1877.8	1874.0
15°	1870.1	1858.9	1834.3	1842.0	1832.5
17.5°	1830.5	1819.3	1794.6	1804.0	1794.6
20°	1787.0	1775.8	1749.4	1754.9	1747.6
22.5°	1743.7	1726.7	1702.0	1702.0	1698.2
25°	1692.6	1677.6	1645.5	1649.1	1645.5
27.5°	1635.9	1622.6	1598.2	1592.6	1583.2
30°	1579.3	1564.2	1535.9	1530.3	1522.7
32.5°	1518.8	1507.6	1477.3	1465.9	1458.4
35°	1460.3	1441.5	1411.2	1399.8	1390.4
37.5°	1394.1	1377.2	1346.9	1333.6	1324.3
40°	1326.3	1311.0	1280.7	1263.9	1256.3
42.5°	1260.1	1244.9	1214.8	1195.7	1184.5
45°	1188.3	1175.1	1146.6	1126.0	1118.4
47.5°	1118.4	1105.1	1074.9	1054.0	1042.8
50°	1044.6	1035.2	1008.8	982.3	972.8
52.5°	972.8	959.6	935.2	914.4	901.1
55°	899.3	887.9	865.2	842.6	833.2
57.5°	825.5	816.1	791.5	768.9	761.2
60°	751.8	744.4	718.0	697.1	691.5
62.5°	680.1	666.9	648.0	629.1	621.5
65°	606.5	595.1	576.2	559.2	549.7
67.5°	531.0	521.4	504.5	491.3	483.6
70°	461.0	453.4	436.3	423.1	415.7
72.5°	389.3	381.6	372.2	359.0	353.3
75°	317.3	313.6	304.1	292.8	296.7
77.5°	253.2	245.5	241.7	236.1	230.5
80°	189.0	187.0	183.2	177.6	173.8
82.5°	128.4	128.4	126.6	119.1	119.1
85°	77.4	75.5	73.7	68.0	66.1
87.5°	34.0	30.3	26.5	20.8	18.9
90°	1.4	17.8	29.5	37.1	39.9
92.5°	37.1	31.1	35.4	38.5	39.9
95°	96.1	47.3	57.7	65.2	63.6
97.5°	173.1	51.8	75.3	80.0	81.4
100°	261.9	59.2	84.3	96.1	99.1
102.5°	359.5	356.7	87.3	103.5	108.0
105°	449.8	494.2	90.3	106.4	112.5
107.5°	554.9	591.7	93.3	109.5	115.4
110°	655.6	686.5	259.0	111.1	116.8

TEST NUMBER: P927564

CATALOG NUMBER: DFN2DIP-HX4F0-050D060US840-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	750.2	776.7	751.6	113.8	118.4
115°	850.8	875.9	913.0	227.9	121.4
117.5°	938.0	967.6	992.8	781.2	393.5
120°	1035.8	1057.9	1084.6	1102.3	902.6
122.5°	1118.5	1142.2	1171.9	1180.7	1182.3
125°	1202.9	1222.2	1250.2	1260.6	1265.0
127.5°	1279.8	1300.5	1322.8	1337.6	1339.0
130°	1352.3	1376.1	1392.2	1408.6	1407.2
132.5°	1426.3	1445.6	1461.8	1475.1	1473.7
135°	1488.5	1512.3	1525.4	1540.3	1537.3
137.5°	1553.5	1571.2	1586.2	1600.9	1596.6
140°	1617.1	1629.1	1645.3	1658.6	1651.2
142.5°	1670.5	1680.9	1700.1	1711.8	1704.4
145°	1726.8	1725.1	1750.3	1760.7	1753.3
147.5°	1775.4	1771.0	1796.1	1803.5	1797.7
150°	1822.9	1812.5	1836.2	1845.0	1837.6
152.5°	1862.8	1851.0	1873.1	1882.1	1871.7
155°	1901.3	1888.0	1905.8	1914.6	1902.8
157.5°	1932.4	1920.5	1933.9	1944.3	1932.4
160°	1959.0	1950.0	1959.0	1967.8	1957.5
162.5°	1982.5	1973.8	1981.1	1991.5	1978.2
165°	2003.3	1994.6	1998.9	2009.3	1998.9
167.5°	2019.6	2010.7	2015.3	2025.7	2012.2
170°	2033.0	2024.0	2027.1	2037.4	2024.0
172.5°	2041.8	2033.0	2036.0	2046.4	2033.0
175°	2049.2	2038.8	2041.8	2052.1	2037.4
177.5°	2052.1	2041.8	2043.3	2053.7	2040.4
180°	2044.7	2044.7	2044.7	2044.7	2044.7

TEST NUMBER: P927564

CATALOG NUMBER: DFN2DIP-HX4F0-050D060US840-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.16	8.98	9.15	9.99	11.32	7.73	8.55	8.72	9.55	10.89
	3H	9.82	10.55	10.82	11.57	12.92	9.34	10.08	10.35	11.10	12.45
	4H	10.40	11.10	11.42	12.12	13.48	9.93	10.63	10.95	11.65	13.01
	6H	10.80	11.44	11.83	12.47	13.84	10.33	10.97	11.35	11.99	13.37
	8H	10.90	11.52	11.94	12.56	13.93	10.43	11.04	11.46	12.08	13.45
	12H	10.95	11.53	11.99	12.57	13.96	10.47	11.05	11.51	12.09	13.48
4H	2H	8.61	9.31	9.64	10.33	11.69	8.27	8.97	9.29	9.99	11.35
	3H	10.48	11.06	11.51	12.11	13.48	10.09	10.67	11.12	11.72	13.09
	4H	11.19	11.73	12.23	12.76	14.16	10.79	11.32	11.83	12.36	13.76
	6H	11.71	12.16	12.76	13.23	14.62	11.30	11.76	12.35	12.82	14.21
	8H	11.86	12.28	12.91	13.34	14.75	11.44	11.87	12.49	12.93	14.34
	12H	11.93	12.31	13.00	13.38	14.80	11.50	11.89	12.57	12.96	14.38
8H	4H	11.39	11.81	12.44	12.87	14.28	11.03	11.45	12.08	12.51	13.92
	6H	12.02	12.37	13.09	13.47	14.87	11.65	12.01	12.73	13.11	14.51
	8H	12.24	12.55	13.32	13.63	15.06	11.87	12.18	12.95	13.26	14.69
	12H	12.37	12.64	13.45	13.72	15.18	11.98	12.26	13.07	13.33	14.80
12H	4H	11.37	11.76	12.44	12.83	14.24	11.02	11.41	12.09	12.47	13.89
	6H	12.05	12.36	13.13	13.44	14.87	11.70	12.01	12.78	13.09	14.51
	8H	12.29	12.56	13.37	13.64	15.10	11.93	12.20	13.02	13.28	14.75