

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P928812

Luminaire Tested: DFN2DIP-HX4F0-120D120US930-FLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P928812
REPORT IS A COMBINATION OF REPORTS P900979 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-120D120US930-FLLONL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 19364.4 lumens
Efficiency: N/A
Efficacy: 87.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 222.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9954
Total Harmonic Distortion (THDi): 0.076
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P928812

CATALOG NUMBER: DFN2DIP-HX4F0-120D120US930-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P928812

CATALOG NUMBER: DFN2DIP-HX4F0-120D120US930-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	98	93	90	86	90	86	83	80	73	71	68	61	59	58	50	48	47
2	89	82	75	70	82	76	70	66	64	60	57	53	51	48	44	42	40
3	81	72	64	59	75	66	60	55	56	52	48	47	44	41	39	36	34
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	35	32	29
5	68	57	48	42	63	53	45	40	45	39	35	38	34	30	31	28	26
6	63	51	43	37	58	47	40	35	40	35	31	34	30	27	28	25	23
7	58	46	38	32	53	43	36	30	37	31	27	31	27	23	26	23	20
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	24	20	18
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	19	16
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2830	2830	2830
5°	2834	2790	2809
10°	2812	2753	2771
15°	2770	2708	2712
20°	2715	2645	2651
25°	2660	2570	2581
30°	2590	2501	2492
35°	2524	2418	2397
40°	2443	2335	2307
45°	2363	2252	2216
50°	2274	2164	2109
55°	2182	2063	2011
60°	2078	1943	1899
65°	1964	1818	1767
70°	1819	1667	1624
75°	1618	1485	1493
80°	1377	1255	1242
85°	999	855	826

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2363 cd/sqm

TEST NUMBER: P928812

CATALOG NUMBER: DFN2DIP-HX4F0-120D120US930-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	358.2	1.8
10°-20°	1007.7	5.2
20°-30°	1481.0	7.6
30°-40°	1720.1	8.9
40°-50°	1718.0	8.9
50°-60°	1498.0	7.7
60°-70°	1107.4	5.7
70°-80°	626.5	3.2
80°-90°	171.2	0.9
90°-100°	108.8	0.6
100°-110°	405.7	2.1
110°-120°	1076.0	5.6
120°-130°	1784.7	9.2
130°-140°	1895.8	9.8
140°-150°	1761.9	9.1
150°-160°	1416.5	7.3
160°-170°	912.8	4.7
170°-180°	314.2	1.6
0°-30°	2846.9	14.7
0°-40°	4567.0	23.6
0°-60°	7783.0	40.2
0°-90°	9688.0	50.0
90°-120°	1590.6	8.2
90°-150°	7033.0	36.3
90°-180°	9676.0	50.0
0°-180°	19364.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3806	3806	3806	3806	3806	
5°	3806	3791	3751	3780	3773	361
15°	3623	3601	3553	3568	3550	1020
25°	3279	3250	3187	3194	3187	1509
35°	2829	2792	2734	2711	2693	1766
45°	2302	2276	2221	2181	2166	1776
55°	1742	1720	1676	1632	1614	1557
65°	1175	1153	1116	1083	1065	1162
75°	615	608	589	567	575	656
85°	150	146	143	132	128	167
90°	2	29	48	60	64	18
95°	155	76	93	105	103	184
105°	726	798	146	172	182	776
115°	1373	1414	1474	368	196	1352
125°	1942	1973	2018	2035	2042	1732
135°	2403	2441	2462	2486	2482	1856
145°	2787	2785	2825	2842	2830	1743
155°	3069	3048	3076	3090	3072	1414
165°	3234	3220	3227	3243	3227	914
175°	3308	3291	3296	3313	3289	315
180°	3301	3301	3301	3301	3301	

TEST NUMBER: P928812

CATALOG NUMBER: DFN2DIP-HX4F0-120D120US930-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3805.5	3805.5	3805.5	3805.5	3805.5
2.5°	3827.6	3809.3	3769.0	3805.5	3798.5
5°	3805.5	3791.1	3750.7	3779.8	3772.8
7.5°	3779.8	3758.0	3717.7	3747.2	3739.9
10°	3739.9	3714.2	3670.4	3699.4	3688.6
12.5°	3684.7	3662.9	3619.1	3637.3	3629.9
15°	3622.6	3600.8	3553.1	3567.8	3549.6
17.5°	3545.7	3524.0	3476.2	3494.5	3476.2
20°	3461.5	3439.7	3388.5	3399.4	3385.0
22.5°	3377.6	3344.6	3296.8	3296.8	3289.5
25°	3278.6	3249.5	3187.4	3194.4	3187.4
27.5°	3168.7	3143.1	3095.8	3084.9	3066.7
30°	3059.3	3029.8	2975.0	2964.2	2949.4
32.5°	2942.0	2920.3	2861.6	2839.5	2824.8
35°	2828.6	2792.2	2733.5	2711.4	2693.2
37.5°	2700.5	2667.6	2608.9	2583.3	2565.0
40°	2569.0	2539.5	2480.8	2448.2	2433.4
42.5°	2440.8	2411.3	2353.1	2316.2	2294.5
45°	2301.8	2276.2	2221.0	2181.1	2166.4
47.5°	2166.4	2140.7	2082.1	2041.7	2020.0
50°	2023.5	2005.2	1954.0	1902.7	1884.4
52.5°	1884.4	1858.9	1811.5	1771.1	1745.5
55°	1742.0	1719.9	1676.0	1632.1	1613.9
57.5°	1599.1	1580.9	1533.1	1489.2	1474.5
60°	1456.2	1441.9	1390.6	1350.3	1339.4
62.5°	1317.3	1291.6	1255.2	1218.7	1203.9
65°	1174.8	1152.7	1116.1	1083.1	1065.0
67.5°	1028.4	1009.8	977.2	951.6	936.8
70°	892.9	878.2	845.2	819.6	805.2
72.5°	754.0	739.2	720.9	695.4	684.4
75°	614.6	607.6	588.9	567.2	574.6
77.5°	490.3	475.6	468.2	457.3	446.5
80°	366.1	362.2	354.9	344.0	336.6
82.5°	248.8	248.8	245.4	230.6	230.6
85°	149.9	146.4	142.9	131.6	128.1
87.5°	66.0	58.6	51.3	40.3	36.5
90°	2.3	28.6	47.7	59.8	64.4
92.5°	59.8	50.2	57.3	62.1	64.4
95°	155.1	76.3	93.0	105.2	102.7
97.5°	279.4	83.7	121.7	129.0	131.3
100°	422.8	95.6	136.1	155.1	160.0
102.5°	580.3	575.7	140.9	167.1	174.4
105°	726.0	797.8	145.8	171.9	181.5
107.5°	895.6	955.2	150.6	176.7	186.3
110°	1058.1	1108.1	418.0	179.2	188.6

TEST NUMBER: P928812

CATALOG NUMBER: DFN2DIP-HX4F0-120D120US930-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1211.0	1253.8	1213.3	183.8	191.1
115°	1373.2	1413.8	1473.6	367.8	196.0
117.5°	1514.2	1561.9	1602.7	1260.9	635.3
120°	1671.9	1707.6	1750.7	1779.4	1456.9
122.5°	1805.5	1843.8	1891.7	1905.9	1908.4
125°	1941.6	1972.8	2018.2	2034.9	2042.0
127.5°	2065.8	2099.3	2135.3	2159.1	2161.4
130°	2182.9	2221.2	2247.3	2273.7	2271.4
132.5°	2302.3	2333.5	2359.6	2381.2	2378.9
135°	2402.7	2441.0	2462.3	2486.4	2481.6
137.5°	2507.7	2536.3	2560.4	2584.2	2577.1
140°	2610.4	2629.6	2655.7	2677.3	2665.4
142.5°	2696.5	2713.3	2744.2	2763.2	2751.3
145°	2787.3	2784.8	2825.3	2842.1	2830.1
147.5°	2865.9	2858.8	2899.4	2911.3	2901.9
150°	2942.4	2925.7	2964.0	2978.2	2966.3
152.5°	3006.8	2987.8	3023.6	3038.0	3021.3
155°	3068.9	3047.6	3076.3	3090.5	3071.5
157.5°	3119.1	3100.1	3121.7	3138.4	3119.1
160°	3162.2	3147.8	3162.2	3176.4	3159.7
162.5°	3200.3	3186.1	3198.0	3214.7	3193.2
165°	3233.7	3219.5	3226.6	3243.4	3226.6
167.5°	3260.1	3245.6	3253.0	3269.7	3248.2
170°	3281.6	3267.2	3272.0	3288.7	3267.2
172.5°	3295.8	3281.6	3286.5	3303.2	3281.6
175°	3307.7	3291.0	3295.8	3312.6	3288.7
177.5°	3312.6	3295.8	3298.4	3315.1	3293.6
180°	3300.7	3300.7	3300.7	3300.7	3300.7

TEST NUMBER: P928812

CATALOG NUMBER: DFN2DIP-HX4F0-120D120US930-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.89	11.75	11.85	12.72	13.99	10.46	11.32	11.41	12.29	13.56
	3H	12.55	13.32	13.52	14.30	15.60	12.08	12.85	13.05	13.83	15.12
	4H	13.14	13.87	14.12	14.86	16.16	12.67	13.40	13.65	14.38	15.68
	6H	13.54	14.21	14.53	15.20	16.52	13.06	13.74	14.06	14.73	16.04
	8H	13.64	14.29	14.64	15.29	16.60	13.17	13.81	14.17	14.82	16.13
	12H	13.69	14.30	14.70	15.30	16.64	13.21	13.82	14.22	14.82	16.16
4H	2H	11.35	12.08	12.34	13.07	14.37	11.01	11.74	11.99	12.72	14.03
	3H	13.22	13.83	14.22	14.84	16.16	12.83	13.44	13.82	14.45	15.77
	4H	13.93	14.49	14.94	15.50	16.84	13.53	14.09	14.53	15.09	16.43
	6H	14.45	14.93	15.47	15.96	17.30	14.04	14.52	15.06	15.55	16.89
	8H	14.60	15.05	15.62	16.07	17.42	14.19	14.64	15.21	15.66	17.01
	12H	14.67	15.08	15.71	16.12	17.48	14.25	14.66	15.29	15.70	17.05
8H	4H	14.13	14.58	15.15	15.60	16.96	13.77	14.22	14.79	15.24	16.59
	6H	14.76	15.14	15.81	16.20	17.55	14.40	14.77	15.44	15.84	17.19
	8H	14.99	15.31	16.04	16.36	17.73	14.62	14.94	15.67	15.99	17.36
	12H	15.12	15.41	16.17	16.45	17.86	14.73	15.02	15.79	16.07	17.48
12H	4H	14.12	14.52	15.15	15.56	16.92	13.76	14.17	14.80	15.21	16.57
	6H	14.79	15.12	15.84	16.17	17.54	14.44	14.77	15.49	15.82	17.19
	8H	15.04	15.33	16.09	16.37	17.78	14.68	14.97	15.73	16.01	17.42

END OF REPORT