

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P927582

Luminaire Tested: DFN2DIP-HX4F0-050D100US840-RLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P927582
REPORT IS A COMBINATION OF REPORTS P900930 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-050D100US840-RLLONL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 14288.7 lumens
Efficiency: N/A
Efficacy: 119.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 119.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9957
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P927582

CATALOG NUMBER: DFN2DIP-HX4F0-050D100US840-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P927582

CATALOG NUMBER: DFN2DIP-HX4F0-050D100US840-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	38	38	38
1	94	90	86	83	84	81	77	75	64	62	60	48	47	46	34	33	32
2	85	78	73	68	76	71	66	62	56	53	50	43	40	39	30	29	28
3	78	69	62	57	70	62	57	52	50	46	42	38	35	33	27	25	24
4	71	61	54	48	64	55	49	44	44	40	36	34	31	28	24	22	21
5	66	55	47	41	59	49	43	38	40	35	31	30	27	25	22	20	18
6	60	49	41	36	54	44	38	33	36	31	27	28	24	22	20	18	16
7	56	44	37	31	50	40	34	29	32	28	24	25	22	19	18	16	15
8	52	40	33	28	46	36	30	25	29	25	21	23	20	17	17	15	13
9	48	37	29	25	43	33	27	23	27	22	19	21	18	15	16	13	12
10	45	33	27	22	40	30	24	20	25	20	17	20	16	14	14	12	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1552	1552	1552
5°	1554	1527	1537
10°	1539	1497	1487
15°	1518	1448	1410
20°	1490	1380	1315
25°	1461	1304	1223
30°	1423	1225	1107
35°	1385	1141	1005
40°	1347	1054	888
45°	1303	957	782
50°	1257	860	679
55°	1209	755	579
60°	1153	646	477
65°	1089	535	429
70°	1012	432	389
75°	915	381	353
80°	774	320	307
85°	541	214	231

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1748 cd/sqm

TEST NUMBER: P927582

CATALOG NUMBER: DFN2DIP-HX4F0-050D100US840-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	195.6	1.4
10°-20°	536.9	3.8
20°-30°	753.8	5.3
30°-40°	821.7	5.8
40°-50°	755.2	5.3
50°-60°	593.1	4.2
60°-70°	386.0	2.7
70°-80°	198.7	1.4
80°-90°	56.7	0.4
90°-100°	112.4	0.8
100°-110°	418.9	2.9
110°-120°	1111.0	7.8
120°-130°	1842.7	12.9
130°-140°	1957.4	13.7
140°-150°	1819.2	12.7
150°-160°	1462.6	10.2
160°-170°	942.4	6.6
170°-180°	324.4	2.3
0°-30°	1486.2	10.4
0°-40°	2307.9	16.2
0°-60°	3656.2	25.6
0°-90°	4297.7	30.1
90°-120°	1642.3	11.5
90°-150°	7261.7	50.8
90°-180°	9991.0	69.9
0°-180°	14288.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2087	2087	2087	2087	2087	
5°	2087	2077	2053	2070	2064	198
15°	1985	1964	1900	1864	1845	559
25°	1802	1741	1616	1539	1511	829
35°	1552	1456	1290	1171	1129	972
45°	1269	1142	944	810	765	980
55°	965	818	614	500	465	862
65°	652	498	329	264	259	646
75°	348	215	151	138	136	368
85°	81	42	36	36	36	93
90°	2	30	49	62	66	13
95°	160	79	96	109	106	190
105°	750	824	151	177	187	801
115°	1418	1460	1522	380	202	1396
125°	2005	2037	2084	2101	2108	1788
135°	2481	2520	2542	2567	2562	1916
145°	2878	2875	2917	2934	2922	1800
155°	3169	3147	3176	3191	3171	1460
165°	3339	3324	3332	3349	3332	943
175°	3415	3398	3403	3420	3396	325
180°	3408	3408	3408	3408	3408	

TEST NUMBER: P927582

CATALOG NUMBER: DFN2DIP-HX4F0-050D100US840-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2086.8	2086.8	2086.8	2086.8	2086.8
2.5°	2096.1	2086.8	2065.9	2084.9	2081.1
5°	2086.8	2077.4	2052.7	2069.7	2064.1
7.5°	2069.7	2058.5	2032.0	2039.5	2030.0
10°	2047.1	2033.8	1996.2	1990.4	1979.1
12.5°	2018.8	2001.8	1950.7	1939.5	1918.6
15°	1984.8	1964.0	1899.8	1864.0	1845.1
17.5°	1945.1	1914.9	1835.5	1794.0	1763.7
20°	1899.8	1862.0	1767.6	1720.5	1678.8
22.5°	1850.8	1807.2	1697.7	1633.6	1605.3
25°	1801.6	1741.1	1616.5	1539.1	1510.7
27.5°	1743.1	1678.8	1541.0	1452.2	1408.8
30°	1680.8	1608.9	1457.8	1361.6	1310.5
32.5°	1620.3	1533.4	1378.7	1265.3	1218.0
35°	1552.4	1456.0	1289.9	1170.9	1129.3
37.5°	1486.2	1382.3	1206.8	1076.3	1029.3
40°	1416.3	1303.1	1119.8	985.8	936.7
42.5°	1344.6	1223.8	1033.0	893.2	846.1
45°	1269.1	1142.5	944.3	810.1	764.7
47.5°	1197.3	1063.3	859.3	725.1	683.6
50°	1118.1	983.9	776.2	645.8	606.3
52.5°	1040.5	898.8	696.9	572.3	536.4
55°	965.0	817.6	613.7	500.5	464.6
57.5°	887.6	736.5	540.1	434.4	404.1
60°	808.2	657.2	462.6	366.5	336.2
62.5°	730.9	579.8	396.5	306.0	290.9
65°	651.5	498.5	328.6	264.5	258.7
67.5°	576.0	423.0	264.5	232.3	226.6
70°	496.7	349.4	219.0	200.1	192.6
72.5°	421.2	281.3	183.2	168.1	164.3
75°	347.5	215.2	151.1	137.8	136.0
77.5°	273.9	152.9	119.1	111.4	107.5
80°	205.8	109.6	90.6	83.1	83.1
82.5°	143.5	73.7	62.3	58.5	58.5
85°	81.2	41.5	35.8	35.8	35.8
87.5°	30.3	15.0	15.0	13.2	13.2
90°	2.3	29.6	49.2	61.8	66.4
92.5°	61.8	51.8	59.2	64.1	66.4
95°	160.2	78.8	96.0	108.7	106.0
97.5°	288.4	86.3	125.6	133.2	135.6
100°	436.6	98.7	140.6	160.2	165.2
102.5°	599.1	594.5	145.5	172.5	180.0
105°	749.7	823.7	150.6	177.4	187.4
107.5°	924.8	986.3	155.5	182.5	192.4
110°	1092.5	1144.1	431.6	185.1	194.7

TEST NUMBER: P927582

CATALOG NUMBER: DFN2DIP-HX4F0-050D100US840-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1250.3	1294.6	1252.8	189.7	197.4
115°	1417.9	1459.8	1521.6	379.8	202.4
117.5°	1563.4	1612.7	1654.8	1301.9	656.0
120°	1726.3	1763.1	1807.6	1837.2	1504.3
122.5°	1864.2	1903.7	1953.2	1967.8	1970.4
125°	2004.8	2037.0	2083.8	2101.1	2108.4
127.5°	2133.0	2167.5	2204.7	2229.3	2231.7
130°	2253.9	2293.5	2320.4	2347.6	2345.3
132.5°	2377.2	2409.4	2436.3	2458.6	2456.2
135°	2480.9	2520.4	2542.4	2567.2	2562.3
137.5°	2589.2	2618.8	2643.7	2668.3	2660.9
140°	2695.2	2715.2	2742.0	2764.3	2752.0
142.5°	2784.2	2801.5	2833.4	2853.0	2840.8
145°	2877.9	2875.3	2917.2	2934.5	2922.2
147.5°	2959.0	2951.7	2993.6	3005.9	2996.3
150°	3038.1	3020.8	3060.4	3075.0	3062.7
152.5°	3104.5	3084.9	3121.9	3136.7	3119.5
155°	3168.8	3146.7	3176.3	3191.0	3171.4
157.5°	3220.6	3201.0	3223.2	3240.4	3220.6
160°	3265.1	3250.1	3265.1	3279.7	3262.5
162.5°	3304.3	3289.6	3301.9	3319.2	3297.0
165°	3338.8	3324.2	3331.5	3348.8	3331.5
167.5°	3366.1	3351.1	3358.8	3376.1	3353.7
170°	3388.3	3373.4	3378.4	3395.7	3373.4
172.5°	3402.9	3388.3	3393.3	3410.6	3388.3
175°	3415.2	3398.0	3402.9	3420.3	3395.7
177.5°	3420.3	3402.9	3405.7	3422.9	3400.6
180°	3408.0	3408.0	3408.0	3408.0	3408.0

TEST NUMBER: P927582

CATALOG NUMBER: DFN2DIP-HX4F0-050D100US840-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.45	7.14	7.57	8.25	9.78	2.43	3.12	3.54	4.22	5.76
	3H	8.12	8.74	9.24	9.85	11.40	3.61	4.22	4.73	5.34	6.89
	4H	8.72	9.31	9.86	10.43	11.98	4.05	4.64	5.18	5.75	7.31
	6H	9.14	9.68	10.28	10.80	12.36	4.37	4.90	5.51	6.02	7.59
	8H	9.26	9.77	10.41	10.91	12.47	4.45	4.97	5.60	6.10	7.66
	12H	9.32	9.80	10.47	10.93	12.51	4.49	4.98	5.64	6.11	7.69
4H	2H	6.45	7.04	7.60	8.16	9.71	3.00	3.59	4.15	4.71	6.26
	3H	8.27	8.76	9.42	9.90	11.47	4.34	4.83	5.49	5.97	7.54
	4H	8.96	9.41	10.11	10.54	12.12	4.89	5.34	6.04	6.47	8.05
	6H	9.47	9.85	10.62	11.01	12.58	5.30	5.68	6.46	6.84	8.41
	8H	9.64	10.00	10.80	11.14	12.74	5.43	5.79	6.58	6.93	8.52
	12H	9.73	10.05	10.90	11.21	12.81	5.49	5.81	6.66	6.97	8.57
8H	4H	8.92	9.27	10.07	10.42	12.01	5.16	5.52	6.31	6.66	8.25
	6H	9.48	9.77	10.65	10.96	12.55	5.67	5.97	6.85	7.16	8.75
	8H	9.70	9.95	10.88	11.12	12.73	5.87	6.12	7.05	7.29	8.90
	12H	9.83	10.06	11.01	11.22	12.86	5.98	6.21	7.16	7.37	9.01
12H	4H	8.86	9.19	10.03	10.34	11.94	5.16	5.48	6.33	6.64	8.24
	6H	9.45	9.71	10.63	10.88	12.49	5.72	5.98	6.90	7.15	8.76
	8H	9.67	9.90	10.85	11.06	12.70	5.93	6.15	7.11	7.32	8.96

END OF REPORT