

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P927590

Luminaire Tested: DFN2DIP-HX4F0-050D120US840-RLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P927590
REPORT IS A COMBINATION OF REPORTS P900966 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-050D120US840-RLLONL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 16288.1 lumens
Efficiency: N/A
Efficacy: 116.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 139.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9957
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P927590

CATALOG NUMBER: DFN2DIP-HX4F0-050D120US840-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P927590

CATALOG NUMBER: DFN2DIP-HX4F0-050D120US840-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	34	34	34
1	93	89	85	82	83	79	76	74	62	60	58	46	44	43	31	30	29
2	85	78	72	67	75	70	65	61	54	51	48	40	38	36	27	26	25
3	77	68	62	56	69	61	56	51	48	44	41	36	33	31	24	23	22
4	71	61	53	47	63	54	48	43	43	38	35	32	29	27	22	20	19
5	65	54	46	41	58	49	42	37	38	34	30	29	26	23	20	18	17
6	60	48	41	35	53	44	37	32	35	30	26	26	23	20	18	16	15
7	55	44	36	31	49	39	33	28	31	27	23	24	20	18	17	15	13
8	51	39	32	27	46	36	29	25	28	24	20	22	18	16	15	13	12
9	48	36	29	24	42	33	26	22	26	21	18	20	17	14	14	12	11
10	44	33	26	21	40	30	24	20	24	19	16	18	15	13	13	11	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1552	1552	1552
5°	1554	1527	1537
10°	1539	1497	1487
15°	1518	1448	1410
20°	1490	1380	1315
25°	1461	1304	1223
30°	1423	1225	1107
35°	1385	1141	1005
40°	1347	1054	888
45°	1303	957	782
50°	1257	860	679
55°	1209	755	579
60°	1153	646	477
65°	1089	535	429
70°	1012	432	389
75°	915	381	353
80°	774	320	307
85°	541	214	231

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2101 cd/sqm

TEST NUMBER: P927590

CATALOG NUMBER: DFN2DIP-HX4F0-050D120US840-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	195.6	1.2
10°-20°	536.9	3.3
20°-30°	753.8	4.6
30°-40°	821.7	5.0
40°-50°	755.2	4.6
50°-60°	593.1	3.6
60°-70°	386.0	2.4
70°-80°	198.7	1.2
80°-90°	57.9	0.4
90°-100°	134.8	0.8
100°-110°	502.7	3.1
110°-120°	1333.2	8.2
120°-130°	2211.3	13.6
130°-140°	2348.9	14.4
140°-150°	2183.0	13.4
150°-160°	1755.1	10.8
160°-170°	1130.9	6.9
170°-180°	389.2	2.4
0°-30°	1486.2	9.1
0°-40°	2307.9	14.2
0°-60°	3656.2	22.4
0°-90°	4298.9	26.4
90°-120°	1970.8	12.1
90°-150°	8714.0	53.5
90°-180°	11989.0	73.6
0°-180°	16288.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2087	2087	2087	2087	2087	
5°	2087	2077	2053	2070	2064	198
15°	1985	1964	1900	1864	1845	559
25°	1802	1741	1616	1539	1511	829
35°	1552	1456	1290	1171	1129	972
45°	1269	1142	944	810	765	980
55°	965	818	614	500	465	862
65°	652	498	329	264	259	646
75°	348	215	151	138	136	368
85°	81	42	36	36	36	93
90°	3	35	59	74	80	15
95°	192	94	115	130	127	228
105°	900	988	181	213	225	961
115°	1701	1752	1826	456	243	1675
125°	2406	2444	2501	2521	2530	2146
135°	2977	3024	3051	3081	3075	2300
145°	3454	3450	3501	3521	3506	2160
155°	3802	3776	3812	3829	3806	1752
165°	4007	3989	3998	4019	3998	1132
175°	4098	4078	4084	4104	4075	390
180°	4090	4090	4090	4090	4090	

TEST NUMBER: P927590

CATALOG NUMBER: DFN2DIP-HX4F0-050D120US840-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2086.8	2086.8	2086.8	2086.8	2086.8
2.5°	2096.1	2086.8	2065.9	2084.9	2081.1
5°	2086.8	2077.4	2052.7	2069.7	2064.1
7.5°	2069.7	2058.5	2032.0	2039.5	2030.0
10°	2047.1	2033.8	1996.2	1990.4	1979.1
12.5°	2018.8	2001.8	1950.7	1939.5	1918.6
15°	1984.8	1964.0	1899.8	1864.0	1845.1
17.5°	1945.1	1914.9	1835.5	1794.0	1763.7
20°	1899.8	1862.0	1767.6	1720.5	1678.8
22.5°	1850.8	1807.2	1697.7	1633.6	1605.3
25°	1801.6	1741.1	1616.5	1539.1	1510.7
27.5°	1743.1	1678.8	1541.0	1452.2	1408.8
30°	1680.8	1608.9	1457.8	1361.6	1310.5
32.5°	1620.3	1533.4	1378.7	1265.3	1218.0
35°	1552.4	1456.0	1289.9	1170.9	1129.3
37.5°	1486.2	1382.3	1206.8	1076.3	1029.3
40°	1416.3	1303.1	1119.8	985.8	936.7
42.5°	1344.6	1223.8	1033.0	893.2	846.1
45°	1269.1	1142.5	944.3	810.1	764.7
47.5°	1197.3	1063.3	859.3	725.1	683.6
50°	1118.1	983.9	776.2	645.8	606.3
52.5°	1040.5	898.8	696.9	572.3	536.4
55°	965.0	817.6	613.7	500.5	464.6
57.5°	887.6	736.5	540.1	434.4	404.1
60°	808.2	657.2	462.6	366.5	336.2
62.5°	730.9	579.8	396.5	306.0	290.9
65°	651.5	498.5	328.6	264.5	258.7
67.5°	576.0	423.0	264.5	232.3	226.6
70°	496.7	349.4	219.0	200.1	192.6
72.5°	421.2	281.3	183.2	168.1	164.3
75°	347.5	215.2	151.1	137.8	136.0
77.5°	273.9	152.9	119.1	111.4	107.5
80°	205.8	109.6	90.6	83.1	83.1
82.5°	143.5	73.7	62.3	58.5	58.5
85°	81.2	41.5	35.8	35.8	35.8
87.5°	30.3	15.0	15.0	13.2	13.2
90°	2.8	35.4	59.1	74.1	79.8
92.5°	74.1	62.2	71.0	76.9	79.8
95°	192.2	94.5	115.2	130.4	127.2
97.5°	346.2	103.7	150.8	159.9	162.7
100°	523.9	118.4	168.6	192.2	198.2
102.5°	719.0	713.3	174.6	207.0	216.1
105°	899.5	988.5	180.7	213.0	224.9
107.5°	1109.7	1183.5	186.6	218.9	230.8
110°	1311.0	1372.9	517.9	222.1	233.7

TEST NUMBER: P927590

CATALOG NUMBER: DFN2DIP-HX4F0-050D120US840-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1500.5	1553.5	1503.3	227.7	236.8
115°	1701.4	1751.7	1825.8	455.7	242.9
117.5°	1876.1	1935.2	1985.8	1562.3	787.1
120°	2071.5	2115.7	2169.2	2204.7	1805.1
122.5°	2237.0	2284.5	2343.8	2361.4	2364.5
125°	2405.6	2444.3	2500.6	2521.3	2530.1
127.5°	2559.5	2601.0	2645.7	2675.2	2678.0
130°	2704.6	2752.1	2784.4	2817.1	2814.3
132.5°	2852.6	2891.3	2923.6	2950.3	2947.5
135°	2977.0	3024.5	3050.8	3080.7	3074.7
137.5°	3107.1	3142.5	3172.4	3201.9	3193.1
140°	3234.3	3258.1	3290.4	3317.2	3302.4
142.5°	3341.0	3361.8	3400.1	3423.6	3408.9
145°	3453.5	3450.4	3500.6	3521.4	3506.5
147.5°	3550.9	3542.1	3592.4	3607.1	3595.5
150°	3645.7	3625.0	3672.4	3690.0	3675.3
152.5°	3725.5	3701.9	3746.3	3764.1	3743.4
155°	3802.4	3776.0	3811.6	3829.2	3805.6
157.5°	3864.6	3841.1	3867.8	3888.5	3864.6
160°	3918.0	3900.2	3918.0	3935.6	3914.9
162.5°	3965.2	3947.6	3962.4	3983.1	3956.4
165°	4006.6	3989.0	3997.8	4018.6	3997.8
167.5°	4039.3	4021.3	4030.5	4051.2	4024.6
170°	4066.0	4048.1	4054.0	4074.7	4048.1
172.5°	4083.5	4066.0	4072.0	4092.7	4066.0
175°	4098.3	4077.6	4083.5	4104.3	4074.7
177.5°	4104.3	4083.5	4086.8	4107.5	4080.8
180°	4089.6	4089.6	4089.6	4089.6	4089.6

TEST NUMBER: P927590

CATALOG NUMBER: DFN2DIP-HX4F0-050D120US840-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.92	6.59	7.06	7.72	9.29	1.89	2.56	3.03	3.69	5.26
	3H	7.59	8.18	8.73	9.32	10.91	3.07	3.67	4.22	4.81	6.40
	4H	8.19	8.76	9.35	9.89	11.49	3.52	4.08	4.67	5.22	6.81
	6H	8.60	9.12	9.77	10.26	11.87	3.83	4.35	4.99	5.49	7.10
	8H	8.72	9.22	9.89	10.37	11.97	3.92	4.41	5.08	5.57	7.16
	12H	8.78	9.25	9.95	10.40	12.02	3.96	4.43	5.13	5.57	7.19
4H	2H	5.92	6.49	7.08	7.62	9.22	2.47	3.04	3.63	4.17	5.77
	3H	7.73	8.21	8.90	9.37	10.98	3.81	4.28	4.98	5.44	7.05
	4H	8.42	8.86	9.59	10.01	11.63	4.35	4.78	5.52	5.93	7.56
	6H	8.93	9.30	10.11	10.47	12.09	4.76	5.13	5.94	6.31	7.92
	8H	9.10	9.45	10.28	10.61	12.24	4.89	5.23	6.06	6.40	8.03
	12H	9.19	9.50	10.38	10.68	12.32	4.95	5.26	6.14	6.44	8.07
8H	4H	8.38	8.72	9.55	9.89	11.52	4.62	4.97	5.79	6.13	7.76
	6H	8.94	9.22	10.13	10.43	12.06	5.13	5.42	6.33	6.63	8.25
	8H	9.16	9.40	10.36	10.59	12.24	5.32	5.57	6.52	6.76	8.41
	12H	9.29	9.51	10.49	10.69	12.37	5.44	5.66	6.64	6.84	8.52
12H	4H	8.32	8.64	9.51	9.81	11.45	4.62	4.93	5.81	6.11	7.74
	6H	8.91	9.16	10.11	10.35	12.00	5.18	5.43	6.38	6.62	8.26
	8H	9.13	9.35	10.33	10.53	12.21	5.39	5.61	6.59	6.79	8.47

END OF REPORT