

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P928868

Luminaire Tested: DFN2DIP-HX4F0-050D080US935-FLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P928868
REPORT IS A COMBINATION OF REPORTS P900893 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-050D080US935-FLLONL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11081.1 lumens
Efficiency: N/A
Efficacy: 108.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 102
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9957
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P928868

CATALOG NUMBER: DFN2DIP-HX4F0-050D080US935-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P928868

CATALOG NUMBER: DFN2DIP-HX4F0-050D080US935-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	95	95	95	95	77	77	77	61	61	61	46	46	46
1	95	91	87	84	86	83	80	77	67	65	63	53	52	50	40	39	38
2	87	79	73	68	78	72	67	63	59	55	52	47	44	42	35	34	32
3	79	70	63	57	71	64	57	52	52	48	44	41	38	36	31	29	28
4	72	62	54	48	65	56	50	44	46	41	37	37	33	30	28	26	24
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	23	21
6	61	49	41	36	55	45	38	33	37	32	28	30	26	23	23	20	18
7	56	44	36	31	51	41	34	29	34	28	25	27	23	20	21	18	16
8	52	40	33	27	47	37	30	25	31	25	22	25	21	18	19	16	14
9	49	37	29	24	44	34	27	23	28	23	19	23	19	16	18	15	13
10	45	33	26	22	41	31	25	20	26	21	17	21	17	15	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1246	1246	1246
5°	1248	1228	1237
10°	1238	1212	1220
15°	1220	1192	1194
20°	1195	1164	1167
25°	1171	1131	1136
30°	1140	1101	1097
35°	1111	1064	1055
40°	1076	1028	1016
45°	1040	991	975
50°	1001	953	928
55°	960	908	885
60°	915	855	836
65°	864	800	778
70°	801	734	715
75°	712	654	658
80°	606	552	547
85°	440	376	364

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1195 cd/sqm

TEST NUMBER: P928868

CATALOG NUMBER: DFN2DIP-HX4F0-050D080US935-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.7	1.4
10°-20°	443.6	4.0
20°-30°	651.9	5.9
30°-40°	757.2	6.8
40°-50°	756.2	6.8
50°-60°	659.4	6.0
60°-70°	487.4	4.4
70°-80°	275.8	2.5
80°-90°	76.9	0.7
90°-100°	76.7	0.7
100°-110°	285.7	2.6
110°-120°	757.9	6.8
120°-130°	1256.9	11.3
130°-140°	1335.2	12.0
140°-150°	1240.9	11.2
150°-160°	997.6	9.0
160°-170°	642.8	5.8
170°-180°	221.3	2.0
0°-30°	1253.2	11.3
0°-40°	2010.3	18.1
0°-60°	3425.9	30.9
0°-90°	4266.0	38.5
90°-120°	1120.2	10.1
90°-150°	4953.3	44.7
90°-180°	6815.0	61.5
0°-180°	11081.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1675	1675	1675	1675	1675	
5°	1675	1669	1651	1664	1661	159
15°	1595	1585	1564	1571	1562	449
25°	1443	1430	1403	1406	1403	664
35°	1245	1229	1203	1194	1186	778
45°	1013	1002	978	960	954	782
55°	767	757	738	718	710	686
65°	517	507	491	477	469	511
75°	270	267	259	250	253	289
85°	66	64	63	58	56	74
90°	2	20	34	42	45	10
95°	109	54	66	74	72	129
105°	511	562	103	121	128	546
115°	967	996	1038	259	138	952
125°	1367	1389	1421	1433	1438	1220
135°	1692	1719	1734	1751	1748	1307
145°	1963	1961	1990	2002	1993	1228
155°	2162	2146	2167	2177	2163	996
165°	2278	2268	2272	2284	2272	643
175°	2330	2318	2321	2333	2316	222
180°	2325	2325	2325	2325	2325	

TEST NUMBER: P928868

CATALOG NUMBER: DFN2DIP-HX4F0-050D080US935-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1675.1	1675.1	1675.1	1675.1	1675.1
2.5°	1684.8	1676.8	1659.1	1675.1	1672.1
5°	1675.1	1668.8	1651.0	1663.8	1660.8
7.5°	1663.8	1654.2	1636.5	1649.5	1646.2
10°	1646.2	1635.0	1615.7	1628.4	1623.7
12.5°	1622.0	1612.4	1593.1	1601.1	1597.8
15°	1594.6	1585.0	1564.0	1570.6	1562.5
17.5°	1560.7	1551.2	1530.2	1538.2	1530.2
20°	1523.7	1514.2	1491.6	1496.3	1490.0
22.5°	1486.8	1472.2	1451.2	1451.2	1447.9
25°	1443.2	1430.4	1403.0	1406.1	1403.0
27.5°	1394.8	1383.5	1362.7	1357.9	1349.9
30°	1346.6	1333.7	1309.6	1304.8	1298.3
32.5°	1295.0	1285.5	1259.6	1249.9	1243.5
35°	1245.1	1229.1	1203.2	1193.5	1185.5
37.5°	1188.7	1174.2	1148.4	1137.1	1129.1
40°	1130.8	1117.8	1092.0	1077.6	1071.2
42.5°	1074.4	1061.4	1035.8	1019.5	1010.0
45°	1013.2	1001.9	977.7	960.1	953.6
47.5°	953.6	942.3	916.5	898.7	889.2
50°	890.7	882.7	860.1	837.6	829.5
52.5°	829.5	818.2	797.4	779.6	768.4
55°	766.8	757.1	737.7	718.4	710.4
57.5°	703.9	695.9	674.9	655.6	649.0
60°	641.0	634.7	612.2	594.3	589.6
62.5°	579.9	568.6	552.5	536.4	529.9
65°	517.1	507.4	491.3	476.8	468.7
67.5°	452.7	444.5	430.2	418.9	412.3
70°	393.0	386.6	372.0	360.8	354.5
72.5°	331.9	325.4	317.4	306.1	301.3
75°	270.5	267.4	259.2	249.7	253.0
77.5°	215.9	209.3	206.1	201.3	196.6
80°	161.2	159.5	156.2	151.4	148.2
82.5°	109.5	109.5	108.0	101.5	101.5
85°	66.0	64.4	62.9	57.9	56.4
87.5°	29.0	25.8	22.6	17.7	16.1
90°	1.6	20.1	33.6	42.1	45.4
92.5°	42.1	35.4	40.4	43.7	45.4
95°	109.3	53.7	65.5	74.1	72.3
97.5°	196.7	58.9	85.7	90.9	92.5
100°	297.8	67.3	95.9	109.3	112.6
102.5°	408.7	405.4	99.3	117.6	122.9
105°	511.3	561.9	102.6	121.1	127.9
107.5°	630.8	672.7	106.1	124.4	131.2
110°	745.3	780.4	294.5	126.2	132.9

TEST NUMBER: P928868

CATALOG NUMBER: DFN2DIP-HX4F0-050D080US935-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	852.9	883.0	854.5	129.4	134.7
115°	967.2	995.7	1037.8	259.1	138.0
117.5°	1066.4	1100.0	1128.8	888.0	447.5
120°	1177.5	1202.6	1233.0	1253.2	1026.1
122.5°	1271.5	1298.6	1332.3	1342.3	1344.1
125°	1367.4	1389.4	1421.3	1433.1	1438.1
127.5°	1454.9	1478.5	1503.9	1520.6	1522.2
130°	1537.4	1564.4	1582.8	1601.4	1599.7
132.5°	1621.5	1643.5	1661.9	1677.1	1675.4
135°	1692.2	1719.2	1734.1	1751.2	1747.7
137.5°	1766.2	1786.3	1803.3	1820.1	1815.1
140°	1838.4	1852.0	1870.4	1885.6	1877.2
142.5°	1899.2	1910.9	1932.7	1946.1	1937.7
145°	1963.1	1961.3	1989.9	2001.7	1993.2
147.5°	2018.4	2013.4	2041.9	2050.4	2043.8
150°	2072.3	2060.5	2087.5	2097.5	2089.1
152.5°	2117.7	2104.3	2129.4	2139.7	2127.9
155°	2161.5	2146.5	2166.6	2176.6	2163.3
157.5°	2196.8	2183.4	2198.6	2210.4	2196.8
160°	2227.1	2217.0	2227.1	2237.1	2225.3
162.5°	2253.9	2243.9	2252.3	2264.1	2248.9
165°	2277.5	2267.5	2272.5	2284.2	2272.5
167.5°	2296.0	2285.9	2291.0	2302.8	2287.7
170°	2311.3	2301.0	2304.5	2316.3	2301.0
172.5°	2321.3	2311.3	2314.6	2326.4	2311.3
175°	2329.6	2317.8	2321.3	2333.0	2316.3
177.5°	2333.0	2321.3	2323.0	2334.8	2319.6
180°	2324.6	2324.6	2324.6	2324.6	2324.6

TEST NUMBER: P928868

CATALOG NUMBER: DFN2DIP-HX4F0-050D080US935-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.87	7.64	7.92	8.69	10.12	6.44	7.20	7.49	8.26	9.68
	3H	8.52	9.21	9.58	10.27	11.72	8.05	8.74	9.11	9.80	11.25
	4H	9.11	9.76	10.18	10.82	12.28	8.63	9.29	9.70	10.35	11.80
	6H	9.50	10.10	10.58	11.17	12.64	9.03	9.63	10.11	10.70	12.16
	8H	9.60	10.18	10.69	11.26	12.72	9.13	9.70	10.21	10.79	12.24
	12H	9.65	10.19	10.74	11.27	12.75	9.17	9.71	10.26	10.79	12.27
4H	2H	7.32	7.97	8.40	9.04	10.49	6.97	7.63	8.05	8.69	10.14
	3H	9.18	9.72	10.26	10.81	12.28	8.79	9.33	9.87	10.42	11.89
	4H	9.89	10.39	10.98	11.47	12.96	9.48	9.98	10.57	11.07	12.55
	6H	10.40	10.83	11.50	11.93	13.41	9.99	10.42	11.09	11.52	13.00
	8H	10.55	10.95	11.65	12.05	13.54	10.14	10.54	11.23	11.63	13.13
	12H	10.62	10.98	11.73	12.09	13.59	10.19	10.56	11.31	11.67	13.17
8H	4H	10.08	10.48	11.18	11.58	13.07	9.72	10.12	10.82	11.22	12.71
	6H	10.71	11.04	11.83	12.18	13.67	10.34	10.68	11.47	11.82	13.31
	8H	10.93	11.22	12.06	12.34	13.85	10.56	10.85	11.69	11.97	13.48
	12H	11.06	11.31	12.19	12.43	13.98	10.67	10.93	11.80	12.04	13.59
12H	4H	10.06	10.42	11.18	11.53	13.03	9.71	10.07	10.82	11.18	12.68
	6H	10.74	11.03	11.86	12.15	13.66	10.39	10.67	11.51	11.80	13.31
	8H	10.98	11.23	12.11	12.35	13.90	10.62	10.87	11.75	11.99	13.54

END OF REPORT