

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P927616

Luminaire Tested: DFN2DIP-HX4F0-060D100US840-FLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P927616
REPORT IS A COMBINATION OF REPORTS P900931 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-060D100US840-FLLONL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15995.3 lumens
Efficiency: N/A
Efficacy: 122.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 130.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P927616

CATALOG NUMBER: DFN2DIP-HX4F0-060D100US840-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P927616

CATALOG NUMBER: DFN2DIP-HX4F0-060D100US840-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	45	45	45
1	95	91	87	83	86	82	79	76	67	65	63	53	51	50	39	39	38
2	86	79	73	68	78	72	67	63	59	55	52	46	44	42	35	33	32
3	79	70	62	57	71	63	57	52	52	47	44	41	38	35	31	29	27
4	72	62	54	48	65	56	49	44	46	41	37	36	33	30	27	25	23
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	22	20
6	61	49	41	35	55	45	38	33	37	32	28	29	26	23	22	20	18
7	56	44	36	31	51	40	34	29	33	28	24	27	23	20	20	18	16
8	52	40	32	27	47	37	30	25	30	25	22	24	21	18	19	16	14
9	48	36	29	24	44	33	27	23	28	23	19	22	19	16	17	15	13
10	45	33	26	22	41	31	24	20	26	21	17	21	17	14	16	13	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1753	1753	1753
5°	1756	1729	1740
10°	1742	1706	1717
15°	1716	1678	1680
20°	1682	1639	1643
25°	1648	1592	1599
30°	1605	1549	1544
35°	1564	1498	1485
40°	1514	1447	1429
45°	1464	1395	1372
50°	1409	1341	1306
55°	1352	1278	1246
60°	1287	1204	1176
65°	1217	1127	1094
70°	1127	1033	1006
75°	1002	920	925
80°	853	777	770
85°	619	529	512

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1748 cd/sqm

TEST NUMBER: P927616

CATALOG NUMBER: DFN2DIP-HX4F0-060D100US840-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	221.9	1.4
10°-20°	624.3	3.9
20°-30°	917.5	5.7
30°-40°	1065.6	6.7
40°-50°	1064.3	6.7
50°-60°	928.0	5.8
60°-70°	686.0	4.3
70°-80°	388.1	2.4
80°-90°	108.4	0.7
90°-100°	112.4	0.7
100°-110°	418.9	2.6
110°-120°	1111.0	6.9
120°-130°	1842.7	11.5
130°-140°	1957.4	12.2
140°-150°	1819.2	11.4
150°-160°	1462.6	9.1
160°-170°	942.4	5.9
170°-180°	324.4	2.0
0°-30°	1763.7	11.0
0°-40°	2829.3	17.7
0°-60°	4821.6	30.1
0°-90°	6004.2	37.5
90°-120°	1642.3	10.3
90°-150°	7261.7	45.4
90°-180°	9991.0	62.5
0°-180°	15995.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2358	2358	2358	2358	2358	
5°	2358	2349	2324	2342	2337	224
15°	2244	2231	2201	2210	2199	632
25°	2031	2013	1975	1979	1975	935
35°	1752	1730	1693	1680	1668	1094
45°	1426	1410	1376	1351	1342	1101
55°	1079	1065	1038	1011	1000	965
65°	728	714	692	671	660	720
75°	381	376	365	351	356	406
85°	93	91	88	82	79	104
90°	2	30	49	62	66	15
95°	160	79	96	109	106	190
105°	750	824	151	177	187	801
115°	1418	1460	1522	380	202	1396
125°	2005	2037	2084	2101	2108	1788
135°	2481	2520	2542	2567	2562	1916
145°	2878	2875	2917	2934	2922	1800
155°	3169	3147	3176	3191	3171	1460
165°	3339	3324	3332	3349	3332	943
175°	3415	3398	3403	3420	3396	325
180°	3408	3408	3408	3408	3408	

TEST NUMBER: P927616

CATALOG NUMBER: DFN2DIP-HX4F0-060D100US840-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2357.5	2357.5	2357.5	2357.5	2357.5
2.5°	2371.2	2359.9	2334.9	2357.5	2353.1
5°	2357.5	2348.6	2323.5	2341.6	2337.3
7.5°	2341.6	2328.2	2303.2	2321.4	2316.9
10°	2316.9	2301.0	2273.8	2291.8	2285.1
12.5°	2282.8	2269.2	2242.1	2253.4	2248.8
15°	2244.2	2230.7	2201.2	2210.4	2199.0
17.5°	2196.6	2183.2	2153.6	2164.8	2153.6
20°	2144.4	2131.0	2099.2	2105.9	2097.1
22.5°	2092.5	2072.0	2042.4	2042.4	2037.9
25°	2031.1	2013.1	1974.6	1978.9	1974.6
27.5°	1963.1	1947.2	1917.8	1911.1	1899.8
30°	1895.3	1876.9	1843.1	1836.3	1827.1
32.5°	1822.6	1809.2	1772.8	1759.1	1750.0
35°	1752.4	1729.8	1693.4	1679.7	1668.4
37.5°	1673.0	1652.5	1616.3	1600.3	1589.0
40°	1591.4	1573.2	1536.9	1516.7	1507.5
42.5°	1512.1	1493.8	1457.7	1434.9	1421.4
45°	1426.0	1410.1	1376.0	1351.2	1342.0
47.5°	1342.0	1326.2	1289.9	1264.9	1251.3
50°	1253.6	1242.3	1210.5	1178.7	1167.4
52.5°	1167.4	1151.6	1122.2	1097.2	1081.4
55°	1079.2	1065.4	1038.3	1011.1	999.8
57.5°	990.7	979.4	949.8	922.7	913.5
60°	902.2	893.3	861.6	836.5	829.8
62.5°	816.0	800.2	777.5	754.9	745.8
65°	727.8	714.1	691.5	671.0	659.7
67.5°	637.1	625.6	605.4	589.5	580.3
70°	553.2	544.1	523.6	507.7	498.8
72.5°	467.0	457.9	446.6	430.8	424.0
75°	380.7	376.5	364.8	351.4	356.0
77.5°	303.7	294.7	290.0	283.3	276.6
80°	226.8	224.4	219.8	213.1	208.5
82.5°	154.2	154.2	152.0	142.9	142.9
85°	92.8	90.7	88.5	81.5	79.4
87.5°	40.9	36.4	31.7	25.0	22.6
90°	2.3	29.6	49.2	61.8	66.4
92.5°	61.8	51.8	59.2	64.1	66.4
95°	160.2	78.8	96.0	108.7	106.0
97.5°	288.4	86.3	125.6	133.2	135.6
100°	436.6	98.7	140.6	160.2	165.2
102.5°	599.1	594.5	145.5	172.5	180.0
105°	749.7	823.7	150.6	177.4	187.4
107.5°	924.8	986.3	155.5	182.5	192.4
110°	1092.5	1144.1	431.6	185.1	194.7

TEST NUMBER: P927616

CATALOG NUMBER: DFN2DIP-HX4F0-060D100US840-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1250.3	1294.6	1252.8	189.7	197.4
115°	1417.9	1459.8	1521.6	379.8	202.4
117.5°	1563.4	1612.7	1654.8	1301.9	656.0
120°	1726.3	1763.1	1807.6	1837.2	1504.3
122.5°	1864.2	1903.7	1953.2	1967.8	1970.4
125°	2004.8	2037.0	2083.8	2101.1	2108.4
127.5°	2133.0	2167.5	2204.7	2229.3	2231.7
130°	2253.9	2293.5	2320.4	2347.6	2345.3
132.5°	2377.2	2409.4	2436.3	2458.6	2456.2
135°	2480.9	2520.4	2542.4	2567.2	2562.3
137.5°	2589.2	2618.8	2643.7	2668.3	2660.9
140°	2695.2	2715.2	2742.0	2764.3	2752.0
142.5°	2784.2	2801.5	2833.4	2853.0	2840.8
145°	2877.9	2875.3	2917.2	2934.5	2922.2
147.5°	2959.0	2951.7	2993.6	3005.9	2996.3
150°	3038.1	3020.8	3060.4	3075.0	3062.7
152.5°	3104.5	3084.9	3121.9	3136.7	3119.5
155°	3168.8	3146.7	3176.3	3191.0	3171.4
157.5°	3220.6	3201.0	3223.2	3240.4	3220.6
160°	3265.1	3250.1	3265.1	3279.7	3262.5
162.5°	3304.3	3289.6	3301.9	3319.2	3297.0
165°	3338.8	3324.2	3331.5	3348.8	3331.5
167.5°	3366.1	3351.1	3358.8	3376.1	3353.7
170°	3388.3	3373.4	3378.4	3395.7	3373.4
172.5°	3402.9	3388.3	3393.3	3410.6	3388.3
175°	3415.2	3398.0	3402.9	3420.3	3395.7
177.5°	3420.3	3402.9	3405.7	3422.9	3400.6
180°	3408.0	3408.0	3408.0	3408.0	3408.0

TEST NUMBER: P927616

CATALOG NUMBER: DFN2DIP-HX4F0-060D100US840-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.95	8.71	9.00	9.77	11.21	7.52	8.28	8.57	9.34	10.78
	3H	9.60	10.28	10.67	11.35	12.81	9.13	9.81	10.19	10.88	12.34
	4H	10.18	10.83	11.26	11.90	13.37	9.71	10.36	10.79	11.43	12.89
	6H	10.58	11.17	11.67	12.25	13.72	10.10	10.70	11.19	11.77	13.25
	8H	10.68	11.25	11.77	12.34	13.81	10.21	10.77	11.30	11.86	13.33
	12H	10.73	11.26	11.82	12.35	13.84	10.25	10.78	11.34	11.87	13.36
4H	2H	8.40	9.04	9.48	10.11	11.58	8.05	8.70	9.14	9.77	11.23
	3H	10.26	10.79	11.35	11.89	13.37	9.86	10.40	10.95	11.50	12.98
	4H	10.97	11.46	12.06	12.55	14.05	10.56	11.05	11.66	12.14	13.64
	6H	11.48	11.90	12.58	13.01	14.50	11.07	11.49	12.17	12.60	14.09
	8H	11.62	12.02	12.73	13.12	14.63	11.21	11.61	12.32	12.71	14.22
	12H	11.69	12.05	12.82	13.17	14.68	11.27	11.63	12.39	12.75	14.26
8H	4H	11.16	11.55	12.26	12.66	14.16	10.79	11.19	11.90	12.29	13.80
	6H	11.78	12.11	12.91	13.26	14.76	11.42	11.75	12.55	12.89	14.40
	8H	12.00	12.29	13.14	13.42	14.94	11.63	11.92	12.77	13.05	14.57
	12H	12.13	12.38	13.27	13.51	15.07	11.75	12.00	12.88	13.12	14.68
12H	4H	11.14	11.49	12.26	12.61	14.12	10.78	11.14	11.91	12.26	13.77
	6H	11.81	12.10	12.95	13.23	14.75	11.46	11.75	12.59	12.87	14.40
	8H	12.05	12.30	13.19	13.43	14.99	11.69	11.95	12.83	13.07	14.63

END OF REPORT

FIELD PERFORMANCE MAY DIFFER FROM LABORATORY PERFORMANCE

8 of 8