

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P908213

Luminaire Tested: DFN2DIP-HX4F0-070D120US840-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P908213
REPORT IS A COMBINATION OF REPORTS P899450 AND P896188
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-070D120US840-RLLFLL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 16733.4 lumens
Efficiency: N/A
Efficacy: 120.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 139.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9972
Total Harmonic Distortion (THDi): 0.128
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P908213

CATALOG NUMBER: DFN2DIP-HX4F0-070D120US840-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P908213

CATALOG NUMBER: DFN2DIP-HX4F0-070D120US840-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	43	43	43
1	95	91	87	84	86	82	79	77	67	64	63	52	51	49	39	38	37
2	87	80	74	69	78	72	68	63	59	55	52	46	44	42	34	33	32
3	79	70	63	58	72	64	58	53	52	48	44	41	38	36	31	29	27
4	73	62	55	49	66	57	50	45	46	42	38	37	34	31	28	26	24
5	67	56	48	42	60	51	44	39	42	37	33	33	30	27	25	23	21
6	62	50	42	37	56	46	39	34	38	33	29	30	26	24	23	21	19
7	57	45	38	32	51	41	35	30	34	29	25	27	24	21	21	19	17
8	53	41	34	28	48	38	31	26	31	26	23	25	21	19	19	17	15
9	49	37	30	25	45	34	28	24	29	24	20	23	20	17	18	15	14
10	46	34	27	23	42	32	25	21	26	22	18	21	18	15	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2172	2172	2172
5°	2176	2138	2152
10°	2155	2096	2082
15°	2125	2027	1974
20°	2086	1932	1841
25°	2046	1825	1713
30°	1992	1715	1550
35°	1940	1598	1407
40°	1886	1476	1243
45°	1824	1340	1095
50°	1759	1204	950
55°	1692	1058	811
60°	1615	905	667
65°	1525	750	601
70°	1417	605	544
75°	1281	533	495
80°	1083	448	430
85°	757	300	324

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2891 cd/sqm

TEST NUMBER: P908213

CATALOG NUMBER: DFN2DIP-HX4F0-070D120US840-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	273.8	1.6
10°-20°	751.7	4.5
20°-30°	1055.3	6.3
30°-40°	1150.4	6.9
40°-50°	1057.3	6.3
50°-60°	830.4	5.0
60°-70°	540.5	3.2
70°-80°	278.2	1.7
80°-90°	81.9	0.5
90°-100°	237.2	1.4
100°-110°	753.5	4.5
110°-120°	1289.5	7.7
120°-130°	1696.0	10.1
130°-140°	1903.6	11.4
140°-150°	1866.7	11.2
150°-160°	1565.9	9.4
160°-170°	1038.5	6.2
170°-180°	363.0	2.2
0°-30°	2080.9	12.4
0°-40°	3231.2	19.3
0°-60°	5118.9	30.6
0°-90°	6019.5	36.0
90°-120°	2280.2	13.6
90°-150°	7746.5	46.3
90°-180°	10714.0	64.0
0°-180°	16733.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2922	2922	2922	2922	2922	
5°	2922	2908	2874	2898	2890	277
15°	2779	2750	2660	2610	2583	783
25°	2522	2438	2263	2155	2115	1160
35°	2173	2038	1806	1639	1581	1360
45°	1777	1600	1322	1134	1071	1372
55°	1351	1145	859	701	651	1207
65°	912	698	460	370	362	904
75°	486	301	212	193	190	515
85°	114	58	50	50	50	130
90°	3	42	113	106	110	17
95°	169	201	207	207	201	188
105°	696	705	712	718	718	734
115°	1294	1313	1307	1303	1294	1280
125°	1882	1911	1902	1892	1888	1682
135°	2434	2470	2477	2474	2465	1882
145°	2956	2979	2997	3001	2988	1847
155°	3380	3389	3399	3416	3405	1556
165°	3677	3673	3673	3696	3680	1037
175°	3826	3816	3810	3832	3813	363
180°	3832	3832	3832	3832	3832	

TEST NUMBER: P908213

CATALOG NUMBER: DFN2DIP-HX4F0-070D120US840-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2921.6	2921.6	2921.6	2921.6	2921.6
2.5°	2934.8	2921.6	2892.5	2919.1	2913.8
5°	2921.6	2908.4	2874.0	2897.8	2889.9
7.5°	2897.8	2882.1	2845.1	2855.4	2842.3
10°	2866.1	2847.6	2794.8	2786.7	2771.0
12.5°	2826.5	2802.7	2731.2	2715.4	2686.2
15°	2778.8	2749.7	2659.9	2609.7	2583.3
17.5°	2723.3	2681.0	2569.9	2511.7	2469.4
20°	2659.9	2606.9	2474.8	2408.8	2350.5
22.5°	2591.2	2530.3	2376.8	2287.0	2247.6
25°	2522.4	2437.7	2263.2	2155.0	2115.2
27.5°	2440.5	2350.5	2157.5	2033.3	1972.4
30°	2353.3	2252.6	2041.0	1906.4	1834.9
32.5°	2268.6	2146.9	1930.3	1771.5	1705.3
35°	2173.4	2038.5	1806.0	1639.4	1581.0
37.5°	2080.9	1935.3	1689.6	1506.9	1441.1
40°	1983.0	1824.5	1567.8	1380.2	1311.4
42.5°	1882.6	1713.4	1446.3	1250.5	1184.7
45°	1776.9	1599.5	1322.1	1134.2	1070.8
47.5°	1676.4	1488.7	1203.2	1015.2	957.2
50°	1565.3	1377.7	1086.7	904.1	848.9
52.5°	1456.7	1258.4	975.6	801.1	750.9
55°	1351.0	1144.8	859.2	700.7	650.6
57.5°	1242.7	1031.2	756.3	608.1	565.8
60°	1131.7	920.1	647.7	513.1	470.7
62.5°	1023.3	811.8	555.1	428.4	407.3
65°	912.2	697.9	460.1	370.3	362.1
67.5°	806.5	592.2	370.3	325.1	317.3
70°	695.4	489.2	306.6	280.2	269.5
72.5°	589.7	393.8	256.4	235.4	230.0
75°	486.5	301.2	211.5	193.0	190.5
77.5°	383.4	214.0	166.6	155.9	150.7
80°	288.1	153.4	126.8	116.4	116.4
82.5°	200.9	103.2	87.3	81.9	81.9
85°	113.6	58.1	50.2	50.2	50.2
87.5°	42.3	21.0	21.0	18.5	18.5
90°	3.4	41.6	113.2	106.3	109.8
92.5°	71.6	97.0	100.5	104.0	104.0
95°	168.6	201.1	206.8	206.8	201.1
97.5°	280.7	310.8	323.6	323.6	323.6
100°	410.2	436.8	446.0	446.0	442.5
102.5°	546.5	566.1	578.9	582.4	578.9
105°	695.6	704.8	711.8	717.5	717.5
107.5°	843.4	857.4	857.4	859.6	843.4
110°	986.7	1005.2	1005.2	1005.2	996.0

TEST NUMBER: P908213

CATALOG NUMBER: DFN2DIP-HX4F0-070D120US840-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1141.6	1161.2	1157.7	1148.5	1141.6
115°	1294.0	1312.6	1306.8	1303.3	1294.0
117.5°	1445.4	1470.9	1454.7	1445.4	1436.2
120°	1598.0	1623.4	1598.0	1598.0	1587.6
122.5°	1736.7	1769.0	1752.8	1743.5	1736.7
125°	1882.2	1911.1	1901.9	1891.5	1887.9
127.5°	2024.4	2060.1	2047.4	2033.6	2024.4
130°	2157.2	2198.8	2193.0	2186.1	2173.3
132.5°	2306.2	2338.6	2340.9	2324.7	2315.5
135°	2434.5	2470.3	2477.3	2473.8	2464.6
137.5°	2577.8	2606.7	2612.4	2610.1	2596.3
140°	2703.7	2732.6	2748.8	2748.8	2736.0
142.5°	2833.2	2862.1	2871.2	2874.7	2862.1
145°	2955.6	2978.7	2997.2	3000.7	2988.0
147.5°	3065.3	3094.2	3108.2	3113.9	3101.2
150°	3178.7	3198.2	3211.0	3221.4	3211.0
152.5°	3279.1	3298.7	3315.0	3327.7	3315.0
155°	3379.6	3388.9	3399.3	3415.5	3405.1
157.5°	3466.4	3473.2	3479.0	3502.1	3486.0
160°	3543.7	3550.7	3554.1	3573.8	3559.9
162.5°	3615.3	3615.3	3618.9	3640.8	3624.6
165°	3676.6	3673.2	3673.2	3696.2	3680.1
167.5°	3732.1	3721.7	3721.7	3744.8	3728.6
170°	3773.7	3764.4	3760.9	3784.1	3764.4
172.5°	3802.5	3793.3	3789.8	3812.9	3793.3
175°	3825.7	3816.4	3809.5	3832.5	3812.9
177.5°	3838.4	3829.1	3822.1	3841.8	3822.1
180°	3832.5	3832.5	3832.5	3832.5	3832.5

TEST NUMBER: P908213

CATALOG NUMBER: DFN2DIP-HX4F0-070D120US840-RLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.37	9.10	9.45	10.17	11.63	4.34	5.07	5.42	6.14	7.60
	3H	10.04	10.69	11.12	11.77	13.25	5.53	6.18	6.61	7.26	8.73
	4H	10.65	11.26	11.74	12.34	13.83	5.97	6.59	7.07	7.67	9.16
	6H	11.06	11.63	12.17	12.71	14.21	6.29	6.86	7.39	7.94	9.44
	8H	11.19	11.73	12.29	12.83	14.32	6.38	6.92	7.49	8.02	9.51
	12H	11.25	11.76	12.36	12.85	14.37	6.42	6.93	7.53	8.03	9.54
4H	2H	8.38	8.99	9.48	10.07	11.56	4.93	5.54	6.03	6.62	8.11
	3H	10.20	10.71	11.31	11.82	13.32	6.27	6.78	7.38	7.89	9.39
	4H	10.89	11.36	12.00	12.46	13.97	6.81	7.29	7.93	8.38	9.90
	6H	11.40	11.80	12.52	12.92	14.43	7.23	7.63	8.35	8.76	10.27
	8H	11.57	11.95	12.69	13.06	14.59	7.36	7.73	8.48	8.85	10.37
	12H	11.66	12.00	12.80	13.13	14.66	7.42	7.76	8.56	8.89	10.42
8H	4H	10.85	11.22	11.97	12.34	13.86	7.09	7.46	8.21	8.58	10.10
	6H	11.41	11.72	12.55	12.88	14.40	7.60	7.91	8.74	9.07	10.59
	8H	11.63	11.90	12.77	13.03	14.58	7.80	8.07	8.94	9.20	10.75
	12H	11.76	12.00	12.91	13.13	14.71	7.91	8.15	9.06	9.28	10.86
12H	4H	10.79	11.13	11.93	12.26	13.79	7.09	7.43	8.22	8.55	10.09
	6H	11.39	11.66	12.53	12.79	14.34	7.65	7.93	8.80	9.06	10.61
	8H	11.60	11.84	12.75	12.97	14.55	7.86	8.10	9.01	9.23	10.81