

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P919109

Luminaire Tested: DFN2DIP-HX4F0-070D040US935-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P919109
REPORT IS A COMBINATION OF REPORTS P899306 AND P896188
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-070D040US935-RLLFLL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8170.8 lumens
Efficiency: N/A
Efficacy: 90.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 90
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9972
Total Harmonic Distortion (THDi): 0.128
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P919109

CATALOG NUMBER: DFN2DIP-HX4F0-070D040US935-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P919109

CATALOG NUMBER: DFN2DIP-HX4F0-070D040US935-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	79	79	79	68	68	68
1	101	97	93	90	95	91	88	85	80	78	76	70	68	67	61	60	58
2	93	85	80	75	87	80	75	71	71	67	64	62	59	57	54	52	50
3	85	76	69	63	79	71	65	60	63	58	54	56	52	49	49	46	43
4	78	67	60	54	73	64	57	51	57	51	47	50	46	42	44	41	38
5	72	61	53	47	67	57	50	45	51	45	41	45	41	37	40	36	33
6	67	55	47	41	62	52	44	39	46	40	36	41	36	33	36	33	30
7	62	50	42	36	58	47	40	35	42	36	32	38	33	29	33	30	27
8	57	45	38	32	54	43	36	31	39	33	29	35	30	26	31	27	24
9	54	42	34	29	50	40	33	28	36	30	26	32	27	24	29	25	22
10	50	38	31	26	47	36	30	25	33	27	24	30	25	22	27	23	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1852	1852	1852
5°	1855	1823	1835
10°	1837	1787	1775
15°	1812	1728	1683
20°	1779	1647	1570
25°	1745	1556	1460
30°	1699	1463	1322
35°	1654	1362	1200
40°	1608	1258	1060
45°	1555	1143	934
50°	1500	1026	810
55°	1443	902	691
60°	1376	771	569
65°	1300	639	512
70°	1208	516	464
75°	1092	455	422
80°	924	382	367
85°	646	256	276

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1555 cd/sqm

TEST NUMBER: P919109

CATALOG NUMBER: DFN2DIP-HX4F0-070D040US935-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	233.5	2.9
10°-20°	640.9	7.8
20°-30°	899.8	11.0
30°-40°	980.8	12.0
40°-50°	901.5	11.0
50°-60°	708.0	8.7
60°-70°	460.8	5.6
70°-80°	237.2	2.9
80°-90°	63.6	0.8
90°-100°	67.4	0.8
100°-110°	214.2	2.6
110°-120°	366.5	4.5
120°-130°	482.0	5.9
130°-140°	541.0	6.6
140°-150°	530.5	6.5
150°-160°	445.0	5.4
160°-170°	295.1	3.6
170°-180°	103.2	1.3
0°-30°	1774.1	21.7
0°-40°	2754.9	33.7
0°-60°	4364.3	53.4
0°-90°	5126.0	62.7
90°-120°	648.0	7.9
90°-150°	2201.5	26.9
90°-180°	3045.0	37.3
0°-180°	8170.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2491	2491	2491	2491	2491	
5°	2491	2480	2450	2471	2464	236
15°	2369	2344	2268	2225	2202	668
25°	2151	2078	1930	1837	1803	989
35°	1853	1738	1540	1398	1348	1160
45°	1515	1364	1127	967	913	1170
55°	1152	976	732	597	555	1029
65°	778	595	392	316	309	771
75°	415	257	180	164	162	439
85°	97	50	43	43	43	111
90°	1	12	32	30	31	8
95°	48	57	59	59	57	53
105°	198	200	202	204	204	209
115°	368	373	371	370	368	364
125°	535	543	540	538	537	478
135°	692	702	704	703	700	535
145°	840	846	852	853	849	525
155°	960	963	966	971	968	442
165°	1045	1044	1044	1050	1046	295
175°	1087	1085	1083	1089	1084	103
180°	1089	1089	1089	1089	1089	

TEST NUMBER: P919109

CATALOG NUMBER: DFN2DIP-HX4F0-070D040US935-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2491.0	2491.0	2491.0	2491.0	2491.0
2.5°	2502.1	2491.0	2466.1	2488.8	2484.2
5°	2491.0	2479.7	2450.3	2470.6	2463.9
7.5°	2470.6	2457.2	2425.7	2434.5	2423.3
10°	2443.6	2427.8	2382.8	2375.9	2362.5
12.5°	2409.8	2389.5	2328.6	2315.1	2290.3
15°	2369.2	2344.3	2267.8	2225.0	2202.5
17.5°	2321.9	2285.8	2191.1	2141.5	2105.4
20°	2267.8	2222.6	2110.0	2053.7	2004.0
22.5°	2209.2	2157.3	2026.4	1949.9	1916.2
25°	2150.6	2078.4	1929.6	1837.3	1803.4
27.5°	2080.8	2004.0	1839.4	1733.5	1681.6
30°	2006.4	1920.5	1740.2	1625.4	1564.4
32.5°	1934.1	1830.4	1645.7	1510.4	1453.9
35°	1853.0	1738.0	1539.8	1397.7	1348.0
37.5°	1774.2	1650.0	1440.5	1284.8	1228.6
40°	1690.7	1555.6	1336.7	1176.7	1118.1
42.5°	1605.1	1460.9	1233.1	1066.2	1010.0
45°	1514.9	1363.7	1127.2	967.0	912.9
47.5°	1429.3	1269.3	1025.8	865.6	816.1
50°	1334.5	1174.6	926.5	770.9	723.8
52.5°	1242.0	1072.9	831.8	683.0	640.2
55°	1151.8	976.0	732.5	597.4	554.7
57.5°	1059.5	879.2	644.8	518.5	482.4
60°	964.8	784.5	552.2	437.5	401.3
62.5°	872.4	692.2	473.3	365.2	347.2
65°	777.7	595.0	392.3	315.7	308.8
67.5°	687.6	504.9	315.7	277.2	270.5
70°	592.9	417.1	261.4	238.9	229.8
72.5°	502.7	335.8	218.6	200.7	196.1
75°	414.7	256.8	180.3	164.5	162.4
77.5°	326.9	182.4	142.1	132.9	128.5
80°	245.6	130.8	108.1	99.3	99.3
82.5°	171.3	88.0	74.4	69.8	69.8
85°	96.9	49.5	42.8	42.8	42.8
87.5°	36.1	17.9	17.9	15.8	15.8
90°	0.9	11.8	32.2	30.2	31.2
92.5°	20.3	27.6	28.6	29.5	29.5
95°	48.0	57.2	58.8	58.8	57.2
97.5°	79.8	88.3	92.0	92.0	92.0
100°	116.6	124.2	126.7	126.7	125.8
102.5°	155.3	160.9	164.5	165.5	164.5
105°	197.7	200.3	202.2	203.9	203.9
107.5°	239.7	243.7	243.7	244.3	239.7
110°	280.4	285.7	285.7	285.7	283.1



TEST NUMBER: P919109

CATALOG NUMBER: DFN2DIP-HX4F0-070D040US935-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	324.4	330.0	329.0	326.4	324.4
115°	367.7	373.1	371.3	370.4	367.7
117.5°	410.8	418.0	413.5	410.8	408.2
120°	454.2	461.3	454.2	454.2	451.2
122.5°	493.5	502.7	498.2	495.5	493.5
125°	534.9	543.1	540.5	537.5	536.6
127.5°	575.3	585.5	581.9	577.9	575.3
130°	613.0	624.9	623.3	621.3	617.7
132.5°	655.4	664.6	665.3	660.6	658.1
135°	691.9	702.1	704.0	703.0	700.4
137.5°	732.6	740.8	742.4	741.7	737.9
140°	768.4	776.6	781.2	781.2	777.6
142.5°	805.2	813.4	816.0	817.0	813.4
145°	840.0	846.5	851.8	852.8	849.2
147.5°	871.2	879.3	883.3	884.9	881.3
150°	903.4	909.0	912.6	915.5	912.6
152.5°	931.9	937.5	942.1	945.7	942.1
155°	960.4	963.1	966.0	970.7	967.7
157.5°	985.2	987.0	988.7	995.3	990.7
160°	1007.1	1009.1	1010.0	1015.6	1011.7
162.5°	1027.4	1027.4	1028.5	1034.7	1030.1
165°	1044.9	1043.9	1043.9	1050.4	1045.9
167.5°	1060.7	1057.6	1057.6	1064.3	1059.6
170°	1072.5	1069.8	1068.8	1075.4	1069.8
172.5°	1080.6	1078.1	1077.0	1083.7	1078.1
175°	1087.3	1084.6	1082.6	1089.2	1083.7
177.5°	1090.9	1088.2	1086.2	1091.8	1086.2
180°	1089.2	1089.2	1089.2	1089.2	1089.2

TEST NUMBER: P919109

CATALOG NUMBER: DFN2DIP-HX4F0-070D040US935-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.40	11.35	11.25	12.21	13.29	6.37	7.32	7.22	8.18	9.26
	3H	12.09	12.93	12.95	13.81	14.92	7.57	8.42	8.43	9.29	10.40
	4H	12.70	13.50	13.58	14.38	15.50	8.03	8.83	8.91	9.71	10.83
	6H	13.13	13.87	14.02	14.75	15.88	8.36	9.09	9.25	9.98	11.11
	8H	13.26	13.96	14.16	14.86	15.99	8.45	9.15	9.35	10.06	11.19
	12H	13.33	13.99	14.23	14.89	16.05	8.50	9.17	9.40	10.07	11.22
4H	2H	10.43	11.23	11.31	12.11	13.23	6.98	7.78	7.87	8.66	9.78
	3H	12.27	12.94	13.17	13.85	14.98	8.35	9.01	9.24	9.92	11.05
	4H	12.97	13.58	13.88	14.48	15.64	8.90	9.50	9.80	10.41	11.57
	6H	13.49	14.01	14.41	14.95	16.11	9.33	9.85	10.25	10.78	11.94
	8H	13.67	14.16	14.59	15.08	16.26	9.46	9.95	10.38	10.87	12.05
	12H	13.77	14.21	14.71	15.15	16.33	9.53	9.97	10.47	10.91	12.09
8H	4H	12.95	13.43	13.87	14.36	15.53	9.19	9.68	10.11	10.60	11.78
	6H	13.52	13.92	14.47	14.89	16.06	9.72	10.12	10.66	11.08	12.26
	8H	13.74	14.09	14.69	15.05	16.24	9.91	10.26	10.86	11.22	12.41
	12H	13.88	14.20	14.84	15.15	16.39	10.03	10.35	10.99	11.30	12.54
12H	4H	12.91	13.34	13.84	14.29	15.47	9.20	9.64	10.14	10.58	11.76
	6H	13.50	13.85	14.45	14.81	16.00	9.76	10.12	10.72	11.08	12.27
	8H	13.72	14.04	14.68	14.99	16.23	9.98	10.29	10.94	11.25	12.49

END OF REPORT