

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P928928

Luminaire Tested: DFN2DIP-HX4F0-070D050US935-FLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P928928
REPORT IS A COMBINATION OF REPORTS P900843 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-070D050US935-FLLONL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10228.8 lumens
Efficiency: N/A
Efficacy: 98.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 103.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9972
Total Harmonic Distortion (THDi): 0.128
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P928928
CATALOG NUMBER: DFN2DIP-HX4F0-070D050US935-FLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P928928

CATALOG NUMBER: DFN2DIP-HX4F0-070D050US935-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	64	64	64	58			58
1	100	95	91	88	93	89	86	82	77	75	72	66	65	63	56	55	54	49			49
2	91	83	77	72	84	78	72	68	68	64	60	58	55	53	50	47	45	41			41
3	83	73	66	60	77	69	62	57	60	55	50	52	48	44	44	41	39	35			35
4	76	65	57	51	70	61	54	48	53	47	43	46	42	38	39	36	33	30			30
5	70	58	50	43	65	54	47	41	48	42	37	41	37	33	35	32	29	26			26
6	64	52	44	38	60	49	41	36	43	37	32	37	33	29	32	29	26	23			23
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	29	26	23	20			20
8	55	43	35	29	51	40	33	28	36	30	26	31	26	23	27	23	20	18			18
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	18	16			16
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	23	19	17	15			15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1744	1744	1744
5°	1747	1720	1731
10°	1733	1697	1708
15°	1707	1669	1671
20°	1673	1630	1634
25°	1639	1584	1591
30°	1596	1541	1536
35°	1556	1490	1477
40°	1506	1439	1422
45°	1456	1388	1365
50°	1402	1334	1300
55°	1345	1271	1239
60°	1280	1197	1170
65°	1210	1121	1089
70°	1121	1027	1001
75°	997	915	920
80°	848	773	765
85°	616	527	510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1456 cd/sqm



TEST NUMBER: P928928

CATALOG NUMBER: DFN2DIP-HX4F0-070D050US935-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	220.7	2.2
10°-20°	621.0	6.1
20°-30°	912.7	8.9
30°-40°	1060.0	10.4
40°-50°	1058.7	10.4
50°-60°	923.2	9.0
60°-70°	682.4	6.7
70°-80°	386.1	3.8
80°-90°	104.5	1.0
90°-100°	47.9	0.5
100°-110°	178.6	1.7
110°-120°	473.7	4.6
120°-130°	785.6	7.7
130°-140°	834.5	8.2
140°-150°	775.6	7.6
150°-160°	623.5	6.1
160°-170°	401.8	3.9
170°-180°	138.3	1.4
0°-30°	1754.4	17.2
0°-40°	2814.5	27.5
0°-60°	4796.3	46.9
0°-90°	5969.3	58.4
90°-120°	700.2	6.8
90°-150°	3095.8	30.3
90°-180°	4259.0	41.6
0°-180°	10228.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2345	2345	2345	2345	2345	
5°	2345	2336	2311	2329	2325	223
15°	2232	2219	2190	2199	2188	629
25°	2020	2002	1964	1969	1964	930
35°	1743	1721	1684	1671	1660	1089
45°	1418	1403	1369	1344	1335	1095
55°	1074	1060	1033	1006	994	960
65°	724	710	688	668	656	716
75°	379	374	363	350	354	404
85°	92	90	88	81	79	103
90°	1	13	21	26	28	9
95°	68	34	41	46	45	81
105°	320	351	64	76	80	342
115°	604	622	649	162	86	595
125°	855	868	888	896	899	762
135°	1058	1074	1084	1094	1092	817
145°	1227	1226	1244	1251	1246	767
155°	1351	1342	1354	1360	1352	623
165°	1423	1417	1420	1428	1420	402
175°	1456	1449	1451	1458	1448	139
180°	1453	1453	1453	1453	1453	



TEST NUMBER: P928928

CATALOG NUMBER: DFN2DIP-HX4F0-070D050US935-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2345.1	2345.1	2345.1	2345.1	2345.1
2.5°	2358.8	2347.5	2322.6	2345.1	2340.8
5°	2345.1	2336.3	2311.4	2329.3	2325.0
7.5°	2329.3	2315.9	2291.0	2309.3	2304.7
10°	2304.7	2288.9	2261.8	2279.8	2273.1
12.5°	2270.7	2257.4	2230.3	2241.5	2237.0
15°	2232.5	2219.1	2189.6	2198.7	2187.5
17.5°	2185.0	2171.7	2142.3	2153.5	2142.3
20°	2133.1	2119.8	2088.2	2094.9	2086.0
22.5°	2081.5	2061.1	2031.7	2031.7	2027.1
25°	2020.5	2002.5	1964.3	1968.6	1964.3
27.5°	1952.7	1937.0	1907.8	1901.1	1889.8
30°	1885.3	1867.1	1833.4	1826.7	1817.6
32.5°	1813.0	1799.7	1763.5	1749.9	1740.8
35°	1743.2	1720.7	1684.5	1670.9	1659.7
37.5°	1664.2	1643.9	1607.7	1592.0	1580.7
40°	1583.1	1565.0	1528.8	1508.7	1499.6
42.5°	1504.2	1486.0	1450.1	1427.4	1413.9
45°	1418.5	1402.7	1368.7	1344.1	1335.0
47.5°	1335.0	1319.2	1283.1	1258.2	1244.8
50°	1247.0	1235.7	1204.1	1172.6	1161.3
52.5°	1161.3	1145.6	1116.4	1091.5	1075.6
55°	1073.5	1059.9	1032.9	1005.8	994.5
57.5°	985.5	974.2	944.8	917.7	908.7
60°	897.4	888.6	857.0	832.2	825.4
62.5°	811.8	796.0	773.5	751.1	741.9
65°	724.0	710.3	687.9	667.5	656.3
67.5°	633.8	622.3	602.2	586.4	577.3
70°	550.3	541.2	520.8	505.1	496.2
72.5°	464.6	455.6	444.3	428.5	421.8
75°	378.8	374.4	362.9	349.6	354.1
77.5°	302.2	293.1	288.5	281.8	275.2
80°	225.6	223.3	218.7	212.0	207.4
82.5°	153.3	153.3	151.2	142.2	142.2
85°	92.4	90.2	88.1	81.1	79.0
87.5°	40.6	36.2	31.6	24.9	22.5
90°	1.0	12.6	21.0	26.3	28.3
92.5°	26.3	22.1	25.2	27.4	28.3
95°	68.3	33.6	41.0	46.3	45.2
97.5°	123.0	36.9	53.6	56.8	57.8
100°	186.1	42.1	59.9	68.3	70.4
102.5°	255.5	253.4	62.1	73.5	76.8
105°	319.6	351.2	64.1	75.7	79.9
107.5°	394.3	420.4	66.3	77.7	82.1
110°	465.8	487.8	184.0	78.9	83.0



TEST NUMBER: P928928

CATALOG NUMBER: DFN2DIP-HX4F0-070D050US935-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	533.0	551.9	534.1	80.9	84.1
115°	604.5	622.3	648.7	162.0	86.3
117.5°	666.5	687.5	705.5	555.0	279.7
120°	735.9	751.7	770.6	783.3	641.3
122.5°	794.7	811.6	832.7	839.0	840.1
125°	854.6	868.4	888.4	895.7	898.9
127.5°	909.3	924.0	940.0	950.4	951.4
130°	960.9	977.8	989.2	1000.8	999.9
132.5°	1013.5	1027.2	1038.6	1048.2	1047.1
135°	1057.7	1074.5	1083.8	1094.5	1092.4
137.5°	1103.8	1116.5	1127.0	1137.6	1134.5
140°	1149.0	1157.5	1169.0	1178.5	1173.3
142.5°	1187.0	1194.4	1208.0	1216.3	1211.1
145°	1226.9	1225.8	1243.6	1251.0	1245.8
147.5°	1261.5	1258.4	1276.3	1281.5	1277.4
150°	1295.2	1287.9	1304.7	1311.0	1305.7
152.5°	1323.5	1315.2	1330.9	1337.3	1329.9
155°	1350.9	1341.5	1354.1	1360.4	1352.0
157.5°	1373.0	1364.6	1374.1	1381.5	1373.0
160°	1392.0	1385.6	1392.0	1398.2	1390.9
162.5°	1408.7	1402.5	1407.6	1415.1	1405.6
165°	1423.4	1417.2	1420.3	1427.6	1420.3
167.5°	1435.0	1428.7	1431.9	1439.2	1429.8
170°	1444.5	1438.1	1440.3	1447.6	1438.1
172.5°	1450.8	1444.5	1446.7	1454.0	1444.5
175°	1456.0	1448.6	1450.8	1458.1	1447.6
177.5°	1458.1	1450.8	1451.9	1459.2	1449.8
180°	1452.9	1452.9	1452.9	1452.9	1452.9



TEST NUMBER: P928928
 CATALOG NUMBER: DFN2DIP-HX4F0-070D050US935-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.94	10.88	10.82	11.79	12.93	9.51	10.45	10.39	11.35	12.50
	3H	11.61	12.45	12.50	13.37	14.54	11.14	11.98	12.03	12.89	14.07
	4H	12.20	13.00	13.11	13.92	15.10	11.73	12.53	12.64	13.44	14.63
	6H	12.61	13.34	13.53	14.27	15.46	12.13	12.87	13.05	13.79	14.99
	8H	12.71	13.42	13.64	14.36	15.55	12.24	12.94	13.17	13.88	15.08
	12H	12.77	13.43	13.70	14.37	15.59	12.28	12.95	13.22	13.89	15.11
4H	2H	10.41	11.21	11.33	12.13	13.31	10.07	10.87	10.98	11.79	12.97
	3H	12.29	12.96	13.21	13.90	15.10	11.90	12.56	12.82	13.51	14.71
	4H	13.01	13.62	13.94	14.56	15.78	12.60	13.21	13.54	14.15	15.38
	6H	13.53	14.05	14.48	15.02	16.24	13.12	13.64	14.07	14.61	15.83
	8H	13.68	14.17	14.63	15.13	16.37	13.27	13.76	14.22	14.72	15.96
	12H	13.76	14.20	14.73	15.18	16.42	13.34	13.78	14.31	14.76	16.00
8H	4H	13.21	13.70	14.16	14.66	15.90	12.85	13.34	13.80	14.30	15.54
	6H	13.85	14.25	14.82	15.26	16.49	13.48	13.89	14.46	14.89	16.13
	8H	14.07	14.43	15.06	15.42	16.67	13.70	14.06	14.69	15.05	16.30
	12H	14.21	14.52	15.20	15.51	16.81	13.82	14.14	14.81	15.12	16.42
12H	4H	13.20	13.64	14.17	14.62	15.86	12.85	13.29	13.82	14.27	15.51
	6H	13.88	14.24	14.86	15.23	16.48	13.53	13.89	14.51	14.88	16.13
	8H	14.12	14.44	15.11	15.43	16.73	13.77	14.08	14.76	15.07	16.37