

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P927690

Luminaire Tested: DFN2DIP-HX4F0-080D100US840-RLLONL

Issue Date: 12/12/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P927690  
REPORT IS A COMBINATION OF REPORTS P900936 AND P896187  
Test Lab: INNOVATION CENTER  
Issue Date: 12/12/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-HX4F0-080D100US840-RLONL  
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 16863.7 lumens  
Efficiency: N/A  
Efficacy: 110.4 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 152.8  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9613  
Total Harmonic Distortion (THDi): 0.083  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P927690  
CATALOG NUMBER: DFN2DIP-HX4F0-080D100US840-RLLONL

### Luminous Intensity Polar Plot





TEST NUMBER: P927690

CATALOG NUMBER: DFN2DIP-HX4F0-080D100US840-RLLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48	48	48	48	41
1	96	92	88	85	87	84	81	78	69	67	65	55	54	53	43	42	41	41	41	41	35
2	88	81	75	70	80	74	69	65	61	57	54	49	47	44	38	36	35	35	35	35	30
3	80	71	64	59	73	65	59	54	54	50	46	44	41	38	34	32	30	30	30	30	26
4	74	63	56	50	67	58	52	46	48	43	40	39	36	33	31	28	26	26	26	26	23
5	68	57	49	43	62	52	45	40	43	38	34	35	32	29	28	25	23	23	23	23	20
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	25	23	21	21	21	21	18
7	58	46	38	33	53	42	36	31	36	30	27	29	25	23	23	21	19	19	19	19	16
8	54	42	34	29	49	39	32	27	33	27	24	27	23	20	21	19	17	17	17	17	14
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	20	17	15	15	15	15	13
10	47	35	28	23	43	32	26	22	28	23	19	23	19	17	18	16	14	14	14	14	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	2483	2483	2483
5°	2487	2443	2459
10°	2462	2396	2379
15°	2429	2317	2256
20°	2384	2208	2104
25°	2338	2086	1957
30°	2277	1960	1771
35°	2217	1826	1608
40°	2155	1686	1421
45°	2084	1532	1251
50°	2011	1376	1086
55°	1934	1209	926
60°	1845	1034	763
65°	1743	856	686
70°	1619	691	622
75°	1463	610	566
80°	1238	512	491
85°	866	343	370

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 2084 cd/sqm



TEST NUMBER: P927690

CATALOG NUMBER: DFN2DIP-HX4F0-080D100US840-RLONL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	312.9	1.9
10°-20°	859.0	5.1
20°-30°	1206.0	7.2
30°-40°	1314.6	7.8
40°-50°	1208.3	7.2
50°-60°	948.9	5.6
60°-70°	617.7	3.7
70°-80°	318.0	1.9
80°-90°	87.2	0.5
90°-100°	112.4	0.7
100°-110°	418.9	2.5
110°-120°	1111.0	6.6
120°-130°	1842.7	10.9
130°-140°	1957.4	11.6
140°-150°	1819.2	10.8
150°-160°	1462.6	8.7
160°-170°	942.4	5.6
170°-180°	324.4	1.9
0°-30°	2378.0	14.1
0°-40°	3692.6	21.9
0°-60°	5849.9	34.7
0°-90°	6872.6	40.8
90°-120°	1642.3	9.7
90°-150°	7261.7	43.1
90°-180°	9991.0	59.2
0°-180°	16863.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	3339	3339	3339	3339	3339	
5°	3339	3324	3284	3312	3303	317
15°	3176	3142	3040	2982	2952	895
25°	2883	2786	2586	2463	2417	1326
35°	2484	2330	2064	1874	1807	1555
45°	2030	1828	1511	1296	1224	1568
55°	1544	1308	982	801	743	1380
65°	1042	798	526	423	414	1033
75°	556	344	242	220	218	588
85°	130	66	57	57	57	149
90°	2	30	49	62	66	16
95°	160	79	96	109	106	190
105°	750	824	151	177	187	801
115°	1418	1460	1522	380	202	1396
125°	2005	2037	2084	2101	2108	1788
135°	2481	2520	2542	2567	2562	1916
145°	2878	2875	2917	2934	2922	1800
155°	3169	3147	3176	3191	3171	1460
165°	3339	3324	3332	3349	3332	943
175°	3415	3398	3403	3420	3396	325
180°	3408	3408	3408	3408	3408	



TEST NUMBER: P927690

CATALOG NUMBER: DFN2DIP-HX4F0-080D100US840-RLONL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	3338.8	3338.8	3338.8	3338.8	3338.8
2.5°	3353.8	3338.8	3305.5	3335.9	3329.8
5°	3338.8	3323.8	3284.3	3311.5	3302.6
7.5°	3311.5	3293.6	3251.3	3263.2	3248.0
10°	3275.3	3254.2	3193.9	3184.6	3166.6
12.5°	3230.1	3202.9	3121.1	3103.1	3069.8
15°	3175.6	3142.3	3039.7	2982.3	2952.2
17.5°	3112.1	3063.7	2936.8	2870.5	2822.0
20°	3039.7	2979.1	2828.1	2752.8	2686.1
22.5°	2961.1	2891.6	2716.3	2613.7	2568.4
25°	2882.6	2785.8	2586.4	2462.7	2417.2
27.5°	2789.0	2686.1	2465.5	2323.5	2254.0
30°	2689.3	2574.2	2332.5	2178.6	2096.8
32.5°	2592.5	2453.4	2205.9	2024.4	1948.8
35°	2483.8	2329.6	2063.8	1873.5	1806.7
37.5°	2378.0	2211.7	1930.8	1722.1	1646.8
40°	2266.2	2085.0	1791.7	1577.2	1498.6
42.5°	2151.4	1958.1	1652.8	1429.2	1353.7
45°	2030.5	1827.9	1510.9	1296.1	1223.7
47.5°	1915.8	1701.3	1374.9	1160.2	1093.8
50°	1788.8	1574.4	1242.0	1033.2	970.0
52.5°	1664.8	1438.1	1114.9	915.6	858.2
55°	1543.9	1308.3	981.9	800.8	743.4
57.5°	1420.2	1178.4	864.3	695.0	646.6
60°	1293.1	1051.5	740.2	586.3	537.9
62.5°	1169.4	927.7	634.5	489.6	465.5
65°	1042.5	797.5	525.7	423.2	413.8
67.5°	921.6	676.8	423.2	371.5	362.6
70°	794.7	559.1	350.4	320.2	308.1
72.5°	673.8	450.1	293.0	269.0	262.9
75°	555.9	344.3	241.7	220.5	217.7
77.5°	438.3	244.6	190.4	178.2	172.2
80°	329.2	175.4	144.9	133.0	133.0
82.5°	229.5	117.9	99.7	93.6	93.6
85°	129.9	66.3	57.4	57.4	57.4
87.5°	48.4	24.0	24.0	21.2	21.2
90°	2.3	29.6	49.2	61.8	66.4
92.5°	61.8	51.8	59.2	64.1	66.4
95°	160.2	78.8	96.0	108.7	106.0
97.5°	288.4	86.3	125.6	133.2	135.6
100°	436.6	98.7	140.6	160.2	165.2
102.5°	599.1	594.5	145.5	172.5	180.0
105°	749.7	823.7	150.6	177.4	187.4
107.5°	924.8	986.3	155.5	182.5	192.4
110°	1092.5	1144.1	431.6	185.1	194.7



TEST NUMBER: P927690

CATALOG NUMBER: DFN2DIP-HX4F0-080D100US840-RLONL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	1250.3	1294.6	1252.8	189.7	197.4
115°	1417.9	1459.8	1521.6	379.8	202.4
117.5°	1563.4	1612.7	1654.8	1301.9	656.0
120°	1726.3	1763.1	1807.6	1837.2	1504.3
122.5°	1864.2	1903.7	1953.2	1967.8	1970.4
125°	2004.8	2037.0	2083.8	2101.1	2108.4
127.5°	2133.0	2167.5	2204.7	2229.3	2231.7
130°	2253.9	2293.5	2320.4	2347.6	2345.3
132.5°	2377.2	2409.4	2436.3	2458.6	2456.2
135°	2480.9	2520.4	2542.4	2567.2	2562.3
137.5°	2589.2	2618.8	2643.7	2668.3	2660.9
140°	2695.2	2715.2	2742.0	2764.3	2752.0
142.5°	2784.2	2801.5	2833.4	2853.0	2840.8
145°	2877.9	2875.3	2917.2	2934.5	2922.2
147.5°	2959.0	2951.7	2993.6	3005.9	2996.3
150°	3038.1	3020.8	3060.4	3075.0	3062.7
152.5°	3104.5	3084.9	3121.9	3136.7	3119.5
155°	3168.8	3146.7	3176.3	3191.0	3171.4
157.5°	3220.6	3201.0	3223.2	3240.4	3220.6
160°	3265.1	3250.1	3265.1	3279.7	3262.5
162.5°	3304.3	3289.6	3301.9	3319.2	3297.0
165°	3338.8	3324.2	3331.5	3348.8	3331.5
167.5°	3366.1	3351.1	3358.8	3376.1	3353.7
170°	3388.3	3373.4	3378.4	3395.7	3373.4
172.5°	3402.9	3388.3	3393.3	3410.6	3388.3
175°	3415.2	3398.0	3402.9	3420.3	3395.7
177.5°	3420.3	3402.9	3405.7	3422.9	3400.6
180°	3408.0	3408.0	3408.0	3408.0	3408.0



TEST NUMBER: P927690  
 CATALOG NUMBER: DFN2DIP-HX4F0-080D100US840-RLONL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.38	10.14	10.42	11.18	12.58	5.35	6.11	6.39	7.15	8.55
	3H	11.05	11.73	12.10	12.78	14.20	6.54	7.22	7.59	8.27	9.68
	4H	11.66	12.30	12.72	13.35	14.78	6.98	7.63	8.05	8.68	10.11
	6H	12.08	12.67	13.15	13.72	15.16	7.30	7.90	8.37	8.95	10.39
	8H	12.20	12.76	13.28	13.84	15.27	7.39	7.96	8.47	9.03	10.46
	12H	12.26	12.80	13.34	13.86	15.32	7.44	7.97	8.51	9.04	10.49
4H	2H	9.39	10.03	10.46	11.08	12.51	5.94	6.58	7.01	7.63	9.06
	3H	11.21	11.75	12.29	12.83	14.27	7.28	7.82	8.36	8.90	10.34
	4H	11.90	12.39	12.98	13.46	14.92	7.83	8.32	8.91	9.39	10.85
	6H	12.42	12.84	13.50	13.93	15.38	8.25	8.67	9.34	9.76	11.22
	8H	12.59	12.98	13.68	14.07	15.54	8.38	8.77	9.47	9.85	11.33
	12H	12.68	13.04	13.79	14.14	15.61	8.44	8.79	9.55	9.89	11.37
8H	4H	11.87	12.26	12.95	13.34	14.81	8.11	8.50	9.20	9.58	11.05
	6H	12.43	12.75	13.54	13.88	15.35	8.62	8.95	9.74	10.08	11.54
	8H	12.65	12.93	13.76	14.04	15.53	8.82	9.10	9.93	10.21	11.70
	12H	12.78	13.03	13.90	14.14	15.66	8.93	9.18	10.05	10.29	11.81
12H	4H	11.81	12.17	12.92	13.27	14.74	8.11	8.46	9.21	9.56	11.04
	6H	12.41	12.69	13.52	13.80	15.29	8.67	8.96	9.79	10.07	11.55
	8H	12.62	12.87	13.74	13.98	15.50	8.88	9.13	10.00	10.24	11.76