

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P919137

Luminaire Tested: DFN2DIP-HX4F0-080D090US935-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P919137
REPORT IS A COMBINATION OF REPORTS P899398 AND P896188
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-080D090US935-RLLFLL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12712.6 lumens
Efficiency: N/A
Efficacy: 99.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 127.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9613
Total Harmonic Distortion (THDi): 0.083
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P919137

CATALOG NUMBER: DFN2DIP-HX4F0-080D090US935-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P919137

CATALOG NUMBER: DFN2DIP-HX4F0-080D090US935-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	53	53	53
1	97	93	90	86	89	86	83	80	72	70	68	59	57	56	47	46	45
2	89	82	76	71	82	75	70	66	63	60	57	52	50	47	42	40	39
3	81	72	65	60	75	67	61	56	56	52	48	47	43	41	38	35	33
4	75	64	57	51	68	59	53	48	50	45	41	42	38	35	34	31	29
5	69	58	50	44	63	53	46	41	45	40	36	38	34	31	31	28	26
6	63	52	44	38	58	48	41	36	41	36	32	34	30	27	28	25	23
7	59	47	39	34	54	44	37	32	37	32	28	31	27	24	26	23	21
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19
9	51	39	32	27	47	36	30	25	31	26	22	26	22	20	22	19	17
10	48	36	29	24	44	33	27	23	29	24	20	25	21	18	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2117	2117	2117
5°	2120	2083	2097
10°	2099	2043	2028
15°	2071	1975	1923
20°	2033	1883	1794
25°	1994	1778	1669
30°	1941	1672	1510
35°	1890	1557	1371
40°	1838	1438	1212
45°	1777	1306	1067
50°	1714	1173	926
55°	1649	1030	790
60°	1573	882	650
65°	1486	730	585
70°	1380	589	530
75°	1248	520	482
80°	1056	437	419
85°	738	293	315

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1848 cd/sqm

TEST NUMBER: P919137

CATALOG NUMBER: DFN2DIP-HX4F0-080D090US935-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	266.8	2.1
10°-20°	732.4	5.8
20°-30°	1028.3	8.1
30°-40°	1120.9	8.8
40°-50°	1030.3	8.1
50°-60°	809.1	6.4
60°-70°	526.6	4.1
70°-80°	271.1	2.1
80°-90°	76.2	0.6
90°-100°	151.6	1.2
100°-110°	481.8	3.8
110°-120°	824.6	6.5
120°-130°	1084.4	8.5
130°-140°	1217.2	9.6
140°-150°	1193.6	9.4
150°-160°	1001.3	7.9
160°-170°	664.0	5.2
170°-180°	232.1	1.8
0°-30°	2027.6	15.9
0°-40°	3148.5	24.8
0°-60°	4987.8	39.2
0°-90°	5861.8	46.1
90°-120°	1458.0	11.5
90°-150°	4953.4	39.0
90°-180°	6851.0	53.9
0°-180°	12712.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2847	2847	2847	2847	2847	
5°	2847	2834	2800	2824	2816	270
15°	2708	2679	2592	2543	2517	763
25°	2458	2375	2205	2100	2061	1130
35°	2118	1986	1760	1597	1540	1326
45°	1731	1559	1288	1105	1043	1337
55°	1316	1116	837	683	634	1176
65°	889	680	448	361	353	881
75°	474	294	206	188	186	501
85°	111	57	49	49	49	127
90°	2	27	72	68	70	13
95°	108	128	132	132	128	120
105°	445	451	455	459	459	469
115°	828	839	836	833	828	818
125°	1204	1222	1216	1209	1207	1076
135°	1557	1580	1584	1582	1576	1203
145°	1890	1905	1916	1919	1911	1181
155°	2161	2167	2174	2184	2177	995
165°	2351	2349	2349	2364	2353	663
175°	2446	2440	2436	2451	2438	232
180°	2451	2451	2451	2451	2451	

TEST NUMBER: P919137

CATALOG NUMBER: DFN2DIP-HX4F0-080D090US935-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2846.8	2846.8	2846.8	2846.8	2846.8
2.5°	2859.6	2846.8	2818.4	2844.3	2839.1
5°	2846.8	2834.0	2800.3	2823.6	2815.9
7.5°	2823.6	2808.2	2772.2	2782.3	2769.4
10°	2792.6	2774.7	2723.3	2715.3	2700.0
12.5°	2754.2	2730.9	2661.2	2645.8	2617.4
15°	2707.7	2679.3	2591.8	2542.9	2517.1
17.5°	2653.5	2612.3	2504.0	2447.5	2406.1
20°	2591.8	2540.1	2411.4	2347.2	2290.3
22.5°	2524.8	2465.5	2316.0	2228.5	2189.9
25°	2457.8	2375.3	2205.3	2099.8	2061.0
27.5°	2378.0	2290.3	2102.2	1981.2	1921.8
30°	2293.0	2194.9	1988.8	1857.6	1787.9
32.5°	2210.4	2091.9	1880.8	1726.1	1661.6
35°	2117.8	1986.3	1759.7	1597.4	1540.5
37.5°	2027.6	1885.8	1646.3	1468.3	1404.1
40°	1932.3	1777.8	1527.7	1344.8	1277.8
42.5°	1834.4	1669.6	1409.3	1218.6	1154.3
45°	1731.3	1558.6	1288.2	1105.1	1043.4
47.5°	1633.5	1450.6	1172.3	989.2	932.6
50°	1525.2	1342.4	1058.9	881.0	827.1
52.5°	1419.4	1226.1	950.6	780.7	731.8
55°	1316.4	1115.5	837.2	682.8	633.9
57.5°	1210.9	1004.8	736.9	592.6	551.3
60°	1102.6	896.6	631.1	499.9	458.7
62.5°	997.1	791.0	541.0	417.4	396.9
65°	888.9	680.0	448.2	360.8	352.8
67.5°	785.8	577.0	360.8	316.8	309.2
70°	677.6	476.7	298.8	273.0	262.7
72.5°	574.5	383.7	249.9	229.4	224.1
75°	474.0	293.6	206.1	188.0	185.6
77.5°	373.7	208.5	162.4	152.0	146.8
80°	280.7	149.6	123.6	113.4	113.4
82.5°	195.7	100.6	85.0	79.8	79.8
85°	110.7	56.6	48.9	48.9	48.9
87.5°	41.2	20.5	20.5	18.1	18.1
90°	2.2	26.6	72.4	67.9	70.2
92.5°	45.8	62.1	64.3	66.5	66.5
95°	107.9	128.5	132.2	132.2	128.5
97.5°	179.5	198.7	206.9	206.9	206.9
100°	262.3	279.3	285.2	285.2	283.0
102.5°	349.5	362.0	370.1	372.4	370.1
105°	444.8	450.6	455.1	458.8	458.8
107.5°	539.3	548.2	548.2	549.7	539.3
110°	630.9	642.8	642.8	642.8	636.9

TEST NUMBER: P919137

CATALOG NUMBER: DFN2DIP-HX4F0-080D090US935-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	730.0	742.5	740.3	734.4	730.0
115°	827.5	839.3	835.6	833.4	827.5
117.5°	924.3	940.6	930.2	924.3	918.3
120°	1021.8	1038.0	1021.8	1021.8	1015.1
122.5°	1110.4	1131.2	1120.8	1114.9	1110.4
125°	1203.6	1222.0	1216.2	1209.4	1207.3
127.5°	1294.4	1317.3	1309.2	1300.4	1294.4
130°	1379.4	1406.0	1402.3	1397.8	1389.7
132.5°	1474.7	1495.4	1496.8	1486.5	1480.7
135°	1556.7	1579.6	1584.1	1581.8	1576.0
137.5°	1648.3	1666.8	1670.5	1669.0	1660.2
140°	1728.9	1747.3	1757.6	1757.6	1749.5
142.5°	1811.6	1830.1	1836.0	1838.2	1830.1
145°	1890.0	1904.7	1916.5	1918.7	1910.6
147.5°	1960.1	1978.6	1987.4	1991.1	1983.1
150°	2032.6	2045.1	2053.2	2059.9	2053.2
152.5°	2096.8	2109.4	2119.7	2127.9	2119.7
155°	2161.1	2167.0	2173.7	2184.0	2177.4
157.5°	2216.5	2220.9	2224.6	2239.4	2229.0
160°	2266.0	2270.5	2272.7	2285.2	2276.3
162.5°	2311.8	2311.8	2314.0	2328.1	2317.7
165°	2351.0	2348.7	2348.7	2363.5	2353.2
167.5°	2386.4	2379.8	2379.8	2394.5	2384.2
170°	2413.0	2407.1	2404.9	2419.7	2407.1
172.5°	2431.5	2425.6	2423.4	2438.2	2425.6
175°	2446.3	2440.3	2435.9	2450.7	2438.2
177.5°	2454.4	2448.5	2444.0	2456.6	2444.0
180°	2450.7	2450.7	2450.7	2450.7	2450.7

TEST NUMBER: P919137

CATALOG NUMBER: DFN2DIP-HX4F0-080D090US935-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.38	10.18	10.37	11.18	12.51	5.35	6.15	6.35	7.15	8.48
	3H	11.05	11.77	12.06	12.78	14.13	6.54	7.25	7.54	8.26	9.61
	4H	11.66	12.34	12.68	13.35	14.71	6.99	7.66	8.01	8.68	10.04
	6H	12.08	12.70	13.11	13.72	15.09	7.31	7.93	8.34	8.95	10.32
	8H	12.21	12.80	13.24	13.84	15.20	7.40	7.99	8.44	9.03	10.39
	12H	12.27	12.83	13.31	13.86	15.25	7.44	8.01	8.48	9.04	10.42
4H	2H	9.39	10.07	10.42	11.08	12.44	5.94	6.62	6.97	7.63	8.99
	3H	11.22	11.78	12.25	12.83	14.20	7.29	7.85	8.33	8.90	10.27
	4H	11.91	12.43	12.95	13.46	14.85	7.84	8.35	8.88	9.39	10.78
	6H	12.43	12.87	13.48	13.93	15.32	8.26	8.70	9.31	9.76	11.15
	8H	12.60	13.01	13.65	14.06	15.47	8.39	8.80	9.44	9.85	11.26
	12H	12.69	13.07	13.76	14.13	15.54	8.45	8.83	9.52	9.89	11.30
8H	4H	11.88	12.29	12.93	13.34	14.74	8.12	8.53	9.17	9.58	10.99
	6H	12.44	12.78	13.52	13.88	15.28	8.64	8.98	9.71	10.07	11.47
	8H	12.66	12.96	13.74	14.04	15.46	8.83	9.13	9.91	10.21	11.63
	12H	12.80	13.06	13.88	14.13	15.60	8.95	9.21	10.03	10.28	11.75
12H	4H	11.83	12.20	12.90	13.27	14.67	8.12	8.49	9.19	9.56	10.97
	6H	12.42	12.72	13.50	13.80	15.22	8.69	8.99	9.77	10.06	11.48
	8H	12.64	12.90	13.72	13.97	15.44	8.90	9.16	9.98	10.23	11.69

END OF REPORT