

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P927746

Luminaire Tested: DFN2DIP-HX4F0-100D060US840-RLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P927746
REPORT IS A COMBINATION OF REPORTS P900868 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-100D060US840-RLLONL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 14581.5 lumens
Efficiency: N/A
Efficacy: 101.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 143.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.946
Total Harmonic Distortion (THDi): 0.132
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P927746

CATALOG NUMBER: DFN2DIP-HX4F0-100D060US840-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P927746

CATALOG NUMBER: DFN2DIP-HX4F0-100D060US840-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64
1	100	96	92	89	94	90	87	84	78	76	74	68	66	64	58	57	55
2	92	85	79	74	86	79	74	70	69	65	62	60	57	55	51	49	48
3	84	75	68	62	78	70	64	59	62	57	53	54	50	47	46	43	41
4	77	67	59	53	72	63	56	51	55	50	46	48	44	41	42	39	36
5	71	60	52	46	66	56	49	44	50	44	40	44	39	36	38	34	32
6	66	54	46	40	61	51	44	38	45	39	35	40	35	32	35	31	28
7	61	49	41	36	57	46	39	34	41	35	31	36	32	28	32	28	25
8	57	45	37	32	53	42	35	30	38	32	28	33	29	25	29	26	23
9	53	41	34	29	50	39	32	27	35	29	25	31	26	23	27	23	21
10	50	38	31	26	46	36	29	25	32	27	23	29	24	21	25	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3103	3103	3103
5°	3108	3054	3074
10°	3078	2995	2974
15°	3036	2896	2819
20°	2980	2760	2630
25°	2923	2607	2447
30°	2846	2451	2214
35°	2771	2282	2010
40°	2694	2108	1776
45°	2605	1915	1564
50°	2513	1719	1357
55°	2417	1511	1158
60°	2306	1293	953
65°	2178	1071	858
70°	2023	864	777
75°	1829	762	707
80°	1547	641	614
85°	1082	429	462

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2605 cd/sqm

TEST NUMBER: P927746

CATALOG NUMBER: DFN2DIP-HX4F0-100D060US840-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	391.1	2.7
10°-20°	1073.8	7.4
20°-30°	1507.5	10.3
30°-40°	1643.3	11.3
40°-50°	1510.4	10.4
50°-60°	1186.2	8.1
60°-70°	772.1	5.3
70°-80°	397.4	2.7
80°-90°	105.1	0.7
90°-100°	67.4	0.5
100°-110°	251.3	1.7
110°-120°	666.6	4.6
120°-130°	1105.6	7.6
130°-140°	1174.4	8.1
140°-150°	1091.5	7.5
150°-160°	877.5	6.0
160°-170°	565.5	3.9
170°-180°	194.6	1.3
0°-30°	2972.4	20.4
0°-40°	4615.8	31.7
0°-60°	7312.3	50.1
0°-90°	8586.9	58.9
90°-120°	985.4	6.8
90°-150°	4357.0	29.9
90°-180°	5995.0	41.1
0°-180°	14581.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4174	4174	4174	4174	4174	
5°	4174	4155	4105	4140	4128	396
15°	3970	3928	3800	3728	3690	1119
25°	3603	3482	3233	3078	3021	1657
35°	3105	2912	2580	2342	2258	1943
45°	2538	2285	1889	1620	1530	1960
55°	1930	1635	1227	1001	929	1724
65°	1303	997	657	529	517	1292
75°	695	430	302	276	272	735
85°	162	83	72	72	72	186
90°	1	18	30	37	40	14
95°	96	47	58	65	64	114
105°	450	494	90	106	112	481
115°	851	876	913	228	121	838
125°	1203	1222	1250	1261	1265	1073
135°	1488	1512	1525	1540	1537	1150
145°	1727	1725	1750	1761	1753	1080
155°	1901	1888	1906	1915	1903	876
165°	2003	1995	1999	2009	1999	566
175°	2049	2039	2042	2052	2037	195
180°	2045	2045	2045	2045	2045	

TEST NUMBER: P927746

CATALOG NUMBER: DFN2DIP-HX4F0-100D060US840-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4173.5	4173.5	4173.5	4173.5	4173.5
2.5°	4192.3	4173.5	4131.8	4169.9	4162.3
5°	4173.5	4154.6	4105.3	4139.5	4128.2
7.5°	4139.5	4117.0	4064.0	4078.9	4060.1
10°	4094.1	4067.7	3992.3	3980.7	3958.3
12.5°	4037.7	4003.6	3901.4	3878.9	3837.2
15°	3969.5	3927.8	3799.6	3727.9	3690.2
17.5°	3890.2	3829.7	3671.0	3588.0	3527.5
20°	3799.6	3723.8	3535.1	3441.0	3357.6
22.5°	3701.4	3614.5	3395.3	3267.1	3210.6
25°	3603.3	3482.3	3233.0	3078.3	3021.4
27.5°	3486.2	3357.6	3081.9	2904.4	2817.4
30°	3361.6	3217.7	2915.6	2723.3	2621.1
32.5°	3240.7	3066.7	2757.4	2530.6	2435.9
35°	3104.7	2912.1	2579.8	2341.8	2258.4
37.5°	2972.5	2764.5	2413.5	2152.7	2058.5
40°	2832.7	2606.3	2239.6	1971.5	1873.4
42.5°	2689.2	2447.6	2066.2	1786.4	1692.2
45°	2538.1	2284.9	1888.6	1620.1	1529.5
47.5°	2394.7	2126.6	1718.7	1450.2	1367.3
50°	2236.0	1967.9	1552.4	1291.5	1212.6
52.5°	2080.9	1797.6	1393.7	1144.4	1072.7
55°	1929.8	1635.4	1227.4	1001.0	929.2
57.5°	1775.2	1473.0	1080.4	868.7	808.2
60°	1616.5	1314.4	925.3	732.9	672.4
62.5°	1461.8	1159.7	793.0	611.9	581.8
65°	1303.1	997.0	657.2	528.9	517.3
67.5°	1152.1	845.9	528.9	464.4	453.2
70°	993.3	698.9	438.0	400.3	385.1
72.5°	842.3	562.6	366.3	336.2	328.6
75°	694.8	430.4	302.1	275.7	272.0
77.5°	547.8	305.8	238.0	222.8	215.2
80°	411.5	219.2	181.2	166.3	166.3
82.5°	286.9	147.4	124.6	117.0	117.0
85°	162.3	82.9	71.7	71.7	71.7
87.5°	60.5	30.1	30.1	26.5	26.5
90°	1.4	17.8	29.5	37.1	39.9
92.5°	37.1	31.1	35.4	38.5	39.9
95°	96.1	47.3	57.7	65.2	63.6
97.5°	173.1	51.8	75.3	80.0	81.4
100°	261.9	59.2	84.3	96.1	99.1
102.5°	359.5	356.7	87.3	103.5	108.0
105°	449.8	494.2	90.3	106.4	112.5
107.5°	554.9	591.7	93.3	109.5	115.4
110°	655.6	686.5	259.0	111.1	116.8

TEST NUMBER: P927746

CATALOG NUMBER: DFN2DIP-HX4F0-100D060US840-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	750.2	776.7	751.6	113.8	118.4
115°	850.8	875.9	913.0	227.9	121.4
117.5°	938.0	967.6	992.8	781.2	393.5
120°	1035.8	1057.9	1084.6	1102.3	902.6
122.5°	1118.5	1142.2	1171.9	1180.7	1182.3
125°	1202.9	1222.2	1250.2	1260.6	1265.0
127.5°	1279.8	1300.5	1322.8	1337.6	1339.0
130°	1352.3	1376.1	1392.2	1408.6	1407.2
132.5°	1426.3	1445.6	1461.8	1475.1	1473.7
135°	1488.5	1512.3	1525.4	1540.3	1537.3
137.5°	1553.5	1571.2	1586.2	1600.9	1596.6
140°	1617.1	1629.1	1645.3	1658.6	1651.2
142.5°	1670.5	1680.9	1700.1	1711.8	1704.4
145°	1726.8	1725.1	1750.3	1760.7	1753.3
147.5°	1775.4	1771.0	1796.1	1803.5	1797.7
150°	1822.9	1812.5	1836.2	1845.0	1837.6
152.5°	1862.8	1851.0	1873.1	1882.1	1871.7
155°	1901.3	1888.0	1905.8	1914.6	1902.8
157.5°	1932.4	1920.5	1933.9	1944.3	1932.4
160°	1959.0	1950.0	1959.0	1967.8	1957.5
162.5°	1982.5	1973.8	1981.1	1991.5	1978.2
165°	2003.3	1994.6	1998.9	2009.3	1998.9
167.5°	2019.6	2010.7	2015.3	2025.7	2012.2
170°	2033.0	2024.0	2027.1	2037.4	2024.0
172.5°	2041.8	2033.0	2036.0	2046.4	2033.0
175°	2049.2	2038.8	2041.8	2052.1	2037.4
177.5°	2052.1	2041.8	2043.3	2053.7	2040.4
180°	2044.7	2044.7	2044.7	2044.7	2044.7

TEST NUMBER: P927746

CATALOG NUMBER: DFN2DIP-HX4F0-100D060US840-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.87	12.78	12.76	13.68	14.82	7.85	8.76	8.73	9.65	10.80
	3H	13.56	14.37	14.46	15.28	16.45	9.04	9.86	9.94	10.76	11.93
	4H	14.17	14.94	15.08	15.85	17.03	9.50	10.27	10.41	11.18	12.36
	6H	14.60	15.30	15.52	16.22	17.41	9.83	10.53	10.75	11.45	12.64
	8H	14.73	15.40	15.66	16.34	17.52	9.92	10.59	10.85	11.53	12.72
	12H	14.79	15.43	15.73	16.36	17.58	9.97	10.61	10.90	11.54	12.75
4H	2H	11.90	12.67	12.82	13.58	14.76	8.45	9.22	9.37	10.13	11.31
	3H	13.74	14.38	14.67	15.32	16.51	9.81	10.45	10.74	11.39	12.59
	4H	14.44	15.02	15.37	15.96	17.17	10.36	10.94	11.30	11.89	13.10
	6H	14.96	15.46	15.91	16.42	17.64	10.79	11.29	11.74	12.25	13.47
	8H	15.13	15.60	16.09	16.56	17.79	10.92	11.39	11.87	12.35	13.58
	12H	15.23	15.65	16.20	16.63	17.86	10.99	11.41	11.96	12.39	13.62
8H	4H	14.41	14.88	15.36	15.83	17.07	10.65	11.12	11.60	12.08	13.31
	6H	14.98	15.37	15.96	16.37	17.59	11.17	11.56	12.15	12.56	13.79
	8H	15.20	15.54	16.19	16.53	17.77	11.37	11.71	12.36	12.70	13.94
	12H	15.34	15.64	16.33	16.62	17.92	11.49	11.79	12.48	12.77	14.07
12H	4H	14.37	14.79	15.34	15.76	17.00	10.66	11.08	11.63	12.06	13.29
	6H	14.96	15.30	15.94	16.29	17.53	11.22	11.56	12.21	12.55	13.80
	8H	15.18	15.48	16.17	16.46	17.76	11.44	11.74	12.43	12.72	14.02

END OF REPORT