

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P919189

Luminaire Tested: DFN2DIP-HX4F0-110D080US935-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P919189
REPORT IS A COMBINATION OF REPORTS P899386 AND P896188
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-110D080US935-RLLFLL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 14146.2 lumens
Efficiency: N/A
Efficacy: 89.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 157.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9967
Total Harmonic Distortion (THDi): 0.063
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P919189

CATALOG NUMBER: DFN2DIP-HX4F0-110D080US935-RLFL

Luminous Intensity Polar Plot



TEST NUMBER: P919189

CATALOG NUMBER: DFN2DIP-HX4F0-110D080US935-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	109	109	109	109		101	101	101	101		87	87	87		74	74	74		63	63	63
1	100	96	92	89		93	89	86	83		77	75	73		66	65	63		56	55	54
2	91	84	78	73		85	79	74	69		68	65	61		59	56	54		50	48	46
3	84	75	67	62		78	70	64	58		61	56	52		53	49	46		45	42	40
4	77	66	59	53		71	62	55	50		54	49	45		47	43	40		40	37	35
5	71	59	52	46		66	56	49	43		49	43	39		43	38	35		37	33	31
6	65	54	46	40		61	50	43	38		44	39	34		39	34	31		34	30	27
7	61	49	41	35		57	46	39	34		40	35	31		35	31	28		31	27	25
8	56	44	37	31		53	42	35	30		37	31	27		33	28	25		28	25	22
9	53	41	33	28		49	38	32	27		34	29	25		30	26	22		26	23	20
10	49	37	30	26		46	35	29	24		32	26	22		28	24	20		24	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2911	2911	2911
5°	2915	2865	2883
10°	2887	2809	2789
15°	2847	2716	2644
20°	2795	2588	2466
25°	2741	2445	2295
30°	2669	2298	2077
35°	2599	2141	1885
40°	2527	1977	1666
45°	2444	1796	1467
50°	2357	1613	1273
55°	2267	1417	1086
60°	2163	1212	894
65°	2043	1004	805
70°	1898	810	729
75°	1716	715	663
80°	1452	601	576
85°	1015	402	433

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2444 cd/sqm

TEST NUMBER: P919189

CATALOG NUMBER: DFN2DIP-HX4F0-110D080US935-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	366.9	2.6
10°-20°	1007.1	7.1
20°-30°	1413.9	10.0
30°-40°	1541.3	10.9
40°-50°	1416.6	10.0
50°-60°	1112.5	7.9
60°-70°	724.2	5.1
70°-80°	372.8	2.6
80°-90°	101.4	0.7
90°-100°	134.8	1.0
100°-110°	428.3	3.0
110°-120°	733.0	5.2
120°-130°	964.0	6.8
130°-140°	1082.0	7.6
140°-150°	1061.0	7.5
150°-160°	890.1	6.3
160°-170°	590.3	4.2
170°-180°	206.3	1.5
0°-30°	2787.9	19.7
0°-40°	4329.1	30.6
0°-60°	6858.3	48.5
0°-90°	8056.5	57.0
90°-120°	1296.1	9.2
90°-150°	4403.1	31.1
90°-180°	6090.0	43.1
0°-180°	14146.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3914	3914	3914	3914	3914	
5°	3914	3897	3850	3882	3872	371
15°	3723	3684	3564	3496	3461	1049
25°	3380	3266	3032	2887	2834	1554
35°	2912	2731	2420	2196	2118	1823
45°	2381	2143	1771	1520	1435	1838
55°	1810	1534	1151	939	872	1617
65°	1222	935	616	496	485	1212
75°	652	404	283	259	255	689
85°	152	78	67	67	67	175
90°	2	24	64	60	62	14
95°	96	114	118	118	114	107
105°	395	401	405	408	408	417
115°	736	746	743	741	736	728
125°	1070	1086	1081	1075	1073	956
135°	1384	1404	1408	1406	1401	1070
145°	1680	1693	1704	1706	1698	1050
155°	1921	1926	1932	1941	1935	884
165°	2090	2088	2088	2101	2092	590
175°	2174	2169	2165	2178	2167	207
180°	2178	2178	2178	2178	2178	

TEST NUMBER: P919189

CATALOG NUMBER: DFN2DIP-HX4F0-110D080US935-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3914.4	3914.4	3914.4	3914.4	3914.4
2.5°	3932.0	3914.4	3875.3	3911.0	3903.9
5°	3914.4	3896.7	3850.5	3882.4	3871.9
7.5°	3882.4	3861.3	3811.7	3825.7	3807.9
10°	3840.0	3815.1	3744.5	3733.5	3712.5
12.5°	3786.9	3755.0	3659.2	3638.1	3599.0
15°	3723.0	3684.0	3563.7	3496.4	3461.0
17.5°	3648.7	3591.9	3443.0	3365.2	3308.5
20°	3563.7	3492.6	3315.6	3227.3	3149.1
22.5°	3471.6	3390.0	3184.5	3064.2	3011.2
25°	3379.5	3266.0	3032.3	2887.2	2833.8
27.5°	3269.8	3149.1	2890.5	2724.0	2642.5
30°	3152.9	3018.0	2734.6	2554.2	2458.3
32.5°	3039.4	2876.2	2586.1	2373.4	2284.7
35°	2912.0	2731.2	2419.7	2196.4	2118.2
37.5°	2788.0	2592.9	2263.6	2019.0	1930.7
40°	2656.8	2444.5	2100.6	1849.1	1757.0
42.5°	2522.2	2295.6	1937.8	1675.5	1587.2
45°	2380.6	2143.0	1771.3	1519.5	1434.6
47.5°	2246.0	1994.6	1612.0	1360.1	1282.4
50°	2097.1	1845.7	1456.0	1211.3	1137.3
52.5°	1951.7	1686.0	1307.2	1073.4	1006.1
55°	1810.0	1533.8	1151.2	938.8	871.6
57.5°	1665.0	1381.6	1013.2	814.8	758.0
60°	1516.1	1232.8	867.8	687.4	630.7
62.5°	1371.1	1087.7	743.8	573.9	545.7
65°	1222.2	935.0	616.4	496.1	485.2
67.5°	1080.6	793.4	496.1	435.6	425.1
70°	931.7	655.5	410.8	375.5	361.2
72.5°	790.0	527.7	343.5	315.3	308.2
75°	651.7	403.6	283.4	258.6	255.2
77.5°	513.8	286.8	223.3	209.0	201.8
80°	386.0	205.6	169.9	156.0	156.0
82.5°	269.1	138.3	116.9	109.8	109.8
85°	152.2	77.8	67.2	67.2	67.2
87.5°	56.7	28.2	28.2	24.8	24.8
90°	2.0	23.7	64.4	60.4	62.4
92.5°	40.7	55.2	57.2	59.1	59.1
95°	95.9	114.3	117.5	117.5	114.3
97.5°	159.6	176.7	183.9	183.9	183.9
100°	233.2	248.2	253.5	253.5	251.5
102.5°	310.6	321.8	329.0	331.0	329.0
105°	395.4	400.6	404.6	407.9	407.9
107.5°	479.4	487.3	487.3	488.6	479.4
110°	560.9	571.4	571.4	571.4	566.1



TEST NUMBER: P919189

CATALOG NUMBER: DFN2DIP-HX4F0-110D080US935-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	648.8	660.0	658.1	652.8	648.8
115°	735.6	746.1	742.8	740.8	735.6
117.5°	821.6	836.0	826.8	821.6	816.3
120°	908.3	922.7	908.3	908.3	902.3
122.5°	987.0	1005.5	996.3	991.0	987.0
125°	1069.8	1086.2	1081.0	1075.0	1073.1
127.5°	1150.6	1171.0	1163.7	1155.9	1150.6
130°	1226.1	1249.7	1246.5	1242.6	1235.4
132.5°	1310.9	1329.2	1330.6	1321.4	1316.1
135°	1383.7	1404.1	1408.1	1406.1	1400.8
137.5°	1465.2	1481.6	1484.9	1483.6	1475.7
140°	1536.8	1553.2	1562.4	1562.4	1555.1
142.5°	1610.3	1626.8	1632.0	1634.0	1626.8
145°	1680.0	1693.1	1703.6	1705.6	1698.3
147.5°	1742.3	1758.8	1766.6	1770.0	1762.7
150°	1806.7	1817.8	1825.1	1831.0	1825.1
152.5°	1863.8	1875.0	1884.2	1891.4	1884.2
155°	1921.0	1926.2	1932.2	1941.3	1935.4
157.5°	1970.2	1974.2	1977.5	1990.5	1981.4
160°	2014.2	2018.2	2020.2	2031.3	2023.4
162.5°	2054.9	2054.9	2056.9	2069.4	2060.2
165°	2089.7	2087.7	2087.7	2100.9	2091.7
167.5°	2121.2	2115.4	2115.4	2128.5	2119.3
170°	2144.9	2139.7	2137.7	2150.9	2139.7
172.5°	2161.4	2156.1	2154.1	2167.2	2156.1
175°	2174.5	2169.2	2165.2	2178.4	2167.2
177.5°	2181.7	2176.4	2172.5	2183.7	2172.5
180°	2178.4	2178.4	2178.4	2178.4	2178.4

TEST NUMBER: P919189

CATALOG NUMBER: DFN2DIP-HX4F0-110D080US935-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.48	12.37	12.39	13.29	14.46	7.46	8.35	8.36	9.26	10.44
	3H	13.17	13.96	14.08	14.89	16.09	8.65	9.45	9.57	10.37	11.57
	4H	13.78	14.53	14.71	15.46	16.67	9.11	9.86	10.04	10.79	12.00
	6H	14.20	14.90	15.15	15.83	17.05	9.43	10.12	10.37	11.06	12.28
	8H	14.33	14.99	15.28	15.95	17.16	9.53	10.18	10.47	11.14	12.36
	12H	14.40	15.02	15.35	15.97	17.21	9.57	10.20	10.53	11.15	12.39
4H	2H	11.51	12.26	12.45	13.19	14.40	8.06	8.81	9.00	9.74	10.95
	3H	13.35	13.97	14.29	14.93	16.15	9.42	10.04	10.36	11.01	12.22
	4H	14.04	14.61	15.00	15.57	16.81	9.97	10.54	10.92	11.50	12.74
	6H	14.56	15.05	15.53	16.03	17.28	10.39	10.88	11.36	11.86	13.11
	8H	14.74	15.20	15.71	16.17	17.43	10.53	10.98	11.50	11.96	13.22
	12H	14.84	15.25	15.82	16.24	17.50	10.59	11.01	11.58	12.00	13.26
8H	4H	14.01	14.47	14.98	15.45	16.70	10.26	10.71	11.22	11.69	12.94
	6H	14.58	14.96	15.58	15.98	17.23	10.78	11.16	11.77	12.17	13.43
	8H	14.80	15.13	15.80	16.14	17.41	10.97	11.30	11.97	12.31	13.58
	12H	14.94	15.24	15.95	16.23	17.56	11.09	11.39	12.10	12.39	13.71
12H	4H	13.97	14.38	14.96	15.37	16.63	10.26	10.68	11.25	11.67	12.93
	6H	14.56	14.89	15.56	15.90	17.17	10.83	11.16	11.83	12.17	13.44
	8H	14.78	15.08	15.79	16.07	17.40	11.04	11.34	12.05	12.33	13.66