

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P927816

Luminaire Tested: DFN2DIP-HX4F0-120D060US840-FLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P927816
REPORT IS A COMBINATION OF REPORTS P900871 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-120D060US840-FLLONL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 17994.6 lumens
Efficiency: N/A
Efficacy: 105.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 170.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9954
Total Harmonic Distortion (THDi): 0.076
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P927816

CATALOG NUMBER: DFN2DIP-HX4F0-120D060US840-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P927816

CATALOG NUMBER: DFN2DIP-HX4F0-120D060US840-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	111	111	111	111	105	105	105	105	93	93	93		82	82	82		71	71	71	67
1	102	97	93	90	95	92	88	85	81	79	76		72	70	68		63	62	60	56
2	92	85	79	73	87	80	75	70	71	67	63		63	60	57		56	53	51	47
3	84	75	67	61	79	71	64	58	63	58	53		56	52	48		49	46	43	40
4	77	66	58	52	72	63	55	50	56	50	45		50	45	41		44	40	37	34
5	71	59	51	44	67	56	48	43	50	44	39		45	40	36		40	36	33	30
6	66	53	45	39	62	50	43	37	45	39	34		41	35	32		36	32	29	26
7	61	48	40	34	57	46	38	33	41	35	30		37	32	28		33	29	26	23
8	56	44	36	30	53	42	34	29	38	31	27		34	29	25		30	26	23	21
9	53	40	32	27	50	38	31	26	35	29	24		31	26	23		28	24	21	19
10	49	37	29	24	46	35	28	24	32	26	22		29	24	20		26	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3506	3506	3506
5°	3512	3457	3481
10°	3484	3411	3434
15°	3433	3355	3360
20°	3364	3278	3285
25°	3295	3185	3198
30°	3209	3098	3087
35°	3128	2996	2970
40°	3027	2893	2859
45°	2927	2790	2745
50°	2818	2681	2613
55°	2704	2556	2492
60°	2574	2407	2353
65°	2433	2253	2189
70°	2254	2065	2013
75°	2005	1840	1850
80°	1706	1554	1539
85°	1238	1059	1024

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2927 cd/sqm

TEST NUMBER: P927816

CATALOG NUMBER: DFN2DIP-HX4F0-120D060US840-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	443.8	2.5
10°-20°	1248.6	6.9
20°-30°	1835.0	10.2
30°-40°	2131.2	11.8
40°-50°	2128.6	11.8
50°-60°	1856.0	10.3
60°-70°	1372.0	7.6
70°-80°	776.3	4.3
80°-90°	208.5	1.2
90°-100°	67.4	0.4
100°-110°	251.3	1.4
110°-120°	666.6	3.7
120°-130°	1105.6	6.1
130°-140°	1174.4	6.5
140°-150°	1091.5	6.1
150°-160°	877.5	4.9
160°-170°	565.5	3.1
170°-180°	194.6	1.1
0°-30°	3527.4	19.6
0°-40°	5658.6	31.4
0°-60°	9643.2	53.6
0°-90°	12000.0	66.7
90°-120°	985.4	5.5
90°-150°	4357.0	24.2
90°-180°	5995.0	33.3
0°-180°	17994.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4715	4715	4715	4715	4715	
5°	4715	4697	4647	4683	4675	448
15°	4488	4462	4402	4421	4398	1264
25°	4062	4026	3949	3958	3949	1869
35°	3505	3460	3387	3360	3337	2189
45°	2852	2820	2752	2702	2684	2201
55°	2158	2131	2077	2022	2000	1930
65°	1456	1428	1383	1342	1320	1439
75°	762	753	730	703	712	813
85°	186	181	177	163	159	207
90°	1	18	30	37	40	17
95°	96	47	58	65	64	114
105°	450	494	90	106	112	481
115°	851	876	913	228	121	838
125°	1203	1222	1250	1261	1265	1073
135°	1488	1512	1525	1540	1537	1150
145°	1727	1725	1750	1761	1753	1080
155°	1901	1888	1906	1915	1903	876
165°	2003	1995	1999	2009	1999	566
175°	2049	2039	2042	2052	2037	195
180°	2045	2045	2045	2045	2045	

TEST NUMBER: P927816

CATALOG NUMBER: DFN2DIP-HX4F0-120D060US840-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4715.1	4715.1	4715.1	4715.1	4715.1
2.5°	4742.4	4719.8	4669.8	4715.1	4706.4
5°	4715.1	4697.2	4647.2	4683.3	4674.6
7.5°	4683.3	4656.3	4606.3	4642.9	4633.8
10°	4633.8	4602.0	4547.6	4583.7	4570.3
12.5°	4565.4	4538.4	4484.1	4506.7	4497.5
15°	4488.5	4461.5	4402.3	4420.6	4398.0
17.5°	4393.2	4366.3	4307.1	4329.7	4307.1
20°	4288.8	4261.9	4198.4	4211.9	4194.1
22.5°	4184.9	4144.0	4084.8	4084.8	4075.8
25°	4062.2	4026.2	3949.2	3957.9	3949.2
27.5°	3926.1	3894.4	3835.7	3822.2	3799.7
30°	3790.5	3753.9	3686.1	3672.6	3654.4
32.5°	3645.2	3618.3	3545.6	3518.2	3500.0
35°	3504.7	3459.6	3386.9	3359.5	3336.9
37.5°	3346.0	3305.2	3232.5	3200.8	3178.1
40°	3183.0	3146.4	3073.7	3033.3	3015.1
42.5°	3024.3	2987.7	2915.5	2869.9	2842.9
45°	2852.0	2820.3	2751.9	2702.4	2684.1
47.5°	2684.1	2652.3	2579.7	2529.8	2502.8
50°	2507.1	2484.5	2421.0	2357.5	2334.9
52.5°	2334.9	2303.2	2244.5	2194.4	2162.7
55°	2158.3	2131.0	2076.6	2022.2	1999.6
57.5°	1981.3	1958.7	1899.5	1845.2	1826.9
60°	1804.3	1786.5	1723.0	1673.0	1659.5
62.5°	1632.1	1600.3	1555.2	1510.0	1491.7
65°	1455.6	1428.2	1382.9	1342.0	1319.5
67.5°	1274.3	1251.1	1210.8	1179.0	1160.8
70°	1106.3	1088.1	1047.2	1015.5	997.7
72.5°	934.2	915.9	893.3	861.6	848.0
75°	761.5	752.8	729.7	702.8	711.9
77.5°	607.5	589.2	580.1	566.6	553.2
80°	453.6	448.8	439.7	426.2	417.0
82.5°	308.3	308.3	304.1	285.8	285.8
85°	185.7	181.4	177.0	163.1	158.7
87.5°	81.8	72.6	63.5	50.0	45.2
90°	1.4	17.8	29.5	37.1	39.9
92.5°	37.1	31.1	35.4	38.5	39.9
95°	96.1	47.3	57.7	65.2	63.6
97.5°	173.1	51.8	75.3	80.0	81.4
100°	261.9	59.2	84.3	96.1	99.1
102.5°	359.5	356.7	87.3	103.5	108.0
105°	449.8	494.2	90.3	106.4	112.5
107.5°	554.9	591.7	93.3	109.5	115.4
110°	655.6	686.5	259.0	111.1	116.8

TEST NUMBER: P927816

CATALOG NUMBER: DFN2DIP-HX4F0-120D060US840-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	750.2	776.7	751.6	113.8	118.4
115°	850.8	875.9	913.0	227.9	121.4
117.5°	938.0	967.6	992.8	781.2	393.5
120°	1035.8	1057.9	1084.6	1102.3	902.6
122.5°	1118.5	1142.2	1171.9	1180.7	1182.3
125°	1202.9	1222.2	1250.2	1260.6	1265.0
127.5°	1279.8	1300.5	1322.8	1337.6	1339.0
130°	1352.3	1376.1	1392.2	1408.6	1407.2
132.5°	1426.3	1445.6	1461.8	1475.1	1473.7
135°	1488.5	1512.3	1525.4	1540.3	1537.3
137.5°	1553.5	1571.2	1586.2	1600.9	1596.6
140°	1617.1	1629.1	1645.3	1658.6	1651.2
142.5°	1670.5	1680.9	1700.1	1711.8	1704.4
145°	1726.8	1725.1	1750.3	1760.7	1753.3
147.5°	1775.4	1771.0	1796.1	1803.5	1797.7
150°	1822.9	1812.5	1836.2	1845.0	1837.6
152.5°	1862.8	1851.0	1873.1	1882.1	1871.7
155°	1901.3	1888.0	1905.8	1914.6	1902.8
157.5°	1932.4	1920.5	1933.9	1944.3	1932.4
160°	1959.0	1950.0	1959.0	1967.8	1957.5
162.5°	1982.5	1973.8	1981.1	1991.5	1978.2
165°	2003.3	1994.6	1998.9	2009.3	1998.9
167.5°	2019.6	2010.7	2015.3	2025.7	2012.2
170°	2033.0	2024.0	2027.1	2037.4	2024.0
172.5°	2041.8	2033.0	2036.0	2046.4	2033.0
175°	2049.2	2038.8	2041.8	2052.1	2037.4
177.5°	2052.1	2041.8	2043.3	2053.7	2040.4
180°	2044.7	2044.7	2044.7	2044.7	2044.7

TEST NUMBER: P927816

CATALOG NUMBER: DFN2DIP-HX4F0-120D060US840-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.04	14.08	13.84	14.90	15.91	12.61	13.65	13.41	14.47	15.48
	3H	14.72	15.65	15.53	16.48	17.52	14.25	15.17	15.06	16.01	17.05
	4H	15.31	16.19	16.14	17.03	18.08	14.84	15.72	15.67	16.56	17.61
	6H	15.72	16.53	16.57	17.38	18.44	15.25	16.06	16.09	16.90	17.97
	8H	15.83	16.60	16.68	17.47	18.54	15.36	16.13	16.21	17.00	18.06
	12H	15.89	16.62	16.74	17.48	18.57	15.41	16.14	16.26	17.00	18.09
4H	2H	13.53	14.40	14.36	15.24	16.29	13.18	14.06	14.02	14.90	15.95
	3H	15.41	16.14	16.25	17.01	18.08	15.02	15.75	15.86	16.62	17.69
	4H	16.13	16.80	16.99	17.67	18.76	15.73	16.39	16.58	17.26	18.36
	6H	16.66	17.23	17.53	18.13	19.23	16.25	16.83	17.12	17.72	18.82
	8H	16.81	17.35	17.69	18.24	19.35	16.40	16.94	17.28	17.83	18.94
	12H	16.89	17.38	17.79	18.29	19.40	16.47	16.96	17.37	17.87	18.98
8H	4H	16.34	16.88	17.22	17.77	18.88	15.98	16.52	16.86	17.41	18.52
	6H	16.98	17.43	17.89	18.36	19.47	16.62	17.07	17.52	18.00	19.11
	8H	17.21	17.60	18.12	18.53	19.65	16.84	17.23	17.75	18.16	19.28
	12H	17.35	17.70	18.26	18.61	19.79	16.96	17.31	17.88	18.23	19.41
12H	4H	16.34	16.82	17.23	17.73	18.85	15.98	16.47	16.88	17.38	18.50
	6H	17.01	17.41	17.93	18.33	19.46	16.66	17.06	17.58	17.98	19.11
	8H	17.27	17.61	18.18	18.53	19.71	16.91	17.26	17.83	18.17	19.35

END OF REPORT