

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P929136

Luminaire Tested: DFN2DIP-HX4F0-120D120US935-FLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P929136
REPORT IS A COMBINATION OF REPORTS P900979 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-120D120US935-FLLONL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 20457.3 lumens
Efficiency: N/A
Efficacy: 92.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 222.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9954
Total Harmonic Distortion (THDi): 0.076
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P929136

CATALOG NUMBER: DFN2DIP-HX4F0-120D120US935-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P929136

CATALOG NUMBER: DFN2DIP-HX4F0-120D120US935-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	98	93	90	86	90	86	83	80	73	71	68	61	59	58	50	48	47
2	89	82	75	70	82	76	70	66	64	60	57	53	51	48	44	42	40
3	81	72	64	59	75	66	60	55	56	52	48	47	44	41	39	36	34
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	35	32	29
5	68	57	48	42	63	53	45	40	45	39	35	38	34	30	31	28	26
6	63	51	43	37	58	47	40	35	40	35	31	34	30	27	28	25	23
7	58	46	38	32	53	43	36	30	37	31	27	31	27	23	26	23	20
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	24	20	18
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	19	16
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2989	2989	2989
5°	2994	2948	2968
10°	2970	2909	2928
15°	2927	2861	2865
20°	2868	2795	2801
25°	2810	2715	2727
30°	2736	2642	2632
35°	2667	2555	2533
40°	2581	2467	2438
45°	2496	2379	2340
50°	2403	2286	2228
55°	2305	2179	2125
60°	2195	2052	2006
65°	2075	1921	1866
70°	1922	1761	1716
75°	1709	1569	1578
80°	1455	1325	1312
85°	1055	903	873

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2496 cd/sqm

TEST NUMBER: P929136

CATALOG NUMBER: DFN2DIP-HX4F0-120D120US935-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	378.4	1.8
10°-20°	1064.6	5.2
20°-30°	1564.6	7.6
30°-40°	1817.2	8.9
40°-50°	1814.9	8.9
50°-60°	1582.5	7.7
60°-70°	1169.9	5.7
70°-80°	661.9	3.2
80°-90°	180.8	0.9
90°-100°	115.0	0.6
100°-110°	428.6	2.1
110°-120°	1136.8	5.6
120°-130°	1885.4	9.2
130°-140°	2002.8	9.8
140°-150°	1861.3	9.1
150°-160°	1496.5	7.3
160°-170°	964.3	4.7
170°-180°	331.9	1.6
0°-30°	3007.6	14.7
0°-40°	4824.8	23.6
0°-60°	8222.2	40.2
0°-90°	10234.8	50.0
90°-120°	1680.4	8.2
90°-150°	7429.9	36.3
90°-180°	10223.0	50.0
0°-180°	20457.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4020	4020	4020	4020	4020	
5°	4020	4005	3962	3993	3986	382
15°	3827	3804	3754	3769	3750	1078
25°	3464	3433	3367	3375	3367	1594
35°	2988	2950	2888	2864	2845	1866
45°	2432	2405	2346	2304	2289	1877
55°	1840	1817	1771	1724	1705	1645
65°	1241	1218	1179	1144	1125	1227
75°	649	642	622	599	607	693
85°	158	155	151	139	135	177
90°	2	30	50	63	68	19
95°	164	81	98	111	108	194
105°	767	843	154	182	192	820
115°	1451	1494	1557	389	207	1428
125°	2051	2084	2132	2150	2157	1829
135°	2538	2579	2601	2627	2622	1961
145°	2945	2942	2985	3002	2990	1842
155°	3242	3220	3250	3265	3245	1494
165°	3416	3401	3409	3426	3409	965
175°	3494	3477	3482	3500	3474	333
180°	3487	3487	3487	3487	3487	

TEST NUMBER: P929136

CATALOG NUMBER: DFN2DIP-HX4F0-120D120US935-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4020.3	4020.3	4020.3	4020.3	4020.3
2.5°	4043.6	4024.3	3981.7	4020.3	4012.9
5°	4020.3	4005.0	3962.4	3993.1	3985.7
7.5°	3993.1	3970.2	3927.5	3958.7	3951.0
10°	3951.0	3923.8	3877.5	3908.3	3896.8
12.5°	3892.7	3869.7	3823.4	3842.6	3834.8
15°	3827.1	3804.1	3753.6	3769.2	3749.9
17.5°	3745.9	3722.9	3672.4	3691.7	3672.4
20°	3656.8	3633.9	3579.8	3591.2	3576.1
22.5°	3568.2	3533.4	3482.9	3482.9	3475.2
25°	3463.6	3432.9	3367.3	3374.7	3367.3
27.5°	3347.6	3320.5	3270.5	3259.0	3239.8
30°	3231.9	3200.8	3142.9	3131.5	3115.9
32.5°	3108.0	3085.1	3023.1	2999.8	2984.2
35°	2988.3	2949.8	2887.8	2864.5	2845.2
37.5°	2852.9	2818.1	2756.1	2729.1	2709.8
40°	2714.0	2682.8	2620.8	2586.4	2570.8
42.5°	2578.6	2547.4	2485.9	2447.0	2424.0
45°	2431.7	2404.7	2346.4	2304.2	2288.6
47.5°	2288.6	2261.5	2199.6	2157.0	2134.0
50°	2137.7	2118.4	2064.2	2010.1	1990.8
52.5°	1990.8	1963.8	1913.7	1871.0	1844.0
55°	1840.3	1817.0	1770.6	1724.2	1705.0
57.5°	1689.4	1670.1	1619.6	1573.3	1557.7
60°	1538.4	1523.3	1469.1	1426.5	1415.0
62.5°	1391.6	1364.5	1326.0	1287.5	1271.9
65°	1241.1	1217.7	1179.1	1144.3	1125.1
67.5°	1086.5	1066.8	1032.3	1005.3	989.7
70°	943.3	927.7	892.9	865.8	850.7
72.5°	796.5	780.9	761.6	734.6	723.1
75°	649.3	641.9	622.2	599.3	607.0
77.5°	518.0	502.4	494.6	483.1	471.7
80°	386.8	382.6	374.9	363.4	355.6
82.5°	262.9	262.9	259.2	243.7	243.7
85°	158.3	154.6	150.9	139.1	135.3
87.5°	69.7	61.9	54.2	42.6	38.6
90°	2.4	30.2	50.4	63.2	68.0
92.5°	63.2	53.0	60.5	65.6	68.0
95°	163.8	80.6	98.2	111.2	108.5
97.5°	295.2	88.4	128.5	136.3	138.7
100°	446.7	101.0	143.8	163.8	169.0
102.5°	613.0	608.2	148.9	176.5	184.3
105°	767.0	842.8	154.0	181.6	191.7
107.5°	946.2	1009.1	159.1	186.7	196.8
110°	1117.8	1170.6	441.6	189.3	199.2



TEST NUMBER: P929136

CATALOG NUMBER: DFN2DIP-HX4F0-120D120US935-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1279.4	1324.6	1281.8	194.2	201.9
115°	1450.7	1493.6	1556.8	388.6	207.1
117.5°	1599.7	1650.0	1693.2	1332.1	671.1
120°	1766.3	1804.0	1849.5	1879.8	1539.1
122.5°	1907.4	1947.8	1998.5	2013.4	2016.1
125°	2051.2	2084.1	2132.1	2149.7	2157.2
127.5°	2182.4	2217.8	2255.8	2281.0	2283.4
130°	2306.1	2346.6	2374.1	2402.0	2399.6
132.5°	2432.2	2465.2	2492.8	2515.6	2513.2
135°	2538.3	2578.8	2601.3	2626.7	2621.7
137.5°	2649.2	2679.4	2704.9	2730.1	2722.6
140°	2757.7	2778.0	2805.6	2828.4	2815.8
142.5°	2848.7	2866.4	2899.1	2919.1	2906.6
145°	2944.6	2942.0	2984.7	3002.5	2989.8
147.5°	3027.6	3020.1	3063.0	3075.6	3065.7
150°	3108.5	3090.8	3131.3	3146.3	3133.7
152.5°	3176.5	3156.4	3194.2	3209.5	3191.8
155°	3242.1	3219.6	3249.9	3264.9	3244.9
157.5°	3295.1	3275.1	3297.9	3315.5	3295.1
160°	3340.7	3325.4	3340.7	3355.7	3338.0
162.5°	3380.9	3365.9	3378.5	3396.1	3373.4
165°	3416.2	3401.2	3408.7	3426.4	3408.7
167.5°	3444.1	3428.8	3436.6	3454.2	3431.5
170°	3466.8	3451.6	3456.7	3474.3	3451.6
172.5°	3481.8	3466.8	3472.0	3489.6	3466.8
175°	3494.4	3476.7	3481.8	3499.5	3474.3
177.5°	3499.5	3481.8	3484.6	3502.2	3479.5
180°	3487.0	3487.0	3487.0	3487.0	3487.0

TEST NUMBER: P929136

CATALOG NUMBER: DFN2DIP-HX4F0-120D120US935-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.08	11.94	12.04	12.91	14.18	10.65	11.51	11.61	12.48	13.75
	3H	12.74	13.51	13.71	14.50	15.79	12.27	13.04	13.24	14.02	15.32
	4H	13.33	14.06	14.31	15.05	16.35	12.86	13.59	13.84	14.57	15.87
	6H	13.73	14.40	14.72	15.39	16.71	13.25	13.93	14.25	14.92	16.23
	8H	13.84	14.48	14.83	15.48	16.80	13.36	14.00	14.36	15.01	16.32
	12H	13.88	14.49	14.89	15.50	16.83	13.40	14.01	14.41	15.01	16.35
4H	2H	11.54	12.27	12.53	13.26	14.56	11.20	11.93	12.19	12.91	14.22
	3H	13.41	14.02	14.41	15.03	16.35	13.02	13.63	14.01	14.64	15.96
	4H	14.12	14.68	15.13	15.69	17.03	13.72	14.28	14.72	15.28	16.62
	6H	14.64	15.12	15.66	16.15	17.49	14.23	14.71	15.25	15.74	17.08
	8H	14.79	15.24	15.81	16.26	17.62	14.38	14.83	15.40	15.85	17.20
	12H	14.86	15.27	15.90	16.31	17.67	14.44	14.85	15.48	15.89	17.24
8H	4H	14.32	14.77	15.34	15.80	17.15	13.96	14.41	14.98	15.43	16.79
	6H	14.95	15.33	16.00	16.39	17.74	14.59	14.96	15.63	16.03	17.38
	8H	15.18	15.50	16.23	16.55	17.92	14.81	15.13	15.86	16.19	17.55
	12H	15.31	15.60	16.36	16.64	18.05	14.92	15.21	15.98	16.26	17.67
12H	4H	14.31	14.71	15.34	15.75	17.11	13.96	14.36	14.99	15.40	16.76
	6H	14.99	15.31	16.04	16.36	17.73	14.63	14.96	15.68	16.01	17.38
	8H	15.23	15.52	16.28	16.56	17.97	14.87	15.16	15.92	16.20	17.61

END OF REPORT