

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P929140

Luminaire Tested: DFN2DIP-HX4F0-040D040US940-FLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P929140
REPORT IS A COMBINATION OF REPORTS P900819 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-040D040US940-FLONL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7064.7 lumens
Efficiency: N/A
Efficacy: 111.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 63.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9977
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P929140
CATALOG NUMBER: DFN2DIP-HX4F0-040D040US940-FLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P929140

CATALOG NUMBER: DFN2DIP-HX4F0-040D040US940-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	56	56	56	50
1	98	93	90	86	90	86	83	80	73	71	68	61	59	58	50	48	47	50	48	47	42
2	89	82	75	70	82	76	70	66	64	60	57	53	51	48	44	42	40	44	42	40	35
3	81	72	64	59	75	66	60	55	56	52	48	47	44	41	39	36	34	39	36	34	30
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	35	32	29	35	32	29	26
5	68	57	48	42	63	53	45	40	45	39	35	38	34	30	31	28	26	31	28	26	22
6	63	51	43	37	58	47	40	35	40	35	31	34	30	27	28	25	23	28	25	23	20
7	58	46	38	32	53	43	36	30	37	31	27	31	27	23	26	23	20	26	23	20	17
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	24	20	18	24	20	18	16
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	19	16	22	19	16	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1032	1032	1032
5°	1034	1018	1025
10°	1026	1004	1011
15°	1011	988	989
20°	990	965	967
25°	970	938	942
30°	945	912	909
35°	921	882	875
40°	891	852	842
45°	862	821	808
50°	830	790	769
55°	796	753	734
60°	758	709	693
65°	717	663	645
70°	664	608	593
75°	590	542	545
80°	502	457	453
85°	365	312	301

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 862 cd/sqm



TEST NUMBER: P929140

CATALOG NUMBER: DFN2DIP-HX4F0-040D040US940-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.7	1.8
10°-20°	367.6	5.2
20°-30°	540.3	7.6
30°-40°	627.5	8.9
40°-50°	626.8	8.9
50°-60°	546.5	7.7
60°-70°	404.0	5.7
70°-80°	228.6	3.2
80°-90°	62.4	0.9
90°-100°	39.7	0.6
100°-110°	148.0	2.1
110°-120°	392.6	5.6
120°-130°	651.1	9.2
130°-140°	691.6	9.8
140°-150°	642.8	9.1
150°-160°	516.8	7.3
160°-170°	333.0	4.7
170°-180°	114.6	1.6
0°-30°	1038.6	14.7
0°-40°	1666.2	23.6
0°-60°	2839.4	40.2
0°-90°	3534.5	50.0
90°-120°	580.3	8.2
90°-150°	2565.8	36.3
90°-180°	3530.0	50.0
0°-180°	7064.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1388	1388	1388	1388	1388	
5°	1388	1383	1368	1379	1376	132
15°	1322	1314	1296	1302	1295	372
25°	1196	1186	1163	1165	1163	550
35°	1032	1019	997	989	982	644
45°	840	830	810	796	790	648
55°	636	627	612	595	589	568
65°	429	420	407	395	389	424
75°	224	222	215	207	210	239
85°	55	53	52	48	47	61
90°	1	10	17	22	24	7
95°	57	28	34	38	38	67
105°	265	291	53	63	66	283
115°	501	516	538	134	72	493
125°	708	720	736	742	745	632
135°	877	891	898	907	905	677
145°	1017	1016	1031	1037	1032	636
155°	1120	1112	1122	1128	1120	516
165°	1180	1175	1177	1183	1177	333
175°	1207	1201	1202	1208	1200	115
180°	1204	1204	1204	1204	1204	



TEST NUMBER: P929140

CATALOG NUMBER: DFN2DIP-HX4F0-040D040US940-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1388.3	1388.3	1388.3	1388.3	1388.3
2.5°	1396.4	1389.7	1375.0	1388.3	1385.8
5°	1388.3	1383.0	1368.3	1378.9	1376.4
7.5°	1378.9	1371.0	1356.3	1367.1	1364.4
10°	1364.4	1355.0	1339.1	1349.7	1345.7
12.5°	1344.2	1336.3	1320.3	1327.0	1324.3
15°	1321.6	1313.6	1296.3	1301.6	1295.0
17.5°	1293.6	1285.6	1268.2	1274.8	1268.2
20°	1262.8	1254.9	1236.2	1240.1	1235.0
22.5°	1232.2	1220.2	1202.8	1202.8	1200.1
25°	1196.1	1185.5	1162.8	1165.4	1162.8
27.5°	1156.0	1146.7	1129.5	1125.4	1118.8
30°	1116.1	1105.4	1085.4	1081.4	1076.0
32.5°	1073.3	1065.4	1044.0	1036.0	1030.5
35°	1032.0	1018.7	997.3	989.2	982.5
37.5°	985.2	973.2	951.8	942.5	935.8
40°	937.2	926.4	905.0	893.2	887.8
42.5°	890.5	879.7	858.5	845.0	837.1
45°	839.7	830.5	810.3	795.8	790.3
47.5°	790.3	780.9	759.6	744.9	737.0
50°	738.2	731.5	712.9	694.2	687.5
52.5°	687.5	678.2	660.9	646.2	636.8
55°	635.6	627.4	611.5	595.4	588.8
57.5°	583.4	576.8	559.3	543.3	538.0
60°	531.3	526.0	507.4	492.7	488.6
62.5°	480.6	471.2	458.0	444.6	439.2
65°	428.6	420.5	407.2	395.2	388.6
67.5°	375.2	368.4	356.5	347.2	341.8
70°	325.8	320.4	308.4	299.0	293.7
72.5°	275.1	269.7	263.1	253.7	249.7
75°	224.2	221.7	214.9	206.9	209.6
77.5°	178.8	173.5	170.8	166.8	162.9
80°	133.5	132.1	129.4	125.5	122.8
82.5°	90.8	90.8	89.6	84.1	84.1
85°	54.7	53.4	52.1	48.0	46.7
87.5°	24.1	21.4	18.7	14.7	13.3
90°	0.8	10.4	17.4	21.9	23.5
92.5°	21.9	18.3	20.9	22.7	23.5
95°	56.6	27.8	33.9	38.4	37.5
97.5°	102.0	30.5	44.4	47.1	47.9
100°	154.2	34.9	49.7	56.6	58.3
102.5°	211.7	210.1	51.4	60.9	63.6
105°	264.8	291.1	53.2	62.7	66.2
107.5°	326.7	348.5	54.9	64.5	68.0
110°	386.1	404.3	152.5	65.4	68.8



TEST NUMBER: P929140

CATALOG NUMBER: DFN2DIP-HX4F0-040D040US940-FLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	441.8	457.4	442.6	67.1	69.8
115°	500.9	515.8	537.6	134.2	71.5
117.5°	552.4	569.8	584.7	460.0	231.7
120°	609.9	623.0	638.7	649.2	531.5
122.5°	658.7	672.7	690.1	695.3	696.2
125°	708.3	719.8	736.3	742.4	745.0
127.5°	753.7	765.9	779.0	787.7	788.5
130°	796.4	810.4	819.8	829.5	828.7
132.5°	839.9	851.3	860.9	868.7	867.9
135°	876.6	890.6	898.3	907.1	905.4
137.5°	914.8	925.3	934.1	942.8	940.2
140°	952.3	959.3	968.9	976.7	972.4
142.5°	983.8	989.9	1001.2	1008.0	1003.8
145°	1016.9	1016.0	1030.7	1036.9	1032.5
147.5°	1045.5	1042.9	1057.7	1062.1	1058.7
150°	1073.4	1067.4	1081.4	1086.5	1082.2
152.5°	1097.0	1090.0	1103.0	1108.3	1102.2
155°	1119.6	1111.9	1122.3	1127.5	1120.5
157.5°	1137.9	1131.0	1138.9	1145.0	1137.9
160°	1153.6	1148.4	1153.6	1158.8	1152.7
162.5°	1167.5	1162.4	1166.7	1172.8	1165.0
165°	1179.8	1174.6	1177.2	1183.2	1177.2
167.5°	1189.4	1184.0	1186.8	1192.9	1185.0
170°	1197.2	1192.0	1193.7	1199.8	1192.0
172.5°	1202.4	1197.2	1199.0	1205.1	1197.2
175°	1206.7	1200.6	1202.4	1208.5	1199.8
177.5°	1208.5	1202.4	1203.3	1209.5	1201.6
180°	1204.2	1204.2	1204.2	1204.2	1204.2



TEST NUMBER: P929140
 CATALOG NUMBER: DFN2DIP-HX4F0-040D040US940-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.39	8.25	8.34	9.22	10.49	6.95	7.82	7.91	8.79	10.06
	3H	9.05	9.82	10.02	10.80	12.10	8.57	9.35	9.54	10.33	11.62
	4H	9.64	10.37	10.62	11.35	12.65	9.16	9.89	10.14	10.88	12.18
	6H	10.04	10.71	11.03	11.70	13.01	9.56	10.23	10.55	11.22	12.54
	8H	10.14	10.78	11.14	11.79	13.10	9.67	10.31	10.66	11.32	12.63
	12H	10.19	10.80	11.19	11.80	13.14	9.71	10.32	10.71	11.32	12.66
4H	2H	7.85	8.58	8.84	9.57	10.87	7.50	8.24	8.49	9.22	10.52
	3H	9.72	10.33	10.71	11.34	12.66	9.32	9.93	10.32	10.95	12.26
	4H	10.43	10.99	11.44	12.00	13.34	10.02	10.58	11.03	11.59	12.93
	6H	10.95	11.43	11.96	12.46	13.79	10.54	11.02	11.55	12.05	13.38
	8H	11.10	11.55	12.12	12.57	13.92	10.68	11.13	11.70	12.16	13.51
	12H	11.17	11.58	12.21	12.62	13.97	10.75	11.15	11.78	12.19	13.55
8H	4H	10.63	11.08	11.65	12.10	13.45	10.27	10.72	11.29	11.74	13.09
	6H	11.26	11.63	12.30	12.70	14.05	10.90	11.27	11.94	12.33	13.68
	8H	11.48	11.81	12.53	12.86	14.23	11.11	11.44	12.16	12.49	13.86
	12H	11.61	11.90	12.67	12.95	14.36	11.23	11.52	12.28	12.56	13.97
12H	4H	10.61	11.02	11.65	12.06	13.42	10.26	10.67	11.30	11.71	13.06
	6H	11.29	11.62	12.34	12.67	14.04	10.94	11.27	11.99	12.32	13.69
	8H	11.53	11.82	12.59	12.87	14.28	11.18	11.46	12.23	12.51	13.92