

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P927872

Luminaire Tested: DFN2DIP-HX4F0-040D110US850-FLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P927872
REPORT IS A COMBINATION OF REPORTS P900945 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-040D110US850-FLLONL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 16468.6 lumens
Efficiency: N/A
Efficacy: 136.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 120.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9977
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P927872

CATALOG NUMBER: DFN2DIP-HX4F0-040D110US850-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P927872

CATALOG NUMBER: DFN2DIP-HX4F0-040D110US850-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	35	35	35
1	93	88	85	81	82	79	76	73	62	59	58	45	44	43	31	30	29
2	84	77	71	66	75	69	64	60	54	51	48	40	38	36	27	26	25
3	77	68	61	55	68	61	55	50	47	43	40	35	33	30	24	22	21
4	70	60	52	46	62	54	47	42	42	38	34	31	28	26	21	20	18
5	64	53	45	40	57	48	41	36	38	33	29	28	25	22	19	17	16
6	59	48	40	34	53	43	36	31	34	29	25	25	22	19	17	15	14
7	55	43	35	30	49	39	32	27	30	26	22	23	20	17	16	14	12
8	50	39	31	26	45	35	28	24	28	23	19	21	18	15	15	12	11
9	47	35	28	23	42	32	25	21	25	21	17	19	16	14	13	11	10
10	44	32	25	21	39	29	23	19	23	19	15	18	14	12	12	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1283	1283	1283
5°	1286	1266	1274
10°	1275	1249	1257
15°	1257	1228	1230
20°	1231	1200	1203
25°	1206	1166	1171
30°	1175	1134	1130
35°	1145	1097	1087
40°	1108	1059	1047
45°	1072	1021	1005
50°	1032	982	957
55°	990	936	912
60°	942	881	861
65°	891	825	801
70°	825	756	737
75°	734	674	677
80°	624	569	564
85°	453	388	375

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2114 cd/sqm

TEST NUMBER: P927872

CATALOG NUMBER: DFN2DIP-HX4F0-040D110US850-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	162.5	1.0
10°-20°	457.1	2.8
20°-30°	671.7	4.1
30°-40°	780.2	4.7
40°-50°	779.2	4.7
50°-60°	679.5	4.1
60°-70°	502.3	3.0
70°-80°	284.2	1.7
80°-90°	82.2	0.5
90°-100°	135.7	0.8
100°-110°	506.1	3.1
110°-120°	1342.2	8.1
120°-130°	2226.1	13.5
130°-140°	2364.7	14.4
140°-150°	2197.7	13.3
150°-160°	1766.9	10.7
160°-170°	1138.5	6.9
170°-180°	391.9	2.4
0°-30°	1291.3	7.8
0°-40°	2071.5	12.6
0°-60°	3530.2	21.4
0°-90°	4398.9	26.7
90°-120°	1984.0	12.0
90°-150°	8772.5	53.3
90°-180°	12070.0	73.3
0°-180°	16468.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1726	1726	1726	1726	1726	
5°	1726	1720	1701	1714	1711	164
15°	1643	1633	1612	1618	1610	463
25°	1487	1474	1446	1449	1446	684
35°	1283	1266	1240	1230	1222	801
45°	1044	1032	1007	989	983	806
55°	790	780	760	740	732	706
65°	533	523	506	491	483	527
75°	279	276	267	257	261	298
85°	68	66	65	60	58	76
90°	3	36	59	75	80	15
95°	194	95	116	131	128	229
105°	906	995	182	214	226	968
115°	1713	1763	1838	459	244	1686
125°	2422	2461	2517	2538	2547	2160
135°	2997	3045	3071	3101	3095	2315
145°	3477	3474	3524	3545	3530	2174
155°	3828	3801	3837	3855	3831	1764
165°	4034	4016	4025	4046	4025	1140
175°	4126	4105	4111	4132	4102	393
180°	4117	4117	4117	4117	4117	

TEST NUMBER: P927872

CATALOG NUMBER: DFN2DIP-HX4F0-040D110US850-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1726.0	1726.0	1726.0	1726.0	1726.0
2.5°	1736.1	1727.8	1709.5	1726.0	1722.9
5°	1726.0	1719.5	1701.2	1714.4	1711.3
7.5°	1714.4	1704.5	1686.2	1699.7	1696.3
10°	1696.3	1684.7	1664.8	1678.0	1673.0
12.5°	1671.3	1661.4	1641.5	1649.9	1646.4
15°	1643.1	1633.2	1611.6	1618.3	1610.0
17.5°	1608.3	1598.4	1576.8	1585.0	1576.8
20°	1570.0	1560.1	1537.0	1541.8	1535.4
22.5°	1532.0	1517.0	1495.4	1495.4	1492.0
25°	1487.1	1473.9	1445.7	1448.9	1445.7
27.5°	1437.3	1425.6	1404.2	1399.2	1391.0
30°	1387.6	1374.3	1349.4	1344.4	1337.8
32.5°	1334.5	1324.6	1298.0	1288.0	1281.2
35°	1283.0	1266.5	1239.9	1229.9	1221.6
37.5°	1224.9	1209.9	1183.3	1171.8	1163.5
40°	1165.2	1151.8	1125.2	1110.4	1103.8
42.5°	1107.1	1093.7	1067.3	1050.6	1040.7
45°	1044.0	1032.5	1007.4	989.3	982.6
47.5°	982.6	970.9	944.4	926.1	916.3
50°	917.8	909.5	886.3	863.0	854.7
52.5°	854.7	843.2	821.7	803.4	791.7
55°	790.2	780.1	760.2	740.3	732.1
57.5°	725.3	717.1	695.3	675.5	668.8
60°	660.5	654.0	630.8	612.5	607.5
62.5°	597.5	585.9	569.4	552.7	546.1
65°	532.9	522.8	506.3	491.3	483.1
67.5°	466.4	458.0	443.3	431.6	425.0
70°	405.0	398.4	383.4	371.7	365.2
72.5°	342.0	335.3	327.0	315.4	310.4
75°	278.8	275.6	267.2	257.3	260.6
77.5°	222.4	215.7	212.4	207.4	202.5
80°	166.0	164.2	160.9	156.0	152.7
82.5°	112.9	112.9	111.3	104.6	104.6
85°	68.0	66.4	64.8	59.7	58.1
87.5°	29.9	26.6	23.3	18.3	16.5
90°	2.9	35.7	59.4	74.6	80.3
92.5°	74.6	62.7	71.4	77.5	80.3
95°	193.5	95.2	116.0	131.2	128.1
97.5°	348.4	104.4	151.7	160.9	163.8
100°	527.4	119.2	169.8	193.5	199.5
102.5°	723.7	718.1	175.8	208.4	217.6
105°	905.6	995.1	181.9	214.4	226.5
107.5°	1117.2	1191.4	187.9	220.4	232.4
110°	1319.8	1382.1	521.5	223.6	235.2

TEST NUMBER: P927872

CATALOG NUMBER: DFN2DIP-HX4F0-040D110US850-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1510.6	1563.9	1513.3	229.2	238.4
115°	1712.9	1763.4	1838.2	458.8	244.4
117.5°	1888.7	1948.2	1999.1	1572.8	792.4
120°	2085.4	2129.9	2183.7	2219.4	1817.2
122.5°	2252.0	2299.7	2359.5	2377.3	2380.5
125°	2421.8	2460.8	2517.3	2538.2	2547.0
127.5°	2576.8	2618.5	2663.4	2693.1	2696.0
130°	2722.8	2770.6	2803.1	2836.0	2833.3
132.5°	2871.8	2910.7	2943.3	2970.1	2967.4
135°	2997.1	3044.8	3071.3	3101.4	3095.3
137.5°	3127.9	3163.6	3193.7	3223.4	3214.5
140°	3256.0	3280.0	3312.6	3339.4	3324.6
142.5°	3363.5	3384.3	3422.9	3446.7	3431.8
145°	3476.7	3473.5	3524.1	3545.0	3530.2
147.5°	3574.8	3565.9	3616.4	3631.3	3619.7
150°	3670.2	3649.4	3697.1	3714.8	3700.0
152.5°	3750.5	3726.8	3771.4	3789.5	3768.6
155°	3828.0	3801.4	3837.1	3854.9	3831.2
157.5°	3890.6	3866.9	3893.8	3914.7	3890.6
160°	3944.4	3926.3	3944.4	3962.0	3941.2
162.5°	3991.7	3974.1	3989.0	4009.8	3983.0
165°	4033.5	4015.8	4024.7	4045.5	4024.7
167.5°	4066.4	4048.4	4057.6	4078.5	4051.6
170°	4093.3	4075.2	4081.2	4102.2	4075.2
172.5°	4111.0	4093.3	4099.3	4120.2	4093.3
175°	4125.8	4105.0	4111.0	4131.9	4102.2
177.5°	4131.9	4111.0	4114.2	4135.0	4108.2
180°	4117.1	4117.1	4117.1	4117.1	4117.1

TEST NUMBER: P927872

CATALOG NUMBER: DFN2DIP-HX4F0-040D110US850-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.46	6.14	6.59	7.27	8.83	5.02	5.71	6.16	6.83	8.40
	3H	7.10	7.72	8.25	8.85	10.43	6.63	7.24	7.77	8.38	9.96
	4H	7.68	8.27	8.83	9.40	10.99	7.21	7.79	8.36	8.93	10.52
	6H	8.07	8.61	9.23	9.75	11.35	7.60	8.13	8.76	9.27	10.87
	8H	8.17	8.68	9.34	9.84	11.43	7.70	8.21	8.86	9.36	10.95
	12H	8.22	8.70	9.38	9.85	11.46	7.74	8.22	8.90	9.36	10.98
4H	2H	5.90	6.48	7.06	7.61	9.20	5.55	6.13	6.71	7.27	8.86
	3H	7.75	8.23	8.91	9.39	10.99	7.35	7.84	8.52	9.00	10.60
	4H	8.45	8.90	9.62	10.05	11.67	8.05	8.50	9.21	9.64	11.26
	6H	8.96	9.34	10.13	10.51	12.12	8.55	8.93	9.72	10.10	11.72
	8H	9.11	9.46	10.28	10.63	12.25	8.69	9.05	9.86	10.21	11.84
	12H	9.17	9.50	10.36	10.67	12.30	8.75	9.07	9.94	10.25	11.88
8H	4H	8.64	8.99	9.81	10.16	11.79	8.28	8.63	9.45	9.80	11.42
	6H	9.26	9.56	10.45	10.76	12.39	8.90	9.19	10.09	10.40	12.02
	8H	9.48	9.74	10.68	10.92	12.57	9.11	9.37	10.31	10.55	12.20
	12H	9.61	9.83	10.81	11.01	12.69	9.22	9.45	10.42	10.63	12.30
12H	4H	8.61	8.94	9.80	10.11	11.74	8.26	8.59	9.45	9.76	11.39
	6H	9.29	9.55	10.49	10.73	12.38	8.94	9.20	10.13	10.38	12.02
	8H	9.53	9.75	10.72	10.93	12.61	9.17	9.39	10.37	10.57	12.25

END OF REPORT