

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P929166

Luminaire Tested: DFN2DIP-HX4F0-040D100US940-RLLONL

Issue Date: 12/12/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P929166  
REPORT IS A COMBINATION OF REPORTS P900928 AND P896187  
Test Lab: INNOVATION CENTER  
Issue Date: 12/12/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-HX4F0-040D100US940-RLONL  
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 11863.6 lumens  
Efficiency: N/A  
Efficacy: 108.4 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')  
CIE Type: Semi-Indirect  
  
Input Watts (W): 109.4  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9977  
Total Harmonic Distortion (THDi): 0.049  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P929166  
CATALOG NUMBER: DFN2DIP-HX4F0-040D100US940-RLLONL

### Luminous Intensity Polar Plot





TEST NUMBER: P929166  
 CATALOG NUMBER: DFN2DIP-HX4F0-040D100US940-RLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34	26			
1	93	88	85	82	82	79	76	73	61	59	58	45	44	43	30	29	29	22			
2	84	77	72	67	75	69	65	60	54	51	48	40	38	36	27	26	25	19			
3	77	68	61	56	69	61	55	51	48	44	41	35	33	31	24	23	21	16			
4	71	60	53	47	63	54	48	43	43	38	35	32	29	26	22	20	19	14			
5	65	54	46	41	58	48	42	37	38	33	30	28	25	23	19	18	16	12			
6	60	48	41	35	53	43	37	32	34	30	26	26	23	20	18	16	14	11			
7	55	43	36	31	49	39	33	28	31	26	23	23	20	18	16	14	13	10			
8	51	39	32	27	45	36	29	25	28	24	20	21	18	16	15	13	12	9			
9	47	36	29	24	42	32	26	22	26	21	18	20	16	14	14	12	10	8			
10	44	33	26	21	39	30	24	20	24	19	16	18	15	13	13	11	10	7			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1097	1097	1097
5°	1098	1079	1086
10°	1088	1058	1051
15°	1073	1023	996
20°	1053	975	929
25°	1033	921	864
30°	1006	866	782
35°	979	806	710
40°	952	745	628
45°	921	676	553
50°	888	608	479
55°	854	534	409
60°	815	457	337
65°	770	378	303
70°	715	305	274
75°	646	269	250
80°	547	226	217
85°	383	151	163

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 90°  
 Luminance: 1545 cd/sqm



TEST NUMBER: P929166

CATALOG NUMBER: DFN2DIP-HX4F0-040D100US940-RLONL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	138.2	1.2
10°-20°	379.4	3.2
20°-30°	532.7	4.5
30°-40°	580.6	4.9
40°-50°	533.7	4.5
50°-60°	419.1	3.5
60°-70°	272.8	2.3
70°-80°	140.4	1.2
80°-90°	41.1	0.3
90°-100°	99.3	0.8
100°-110°	370.0	3.1
110°-120°	981.4	8.3
120°-130°	1627.8	13.7
130°-140°	1729.1	14.6
140°-150°	1607.0	13.5
150°-160°	1292.0	10.9
160°-170°	832.5	7.0
170°-180°	286.5	2.4
0°-30°	1050.3	8.9
0°-40°	1630.9	13.7
0°-60°	2583.7	21.8
0°-90°	3038.1	25.6
90°-120°	1450.7	12.2
90°-150°	6414.5	54.1
90°-180°	8826.0	74.4
0°-180°	11863.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1475	1475	1475	1475	1475	
5°	1475	1468	1451	1463	1459	140
15°	1403	1388	1342	1317	1304	395
25°	1273	1230	1142	1088	1068	586
35°	1097	1029	912	827	798	687
45°	897	807	667	572	540	693
55°	682	578	434	354	328	609
65°	460	352	232	187	183	457
75°	246	152	107	97	96	260
85°	57	29	25	25	25	66
90°	2	26	43	55	59	11
95°	142	70	85	96	94	168
105°	662	728	133	157	166	708
115°	1252	1290	1344	336	179	1233
125°	1771	1799	1841	1856	1862	1579
135°	2192	2226	2246	2268	2263	1693
145°	2542	2540	2577	2592	2581	1590
155°	2799	2780	2806	2819	2801	1290
165°	2949	2936	2943	2958	2943	833
175°	3017	3002	3006	3021	3000	287
180°	3010	3010	3010	3010	3010	



TEST NUMBER: P929166

CATALOG NUMBER: DFN2DIP-HX4F0-040D100US940-RLONL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1474.7	1474.7	1474.7	1474.7	1474.7
2.5°	1481.3	1474.7	1459.9	1473.4	1470.6
5°	1474.7	1468.0	1450.6	1462.6	1458.7
7.5°	1462.6	1454.7	1436.0	1441.2	1434.6
10°	1446.6	1437.3	1410.6	1406.5	1398.7
12.5°	1426.7	1414.6	1378.5	1370.6	1355.8
15°	1402.6	1387.9	1342.5	1317.2	1303.9
17.5°	1374.6	1353.2	1297.1	1267.8	1246.4
20°	1342.5	1315.8	1249.1	1215.8	1186.4
22.5°	1307.9	1277.2	1199.7	1154.3	1134.4
25°	1273.2	1230.4	1142.3	1087.7	1067.5
27.5°	1231.9	1186.4	1089.0	1026.2	995.5
30°	1187.8	1136.9	1030.2	962.2	926.2
32.5°	1145.1	1083.6	974.2	894.1	860.7
35°	1097.1	1028.9	911.5	827.4	798.0
37.5°	1050.3	976.8	852.8	760.6	727.3
40°	1000.9	920.9	791.4	696.7	662.0
42.5°	950.2	864.8	730.0	631.2	597.9
45°	896.8	807.3	667.3	572.5	540.5
47.5°	846.2	751.4	607.3	512.5	483.1
50°	790.0	695.3	548.5	456.3	428.4
52.5°	735.3	635.2	492.5	404.3	379.0
55°	681.9	577.8	433.7	353.7	328.3
57.5°	627.3	520.5	381.7	306.9	285.6
60°	571.1	464.4	326.9	258.9	237.6
62.5°	516.6	409.8	280.2	216.2	205.6
65°	460.5	352.3	232.2	186.9	182.8
67.5°	407.1	298.9	186.9	164.1	160.1
70°	351.0	246.9	154.8	141.5	136.0
72.5°	297.7	198.8	129.4	118.8	116.1
75°	245.5	152.1	106.8	97.4	96.2
77.5°	193.6	108.0	84.1	78.8	76.0
80°	145.4	77.4	64.0	58.8	58.8
82.5°	101.4	52.1	44.1	41.3	41.3
85°	57.4	29.3	25.3	25.3	25.3
87.5°	21.4	10.6	10.6	9.4	9.4
90°	2.1	26.1	43.4	54.6	58.7
92.5°	54.6	45.8	52.3	56.6	58.7
95°	141.5	69.6	84.8	96.0	93.7
97.5°	254.8	76.3	111.0	117.7	119.8
100°	385.7	87.1	124.2	141.5	145.9
102.5°	529.2	525.1	128.5	152.4	159.0
105°	662.2	727.6	133.0	156.7	165.6
107.5°	816.9	871.2	137.4	161.2	169.9
110°	965.1	1010.6	381.2	163.5	172.0



TEST NUMBER: P929166

CATALOG NUMBER: DFN2DIP-HX4F0-040D100US940-RLONL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	1104.5	1143.5	1106.6	167.6	174.4
115°	1252.5	1289.5	1344.1	335.5	178.8
117.5°	1381.0	1424.5	1461.7	1150.1	579.4
120°	1524.9	1557.4	1596.8	1622.9	1328.8
122.5°	1646.7	1681.6	1725.3	1738.2	1740.6
125°	1770.9	1799.3	1840.7	1856.0	1862.4
127.5°	1884.2	1914.7	1947.5	1969.3	1971.3
130°	1990.9	2025.9	2049.7	2073.7	2071.7
132.5°	2099.9	2128.3	2152.1	2171.8	2169.7
135°	2191.5	2226.3	2245.8	2267.7	2263.4
137.5°	2287.2	2313.3	2335.3	2357.0	2350.5
140°	2380.7	2398.4	2422.1	2441.8	2431.0
142.5°	2459.4	2474.7	2502.9	2520.2	2509.4
145°	2542.2	2539.9	2576.9	2592.2	2581.3
147.5°	2613.8	2607.4	2644.3	2655.2	2646.7
150°	2683.7	2668.4	2703.4	2716.3	2705.4
152.5°	2742.4	2725.1	2757.7	2770.8	2755.6
155°	2799.1	2779.7	2805.8	2818.7	2801.4
157.5°	2844.9	2827.6	2847.2	2862.4	2844.9
160°	2884.2	2871.0	2884.2	2897.1	2881.9
162.5°	2918.8	2905.9	2916.8	2932.0	2912.4
165°	2949.3	2936.4	2942.9	2958.1	2942.9
167.5°	2973.4	2960.2	2967.0	2982.2	2962.5
170°	2993.0	2979.9	2984.3	2999.5	2979.9
172.5°	3006.0	2993.0	2997.5	3012.7	2993.0
175°	3016.8	3001.6	3006.0	3021.3	2999.5
177.5°	3021.3	3006.0	3008.4	3023.6	3003.9
180°	3010.4	3010.4	3010.4	3010.4	3010.4



TEST NUMBER: P929166  
 CATALOG NUMBER: DFN2DIP-HX4F0-040D100US940-RLONL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	4.59	5.26	5.74	6.39	7.97	0.56	1.23	1.71	2.36	3.94
	3H	6.26	6.85	7.41	7.99	9.59	1.74	2.34	2.90	3.48	5.08
	4H	6.86	7.42	8.02	8.56	10.17	2.19	2.75	3.35	3.89	5.49
	6H	7.27	7.79	8.44	8.94	10.55	2.50	3.02	3.67	4.16	5.78
	8H	7.40	7.89	8.57	9.05	10.65	2.59	3.08	3.76	4.24	5.84
	12H	7.45	7.92	8.63	9.07	10.70	2.63	3.09	3.80	4.25	5.87
4H	2H	4.59	5.15	5.76	6.30	7.90	1.14	1.70	2.31	2.84	4.45
	3H	6.41	6.88	7.58	8.04	9.66	2.48	2.95	3.65	4.11	5.73
	4H	7.09	7.52	8.27	8.68	10.31	3.02	3.45	4.20	4.61	6.24
	6H	7.60	7.97	8.78	9.15	10.77	3.43	3.80	4.61	4.98	6.60
	8H	7.77	8.12	8.95	9.29	10.93	3.56	3.90	4.74	5.07	6.71
	12H	7.86	8.17	9.06	9.35	11.00	3.62	3.93	4.81	5.11	6.75
8H	4H	7.05	7.39	8.23	8.56	10.20	3.29	3.63	4.47	4.80	6.44
	6H	7.61	7.89	8.81	9.10	10.74	3.80	4.09	5.00	5.30	6.94
	8H	7.83	8.07	9.03	9.26	10.92	4.00	4.24	5.20	5.43	7.09
	12H	7.96	8.18	9.17	9.36	11.05	4.11	4.33	5.32	5.51	7.20
12H	4H	6.99	7.31	8.19	8.48	10.13	3.29	3.60	4.48	4.78	6.42
	6H	7.58	7.83	8.79	9.02	10.68	3.85	4.10	5.06	5.29	6.95
	8H	7.80	8.02	9.01	9.20	10.89	4.06	4.27	5.27	5.46	7.15