

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P910907

Luminaire Tested: DFN2DIP-HX4F0-060D040US850-RLLFLL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P910907  
REPORT IS A COMBINATION OF REPORTS P899304 AND P896188  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-HX4F0-060D040US850-RLLFLL  
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9581.7 lumens  
Efficiency: N/A  
Efficacy: 123.0 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 77.9  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.099  
Total Harmonic Distortion (THDi): 0.979  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P910907  
CATALOG NUMBER: DFN2DIP-HX4F0-060D040US850-RLLFLL

### Luminous Intensity Polar Plot





TEST NUMBER: P910907

CATALOG NUMBER: DFN2DIP-HX4F0-060D040US850-RLLFLL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59			59
1	100	96	92	89	94	90	87	84	78	76	74	68	66	64	58	57	56	51			51
2	92	85	79	74	86	79	74	70	69	65	62	60	57	55	52	50	48	44			44
3	84	75	68	62	78	70	64	59	62	57	53	54	50	47	46	44	41	38			38
4	77	67	59	53	72	63	56	51	55	50	46	48	44	41	42	39	36	33			33
5	71	60	52	46	66	56	49	44	50	44	40	44	39	36	38	34	32	29			29
6	66	54	46	40	61	51	44	39	45	39	35	40	35	32	35	31	28	26			26
7	61	49	41	36	57	46	39	34	41	35	31	36	32	28	32	28	25	23			23
8	57	45	37	32	53	42	35	30	38	32	28	33	29	25	29	26	23	21			21
9	53	41	34	29	50	39	32	27	35	29	25	31	26	23	27	24	21	19			19
10	50	38	31	26	47	36	29	25	32	27	23	29	24	21	25	22	19	17			17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	2045	2045	2045
5°	2048	2013	2025
10°	2028	1973	1960
15°	2000	1908	1858
20°	1964	1819	1733
25°	1926	1718	1612
30°	1875	1615	1459
35°	1826	1504	1325
40°	1775	1389	1170
45°	1717	1262	1031
50°	1656	1133	894
55°	1593	996	763
60°	1520	852	628
65°	1436	706	566
70°	1333	569	512
75°	1205	502	466
80°	1020	422	405
85°	713	282	304

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1717 cd/sqm



TEST NUMBER: P910907

CATALOG NUMBER: DFN2DIP-HX4F0-060D040US850-RLFL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	257.7	2.7
10°-20°	707.6	7.4
20°-30°	993.4	10.4
30°-40°	1082.8	11.3
40°-50°	995.2	10.4
50°-60°	781.6	8.2
60°-70°	508.8	5.3
70°-80°	261.9	2.7
80°-90°	70.8	0.7
90°-100°	86.8	0.9
100°-110°	275.8	2.9
110°-120°	472.0	4.9
120°-130°	620.8	6.5
130°-140°	696.8	7.3
140°-150°	683.3	7.1
150°-160°	573.2	6.0
160°-170°	380.1	4.0
170°-180°	132.9	1.4
0°-30°	1958.7	20.4
0°-40°	3041.5	31.7
0°-60°	4818.4	50.3
0°-90°	5659.9	59.1
90°-120°	834.7	8.7
90°-150°	2835.6	29.6
90°-180°	3922.0	40.9
0°-180°	9581.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2750	2750	2750	2750	2750	
5°	2750	2738	2705	2728	2720	261
15°	2616	2588	2504	2456	2432	737
25°	2374	2295	2130	2028	1991	1092
35°	2046	1919	1700	1543	1488	1281
45°	1672	1506	1244	1068	1008	1292
55°	1272	1078	809	660	612	1136
65°	859	657	433	349	341	851
75°	458	284	199	182	179	484
85°	107	55	47	47	47	123
90°	1	15	42	39	40	9
95°	62	74	76	76	74	69
105°	255	258	260	263	263	269
115°	474	480	478	477	474	469
125°	689	700	696	692	691	616
135°	891	904	907	906	902	689
145°	1082	1090	1097	1098	1094	676
155°	1237	1240	1244	1250	1246	569
165°	1346	1345	1345	1353	1347	380
175°	1400	1397	1394	1403	1396	133
180°	1403	1403	1403	1403	1403	



TEST NUMBER: P910907

CATALOG NUMBER: DFN2DIP-HX4F0-060D040US850-RLFL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2750.1	2750.1	2750.1	2750.1	2750.1
2.5°	2762.5	2750.1	2722.6	2747.7	2742.7
5°	2750.1	2737.7	2705.2	2727.7	2720.3
7.5°	2727.7	2712.8	2678.0	2687.8	2675.4
10°	2697.8	2680.3	2630.8	2623.1	2608.3
12.5°	2660.6	2638.1	2570.8	2556.0	2528.5
15°	2615.7	2588.2	2503.7	2456.4	2431.6
17.5°	2563.5	2523.5	2419.0	2364.3	2324.5
20°	2503.7	2453.8	2329.5	2267.4	2212.5
22.5°	2439.0	2381.7	2237.3	2152.8	2115.5
25°	2374.4	2294.6	2130.4	2028.5	1991.0
27.5°	2297.3	2212.5	2030.8	1913.8	1856.6
30°	2215.1	2120.3	1921.2	1794.5	1727.2
32.5°	2135.4	2020.8	1817.0	1667.5	1605.2
35°	2045.9	1918.9	1700.0	1543.1	1488.2
37.5°	1958.7	1821.6	1590.4	1418.5	1356.4
40°	1866.6	1717.4	1475.7	1299.1	1234.4
42.5°	1772.1	1612.8	1361.4	1177.1	1115.1
45°	1672.5	1505.6	1244.5	1067.5	1007.9
47.5°	1578.0	1401.3	1132.5	955.6	901.0
50°	1473.4	1296.8	1022.9	851.0	799.0
52.5°	1371.2	1184.5	918.4	754.1	706.9
55°	1271.7	1077.6	808.8	659.6	612.3
57.5°	1169.8	970.6	711.9	572.5	532.5
60°	1065.2	866.1	609.7	483.0	443.0
62.5°	963.3	764.2	522.6	403.2	383.4
65°	858.7	657.0	433.1	348.6	340.9
67.5°	759.1	557.4	348.6	306.1	298.7
70°	654.5	460.5	288.6	263.8	253.7
72.5°	555.1	370.7	241.3	221.6	216.5
75°	457.9	283.6	199.1	181.7	179.3
77.5°	361.0	201.5	156.8	146.8	141.8
80°	271.2	144.4	119.3	109.6	109.6
82.5°	189.1	97.1	82.1	77.1	77.1
85°	106.9	54.7	47.2	47.2	47.2
87.5°	39.9	19.9	19.9	17.4	17.4
90°	1.2	15.2	41.5	38.9	40.1
92.5°	26.2	35.5	36.8	38.0	38.0
95°	61.8	73.6	75.7	75.7	73.6
97.5°	102.8	113.8	118.4	118.4	118.4
100°	150.2	159.9	163.2	163.2	162.0
102.5°	200.1	207.3	211.9	213.1	211.9
105°	254.6	258.0	260.5	262.6	262.6
107.5°	308.7	313.8	313.8	314.6	308.7
110°	361.2	368.0	368.0	368.0	364.6



TEST NUMBER: P910907

CATALOG NUMBER: DFN2DIP-HX4F0-060D040US850-RLFL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	417.9	425.1	423.7	420.4	417.9
115°	473.7	480.5	478.3	477.1	473.7
117.5°	529.1	538.4	532.5	529.1	525.8
120°	585.0	594.2	585.0	585.0	581.1
122.5°	635.7	647.5	641.7	638.2	635.7
125°	689.0	699.6	696.2	692.3	691.1
127.5°	741.0	754.1	749.5	744.4	741.0
130°	789.6	804.9	802.8	800.3	795.6
132.5°	844.2	856.0	856.9	850.9	847.6
135°	891.2	904.3	906.8	905.5	902.2
137.5°	943.6	954.2	956.3	955.4	950.4
140°	989.7	1000.3	1006.2	1006.2	1001.5
142.5°	1037.1	1047.7	1051.0	1052.3	1047.7
145°	1081.9	1090.4	1097.1	1098.5	1093.8
147.5°	1122.1	1132.6	1137.7	1139.8	1135.2
150°	1163.6	1170.8	1175.4	1179.2	1175.4
152.5°	1200.4	1207.5	1213.5	1218.1	1213.5
155°	1237.1	1240.5	1244.3	1250.3	1246.4
157.5°	1268.9	1271.4	1273.5	1282.0	1276.0
160°	1297.2	1299.7	1301.0	1308.2	1303.1
162.5°	1323.4	1323.4	1324.7	1332.7	1326.8
165°	1345.9	1344.6	1344.6	1353.0	1347.1
167.5°	1366.2	1362.3	1362.3	1370.8	1364.8
170°	1381.4	1377.9	1376.7	1385.1	1377.9
172.5°	1391.9	1388.6	1387.2	1395.8	1388.6
175°	1400.4	1397.0	1394.5	1402.9	1395.8
177.5°	1405.1	1401.7	1399.1	1406.3	1399.1
180°	1402.9	1402.9	1402.9	1402.9	1402.9



TEST NUMBER: P910907  
 CATALOG NUMBER: DFN2DIP-HX4F0-060D040US850-RLLFLL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.44	11.35	11.32	12.25	13.39	6.41	7.32	7.30	8.22	9.36
	3H	12.12	12.94	13.02	13.84	15.01	7.61	8.42	8.50	9.33	10.49
	4H	12.74	13.50	13.65	14.42	15.59	8.06	8.83	8.98	9.75	10.92
	6H	13.16	13.87	14.08	14.79	15.98	8.39	9.10	9.31	10.02	11.20
	8H	13.29	13.97	14.22	14.90	16.09	8.49	9.16	9.41	10.09	11.28
	12H	13.36	14.00	14.29	14.93	16.14	8.53	9.17	9.47	10.10	11.31
4H	2H	10.47	11.24	11.38	12.15	13.32	7.02	7.79	7.93	8.70	9.87
	3H	12.31	12.94	13.23	13.89	15.08	8.38	9.02	9.30	9.96	11.15
	4H	13.00	13.58	13.94	14.52	15.74	8.93	9.51	9.87	10.45	11.67
	6H	13.52	14.02	14.47	14.99	16.20	9.36	9.86	10.31	10.82	12.03
	8H	13.70	14.17	14.65	15.12	16.35	9.49	9.96	10.44	10.91	12.14
	12H	13.80	14.22	14.77	15.19	16.43	9.56	9.98	10.53	10.95	12.19
8H	4H	12.98	13.44	13.93	14.40	15.63	9.22	9.68	10.17	10.64	11.87
	6H	13.55	13.93	14.52	14.93	16.16	9.74	10.13	10.72	11.13	12.35
	8H	13.76	14.10	14.75	15.09	16.34	9.93	10.27	10.92	11.26	12.51
	12H	13.91	14.21	14.89	15.19	16.48	10.06	10.36	11.05	11.34	12.63
12H	4H	12.93	13.35	13.90	14.33	15.56	9.23	9.65	10.20	10.62	11.85
	6H	13.52	13.86	14.51	14.85	16.10	9.79	10.13	10.78	11.12	12.36
	8H	13.75	14.05	14.74	15.03	16.32	10.01	10.31	10.99	11.29	12.58