

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P910909

Luminaire Tested: DFN2DIP-HX4F0-060D050US850-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P910909
REPORT IS A COMBINATION OF REPORTS P899322 AND P896188
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-060D050US850-RLLFLL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10563.3 lumens
Efficiency: N/A
Efficacy: 127.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 82.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P910909

CATALOG NUMBER: DFN2DIP-HX4F0-060D050US850-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P910909

CATALOG NUMBER: DFN2DIP-HX4F0-060D050US850-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59
1	99	95	91	88	92	88	85	82	76	73	71	64	62	61	53	52	51
2	91	84	78	73	84	78	73	68	67	63	60	57	54	52	48	46	44
3	83	74	67	61	77	69	63	58	59	55	51	51	47	44	43	40	38
4	76	66	58	52	71	61	55	49	53	48	44	46	42	38	38	36	33
5	70	59	51	45	65	55	48	43	48	42	38	41	37	34	35	32	29
6	65	53	45	39	60	50	43	37	43	38	34	37	33	30	32	29	26
7	60	48	40	35	56	45	38	33	39	34	30	34	30	27	29	26	23
8	56	44	36	31	52	41	34	30	36	31	27	31	27	24	27	24	21
9	52	40	33	28	48	38	31	27	33	28	24	29	25	22	25	22	19
10	49	37	30	25	45	35	28	24	31	25	22	27	23	20	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2045	2045	2045
5°	2048	2013	2025
10°	2028	1973	1960
15°	2000	1908	1858
20°	1964	1819	1733
25°	1926	1718	1612
30°	1875	1615	1459
35°	1826	1504	1325
40°	1775	1389	1170
45°	1717	1262	1031
50°	1656	1133	894
55°	1593	996	763
60°	1520	852	628
65°	1436	706	566
70°	1333	569	512
75°	1205	502	466
80°	1020	422	405
85°	713	282	304

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1717 cd/sqm

TEST NUMBER: P910909

CATALOG NUMBER: DFN2DIP-HX4F0-060D050US850-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	257.7	2.4
10°-20°	707.6	6.7
20°-30°	993.4	9.4
30°-40°	1082.8	10.3
40°-50°	995.2	9.4
50°-60°	781.6	7.4
60°-70°	508.8	4.8
70°-80°	261.9	2.5
80°-90°	71.8	0.7
90°-100°	108.5	1.0
100°-110°	344.8	3.3
110°-120°	590.1	5.6
120°-130°	776.0	7.3
130°-140°	871.0	8.2
140°-150°	854.2	8.1
150°-160°	716.5	6.8
160°-170°	475.2	4.5
170°-180°	166.1	1.6
0°-30°	1958.7	18.5
0°-40°	3041.5	28.8
0°-60°	4818.4	45.6
0°-90°	5660.9	53.6
90°-120°	1043.4	9.9
90°-150°	3544.6	33.6
90°-180°	4902.0	46.4
0°-180°	10563.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2750	2750	2750	2750	2750	
5°	2750	2738	2705	2728	2720	261
15°	2616	2588	2504	2456	2432	737
25°	2374	2295	2130	2028	1991	1092
35°	2046	1919	1700	1543	1488	1281
45°	1672	1506	1244	1068	1008	1292
55°	1272	1078	809	660	612	1136
65°	859	657	433	349	341	851
75°	458	284	199	182	179	484
85°	107	55	47	47	47	123
90°	2	19	52	49	50	10
95°	77	92	95	95	92	86
105°	318	322	326	328	328	336
115°	592	601	598	596	592	586
125°	861	874	870	866	864	770
135°	1114	1130	1134	1132	1128	861
145°	1352	1363	1371	1373	1367	845
155°	1546	1551	1555	1563	1558	712
165°	1682	1681	1681	1691	1684	475
175°	1751	1746	1743	1754	1745	166
180°	1754	1754	1754	1754	1754	

TEST NUMBER: P910909

CATALOG NUMBER: DFN2DIP-HX4F0-060D050US850-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2750.1	2750.1	2750.1	2750.1	2750.1
2.5°	2762.5	2750.1	2722.6	2747.7	2742.7
5°	2750.1	2737.7	2705.2	2727.7	2720.3
7.5°	2727.7	2712.8	2678.0	2687.8	2675.4
10°	2697.8	2680.3	2630.8	2623.1	2608.3
12.5°	2660.6	2638.1	2570.8	2556.0	2528.5
15°	2615.7	2588.2	2503.7	2456.4	2431.6
17.5°	2563.5	2523.5	2419.0	2364.3	2324.5
20°	2503.7	2453.8	2329.5	2267.4	2212.5
22.5°	2439.0	2381.7	2237.3	2152.8	2115.5
25°	2374.4	2294.6	2130.4	2028.5	1991.0
27.5°	2297.3	2212.5	2030.8	1913.8	1856.6
30°	2215.1	2120.3	1921.2	1794.5	1727.2
32.5°	2135.4	2020.8	1817.0	1667.5	1605.2
35°	2045.9	1918.9	1700.0	1543.1	1488.2
37.5°	1958.7	1821.6	1590.4	1418.5	1356.4
40°	1866.6	1717.4	1475.7	1299.1	1234.4
42.5°	1772.1	1612.8	1361.4	1177.1	1115.1
45°	1672.5	1505.6	1244.5	1067.5	1007.9
47.5°	1578.0	1401.3	1132.5	955.6	901.0
50°	1473.4	1296.8	1022.9	851.0	799.0
52.5°	1371.2	1184.5	918.4	754.1	706.9
55°	1271.7	1077.6	808.8	659.6	612.3
57.5°	1169.8	970.6	711.9	572.5	532.5
60°	1065.2	866.1	609.7	483.0	443.0
62.5°	963.3	764.2	522.6	403.2	383.4
65°	858.7	657.0	433.1	348.6	340.9
67.5°	759.1	557.4	348.6	306.1	298.7
70°	654.5	460.5	288.6	263.8	253.7
72.5°	555.1	370.7	241.3	221.6	216.5
75°	457.9	283.6	199.1	181.7	179.3
77.5°	361.0	201.5	156.8	146.8	141.8
80°	271.2	144.4	119.3	109.6	109.6
82.5°	189.1	97.1	82.1	77.1	77.1
85°	106.9	54.7	47.2	47.2	47.2
87.5°	39.9	19.9	19.9	17.4	17.4
90°	1.6	19.1	51.8	48.7	50.2
92.5°	32.8	44.4	46.0	47.6	47.6
95°	77.2	92.0	94.6	94.6	92.0
97.5°	128.4	142.2	148.1	148.1	148.1
100°	187.6	199.8	204.1	204.1	202.5
102.5°	250.1	259.1	264.8	266.5	264.8
105°	318.3	322.5	325.7	328.3	328.3
107.5°	385.9	392.3	392.3	393.4	385.9
110°	451.5	460.0	460.0	460.0	455.7

TEST NUMBER: P910909

CATALOG NUMBER: DFN2DIP-HX4F0-060D050US850-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	522.3	531.3	529.8	525.6	522.3
115°	592.1	600.6	598.0	596.4	592.1
117.5°	661.4	673.1	665.6	661.4	657.2
120°	731.2	742.8	731.2	731.2	726.4
122.5°	794.6	809.5	802.0	797.8	794.6
125°	861.2	874.4	870.2	865.5	863.9
127.5°	926.2	942.6	936.9	930.5	926.2
130°	987.1	1006.1	1003.4	1000.3	994.4
132.5°	1055.3	1070.1	1071.2	1063.8	1059.5
135°	1114.0	1130.3	1133.5	1132.0	1127.7
137.5°	1179.5	1192.7	1195.4	1194.3	1188.0
140°	1237.1	1250.4	1257.7	1257.7	1252.0
142.5°	1296.3	1309.6	1313.8	1315.4	1309.6
145°	1352.4	1363.0	1371.4	1373.1	1367.2
147.5°	1402.7	1415.9	1422.2	1424.8	1419.0
150°	1454.5	1463.4	1469.2	1474.0	1469.2
152.5°	1500.5	1509.5	1516.8	1522.7	1516.8
155°	1546.4	1550.6	1555.4	1562.8	1558.0
157.5°	1586.1	1589.2	1591.9	1602.5	1595.1
160°	1621.5	1624.7	1626.2	1635.2	1628.9
162.5°	1654.3	1654.3	1655.8	1665.9	1658.5
165°	1682.4	1680.7	1680.7	1691.3	1683.9
167.5°	1707.6	1702.9	1702.9	1713.5	1706.1
170°	1726.7	1722.5	1720.9	1731.5	1722.5
172.5°	1739.9	1735.7	1734.1	1744.7	1735.7
175°	1750.6	1746.2	1743.1	1753.7	1744.7
177.5°	1756.3	1752.1	1748.9	1757.9	1748.9
180°	1753.7	1753.7	1753.7	1753.7	1753.7

TEST NUMBER: P910909

CATALOG NUMBER: DFN2DIP-HX4F0-060D050US850-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.96	10.82	10.89	11.77	12.99	5.93	6.80	6.87	7.74	8.96
	3H	11.64	12.41	12.59	13.37	14.61	7.13	7.90	8.07	8.85	10.10
	4H	12.25	12.98	13.21	13.94	15.19	7.58	8.31	8.54	9.27	10.52
	6H	12.68	13.35	13.65	14.31	15.58	7.90	8.57	8.87	9.54	10.81
	8H	12.80	13.44	13.78	14.42	15.69	8.00	8.63	8.97	9.61	10.88
	12H	12.87	13.47	13.85	14.45	15.74	8.04	8.65	9.02	9.62	10.91
4H	2H	9.98	10.71	10.95	11.67	12.92	6.53	7.26	7.50	8.22	9.48
	3H	11.82	12.42	12.79	13.41	14.68	7.89	8.49	8.86	9.48	10.75
	4H	12.51	13.06	13.49	14.04	15.34	8.44	8.99	9.42	9.97	11.27
	6H	13.03	13.50	14.02	14.51	15.80	8.86	9.34	9.86	10.34	11.63
	8H	13.21	13.65	14.20	14.65	15.95	8.99	9.44	9.99	10.44	11.74
	12H	13.30	13.70	14.32	14.72	16.03	9.06	9.46	10.08	10.48	11.79
8H	4H	12.48	12.92	13.48	13.92	15.23	8.72	9.17	9.72	10.16	11.47
	6H	13.05	13.42	14.07	14.46	15.76	9.24	9.61	10.27	10.65	11.95
	8H	13.27	13.59	14.30	14.62	15.94	9.44	9.76	10.47	10.79	12.11
	12H	13.41	13.69	14.44	14.71	16.08	9.56	9.84	10.59	10.86	12.23
12H	4H	12.43	12.83	13.45	13.85	15.16	8.73	9.13	9.74	10.14	11.45
	6H	13.03	13.35	14.05	14.38	15.70	9.29	9.62	10.32	10.64	11.97
	8H	13.25	13.53	14.28	14.55	15.92	9.51	9.79	10.54	10.81	12.18

END OF REPORT