

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P929244

Luminaire Tested: DFN2DIP-HX4F0-060D120US940-FLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P929244
REPORT IS A COMBINATION OF REPORTS P900967 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-060D120US940-FLLONL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15895.4 lumens
Efficiency: N/A
Efficacy: 105.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 150.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P929244

CATALOG NUMBER: DFN2DIP-HX4F0-060D120US940-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P929244

CATALOG NUMBER: DFN2DIP-HX4F0-060D120US940-FLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41
1	94	90	86	83	85	81	78	75	65	63	61	50	48	47	36	35	34
2	86	78	72	67	77	71	66	62	57	53	50	44	41	39	32	30	29
3	78	69	62	56	70	62	56	51	50	46	42	39	36	33	28	26	25
4	71	61	53	47	64	55	49	43	44	40	36	34	31	28	25	23	21
5	65	54	46	40	59	49	42	37	40	35	31	31	27	25	23	20	18
6	60	48	41	35	54	44	37	32	36	31	27	28	24	21	20	18	16
7	56	44	36	30	50	40	33	28	32	27	23	25	22	19	19	16	14
8	51	39	32	27	46	36	29	25	29	24	21	23	19	17	17	15	13
9	48	36	29	24	43	33	26	22	27	22	19	21	18	15	16	13	12
10	45	33	26	21	40	30	24	20	25	20	17	19	16	14	15	12	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1548	1548	1548
5°	1551	1527	1537
10°	1539	1507	1516
15°	1516	1482	1484
20°	1486	1448	1451
25°	1455	1407	1412
30°	1417	1368	1364
35°	1381	1323	1312
40°	1337	1278	1263
45°	1293	1232	1212
50°	1245	1184	1154
55°	1194	1129	1101
60°	1137	1063	1039
65°	1075	995	967
70°	995	912	889
75°	885	813	817
80°	753	686	680
85°	547	467	452

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1856 cd/sqm

TEST NUMBER: P929244

CATALOG NUMBER: DFN2DIP-HX4F0-060D120US940-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	196.0	1.2
10°-20°	551.5	3.5
20°-30°	810.5	5.1
30°-40°	941.3	5.9
40°-50°	940.1	5.9
50°-60°	819.8	5.2
60°-70°	606.0	3.8
70°-80°	342.9	2.2
80°-90°	96.8	0.6
90°-100°	119.1	0.7
100°-110°	444.1	2.8
110°-120°	1177.7	7.4
120°-130°	1953.3	12.3
130°-140°	2074.9	13.1
140°-150°	1928.4	12.1
150°-160°	1550.3	9.8
160°-170°	999.0	6.3
170°-180°	343.8	2.2
0°-30°	1558.0	9.8
0°-40°	2499.3	15.7
0°-60°	4259.1	26.8
0°-90°	5304.8	33.4
90°-120°	1740.9	11.0
90°-150°	7697.4	48.4
90°-180°	10591.0	66.6
0°-180°	15895.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2082	2082	2082	2082	2082	
5°	2082	2075	2052	2068	2065	198
15°	1982	1970	1944	1952	1942	558
25°	1794	1778	1744	1748	1744	826
35°	1548	1528	1496	1484	1474	967
45°	1260	1246	1215	1194	1186	972
55°	953	941	917	893	883	852
65°	643	631	611	593	583	636
75°	336	332	322	310	314	359
85°	82	80	78	72	70	91
90°	2	31	52	66	70	15
95°	170	84	102	115	112	201
105°	795	873	160	188	199	849
115°	1503	1547	1613	403	214	1480
125°	2125	2159	2209	2227	2235	1895
135°	2630	2672	2695	2721	2716	2031
145°	3051	3048	3092	3111	3098	1908
155°	3359	3336	3367	3382	3362	1548
165°	3539	3524	3531	3550	3531	1000
175°	3620	3602	3607	3626	3599	345
180°	3612	3612	3612	3612	3612	

TEST NUMBER: P929244

CATALOG NUMBER: DFN2DIP-HX4F0-060D120US940-FLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2082.5	2082.5	2082.5	2082.5	2082.5
2.5°	2094.6	2084.6	2062.5	2082.5	2078.6
5°	2082.5	2074.6	2052.5	2068.5	2064.6
7.5°	2068.5	2056.6	2034.5	2050.6	2046.6
10°	2046.6	2032.6	2008.5	2024.5	2018.5
12.5°	2016.5	2004.5	1980.5	1990.5	1986.5
15°	1982.4	1970.5	1944.4	1952.5	1942.5
17.5°	1940.4	1928.5	1902.4	1912.3	1902.4
20°	1894.3	1882.4	1854.3	1860.3	1852.4
22.5°	1848.4	1830.3	1804.2	1804.2	1800.1
25°	1794.2	1778.3	1744.2	1748.1	1744.2
27.5°	1734.0	1720.0	1694.1	1688.2	1678.2
30°	1674.2	1658.0	1628.1	1622.1	1614.0
32.5°	1610.0	1598.1	1566.0	1553.9	1545.8
35°	1548.0	1528.0	1495.9	1483.8	1473.8
37.5°	1477.9	1459.8	1427.7	1413.6	1403.7
40°	1405.8	1389.6	1357.6	1339.8	1331.7
42.5°	1335.7	1319.5	1287.7	1267.5	1255.6
45°	1259.7	1245.6	1215.4	1193.6	1185.5
47.5°	1185.5	1171.5	1139.4	1117.3	1105.4
50°	1107.3	1097.3	1069.3	1041.2	1031.2
52.5°	1031.2	1017.2	991.3	969.2	955.2
55°	953.3	941.1	917.2	893.2	883.2
57.5°	875.1	865.2	839.0	815.0	806.9
60°	796.9	789.1	761.1	738.9	733.0
62.5°	720.8	706.8	686.8	666.9	658.8
65°	642.9	630.8	610.8	592.7	582.7
67.5°	562.8	552.6	534.8	520.7	512.6
70°	488.6	480.6	462.5	448.5	440.6
72.5°	412.6	404.5	394.5	380.5	374.6
75°	336.3	332.5	322.3	310.4	314.4
77.5°	268.3	260.3	256.2	250.3	244.3
80°	200.3	198.2	194.2	188.2	184.2
82.5°	136.2	136.2	134.2	126.2	126.2
85°	82.0	80.1	78.1	72.0	70.1
87.5°	36.1	32.1	28.0	22.1	20.0
90°	2.5	31.3	52.2	65.5	70.5
92.5°	65.5	54.9	62.7	68.0	70.5
95°	169.7	83.5	101.8	115.2	112.4
97.5°	305.8	91.6	133.2	141.2	143.7
100°	462.8	104.6	149.0	169.7	175.1
102.5°	635.1	630.1	154.2	182.9	190.9
105°	794.6	873.2	159.6	188.1	198.6
107.5°	980.2	1045.4	164.8	193.4	203.9
110°	1158.1	1212.8	457.5	196.2	206.4

TEST NUMBER: P929244

CATALOG NUMBER: DFN2DIP-HX4F0-060D120US940-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1325.4	1372.3	1327.9	201.1	209.2
115°	1502.9	1547.4	1612.8	402.6	214.5
117.5°	1657.2	1709.4	1754.1	1380.0	695.3
120°	1829.8	1868.9	1916.1	1947.5	1594.5
122.5°	1976.0	2018.0	2070.4	2085.9	2088.7
125°	2125.0	2159.2	2208.9	2227.1	2234.9
127.5°	2261.0	2297.6	2337.0	2363.1	2365.6
130°	2389.1	2431.1	2459.6	2488.5	2486.0
132.5°	2519.8	2554.0	2582.5	2606.2	2603.7
135°	2629.7	2671.6	2694.9	2721.3	2716.1
137.5°	2744.6	2775.9	2802.3	2828.4	2820.6
140°	2857.0	2878.0	2906.6	2930.2	2917.2
142.5°	2951.3	2969.6	3003.5	3024.2	3011.2
145°	3050.6	3047.9	3092.2	3110.6	3097.5
147.5°	3136.6	3128.9	3173.3	3186.3	3176.1
150°	3220.4	3202.1	3244.0	3259.5	3246.5
152.5°	3290.9	3270.1	3309.2	3325.0	3306.7
155°	3358.8	3335.5	3366.9	3382.5	3361.7
157.5°	3413.8	3393.0	3416.6	3434.9	3413.8
160°	3461.0	3445.2	3461.0	3476.5	3458.2
162.5°	3502.6	3487.1	3500.1	3518.4	3494.9
165°	3539.2	3523.7	3531.4	3549.8	3531.4
167.5°	3568.1	3552.2	3560.3	3578.6	3555.1
170°	3591.6	3575.8	3581.1	3599.4	3575.8
172.5°	3607.2	3591.6	3597.0	3615.3	3591.6
175°	3620.2	3601.9	3607.2	3625.5	3599.4
177.5°	3625.5	3607.2	3610.0	3628.3	3604.8
180°	3612.5	3612.5	3612.5	3612.5	3612.5

TEST NUMBER: P929244

CATALOG NUMBER: DFN2DIP-HX4F0-060D120US940-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.02	7.75	8.11	8.84	10.33	6.59	7.32	7.68	8.40	9.89
	3H	8.67	9.32	9.77	10.42	11.93	8.20	8.85	9.29	9.95	11.45
	4H	9.25	9.87	10.36	10.97	12.48	8.78	9.40	9.89	10.50	12.01
	6H	9.65	10.22	10.76	11.32	12.84	9.17	9.74	10.29	10.84	12.37
	8H	9.75	10.29	10.87	11.41	12.92	9.27	9.82	10.39	10.93	12.45
	12H	9.79	10.31	10.92	11.42	12.96	9.31	9.83	10.43	10.93	12.48
4H	2H	7.47	8.09	8.58	9.18	10.70	7.12	7.74	8.24	8.84	10.35
	3H	9.32	9.84	10.44	10.96	12.49	8.93	9.44	10.05	10.57	12.09
	4H	10.03	10.51	11.15	11.62	13.16	9.62	10.10	10.75	11.21	12.76
	6H	10.54	10.95	11.67	12.08	13.62	10.13	10.54	11.26	11.67	13.21
	8H	10.69	11.07	11.82	12.19	13.75	10.27	10.65	11.40	11.78	13.34
	12H	10.75	11.10	11.90	12.24	13.80	10.33	10.68	11.48	11.81	13.37
8H	4H	10.22	10.60	11.35	11.72	13.28	9.86	10.24	10.99	11.36	12.92
	6H	10.84	11.16	12.00	12.33	13.88	10.48	10.79	11.63	11.96	13.52
	8H	11.06	11.34	12.22	12.49	14.06	10.69	10.97	11.85	12.12	13.69
	12H	11.19	11.43	12.35	12.58	14.18	10.80	11.05	11.97	12.19	13.80
12H	4H	10.20	10.54	11.34	11.68	13.24	9.84	10.19	10.99	11.33	12.89
	6H	10.87	11.15	12.03	12.30	13.87	10.52	10.80	11.68	11.94	13.52
	8H	11.11	11.35	12.27	12.50	14.10	10.75	10.99	11.91	12.14	13.75

END OF REPORT