

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P929264

Luminaire Tested: DFN2DIP-HX4F0-070D080US940-FLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P929264
REPORT IS A COMBINATION OF REPORTS P900897 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-070D080US940-FLONL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 13246.2 lumens
Efficiency: N/A
Efficacy: 106.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 124.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9972
Total Harmonic Distortion (THDi): 0.128
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P929264
CATALOG NUMBER: DFN2DIP-HX4F0-070D080US940-FLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P929264

CATALOG NUMBER: DFN2DIP-HX4F0-070D080US940-FLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	106	106	106	106	98	98	98	98	81	81	81	67	67	67	53	53	53	47	47	47	47
1	97	93	89	85	89	85	82	79	71	69	67	59	57	56	47	46	45	39	39	39	39
2	88	81	75	70	81	75	69	65	63	59	55	52	49	46	41	39	38	33	33	33	33
3	81	71	64	58	74	66	59	54	55	50	47	46	42	39	37	34	32	28	28	28	28
4	74	63	55	49	67	58	51	46	49	44	40	41	37	34	33	30	28	24	24	24	24
5	68	56	48	42	62	52	45	39	44	38	34	36	32	29	29	27	24	21	21	21	21
6	62	50	42	36	57	47	39	34	40	34	30	33	29	25	27	24	21	18	18	18	18
7	58	45	37	32	53	42	35	30	36	30	26	30	26	23	24	21	19	16	16	16	16
8	53	41	33	28	49	38	31	27	33	27	23	27	23	20	22	19	17	15	15	15	15
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	21	18	15	13	13	13	13
10	46	34	27	22	43	32	26	21	28	22	19	23	19	16	19	16	14	12	12	12	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1806	1806	1806
5°	1810	1782	1794
10°	1795	1758	1769
15°	1769	1729	1731
20°	1733	1689	1693
25°	1698	1641	1648
30°	1654	1596	1591
35°	1612	1544	1530
40°	1560	1491	1473
45°	1508	1438	1414
50°	1452	1382	1346
55°	1393	1317	1284
60°	1326	1240	1212
65°	1254	1161	1128
70°	1161	1064	1037
75°	1033	948	954
80°	879	801	793
85°	638	546	528

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1508 cd/sqm



TEST NUMBER: P929264

CATALOG NUMBER: DFN2DIP-HX4F0-070D080US940-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	228.7	1.7
10°-20°	643.4	4.9
20°-30°	945.5	7.1
30°-40°	1098.2	8.3
40°-50°	1096.8	8.3
50°-60°	956.4	7.2
60°-70°	707.0	5.3
70°-80°	400.0	3.0
80°-90°	109.8	0.8
90°-100°	79.4	0.6
100°-110°	296.0	2.2
110°-120°	785.1	5.9
120°-130°	1302.2	9.8
130°-140°	1383.2	10.4
140°-150°	1285.6	9.7
150°-160°	1033.6	7.8
160°-170°	666.0	5.0
170°-180°	229.2	1.7
0°-30°	1817.6	13.7
0°-40°	2915.8	22.0
0°-60°	4969.0	37.5
0°-90°	6185.8	46.7
90°-120°	1160.6	8.8
90°-150°	5131.6	38.7
90°-180°	7060.0	53.3
0°-180°	13246.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2430	2430	2430	2430	2430	
5°	2430	2420	2395	2413	2409	231
15°	2313	2299	2268	2278	2266	651
25°	2093	2075	2035	2040	2035	963
35°	1806	1783	1745	1731	1719	1128
45°	1470	1453	1418	1392	1383	1134
55°	1112	1098	1070	1042	1030	994
65°	750	736	713	692	680	742
75°	392	388	376	362	367	419
85°	96	94	91	84	82	107
90°	2	21	35	44	47	12
95°	113	56	68	77	75	134
105°	530	582	106	125	132	566
115°	1002	1032	1075	268	143	986
125°	1417	1439	1472	1485	1490	1263
135°	1753	1781	1797	1814	1811	1354
145°	2034	2032	2062	2074	2065	1272
155°	2239	2224	2245	2255	2241	1032
165°	2360	2349	2354	2366	2354	667
175°	2414	2401	2405	2417	2400	230
180°	2408	2408	2408	2408	2408	



TEST NUMBER: P929264

CATALOG NUMBER: DFN2DIP-HX4F0-070D080US940-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2429.5	2429.5	2429.5	2429.5	2429.5
2.5°	2443.7	2432.0	2406.3	2429.5	2425.1
5°	2429.5	2420.4	2394.7	2413.2	2408.8
7.5°	2413.2	2399.3	2373.5	2392.4	2387.7
10°	2387.7	2371.3	2343.3	2361.9	2355.0
12.5°	2352.5	2338.6	2310.6	2322.2	2317.5
15°	2312.9	2299.0	2268.4	2277.9	2266.2
17.5°	2263.7	2249.9	2219.4	2231.1	2219.4
20°	2209.9	2196.1	2163.4	2170.3	2161.1
22.5°	2156.4	2135.4	2104.9	2104.9	2100.1
25°	2093.3	2074.6	2035.0	2039.5	2035.0
27.5°	2023.1	2006.7	1976.5	1969.5	1957.9
30°	1953.2	1934.3	1899.4	1892.5	1883.0
32.5°	1878.3	1864.5	1827.0	1812.9	1803.4
35°	1805.9	1782.7	1745.2	1731.1	1719.4
37.5°	1724.1	1703.1	1665.6	1649.3	1637.6
40°	1640.1	1621.3	1583.8	1563.1	1553.6
42.5°	1558.3	1539.5	1502.3	1478.8	1464.8
45°	1469.6	1453.2	1418.0	1392.5	1383.0
47.5°	1383.0	1366.7	1329.3	1303.5	1289.7
50°	1291.9	1280.2	1247.5	1214.8	1203.1
52.5°	1203.1	1186.8	1156.6	1130.8	1114.4
55°	1112.1	1098.1	1070.0	1042.0	1030.3
57.5°	1021.0	1009.3	978.8	950.8	941.4
60°	929.7	920.5	887.9	862.1	855.2
62.5°	841.0	824.7	801.4	778.1	768.6
65°	750.1	735.9	712.6	691.6	679.9
67.5°	656.6	644.7	623.9	607.5	598.1
70°	570.1	560.7	539.6	523.2	514.1
72.5°	481.3	472.0	460.3	443.9	437.0
75°	392.4	387.9	376.0	362.2	366.9
77.5°	313.1	303.6	298.9	292.0	285.1
80°	233.7	231.3	226.6	219.6	214.9
82.5°	158.9	158.9	156.6	147.3	147.3
85°	95.7	93.5	91.3	84.0	81.8
87.5°	42.1	37.5	32.7	25.8	23.3
90°	1.7	20.9	34.8	43.6	47.0
92.5°	43.6	36.7	41.8	45.3	47.0
95°	113.2	55.7	67.9	76.8	74.9
97.5°	203.8	61.0	88.8	94.2	95.8
100°	308.5	69.8	99.4	113.2	116.7
102.5°	423.4	420.0	102.8	121.8	127.3
105°	529.8	582.1	106.3	125.4	132.5
107.5°	653.5	696.9	109.9	128.9	135.9
110°	772.1	808.5	305.1	130.8	137.6



TEST NUMBER: P929264

CATALOG NUMBER: DFN2DIP-HX4F0-070D080US940-FLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	883.6	914.8	885.3	134.1	139.5
115°	1002.0	1031.6	1075.2	268.4	143.0
117.5°	1104.8	1139.6	1169.4	920.0	463.6
120°	1219.9	1245.9	1277.4	1298.3	1063.0
122.5°	1317.3	1345.3	1380.3	1390.6	1392.5
125°	1416.7	1439.4	1472.5	1484.7	1489.9
127.5°	1507.3	1531.7	1558.1	1575.4	1577.1
130°	1592.8	1620.7	1639.8	1659.0	1657.3
132.5°	1679.9	1702.6	1721.7	1737.4	1735.7
135°	1753.1	1781.1	1796.6	1814.2	1810.7
137.5°	1829.8	1850.6	1868.2	1885.6	1880.4
140°	1904.6	1918.7	1937.8	1953.5	1944.7
142.5°	1967.6	1979.7	2002.3	2016.2	2007.4
145°	2033.8	2031.9	2061.5	2073.7	2065.0
147.5°	2091.1	2085.9	2115.5	2124.2	2117.3
150°	2147.0	2134.7	2162.7	2173.0	2164.3
152.5°	2194.0	2180.0	2206.1	2216.7	2204.5
155°	2239.3	2223.8	2244.6	2255.0	2241.2
157.5°	2275.8	2262.0	2277.7	2289.9	2275.8
160°	2307.3	2296.8	2307.3	2317.7	2305.5
162.5°	2335.1	2324.7	2333.4	2345.6	2329.9
165°	2359.5	2349.2	2354.3	2366.5	2354.3
167.5°	2378.7	2368.2	2373.5	2385.7	2370.0
170°	2394.5	2383.9	2387.4	2399.7	2383.9
172.5°	2404.8	2394.5	2398.0	2410.2	2394.5
175°	2413.5	2401.3	2404.8	2417.0	2399.7
177.5°	2417.0	2404.8	2406.6	2418.8	2403.1
180°	2408.3	2408.3	2408.3	2408.3	2408.3



TEST NUMBER: P929264
 CATALOG NUMBER: DFN2DIP-HX4F0-070D080US940-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.01	9.85	10.00	10.84	12.16	8.58	9.41	9.57	10.41	11.73
	3H	10.67	11.42	11.67	12.43	13.77	10.20	10.95	11.20	11.95	13.29
	4H	11.26	11.97	12.27	12.98	14.32	10.79	11.49	11.80	12.50	13.85
	6H	11.66	12.31	12.68	13.33	14.68	11.18	11.83	12.20	12.85	14.21
	8H	11.76	12.38	12.79	13.41	14.77	11.29	11.91	12.31	12.94	14.29
	12H	11.81	12.40	12.84	13.43	14.81	11.33	11.92	12.36	12.94	14.32
4H	2H	9.47	10.18	10.49	11.19	12.54	9.13	9.84	10.14	10.84	12.19
	3H	11.34	11.93	12.36	12.97	14.33	10.94	11.53	11.97	12.57	13.93
	4H	12.05	12.59	13.08	13.62	15.01	11.65	12.19	12.68	13.22	14.60
	6H	12.57	13.03	13.61	14.08	15.46	12.16	12.62	13.20	13.67	15.05
	8H	12.72	13.15	13.76	14.20	15.59	12.30	12.74	13.35	13.78	15.18
	12H	12.79	13.18	13.85	14.24	15.64	12.37	12.76	13.43	13.82	15.22
8H	4H	12.25	12.68	13.29	13.73	15.12	11.89	12.32	12.93	13.37	14.76
	6H	12.88	13.24	13.94	14.33	15.72	12.51	12.87	13.58	13.96	15.35
	8H	13.10	13.41	14.17	14.49	15.90	12.73	13.05	13.80	14.12	15.53
	12H	13.23	13.51	14.31	14.58	16.03	12.85	13.12	13.92	14.19	15.64
12H	4H	12.23	12.62	13.29	13.68	15.08	11.88	12.27	12.94	13.33	14.73
	6H	12.91	13.22	13.98	14.30	15.71	12.56	12.87	13.63	13.94	15.36
	8H	13.15	13.43	14.23	14.50	15.95	12.79	13.07	13.87	14.14	15.59