

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P921852

Luminaire Tested: DFN2DIP-HX4F0-070D120US940-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P921852
REPORT IS A COMBINATION OF REPORTS P899449 AND P896188
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-070D120US940-FLLFLL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 15649.5 lumens
Efficiency: N/A
Efficacy: 112.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 139.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9972
Total Harmonic Distortion (THDi): 0.128
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P921852
CATALOG NUMBER: DFN2DIP-HX4F0-070D120US940-FLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P921852

CATALOG NUMBER: DFN2DIP-HX4F0-070D120US940-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	105	105	105	105	95	95	95	95	78	78	78	61	61	61	47	47	47	47	47	47	40
1	95	91	87	84	87	83	80	77	68	66	64	54	52	51	41	40	39	39	39	39	33
2	87	80	74	68	79	73	67	63	59	56	53	47	45	43	36	35	33	33	33	33	28
3	79	70	63	57	72	64	58	53	52	48	44	42	39	36	32	30	28	28	28	28	24
4	72	62	54	48	66	57	50	45	47	42	38	37	34	31	29	26	24	24	24	24	20
5	66	55	47	41	60	50	43	38	42	36	32	33	30	27	26	23	21	21	21	21	18
6	61	49	41	36	55	45	38	33	37	32	28	30	26	23	23	21	19	19	19	19	15
7	56	44	37	31	51	41	34	29	34	29	25	27	24	21	21	19	16	16	16	16	14
8	52	40	33	27	48	37	30	26	31	26	22	25	21	18	20	17	15	15	15	15	12
9	49	37	29	24	44	34	27	23	28	23	20	23	19	16	18	15	13	13	13	13	11
10	45	34	27	22	41	31	25	20	26	21	18	21	17	15	17	14	12	12	12	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1806	1806	1806
5°	1809	1781	1793
10°	1794	1757	1769
15°	1768	1728	1731
20°	1733	1688	1692
25°	1697	1640	1647
30°	1653	1596	1590
35°	1611	1543	1530
40°	1559	1490	1473
45°	1508	1437	1414
50°	1452	1381	1346
55°	1393	1317	1283
60°	1326	1240	1212
65°	1253	1161	1128
70°	1161	1064	1037
75°	1033	948	953
80°	878	801	793
85°	638	546	528

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 90°
 Luminance: 2551 cd/sqm



TEST NUMBER: P921852

CATALOG NUMBER: DFN2DIP-HX4F0-070D120US940-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	228.6	1.5
10°-20°	643.2	4.1
20°-30°	945.2	6.0
30°-40°	1097.8	7.0
40°-50°	1096.5	7.0
50°-60°	956.1	6.1
60°-70°	706.8	4.5
70°-80°	399.9	2.6
80°-90°	115.2	0.7
90°-100°	209.4	1.3
100°-110°	665.4	4.3
110°-120°	1138.7	7.3
120°-130°	1497.5	9.6
130°-140°	1680.9	10.7
140°-150°	1648.3	10.5
150°-160°	1382.7	8.8
160°-170°	917.0	5.9
170°-180°	320.5	2.0
0°-30°	1817.0	11.6
0°-40°	2914.9	18.6
0°-60°	4967.4	31.7
0°-90°	6189.2	39.5
90°-120°	2013.4	12.9
90°-150°	6840.1	43.7
90°-180°	9460.0	60.4
0°-180°	15649.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2429	2429	2429	2429	2429	
5°	2429	2420	2394	2412	2408	231
15°	2312	2298	2268	2277	2266	651
25°	2093	2074	2034	2039	2034	963
35°	1805	1782	1745	1730	1719	1127
45°	1469	1453	1418	1392	1383	1134
55°	1112	1098	1070	1042	1030	994
65°	750	736	712	691	680	741
75°	392	388	376	362	367	419
85°	96	94	91	84	82	107
90°	3	37	100	94	97	15
95°	149	178	183	183	178	166
105°	614	622	628	634	634	648
115°	1143	1159	1154	1151	1143	1130
125°	1662	1688	1679	1670	1667	1485
135°	2150	2181	2188	2184	2176	1662
145°	2610	2630	2646	2650	2638	1631
155°	2984	2992	3002	3016	3007	1374
165°	3246	3243	3243	3264	3250	916
175°	3378	3370	3364	3384	3367	321
180°	3384	3384	3384	3384	3384	



TEST NUMBER: P921852

CATALOG NUMBER: DFN2DIP-HX4F0-070D120US940-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2428.8	2428.8	2428.8	2428.8	2428.8
2.5°	2442.9	2431.2	2405.5	2428.8	2424.3
5°	2428.8	2419.7	2393.9	2412.4	2408.0
7.5°	2412.4	2398.5	2372.8	2391.7	2386.9
10°	2386.9	2370.5	2342.5	2361.2	2354.2
12.5°	2351.7	2337.9	2309.9	2321.5	2316.8
15°	2312.1	2298.2	2267.7	2277.2	2265.5
17.5°	2263.0	2249.2	2218.7	2230.3	2218.7
20°	2209.2	2195.4	2162.7	2169.6	2160.4
22.5°	2155.7	2134.7	2104.2	2104.2	2099.4
25°	2092.6	2073.9	2034.3	2038.8	2034.3
27.5°	2022.4	2006.1	1975.9	1968.9	1957.2
30°	1952.6	1933.7	1898.8	1891.9	1882.4
32.5°	1877.7	1863.9	1826.4	1812.3	1802.9
35°	1805.4	1782.1	1744.6	1730.5	1718.9
37.5°	1723.6	1702.5	1665.1	1648.8	1637.1
40°	1639.6	1620.8	1583.3	1562.5	1553.1
42.5°	1557.8	1539.0	1501.8	1478.3	1464.4
45°	1469.1	1452.8	1417.6	1392.0	1382.6
47.5°	1382.6	1366.3	1328.8	1303.1	1289.2
50°	1291.5	1279.8	1247.1	1214.4	1202.7
52.5°	1202.7	1186.4	1156.2	1130.4	1114.0
55°	1111.8	1097.7	1069.7	1041.7	1030.0
57.5°	1020.7	1009.0	978.5	950.5	941.1
60°	929.4	920.2	887.6	861.8	854.9
62.5°	840.7	824.4	801.1	777.8	768.4
65°	749.8	735.7	712.4	691.3	679.7
67.5°	656.4	644.5	623.7	607.3	597.9
70°	569.9	560.5	539.4	523.1	513.9
72.5°	481.2	471.8	460.1	443.8	436.8
75°	392.3	387.8	375.9	362.0	366.8
77.5°	313.0	303.5	298.8	291.9	285.0
80°	233.6	231.2	226.5	219.5	214.8
82.5°	158.8	158.8	156.6	147.2	147.2
85°	95.7	93.5	91.2	84.0	81.8
87.5°	42.1	37.5	32.7	25.8	23.3
90°	3.0	36.7	100.0	93.9	96.9
92.5°	63.2	85.7	88.7	91.8	91.8
95°	148.9	177.5	182.6	182.6	177.5
97.5°	247.9	274.5	285.7	285.7	285.7
100°	362.2	385.7	393.8	393.8	390.7
102.5°	482.6	499.9	511.1	514.2	511.1
105°	614.2	622.3	628.5	633.6	633.6
107.5°	744.8	757.1	757.1	759.0	744.8
110°	871.3	887.6	887.6	887.6	879.5



TEST NUMBER: P921852

CATALOG NUMBER: DFN2DIP-HX4F0-070D120US940-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1008.0	1025.4	1022.3	1014.1	1008.0
115°	1142.6	1159.0	1153.9	1150.8	1142.6
117.5°	1276.3	1298.8	1284.5	1276.3	1268.2
120°	1411.0	1433.4	1411.0	1411.0	1401.9
122.5°	1533.5	1562.0	1547.7	1539.5	1533.5
125°	1662.0	1687.5	1679.4	1670.2	1667.1
127.5°	1787.5	1819.1	1807.9	1795.6	1787.5
130°	1904.8	1941.5	1936.4	1930.3	1919.0
132.5°	2036.4	2065.0	2067.0	2052.7	2044.6
135°	2149.6	2181.3	2187.5	2184.3	2176.2
137.5°	2276.2	2301.7	2306.8	2304.7	2292.5
140°	2387.4	2412.9	2427.1	2427.1	2415.9
142.5°	2501.7	2527.2	2535.3	2538.3	2527.2
145°	2609.8	2630.2	2646.5	2649.6	2638.4
147.5°	2706.7	2732.2	2744.5	2749.6	2738.4
150°	2806.7	2824.0	2835.3	2844.5	2835.3
152.5°	2895.5	2912.8	2927.1	2938.4	2927.1
155°	2984.2	2992.4	3001.6	3015.9	3006.7
157.5°	3060.8	3066.9	3071.9	3092.4	3078.1
160°	3129.1	3135.3	3138.3	3155.7	3143.4
162.5°	3192.3	3192.3	3195.4	3214.8	3200.5
165°	3246.4	3243.4	3243.4	3263.7	3249.5
167.5°	3295.4	3286.2	3286.2	3306.6	3292.4
170°	3332.1	3323.9	3320.9	3341.3	3323.9
172.5°	3357.6	3349.4	3346.4	3366.8	3349.4
175°	3378.1	3369.9	3363.8	3384.1	3366.8
177.5°	3389.3	3381.1	3374.9	3392.3	3374.9
180°	3384.1	3384.1	3384.1	3384.1	3384.1



TEST NUMBER: P921852
 CATALOG NUMBER: DFN2DIP-HX4F0-070D120US940-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.27	9.05	9.32	10.10	11.51	7.84	8.62	8.88	9.66	11.08
	3H	9.93	10.62	10.98	11.68	13.11	9.46	10.15	10.51	11.21	12.64
	4H	10.51	11.17	11.58	12.23	13.67	10.04	10.70	11.10	11.76	13.19
	6H	10.91	11.51	11.98	12.58	14.03	10.43	11.04	11.51	12.10	13.55
	8H	11.01	11.59	12.09	12.67	14.11	10.54	11.11	11.61	12.19	13.64
	12H	11.06	11.61	12.14	12.68	14.15	10.58	11.12	11.66	12.20	13.67
4H	2H	8.73	9.38	9.80	10.44	11.88	8.38	9.04	9.45	10.10	11.54
	3H	10.58	11.13	11.66	12.22	13.67	10.19	10.74	11.27	11.83	13.28
	4H	11.30	11.80	12.38	12.88	14.35	10.89	11.39	11.97	12.47	13.94
	6H	11.81	12.24	12.90	13.34	14.81	11.40	11.83	12.49	12.93	14.40
	8H	11.96	12.36	13.05	13.45	14.93	11.54	11.95	12.63	13.04	14.52
	12H	12.02	12.39	13.13	13.50	14.98	11.60	11.97	12.71	13.07	14.56
8H	4H	11.49	11.89	12.58	12.98	14.47	11.13	11.53	12.22	12.62	14.10
	6H	12.12	12.45	13.23	13.58	15.06	11.75	12.09	12.87	13.22	14.70
	8H	12.34	12.63	13.46	13.74	15.24	11.97	12.26	13.09	13.37	14.87
	12H	12.46	12.72	13.59	13.83	15.37	12.08	12.34	13.20	13.45	14.99
12H	4H	11.47	11.83	12.58	12.94	14.43	11.12	11.48	12.22	12.59	14.07
	6H	12.14	12.44	13.27	13.55	15.05	11.79	12.09	12.91	13.20	14.70
	8H	12.38	12.64	13.51	13.75	15.29	12.03	12.28	13.15	13.40	14.93