

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P927976

Luminaire Tested: DFN2DIP-HX4F0-070D100US850-FLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P927976
REPORT IS A COMBINATION OF REPORTS P900933 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-070D100US850-FLLONL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 18664.5 lumens
Efficiency: N/A
Efficacy: 131.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 142.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9972
Total Harmonic Distortion (THDi): 0.128
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P927976

CATALOG NUMBER: DFN2DIP-HX4F0-070D100US850-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P927976

CATALOG NUMBER: DFN2DIP-HX4F0-070D100US850-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	78	78	78	63	63	63	48	48	48
1	96	92	88	84	87	84	80	77	69	66	64	55	54	52	42	41	41
2	87	80	74	69	79	73	68	63	60	56	53	48	46	43	37	36	34
3	80	70	63	57	72	64	58	53	53	49	45	43	39	37	33	31	29
4	73	62	54	48	66	57	50	45	47	42	38	38	34	31	30	27	25
5	67	55	47	41	61	51	44	38	42	37	33	34	30	27	27	24	22
6	61	50	42	36	56	46	38	33	38	33	29	31	27	24	24	21	19
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17
8	53	40	33	28	48	37	31	26	31	26	22	26	22	19	20	17	15
9	49	37	30	25	45	34	27	23	29	23	20	24	20	17	19	16	14
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2246	2246	2246
5°	2250	2215	2230
10°	2232	2185	2200
15°	2199	2150	2153
20°	2155	2100	2104
25°	2111	2040	2049
30°	2056	1985	1978
35°	2004	1919	1903
40°	1939	1853	1831
45°	1875	1787	1758
50°	1805	1718	1674
55°	1732	1638	1596
60°	1649	1542	1507
65°	1559	1443	1402
70°	1444	1323	1289
75°	1284	1179	1185
80°	1093	996	986
85°	793	679	656

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1922 cd/sqm

TEST NUMBER: P927976

CATALOG NUMBER: DFN2DIP-HX4F0-070D100US850-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	284.3	1.5
10°-20°	799.9	4.3
20°-30°	1175.6	6.3
30°-40°	1365.3	7.3
40°-50°	1363.6	7.3
50°-60°	1189.1	6.4
60°-70°	879.0	4.7
70°-80°	497.3	2.7
80°-90°	137.9	0.7
90°-100°	123.4	0.7
100°-110°	460.1	2.5
110°-120°	1220.2	6.5
120°-130°	2023.8	10.8
130°-140°	2149.7	11.5
140°-150°	1997.9	10.7
150°-160°	1606.3	8.6
160°-170°	1035.0	5.5
170°-180°	356.2	1.9
0°-30°	2259.8	12.1
0°-40°	3625.1	19.4
0°-60°	6177.8	33.1
0°-90°	7692.0	41.2
90°-120°	1803.7	9.7
90°-150°	7975.0	42.7
90°-180°	10973.0	58.8
0°-180°	18664.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3021	3021	3021	3021	3021	
5°	3021	3009	2977	3000	2995	287
15°	2876	2858	2820	2832	2818	810
25°	2602	2579	2530	2536	2530	1198
35°	2245	2216	2170	2152	2138	1402
45°	1827	1807	1763	1731	1720	1410
55°	1383	1365	1330	1296	1281	1236
65°	933	915	886	860	845	922
75°	488	482	467	450	456	521
85°	119	116	114	104	102	133
90°	3	32	54	68	73	17
95°	176	86	106	119	116	208
105°	823	905	165	195	206	880
115°	1557	1603	1671	417	222	1533
125°	2202	2237	2288	2308	2316	1964
135°	2725	2768	2792	2819	2814	2105
145°	3161	3158	3204	3223	3209	1977
155°	3480	3456	3488	3504	3483	1604
165°	3667	3651	3659	3678	3659	1036
175°	3751	3732	3737	3756	3729	357
180°	3743	3743	3743	3743	3743	

TEST NUMBER: P927976

CATALOG NUMBER: DFN2DIP-HX4F0-070D100US850-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3020.6	3020.6	3020.6	3020.6	3020.6
2.5°	3038.2	3023.7	2991.6	3020.6	3015.0
5°	3020.6	3009.3	2977.2	3000.3	2994.7
7.5°	3000.3	2983.0	2950.9	2974.4	2968.6
10°	2968.6	2948.2	2913.3	2936.5	2927.9
12.5°	2924.8	2907.6	2872.8	2887.2	2881.3
15°	2875.5	2858.2	2820.3	2832.1	2817.5
17.5°	2814.4	2797.2	2759.3	2773.8	2759.3
20°	2747.5	2730.4	2689.7	2698.3	2686.9
22.5°	2681.0	2654.8	2616.9	2616.9	2611.0
25°	2602.5	2579.3	2530.1	2535.6	2530.1
27.5°	2515.2	2494.9	2457.3	2448.7	2434.1
30°	2428.4	2404.9	2361.5	2352.9	2341.1
32.5°	2335.2	2318.0	2271.5	2253.9	2242.2
35°	2245.3	2216.3	2169.8	2152.2	2137.7
37.5°	2143.6	2117.4	2070.8	2050.5	2036.0
40°	2039.1	2015.7	1969.1	1943.3	1931.5
42.5°	1937.4	1914.0	1867.8	1838.5	1821.2
45°	1827.1	1806.8	1763.0	1731.3	1719.5
47.5°	1719.5	1699.2	1652.6	1620.6	1603.4
50°	1606.2	1591.6	1550.9	1510.3	1495.8
52.5°	1495.8	1475.5	1437.9	1405.9	1385.5
55°	1382.7	1365.2	1330.4	1295.5	1281.0
57.5°	1269.4	1254.8	1216.9	1182.1	1170.4
60°	1155.9	1144.5	1103.9	1071.8	1063.2
62.5°	1045.6	1025.3	996.3	967.4	955.6
65°	932.6	914.9	886.0	859.8	845.3
67.5°	816.3	801.6	775.6	755.3	743.6
70°	708.8	697.1	670.8	650.5	639.1
72.5°	598.4	586.8	572.2	551.9	543.3
75°	487.8	482.3	467.4	450.3	456.1
77.5°	389.3	377.5	371.6	363.0	354.4
80°	290.6	287.6	281.7	273.0	267.2
82.5°	197.5	197.5	194.7	183.1	183.1
85°	119.0	116.2	113.5	104.5	101.7
87.5°	52.3	46.6	40.7	32.1	28.9
90°	2.6	32.5	54.0	67.9	73.0
92.5°	67.9	56.9	65.0	70.4	73.0
95°	175.9	86.5	105.5	119.3	116.4
97.5°	316.7	94.8	138.0	146.3	148.9
100°	479.5	108.3	154.4	175.9	181.4
102.5°	658.0	652.9	159.8	189.4	197.7
105°	823.3	904.6	165.4	194.9	205.8
107.5°	1015.6	1083.2	170.8	200.4	211.3
110°	1199.8	1256.5	474.0	203.3	213.8

TEST NUMBER: P927976

CATALOG NUMBER: DFN2DIP-HX4F0-070D100US850-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1373.2	1421.7	1375.8	208.4	216.8
115°	1557.1	1603.2	1671.0	417.1	222.2
117.5°	1717.0	1771.1	1817.3	1429.8	720.4
120°	1895.8	1936.3	1985.2	2017.7	1652.1
122.5°	2047.3	2090.7	2145.0	2161.1	2164.0
125°	2201.7	2237.1	2288.5	2307.5	2315.5
127.5°	2342.5	2380.5	2421.3	2448.3	2450.9
130°	2475.3	2518.8	2548.4	2578.2	2575.7
132.5°	2610.7	2646.1	2675.7	2700.1	2697.5
135°	2724.6	2768.0	2792.1	2819.4	2814.0
137.5°	2843.6	2876.1	2903.4	2930.4	2922.3
140°	2959.9	2981.9	3011.4	3035.9	3022.4
142.5°	3057.7	3076.7	3111.7	3133.3	3119.8
145°	3160.6	3157.8	3203.8	3222.8	3209.2
147.5°	3249.7	3241.7	3287.6	3301.2	3290.6
150°	3336.5	3317.6	3361.0	3377.1	3363.6
152.5°	3409.5	3388.0	3428.6	3444.9	3425.9
155°	3480.0	3455.9	3488.4	3504.4	3482.9
157.5°	3536.9	3515.4	3539.8	3558.8	3536.9
160°	3585.8	3569.4	3585.8	3601.9	3583.0
162.5°	3628.9	3612.8	3626.3	3645.3	3620.9
165°	3666.8	3650.7	3658.8	3677.8	3658.8
167.5°	3696.7	3680.3	3688.8	3707.7	3683.2
170°	3721.1	3704.8	3710.3	3729.2	3704.8
172.5°	3737.2	3721.1	3726.7	3745.6	3721.1
175°	3750.7	3731.8	3737.2	3756.3	3729.2
177.5°	3756.3	3737.2	3740.2	3759.2	3734.7
180°	3742.8	3742.8	3742.8	3742.8	3742.8

TEST NUMBER: P927976

CATALOG NUMBER: DFN2DIP-HX4F0-070D100US850-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.21	10.00	10.24	11.04	12.43	8.78	9.57	9.81	10.61	12.00
	3H	10.87	11.57	11.91	12.62	14.03	10.40	11.10	11.43	12.15	13.56
	4H	11.45	12.12	12.50	13.17	14.59	10.98	11.65	12.03	12.70	14.11
	6H	11.85	12.47	12.91	13.52	14.95	11.37	11.99	12.44	13.04	14.47
	8H	11.95	12.54	13.02	13.61	15.03	11.48	12.06	12.54	13.13	14.56
	12H	12.00	12.56	13.07	13.62	15.07	11.52	12.08	12.59	13.14	14.59
4H	2H	9.67	10.34	10.72	11.38	12.80	9.32	9.99	10.38	11.04	12.46
	3H	11.53	12.09	12.59	13.16	14.59	11.13	11.69	12.20	12.77	14.20
	4H	12.24	12.75	13.31	13.82	15.27	11.83	12.35	12.90	13.41	14.86
	6H	12.75	13.19	13.83	14.28	15.73	12.34	12.78	13.42	13.87	15.32
	8H	12.90	13.31	13.98	14.39	15.85	12.49	12.90	13.57	13.98	15.44
	12H	12.97	13.34	14.07	14.44	15.90	12.55	12.92	13.65	14.01	15.48
8H	4H	12.43	12.84	13.51	13.92	15.39	12.07	12.48	13.15	13.56	15.03
	6H	13.06	13.40	14.16	14.52	15.98	12.70	13.04	13.80	14.16	15.62
	8H	13.28	13.58	14.39	14.68	16.16	12.91	13.21	14.02	14.31	15.79
	12H	13.41	13.67	14.52	14.77	16.29	13.02	13.29	14.14	14.39	15.91
12H	4H	12.41	12.78	13.51	13.88	15.35	12.06	12.43	13.16	13.53	15.00
	6H	13.09	13.39	14.20	14.49	15.97	12.74	13.04	13.85	14.14	15.62
	8H	13.33	13.59	14.44	14.69	16.21	12.97	13.23	14.09	14.33	15.85

END OF REPORT