

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P921861

Luminaire Tested: DFN2DIP-HX4F0-080D070US940-RLLFLL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P921861  
REPORT IS A COMBINATION OF REPORTS P899362 AND P896188  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-HX4F0-080D070US940-RLLFLL  
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 11587.8 lumens  
Efficiency: N/A  
Efficacy: 99.7 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 116.2  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9613  
Total Harmonic Distortion (THDi): 0.083  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P921861  
CATALOG NUMBER: DFN2DIP-HX4F0-080D070US940-RLFL

### Luminous Intensity Polar Plot





TEST NUMBER: P921861

CATALOG NUMBER: DFN2DIP-HX4F0-080D070US940-RLFL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58	58	58	58	52
1	99	95	91	88	91	88	85	82	75	73	71	63	62	60	52	51	50	52	51	50	45
2	90	83	77	72	83	77	72	68	66	63	59	56	53	51	47	45	43	47	45	43	39
3	83	74	67	61	76	69	62	57	59	54	50	50	47	44	42	39	37	42	39	37	33
4	76	66	58	52	70	61	54	49	53	48	43	45	41	38	38	35	33	38	35	33	29
5	70	59	51	45	65	55	48	43	47	42	38	41	36	33	34	31	29	34	31	29	26
6	65	53	45	39	60	49	42	37	43	37	33	37	33	29	31	28	25	31	28	25	23
7	60	48	40	35	55	45	38	33	39	34	30	34	29	26	29	25	23	29	25	23	20
8	56	44	36	31	52	41	34	29	36	30	26	31	27	23	26	23	21	26	23	21	18
9	52	40	33	28	48	38	31	26	33	28	24	29	24	21	24	21	19	24	21	19	17
10	49	37	30	25	45	35	28	24	30	25	22	26	22	19	23	20	17	23	20	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	2192	2192	2192
5°	2196	2158	2171
10°	2174	2116	2101
15°	2145	2046	1992
20°	2105	1950	1858
25°	2065	1842	1728
30°	2011	1731	1564
35°	1957	1612	1420
40°	1903	1489	1255
45°	1841	1353	1105
50°	1775	1215	959
55°	1708	1067	818
60°	1629	913	673
65°	1539	756	606
70°	1430	610	549
75°	1292	538	500
80°	1093	452	433
85°	765	303	326

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1841 cd/sqm



TEST NUMBER: P921861

CATALOG NUMBER: DFN2DIP-HX4F0-080D070US940-RLFL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	276.3	2.4
10°-20°	758.6	6.5
20°-30°	1065.0	9.2
30°-40°	1160.9	10.0
40°-50°	1067.0	9.2
50°-60°	838.0	7.2
60°-70°	545.4	4.7
70°-80°	280.8	2.4
80°-90°	77.3	0.7
90°-100°	122.2	1.1
100°-110°	388.1	3.3
110°-120°	664.2	5.7
120°-130°	873.6	7.5
130°-140°	980.5	8.5
140°-150°	961.5	8.3
150°-160°	806.6	7.0
160°-170°	534.9	4.6
170°-180°	187.0	1.6
0°-30°	2099.9	18.1
0°-40°	3260.8	28.1
0°-60°	5165.8	44.6
0°-90°	6069.3	52.4
90°-120°	1174.5	10.1
90°-150°	3990.1	34.4
90°-180°	5519.0	47.6
0°-180°	11587.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2948	2948	2948	2948	2948	
5°	2948	2935	2900	2924	2916	280
15°	2804	2775	2684	2634	2607	790
25°	2546	2460	2284	2175	2134	1171
35°	2193	2057	1822	1654	1595	1373
45°	1793	1614	1334	1144	1081	1385
55°	1363	1155	867	707	656	1218
65°	921	704	464	374	365	913
75°	491	304	214	195	192	519
85°	115	59	51	51	51	132
90°	2	21	58	55	56	11
95°	87	104	107	107	104	97
105°	358	363	367	370	370	378
115°	667	676	673	671	667	659
125°	970	984	980	974	972	866
135°	1254	1272	1276	1274	1269	969
145°	1522	1534	1544	1546	1539	951
155°	1741	1746	1751	1759	1754	801
165°	1894	1892	1892	1904	1896	534
175°	1970	1966	1962	1974	1964	187
180°	1974	1974	1974	1974	1974	



TEST NUMBER: P921861

CATALOG NUMBER: DFN2DIP-HX4F0-080D070US940-RLFL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2948.4	2948.4	2948.4	2948.4	2948.4
2.5°	2961.6	2948.4	2918.9	2945.8	2940.4
5°	2948.4	2935.1	2900.2	2924.3	2916.3
7.5°	2924.3	2908.4	2871.0	2881.6	2868.2
10°	2892.3	2873.6	2820.4	2812.2	2796.3
12.5°	2852.4	2828.3	2756.1	2740.2	2710.8
15°	2804.3	2774.8	2684.2	2633.6	2606.9
17.5°	2748.2	2705.4	2593.4	2534.8	2492.0
20°	2684.2	2630.7	2497.4	2430.9	2371.9
22.5°	2614.9	2553.4	2398.6	2308.0	2268.1
25°	2545.5	2460.1	2283.9	2174.7	2134.5
27.5°	2462.8	2371.9	2177.2	2051.8	1990.4
30°	2374.8	2273.1	2059.8	1923.9	1851.6
32.5°	2289.3	2166.5	1947.9	1787.7	1720.9
35°	2193.3	2057.2	1822.5	1654.4	1595.4
37.5°	2099.9	1953.0	1705.0	1520.7	1454.2
40°	2001.2	1841.2	1582.2	1392.8	1323.4
42.5°	1899.8	1729.1	1459.6	1262.0	1195.4
45°	1793.1	1614.2	1334.2	1144.5	1080.6
47.5°	1691.8	1502.4	1214.2	1024.5	965.9
50°	1579.6	1390.3	1096.7	912.4	856.6
52.5°	1470.1	1269.9	984.5	808.5	757.9
55°	1363.3	1155.3	867.1	707.1	656.5
57.5°	1254.1	1040.6	763.2	613.8	571.0
60°	1141.9	928.5	653.6	517.7	475.0
62.5°	1032.7	819.2	560.3	432.3	411.1
65°	920.6	704.3	464.2	373.7	365.4
67.5°	813.9	597.6	373.7	328.1	320.2
70°	701.8	493.7	309.4	282.8	272.1
72.5°	595.0	397.4	258.8	237.6	232.1
75°	490.9	304.1	213.5	194.7	192.3
77.5°	387.0	216.0	168.2	157.4	152.0
80°	290.7	154.9	128.0	117.4	117.4
82.5°	202.7	104.2	88.0	82.7	82.7
85°	114.7	58.6	50.6	50.6	50.6
87.5°	42.7	21.2	21.2	18.7	18.7
90°	1.8	21.4	58.3	54.8	56.5
92.5°	36.9	50.0	51.8	53.6	53.6
95°	86.9	103.5	106.6	106.6	103.5
97.5°	144.6	160.1	166.7	166.7	166.7
100°	211.2	225.0	229.7	229.7	227.9
102.5°	281.5	291.6	298.2	300.0	298.2
105°	358.3	363.0	366.6	369.6	369.6
107.5°	434.4	441.6	441.6	442.8	434.4
110°	508.3	517.8	517.8	517.8	513.0



TEST NUMBER: P921861

CATALOG NUMBER: DFN2DIP-HX4F0-080D070US940-RLFL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	588.0	598.2	596.4	591.6	588.0
115°	666.6	676.1	673.2	671.4	666.6
117.5°	744.5	757.6	749.3	744.5	739.8
120°	823.0	836.2	823.0	823.0	817.7
122.5°	894.5	911.1	902.9	898.0	894.5
125°	969.5	984.4	979.6	974.3	972.5
127.5°	1042.7	1061.1	1054.6	1047.5	1042.7
130°	1111.2	1132.6	1129.6	1126.1	1119.5
132.5°	1187.9	1204.6	1205.8	1197.5	1192.7
135°	1254.0	1272.4	1276.0	1274.2	1269.4
137.5°	1327.8	1342.6	1345.6	1344.4	1337.3
140°	1392.7	1407.6	1415.9	1415.9	1409.3
142.5°	1459.3	1474.2	1478.9	1480.7	1474.2
145°	1522.4	1534.3	1543.8	1545.6	1539.1
147.5°	1579.0	1593.8	1601.0	1603.9	1597.4
150°	1637.3	1647.3	1653.9	1659.3	1653.9
152.5°	1689.0	1699.2	1707.4	1714.0	1707.4
155°	1740.8	1745.5	1751.0	1759.3	1753.9
157.5°	1785.5	1789.0	1792.0	1803.9	1795.5
160°	1825.3	1828.9	1830.7	1840.8	1833.6
162.5°	1862.2	1862.2	1864.0	1875.3	1867.0
165°	1893.7	1891.9	1891.9	1903.9	1895.5
167.5°	1922.3	1917.0	1917.0	1928.9	1920.6
170°	1943.8	1939.0	1937.2	1949.1	1939.0
172.5°	1958.6	1953.8	1952.0	1964.0	1953.8
175°	1970.5	1965.8	1962.2	1974.1	1964.0
177.5°	1977.1	1972.3	1968.7	1978.9	1968.7
180°	1974.1	1974.1	1974.1	1974.1	1974.1



TEST NUMBER: P921861  
 CATALOG NUMBER: DFN2DIP-HX4F0-080D070US940-RLLFLL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.09	10.94	11.04	11.90	13.14	6.07	6.92	7.01	7.87	9.11
	3H	11.77	12.53	12.73	13.50	14.76	7.26	8.02	8.21	8.98	10.25
	4H	12.38	13.10	13.35	14.07	15.34	7.71	8.43	8.68	9.40	10.67
	6H	12.81	13.47	13.79	14.44	15.73	8.03	8.70	9.01	9.67	10.95
	8H	12.93	13.56	13.92	14.55	15.84	8.13	8.76	9.11	9.75	11.03
	12H	13.00	13.60	13.99	14.58	15.88	8.17	8.77	9.16	9.75	11.06
4H	2H	10.11	10.83	11.09	11.80	13.07	6.67	7.38	7.64	8.35	9.62
	3H	11.95	12.54	12.93	13.54	14.83	8.02	8.62	9.00	9.61	10.90
	4H	12.64	13.19	13.63	14.18	15.49	8.57	9.11	9.56	10.11	11.42
	6H	13.16	13.63	14.16	14.64	15.95	8.99	9.46	10.00	10.47	11.78
	8H	13.33	13.77	14.34	14.78	16.10	9.12	9.56	10.13	10.57	11.89
	12H	13.43	13.82	14.45	14.85	16.18	9.19	9.58	10.21	10.61	11.93
8H	4H	12.61	13.05	13.62	14.06	15.38	8.85	9.29	9.86	10.30	11.62
	6H	13.18	13.54	14.21	14.59	15.91	9.37	9.73	10.40	10.78	12.10
	8H	13.40	13.71	14.43	14.75	16.09	9.57	9.88	10.60	10.92	12.26
	12H	13.54	13.82	14.58	14.85	16.23	9.69	9.97	10.73	11.00	12.38
12H	4H	12.56	12.96	13.59	13.98	15.31	8.86	9.25	9.88	10.28	11.60
	6H	13.15	13.47	14.19	14.51	15.85	9.42	9.74	10.46	10.78	12.12
	8H	13.38	13.66	14.42	14.69	16.07	9.64	9.92	10.68	10.95	12.33