

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P910951

Luminaire Tested: DFN2DIP-HX4F0-080D080US850-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P910951
REPORT IS A COMBINATION OF REPORTS P899380 AND P896188
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-080D080US850-RLLFLL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 15392.9 lumens
Efficiency: N/A
Efficacy: 126.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 122
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9613
Total Harmonic Distortion (THDi): 0.083
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P910951
CATALOG NUMBER: DFN2DIP-HX4F0-080D080US850-RLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P910951
 CATALOG NUMBER: DFN2DIP-HX4F0-080D080US850-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	107	107	107	107	99	99	99	99	83	83	83	68	68	68	55	55	55	49			49
1	98	94	90	87	90	87	84	81	73	71	69	61	59	58	50	49	48	42			42
2	90	83	77	72	82	76	71	67	65	61	58	54	51	49	44	42	41	36			36
3	82	73	66	60	75	68	61	57	58	53	49	48	45	42	40	37	35	31			31
4	75	65	57	51	69	60	54	48	51	46	42	43	40	36	36	33	31	27			27
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	32	29	27	24			24
6	64	52	44	39	59	49	42	37	42	36	32	35	31	28	30	26	24	21			21
7	59	47	40	34	55	44	37	32	38	33	29	32	28	25	27	24	22	19			19
8	55	43	36	30	51	40	33	29	35	29	26	30	26	23	25	22	20	17			17
9	51	39	32	27	47	37	30	26	32	27	23	27	23	20	23	20	18	16			16
10	48	36	29	24	44	34	28	23	30	24	21	25	21	19	22	18	16	14			14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2727	2727	2727
5°	2731	2683	2701
10°	2704	2631	2613
15°	2667	2544	2477
20°	2618	2425	2310
25°	2568	2291	2150
30°	2501	2153	1945
35°	2434	2005	1766
40°	2367	1852	1561
45°	2289	1682	1374
50°	2208	1511	1192
55°	2124	1327	1017
60°	2026	1136	838
65°	1914	941	754
70°	1778	759	683
75°	1607	670	621
80°	1359	562	539
85°	951	377	406

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2289 cd/sqm



TEST NUMBER: P910951

CATALOG NUMBER: DFN2DIP-HX4F0-080D080US850-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	343.7	2.2
10°-20°	943.4	6.1
20°-30°	1324.5	8.6
30°-40°	1443.8	9.4
40°-50°	1327.0	8.6
50°-60°	1042.1	6.8
60°-70°	678.3	4.4
70°-80°	349.2	2.3
80°-90°	97.1	0.6
90°-100°	173.6	1.1
100°-110°	551.7	3.6
110°-120°	944.1	6.1
120°-130°	1241.6	8.1
130°-140°	1393.7	9.1
140°-150°	1366.6	8.9
150°-160°	1146.4	7.4
160°-170°	760.3	4.9
170°-180°	265.7	1.7
0°-30°	2611.6	17.0
0°-40°	4055.4	26.3
0°-60°	6424.5	41.7
0°-90°	7549.2	49.0
90°-120°	1669.4	10.8
90°-150°	5671.3	36.8
90°-180°	7844.0	51.0
0°-180°	15392.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3667	3667	3667	3667	3667	
5°	3667	3650	3607	3637	3627	348
15°	3488	3451	3338	3275	3242	983
25°	3166	3060	2840	2705	2655	1456
35°	2728	2558	2267	2058	1984	1707
45°	2230	2008	1659	1423	1344	1722
55°	1696	1437	1078	879	816	1515
65°	1145	876	577	465	454	1135
75°	610	378	266	242	239	646
85°	143	73	63	63	63	164
90°	3	30	83	78	80	15
95°	124	147	151	151	147	137
105°	509	516	521	525	525	537
115°	947	961	957	954	947	937
125°	1378	1399	1392	1385	1382	1231
135°	1782	1809	1814	1811	1804	1378
145°	2164	2181	2194	2197	2188	1352
155°	2474	2481	2489	2500	2493	1139
165°	2692	2689	2689	2706	2694	759
175°	2801	2794	2789	2806	2792	266
180°	2806	2806	2806	2806	2806	



TEST NUMBER: P910951

CATALOG NUMBER: DFN2DIP-HX4F0-080D080US850-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3666.8	3666.8	3666.8	3666.8	3666.8
2.5°	3683.3	3666.8	3630.2	3663.6	3656.9
5°	3666.8	3650.3	3606.9	3636.9	3627.0
7.5°	3636.9	3617.1	3570.6	3583.7	3567.1
10°	3597.0	3573.9	3507.7	3497.5	3477.7
12.5°	3547.5	3517.5	3427.7	3408.0	3371.4
15°	3487.6	3451.0	3338.3	3275.3	3242.2
17.5°	3417.8	3364.7	3225.3	3152.4	3099.2
20°	3338.3	3271.8	3106.0	3023.2	2949.9
22.5°	3252.0	3175.6	2983.1	2870.4	2820.7
25°	3165.8	3059.5	2840.5	2704.6	2654.6
27.5°	3062.9	2949.9	2707.7	2551.8	2475.4
30°	2953.5	2827.1	2561.7	2392.7	2302.8
32.5°	2847.1	2694.4	2422.6	2223.3	2140.3
35°	2727.8	2558.5	2266.6	2057.5	1984.2
37.5°	2611.6	2428.9	2120.5	1891.3	1808.6
40°	2488.8	2289.9	1967.7	1732.1	1645.9
42.5°	2362.7	2150.5	1815.2	1569.6	1486.7
45°	2230.0	2007.5	1659.3	1423.4	1343.9
47.5°	2104.0	1868.4	1510.0	1274.1	1201.3
50°	1964.5	1729.0	1364.0	1134.7	1065.3
52.5°	1828.3	1579.3	1224.4	1005.5	942.5
55°	1695.6	1436.8	1078.4	879.4	816.4
57.5°	1559.7	1294.2	949.2	763.3	710.1
60°	1420.2	1154.8	812.9	643.9	590.8
62.5°	1284.3	1018.8	696.8	537.6	511.2
65°	1144.9	875.9	577.3	464.8	454.5
67.5°	1012.2	743.3	464.8	408.0	398.2
70°	872.8	614.1	384.8	351.7	338.4
72.5°	740.0	494.3	321.8	295.4	288.7
75°	610.5	378.2	265.5	242.2	239.1
77.5°	481.3	268.6	209.2	195.7	189.1
80°	361.5	192.6	159.1	146.1	146.1
82.5°	252.1	129.5	109.5	102.8	102.8
85°	142.6	72.9	63.0	63.0	63.0
87.5°	53.1	26.4	26.4	23.3	23.3
90°	2.6	30.5	83.0	77.9	80.4
92.5°	52.5	71.1	73.6	76.1	76.1
95°	123.5	147.2	151.4	151.4	147.2
97.5°	205.6	227.6	236.9	236.9	236.9
100°	300.3	319.7	326.5	326.5	323.9
102.5°	400.1	414.5	423.7	426.3	423.7
105°	509.3	516.0	521.1	525.3	525.3
107.5°	617.5	627.7	627.7	629.4	617.5
110°	722.4	735.9	735.9	735.9	729.2



TEST NUMBER: P910951

CATALOG NUMBER: DFN2DIP-HX4F0-080D080US850-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	835.7	850.2	847.6	840.8	835.7
115°	947.4	960.9	956.7	954.2	947.4
117.5°	1058.2	1076.8	1065.0	1058.2	1051.4
120°	1169.9	1188.5	1169.9	1169.9	1162.2
122.5°	1271.4	1295.1	1283.2	1276.5	1271.4
125°	1377.9	1399.1	1392.3	1384.7	1382.3
127.5°	1482.1	1508.2	1498.9	1488.8	1482.1
130°	1579.3	1609.7	1605.5	1600.5	1591.2
132.5°	1688.5	1712.1	1713.8	1702.0	1695.2
135°	1782.3	1808.6	1813.7	1811.1	1804.3
137.5°	1887.2	1908.4	1912.6	1910.9	1900.7
140°	1979.5	2000.5	2012.4	2012.4	2003.1
142.5°	2074.2	2095.3	2102.1	2104.7	2095.3
145°	2163.9	2180.7	2194.3	2196.8	2187.5
147.5°	2244.2	2265.4	2275.4	2279.8	2270.5
150°	2327.1	2341.4	2350.7	2358.4	2350.7
152.5°	2400.7	2415.1	2426.9	2436.3	2426.9
155°	2474.3	2481.1	2488.7	2500.5	2492.9
157.5°	2537.7	2542.8	2547.0	2563.9	2552.1
160°	2594.4	2599.5	2602.0	2616.4	2606.3
162.5°	2646.9	2646.9	2649.4	2665.5	2653.6
165°	2691.7	2689.1	2689.1	2706.1	2694.2
167.5°	2732.2	2724.7	2724.7	2741.6	2729.7
170°	2762.7	2756.0	2753.4	2770.4	2756.0
172.5°	2783.9	2777.2	2774.6	2791.5	2777.2
175°	2800.8	2794.0	2788.9	2805.9	2791.5
177.5°	2810.1	2803.3	2798.2	2812.6	2798.2
180°	2805.9	2805.9	2805.9	2805.9	2805.9



TEST NUMBER: P910951
 CATALOG NUMBER: DFN2DIP-HX4F0-080D080US850-RLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.54	11.36	11.51	12.34	13.63	6.51	7.34	7.49	8.32	9.61
	3H	12.22	12.95	13.20	13.94	15.25	7.70	8.44	8.69	9.43	10.74
	4H	12.83	13.52	13.82	14.52	15.84	8.16	8.85	9.15	9.84	11.16
	6H	13.25	13.89	14.26	14.89	16.22	8.48	9.12	9.48	10.12	11.45
	8H	13.38	13.98	14.39	15.00	16.33	8.57	9.18	9.58	10.19	11.52
	12H	13.44	14.02	14.46	15.03	16.38	8.61	9.19	9.63	10.20	11.55
4H	2H	10.56	11.25	11.56	12.25	13.57	7.11	7.80	8.11	8.80	10.12
	3H	12.39	12.97	13.40	13.99	15.32	8.46	9.04	9.47	10.06	11.39
	4H	13.08	13.61	14.10	14.62	15.98	9.01	9.54	10.03	10.55	11.91
	6H	13.60	14.05	14.63	15.09	16.44	9.43	9.88	10.46	10.92	12.27
	8H	13.77	14.20	14.80	15.23	16.59	9.56	9.98	10.59	11.02	12.38
	12H	13.87	14.25	14.92	15.30	16.67	9.63	10.01	10.67	11.06	12.43
8H	4H	13.05	13.47	14.08	14.50	15.87	9.29	9.71	10.32	10.75	12.11
	6H	13.62	13.97	14.67	15.04	16.40	9.81	10.16	10.86	11.23	12.60
	8H	13.83	14.14	14.89	15.20	16.58	10.00	10.31	11.06	11.37	12.75
	12H	13.97	14.24	15.04	15.30	16.72	10.12	10.39	11.19	11.45	12.87
12H	4H	13.00	13.38	14.05	14.43	15.80	9.29	9.68	10.34	10.72	12.09
	6H	13.59	13.90	14.65	14.96	16.34	9.86	10.17	10.92	11.23	12.61
	8H	13.81	14.08	14.88	15.14	16.56	10.07	10.34	11.14	11.40	12.82